

TMT36 iTEMP Programmable Temperature Transmitters with IO-LINK

Part No. [TMT36-13A9/101](#)Part No. [TMT36-13C0/101](#)

The Endress+Hauser TMT36 iTEMP[®] programmable temperature transmitters work with Pt100 or Pt1000 RTD sensors. IO-Link communication output enables access to various temperature process variable, configuration, diagnostic, and logging parameters. These transmitters mount in a DIN Form B sensor connection head and are available with either screw or push-in terminals for electrical connection.

Features

- Sensor Types: RTD: Pt100 or Pt1000
- IO-Link communication output that enables access to various temperature process variable, configuration, diagnostic, and logging parameters.
- DIN Form B sensor connection head mounting
- Screw or push-in terminals
- Compatible with Endress+Hauser TID10-1009/0 display




For a variety of cable options see our website www.AutomationDirect.com

Endress + Hauser TMT36 iTEMP Temperature Transmitter Selection


Part Number	Transmitter Type	Input	Output	Operating Voltage	Connection Head Mount	Electrical Connection	Weight (lb)	Price
TMT36-13A9/101	Non-isolated	1-channel, RTD	1-channel, IO-Link	18-30 VDC	DIN Form B connection head	Screw terminals	0.38	\$210.00
TMT36-13C0/101						Push-in terminals	0.37	\$210.00

Endress + Hauser TMT36 Series iTEMP Programmable Temperature Transmitter Information

Part Number	Drawing Links	Manufacturer Tech Specs	Manufacturer Quick Start	Manufacturer Manual
TMT36-13A9/101	PDF	PDF	PDF	PDF
TMT36-13C0/101	PDF			

For complete technical information and installation see [Manufacturer Tech Specs](#) and [Manual](#) links.

Wiring Information

TMT36 shown with optional [TID10-1009/0](#) display

TMT36 & TMT72 iTEMP

Programmable Temperature Transmitters Accessory

Part No. [TID10-1009/0](#)

The [TID10-1009/0](#) is a convenient, easy to use display accessory for the Endress+Hauser TMT36 and TMT72 connection head temperature transmitters. Simply clip the display on the TMT36 or TMT72 transmitter to get a digital readout of the transmitter scaled output. Transmitter configuration parameters are automatically read by the TID10, so no additional configuration is required. A DIP switch setting is available to rotate the display reading 180 degrees.



For a variety of cable options see our website www.AutomationDirect.com

Endress+Hauser TMT36 & TMT72 Programmable Temperature Transmitter Accessory

Part Number	Description	Weight (lb)	Price
TID10-1009/0	Endress+Hauser display, polycarbonate. For use with Endress+Hauser TMT36 and TMT72 programmable temperature transmitters.	0.36	\$121.00

Display Information

Part Number	Drawing Links	Manufacturer Manual
TID10-1009/0	PDF	PDF

For complete technical information and installation see [Manufacturer Manual link](#).



[TID10-1009/0](#) shown mounted on a TMT72 transmitter.

Display Information

Pos.	Short description
1	Displays the TAG
2	Configuration locked
3	'Communication' symbol
4	Channel display C1, C2 (P1, S1)
5	Measured value and channel display or warning/error message
6	Bargraph display (for HART® head transmitter)
A	Connection to head transmitter
B	DIP switch address setup
C	DIP switch device setup

DIP-Switches Default = OFF