

CF Series Fiberglass In-Line Pushbutton Enclosures 30mm and 22mm with Lift-off Cover

STÄHLIN
A ROBROY ENCLOSURES® BRAND



Construction

- Hot compression molded fiberglass reinforced thermoset polyester
- Poured polyurethane seamless gasket provides watertight, dust-tight environmental seal
- Recessed captive stainless steel screws
- 300 Series stainless steel used on all external hardware
- Workable material cuts, drills, punches and saws with ease and accuracy
- Optional mounting feet
- Rounded edges, minimal protrusions or exposed pocket prevents accumulation of dust or debris
-
- Metal grounding strap
- Submersible, non-corrosive environmental design
- Lift-off cover with four cover screws
- Non-conductive, impact-resistant, UV-resistant
- Non-flame propagating
- Subpanel not required
- Smooth surface, no color variations, swirls or color pockets, no voids
- Color: Gray

Listings

- UL/cUL [File E64358]
- NEMA Types 1, 3R, 4X, 6P, and 12 [Files 508A, 50, and 50e]
- CSA Standard C22.2 Types 1, 3R, 4X, 6P, and 12 [File LR069014]
- IEC 60529 Ratings IP66, IP67, IP68 [File E362920]
- UL 1741 [File E333478]
- Temperature Range -76°F to +274°F [-60°C to +134°C]
- Flammability Rating UL94-5V
 - Self-extinguishing
 - Non-halogenated
 - Non-flame propagating
- NFPA No. 101 Flame Spread Class A (1)

Certifications

- cULus, CSA, IEC, REACH
- Outdoor UV Exposure Rated [UL 746C (F1)]
- Plenum Space Rating [File 2043]



CF Series 30mm Fiberglass In-Line Pushbutton				
Part Number	Price	# Holes	Enclosure Overall Size HxWxD	Drawing Link
CF6PB	\$66.00	1	6.63 x 3.81 x 3.89 [168 x 97 x 99]	PDF
CF2PB	\$68.00	2	6.63 x 3.81 x 3.89 [168 x 97 x 99]	PDF
CF3PB	\$74.00	3	8.88 x 3.81 x 3.89 [226 x 97 x 99]	PDF
CF4PB	\$75.00	4	11.13 x 3.81 x 3.89 [283 x 97 x 99]	PDF
CF5PB	\$87.00	5	13.78 x 3.63 x 3.14 [350 x 92 x 80]	PDF
CF6PB	\$101.00	6	17.35 x 3.63 x 3.14 [441 x 92 x 80]	PDF

**Notes: Subpanels not required.
Dimensions in inches [millimeters].**



CF Series 22mm Fiberglass In-Line Pushbutton				
Part Number	Price	# Holes	Enclosure Overall Size HxWxD	Drawing Link
CF1PB22	\$66.00	1	6.63 x 3.81 x 3.89 [168 x 97 x 99]	PDF
CF2PB22	\$68.00	2	6.63 x 3.81 x 3.89 [168 x 97 x 99]	PDF
CF3PB22	\$74.00	3	6.63 x 3.81 x 3.89 [168 x 97 x 99]	PDF
CF4PB22	\$75.00	4	8.88 x 3.81 x 3.89 [226 x 97 x 99]	PDF
CF5PB22	\$87.00	5	11.13 x 3.81 x 3.89 [283 x 97 x 99]	PDF
CF6PB22	\$101.00	6	11.13 x 3.81 x 3.89 [283 x 97 x 99]	PDF

**Notes: Subpanels not required.
Dimensions in inches [millimeters].**

