

# SC931YN16VDBA5F Cutsheet



CFA solenoid valve bank, (3) stations, 2-port (2-way), N.C., 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=0.14, individual metering, stainless steel body, 24 VDC, 4W, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC931YN16VDBA5F>

## Technical Specifications

|                                   |                                  |
|-----------------------------------|----------------------------------|
| <b>Brand</b>                      | CFA                              |
| <b>Item</b>                       | Valve bank                       |
| <b>Working Fluid</b>              | Air, inert gas, water or coolant |
| <b>Valve Type</b>                 | Solenoid process                 |
| <b>Number of Stations</b>         | 3                                |
| <b>Port Quantity</b>              | 2-port (2-way)                   |
| <b>Number Of Positions</b>        | 2                                |
| <b>Valve Configuration</b>        | N.C.                             |
| <b>Body Material</b>              | Stainless steel                  |
| <b>Inlet Port</b>                 | 1/4in female NPT                 |
| <b>Outlet Port</b>                | 1/4in female NPT                 |
| <b>Flow Coefficient</b>           | 0.14                             |
| <b>Metering</b>                   | Individual                       |
| <b>Maximum Operating Pressure</b> | 87 psi                           |
| <b>Minimum Operating Pressure</b> | 0 psi                            |
| <b>Operating Voltage</b>          | 24 VDC                           |
| <b>Power Rating</b>               | 4W                               |
| <b>Electrical Connection</b>      | 11mm DIN style wiring plug       |
| <b>Includes</b>                   | Individual metering              |

## Agency Approvals

|                    |  |
|--------------------|--|
| <b>CE</b>          | <a href="#">View CE declarations</a>   |
| <b>RoHS Status</b> | Yes (See CE Doc)                       |
| <b>EU REACH</b>    | <a href="#">View EU REACH document</a> |
| <b>Other</b>       | None                                   |