

DIN Rail Receptacles

Overview

The FA-REC3 is a triple straight blade AC receptacle, 15A, 125VAC used for powering laptop computers and test equipment. This unit can be mounted on 35mm, 32mm, or 15mm DIN rail.





DIN Rail Receptacles Specifications

Part Number	FA-REC3
Price	\$36.00
Output Voltage	125VAC
Outlet Type	NEMA 5-15R
Output Current	15A maximum
Total Current	Must not exceed 15A if all outlets are used
GFCI	None
Number of Phases	1
Number of Poles	2
Number of Wires	3
Mounting	35mm, 32mm, or 15mm DIN rail
Wire Capacity	14 to 12 AWG
Screw Torque	0.5 N·m [4.4 lbf·in]
Operating Temperature	0 to 60°C [32 to 140°F]
Circuit Protection	None
Housing Material	Plastic
Agency Approval	cULus E139594

Dimensions

inches [mm]



See our website: www.automationdirect.com for complete engineering drawings.

DIN Rail Receptacles

Overview

Duplex straight blade AC receptacles are 35mm DIN Rail or panel mounted used for powering laptop computers and test equipment. The [FA-REC2](#) is a standard 125VAC, 15A receptacle and [FA-GFCI](#) is a 125VAC, 15A Ground-Fault Circuit Interrupter.




FA-GFCI

DIN Rail Receptacles Specifications

Part Number	FA-REC2	FA-GFCI
Price	\$43.50	\$62.00
Output Voltage	125VAC	
Output Type	NEMA 5-15	
Output Current	15A Maximum	
Circuit Protection	No	Yes
Mounting	Panel Mount or 35mm DIN Rail	
Number of Phases	1	
Number of Poles	2	
Number of Wires	3	
Wire Capacity	14–12 AWG (solid or stranded)	
Wire Strip Length	6–7 mm	
Tightening Torque	0.51 N·m [4.5 lbf·in]	
Operating Temperature	0 to 60°C [32 to 140°F]	
Circuit Protection	None	Ground-fault circuit interruption
Wire Type	Copper or Copper Clad	
Housing Material	PA66/6, Nylon	
Weight	180g [6.35 oz]	230g [8.11 oz]
Agency Approval	cULus E139594	

Dimensions

inches [mm]



FA-REC2

FA-GFCI

See our website: www.automationdirect.com for complete engineering drawings.