


# Datalogic Safety Light Curtains

## Advanced Series, Finger-safe



### Programmable safety light curtain with 14mm resolution

- Includes both sender and receiver
- Type 4, PLe, SIL3
- 14mm resolution integrated light curtain for finger protection
- Operating distance up to 7m (selectable)
- 300-900 mm protected height
- Zero dead zone
- Basic Configuration Mode (BCM) through pushbuttons
- Advanced Configuration Mode (ACM) through GUI (SG EXTENDED GUI software included)
- CASCADE (No differentiation between master and slave models)
- Integrated MUTING and BLANKING functions
- Compact housing
- Proprietary 18-pin to standard M12 connectors
- 8 signalling LEDs
- Alignment level bar graph on both TX and RX units
- IP65 rated
- UL, CE, TUV and RoHS compliant
- • Accessory Dongle for:
  - Configuration cloning
  - Ethernet (TCP/IP connection)
  - Remote monitoring
  - Remote programming




**SG4-14 Programmable Series Selection Table**

| Part Number                            | Price      | Protected Height<br>mm[in] | Total Height<br>A<br>mm[in] | Number<br>of Beams | Response<br>Time<br>[ms] | Response Time<br>with Code<br>[ms] | Approximate<br>Product Weight<br>per Unit<br>kg [lb] |
|----------------------------------------|------------|----------------------------|-----------------------------|--------------------|--------------------------|------------------------------------|------------------------------------------------------|
| <a href="#"><u>SG4-14-030-00-P</u></a> | \$961.00   | 300 [11.81]                | 306.3 [12.06]               | 32                 | 15                       | 20                                 | 2.10 [4.63]                                          |
| <a href="#"><u>SG4-14-045-00-P</u></a> | \$1,182.00 | 450 [17.72]                | 456.3 [17.96]               | 48                 | 17                       | 25                                 | 2.10 [4.63]                                          |
| <a href="#"><u>SG4-14-060-00-P</u></a> | \$1,405.00 | 600 [23.62]                | 606.3 [23.87]               | 64                 | 19                       | 29                                 | 3.00 [6.61]                                          |
| <a href="#"><u>SG4-14-075-00-P</u></a> | \$1,603.00 | 750 [29.53]                | 756.3 [29.78]               | 80                 | 20                       | 34                                 | 4.30 [9.48]                                          |
| <a href="#"><u>SG4-14-090-00-P</u></a> | \$1,871.00 | 900 [35.43]                | 906.3 [35.68]               | 96                 | 22                       | 38                                 | 4.30 [9.48]                                          |

## Dimensions

mm [in]



# Datalogic Safety Light Curtains

## Advanced Series




### SG4-14 and SG4-30 Programmable Series Specifications

| Electrical Data                   |                                                                                                                                                                                          |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Supply Voltage                    | 24VDC $\pm$ 20%                                                                                                                                                                          |
| Current Consumption (Transmitter) | 3W maximum                                                                                                                                                                               |
| Current Consumption (Receiver)    | 5W maximum (without load)                                                                                                                                                                |
| Outputs                           | 2 PNP OSSD outputs with short circuit protection (1.4 A @ 55°C)                                                                                                                          |
| Output Current                    | 0.5 A maximum on each output                                                                                                                                                             |
| Output Voltage – ON status:       | Vdd-1V                                                                                                                                                                                   |
| Output Voltage – OFF status:      | 0.2 V                                                                                                                                                                                    |
| Leakage Current                   | < 1mA                                                                                                                                                                                    |
| Output Capacitive Load            | 2.2 $\mu$ F @ 24VDC                                                                                                                                                                      |
| Recovery Time                     | 100ms typical                                                                                                                                                                            |
| Protected Height                  | 300 - 1800 mm                                                                                                                                                                            |
| Safety Category                   | Type 4 (ref. EN 61496-1)                                                                                                                                                                 |
| Auxiliary Functions               | Reset, Restart selection, Alignment, EDM, Test, Muting, Partial Muting, Override, Coding, Range reduction, Fixed Blanking, Floating Blanking, Cascade, PNP / NPN output, GUI programming |
| Electrical Protection             | Class I / Class III                                                                                                                                                                      |
| Electrical Connections            | M12 5-pole for sender                                                                                                                                                                    |
|                                   | M12 12-pole + M12 5-pole for receiver muting applications                                                                                                                                |
|                                   | M12 12-pole for receiver blanking applications                                                                                                                                           |
| Cable Length (for supply power)   | 50m (164ft) maximum                                                                                                                                                                      |
| Pollution Degree                  | 2                                                                                                                                                                                        |
| Optical Data                      |                                                                                                                                                                                          |
| Light Emission                    | Infrared LED (950nm)                                                                                                                                                                     |
| Resolution                        | 14mm                                                                                                                                                                                     |
|                                   | 30mm                                                                                                                                                                                     |
| Operating Distance                | 0.2 - 7 m / 0.2 - 4 m (0.7 - 23 ft / 0.7 - 13 ft) for 14mm resolution<br>0.2 - 20 m / 0.2 - 12 m (0.7 - 66 ft / 0.7 - 39 ft) for 30mm resolution                                         |
| Ambient Light Rejection           | IEC 61496-2                                                                                                                                                                              |
| Mechanical and Environmental Data |                                                                                                                                                                                          |
| Operating Temperature             | 0 to 55°C (32 to 131°F)                                                                                                                                                                  |
| Storage Temperature               | -25 to 70°C (-13 to 158°F)                                                                                                                                                               |
| Temperature Class                 | T6                                                                                                                                                                                       |
| Humidity                          | 15 - 95% (non-condensing)                                                                                                                                                                |
| Mechanical Protection             | IP65 (EN 60529)                                                                                                                                                                          |
| Vibrations                        | Width 0.35 mm                                                                                                                                                                            |
|                                   | Frequency 10 - 55 Hz 20 sweep per axis                                                                                                                                                   |
|                                   | 1 octave / min (EN 60068-2-6)                                                                                                                                                            |
| Shock Resistance                  | 16ms (10g) 1000 shock for each axis (EN60068-2-29)                                                                                                                                       |
| Housing Material                  | Painted aluminum (yellow RAL 1003) front screen                                                                                                                                          |
| Cap Material                      | PBT Valox 508 (pantone 072-CVC)                                                                                                                                                          |
| Front Glass Material              | PMMA (Polymethylmethacrylate [acrylic])                                                                                                                                                  |
| Connectors                        | Proprietary 18-pin to standard M12                                                                                                                                                       |
| Agency Approvals                  | UL E226479, CE, TUV, RoHS                                                                                                                                                                |


To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at [www.AutomationDirect.com](http://www.AutomationDirect.com)

## Status Indicators

Receiver




Sender



# Datalogic Safety Light Curtains

## Advanced Series Accessories

### Basic Mode / Blanking Accessories




#### Pigtail Cable Blanking Configuration for Receiver (CS-G1-70-B-002)



##### M12 12-pin:

|     |                                 |
|-----|---------------------------------|
| 1.  | 24V (brown)                     |
| 2.  | 0V (blue)                       |
| 3.  | Reset / Restart / Align (white) |
| 4.  | Teach In (green)                |
| 5.  | OSSD2 (pink)                    |
| 6.  | EDM (yellow)                    |
| 7.  | N.C. (black)                    |
| 8.  | OSSD1 (gray)                    |
| 9.  | Tolerance (red)                 |
| 10. | Lamp (violet)                   |
| 11. | N.C. (gray / pink)              |
| 12. | Earth (red / blue)              |




#### Pigtail Cable for Sender (CS-G1-50-B-002)



##### M12 5-pin:

|    |                 |
|----|-----------------|
| 1. | 24V (brown)     |
| 2. | Test (white)    |
| 3. | 0V (blue)       |
| 4. | Earth (black)   |
| 5. | Not Used (gray) |




Note: Confirm the specific color to each pinout based on the cable used during installation.

# Datalogic Safety Light Curtains

## Advanced Series Accessories


### Muting Accessories



#### Pigtail Cable Muting Configuration for Receiver (CS-R1-75-B-002)




##### M12 12-pin:



|     |                                 |
|-----|---------------------------------|
| 1.  | 24V (brown)                     |
| 2.  | 0V (blue)                       |
| 3.  | Reset / Restart / Align (white) |
| 4.  | Teach In (green)                |
| 5.  | OSSD2 (pink)                    |
| 6.  | EDM (yellow)                    |
| 7.  | N.C. (black)                    |
| 8.  | OSSD1 (gray)                    |
| 9.  | Tolerance (red)                 |
| 10. | Lamp (violet)                   |
| 11. | N.C. (gray / pink)              |
| 12. | Earth (red / blue)              |

##### M12 5-pin:




|    |                 |
|----|-----------------|
| 1. | 24V (brown)     |
| 2. | Muting2 (white) |
| 3. | 0V (blue)       |
| 4. | Muting1 (black) |
| 5. | N.C. (gray)     |

#### Pigtail Cable for Sender (CS-G1-50-B-002)



##### M12 5-pin:




|    |                 |
|----|-----------------|
| 1. | 24V (brown)     |
| 2. | Test (white)    |
| 3. | 0V (blue)       |
| 4. | Earth (black)   |
| 5. | Not Used (gray) |

Note: Confirm the specific color to each pinout based on the cable used during installation.

# Datalogic Safety Light Curtains

## Advanced Series Accessories

### Cascading Cables



*Note: A maximum number of three units, one master and two slaves, may be cascaded. The maximum length of the master unit is 1800mm and the maximum length of each slave is 1200mm.*

# Datalogic Safety Light Curtains

## Advanced Series Accessories



| Safety Light Curtains Cables           |         |                                                                                                                                                    |
|----------------------------------------|---------|----------------------------------------------------------------------------------------------------------------------------------------------------|
| Part Number                            | Price   | Description                                                                                                                                        |
| <a href="#"><u>CS-R1-75-B-002</u></a>  | \$52.00 | Datalogic cable, muting, PVC jacket, 0.2 m cable length, 18-pin proprietary to 5-pin M12 male quick-disconnect to 12-pin M12 male quick-disconnect |
| <a href="#"><u>CS-G1-70-B-002</u></a>  | \$41.00 | Datalogic cable, blanking, PVC jacket, 0.2 m cable length, 18-pin proprietary to 12-pin M12 male quick-disconnect                                  |
| <a href="#"><u>CS-G1-50-B-002</u></a>  | \$41.00 | Datalogic cable, emitter, PVC jacket, 0.2 m cable length, 18-pin proprietary to 5-pin M12 male quick-disconnect                                    |
| <a href="#"><u>CS-F1-80-B-0005</u></a> | \$34.50 | Datalogic cable, cascading, PVC jacket, 0.05 m cable length, 18-pin proprietary to 18-pin proprietary                                              |
| <a href="#"><u>CS-F1-80-B-005</u></a>  | \$34.50 | Datalogic cable, cascading, PVC jacket, 0.5 m cable length, 18-pin proprietary to 18-pin proprietary                                               |
| <a href="#"><u>CS-F1-80-B-01</u></a>   | \$51.00 | Datalogic cable, cascading, PVC jacket, 1m cable length, 18-pin proprietary to 18-pin proprietary                                                  |

**CS-R1-75-B-002****CS-G1-70-B-002****CS-G1-50-B-002****CS-F1-80-B-0005****CS-F1-80-B-005****CS-F1-80-B-01**

# Datalogic Safety Light Curtains

## Advanced Series Accessories

### L-Muting Arms

SG-L-ARMS L muting arms provide an optional method of achieving unidirectional muting.

#### SG-L-ARMS


**\$390.00**

- Operating distance up to 3m
- Detectable objects down to 16.5 cm (6.5 in) in length. (See manual for exact formulas.)



### Dimensions

**mm [in]**



# Datalogic Safety Light Curtains

## Advanced Series Accessories



### T-Muting Arms

SG-T-ARMS T muting arms provide an optional method of achieving bidirectional muting.

#### SG-T-ARMS


\$679.00

- Operating distance up to 3m
- Detectable objects down to 34.5 cm (13.6 in). (See manual for exact formulas.)



### Dimensions

mm [in]




# Datalogic Safety Light Curtains

## Advanced Series Accessories




### L-Muting Arm and Cable



*Note: Active side shown*

### T-Muting Arms and Cable



*Note: Active side shown*

# Datalogic Safety Light Curtains

## Advanced Series Accessories



| Safety Light Curtains Muting Arms and Cables |          |                                                                                                                                                                        |
|----------------------------------------------|----------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Part Number                                  | Price    | Description                                                                                                                                                            |
| <a href="#"><u>SG-L-ARMS</u></a>             | \$390.00 | Muting arm pair, L-type, 4-pin M12 female quick-disconnect. For use with SG4 series (-P) light curtains.                                                               |
| <a href="#"><u>SG-T-ARMS</u></a>             | \$679.00 | Muting arm pair, T-type, 4-pin M12 female quick-disconnect. For use with SG4 series (-P) light curtains.                                                               |
| <a href="#"><u>CV-L1-02-B-007</u></a>        | \$30.00  | Datalogic cable, L-muting, PVC jacket, 0.5 m cable length, 5-pin M12 female quick-disconnect to 5-pin M12 female quick-disconnect                                      |
| <a href="#"><u>CV-Y1-02-B-007</u></a>        | \$35.50  | Datalogic cable, T-muting, PVC jacket, 0.5 m cable length, 5-pin M12 female quick-disconnect to 5-pin M12 female quick-disconnect to 5-pin M12 female quick-disconnect |

**[SG-L-ARMS](#)****[SG-T-ARMS](#)****[CV-L1-02-B-007](#)****[CV-Y1-02-B-007](#)**

# Datalogic Safety Light Curtains

## Advanced Series Accessories



### Communication Interface



**SG4-DONGLE**



SG4-DONGLE communication interface attaches to programmable Datalogic Safety Light Curtains and a PC through an Ethernet TCP/IP connection allowing remote monitoring and remote programming. Configuring, cloning, error logging and remote monitoring and programming are simplified through the free downloadable software.\*

*\*Note: To connect SG4-DONGLE directly to a PC, order Ethernet cable CAB-ETH-M01.*


- Configuration cloning
- Ethernet TCP/IP connection
- Remote monitoring
- Remote programming using SG-EXTENDED-GUI software
- CE compliant

### Safety Light Curtains Communication Interface and Software

| Part Number                   | Price    | Description                                                                                                                                                   |
|-------------------------------|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <u><b>SG4-DONGLE</b></u>      | \$241.00 | Programming dongle. Requires programming software included with SG4 (-P) light curtains.                                                                      |
| <u><b>SG-EXTENDED-GUI</b></u> | \$23.50  | Programming software for SG4 series (-P) on CD; software also available for free download from <a href="http://Automationdirect.com">Automationdirect.com</a> |

### Dimensions

mm [in]



# Datalogic Safety Light Curtains

## Advanced Series Accessories



### Communication Software

**SG-EXTENDED-GUI** communication software is available for download free of charge at [www.automationdirect.com](http://www.automationdirect.com).  
Remote monitoring and programming are simplified through the software.\*

\*Note: To connect directly to a PC, order Ethernet cable [CAB-ETH-M01](#).

- Remote monitoring
- Remote configuration

**Part No. SG-EXTENDED-GUI**

**\$23.50**

**Software CD**


| Datalogic Parameters      |                                                                     |                                                                                             |
|---------------------------|---------------------------------------------------------------------|---------------------------------------------------------------------------------------------|
| Function                  | Parameters with BCM (Basic Configuration Mode):<br>Without GUI      | Parameters with ACM (Advanced Configuration Mode):<br>With GUI                              |
| <b>Coding</b>             | None / Code 1 / Code 2                                              | None / Code 1 / Code 2                                                                      |
| <b>Restart Mode</b>       | Auto / Manual Restart                                               | Auto / Manual Restart                                                                       |
| <b>Override Restart</b>   | Manual                                                              | Manual / Auto                                                                               |
| <b>EDM</b>                | Enable / Disable                                                    | Enable / Disable                                                                            |
| <b>Range Reduction</b>    | Long / Short                                                        | Long / Short                                                                                |
| <b>Muting Type</b>        | T-muting / L-muting                                                 | T-muting / L-muting<br>For L-muting: T12 time interval selection, T12 multiplier selection  |
| <b>Muting Timeout</b>     | 10 minute / infinite                                                | Selectable length in steps of 1 minute from 10min to 1080 minutes                           |
| <b>Muting Filter</b>      | None                                                                | ON (100ms) or OFF                                                                           |
| <b>Muting Delay</b>       | None                                                                | Selectable in steps of 100ms up to 1000ms                                                   |
| <b>Partial Muting</b>     | None                                                                | Possible to define up to 5 zones each defined in position and dimension                     |
| <b>Override Mode</b>      | Level / Edge                                                        | Level / Edge                                                                                |
| <b>Override Timeout</b>   | 120 seconds                                                         | Selectable in steps of 1 minute from 1 to 256 minutes                                       |
| <b>Fixed Blanking</b>     | Two zones can be configured                                         | 5 zones can be configured, also with increased tolerance ( top or bottom)                   |
| <b>Floating Blanking</b>  | 1 or 2 beams floating blanking with partial surveillance selectable | **5 zones can be configured, total or partial surveillance without limit of number of beams |
| <b>Reduced Resolution</b> | 4 beams                                                             | 1 / 2 / 3 / 4 beams selectable                                                              |

\*\*Note - Blocking the two beams on both ends at the same time is not permitted.

# Datalogic Safety Light Curtains

## Accessories

### Communication Interface




# Datalogic – Ethernet Cables





| Datalogic Communication Cables |         |                                                                                                             |
|--------------------------------|---------|-------------------------------------------------------------------------------------------------------------|
| Part Number                    | Price   | Description                                                                                                 |
| <b><u>CAB-ETH-M01</u></b>      | \$52.00 | Datalogic cable, Ethernet, PVC jacket, shielded, 1m [3.28 ft] cable length, M12 4-pin male D-coded to RJ45  |
| <b><u>CAB-ETH-M03</u></b>      | \$63.00 | Datalogic cable, Ethernet, PVC jacket, shielded, 3m [9.84 ft] cable length, M12 4-pin male D-coded to RJ45  |
| <b><u>CAB-ETH-M05</u></b>      | \$75.00 | Datalogic cable, Ethernet, PVC jacket, shielded, 5m [16.40 ft] cable length, M12 4-pin male D-coded to RJ45 |

**CAB-ETH-M01****CAB-ETH-M03****CAB-ETH-M05**

## Diagrams



Pin assignment M12 male connector,  
4-pos., D-coded, male side



Connector pin assignment plug RJ45



Cable cross section

# Datalogic Safety Light Curtains

## Accessories

### Mounting Brackets

**Datalogic Safety Light Curtains Mounting Brackets Selection Guide**

| Part Number                        | Price   | Mounting Bracket Type | For Use With                          | Qty Per Package | Drawing                    |
|------------------------------------|---------|-----------------------|---------------------------------------|-----------------|----------------------------|
| <a href="#"><u>ST-K4ROT</u></a>    | \$20.00 | Rotational            | SG4 Base Series (-E) light curtains   | 4               | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>ST-K4ROT-SH</u></a> | \$66.00 | Rotational            | All SH4 Series light curtains         | 4               | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>ST-KSTD</u></a>     | \$10.00 | Standard              | All SG4 and SH4 Series light curtains | 4               | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>ST-K4OR</u></a>     | \$47.00 | Lateral orientable    | All SG4 and SH4 Series light curtains | 4               | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>ST-K4AV</u></a>     | \$20.00 | Anti-vibration        | All SG4 and SH4 Series light curtains | 4               | <a href="#"><u>PDF</u></a> |



[ST-K4ROT](#)



[ST-K4ROT-SH](#)



[ST-KSTD](#)



[ST-K4OR](#)



[ST-K4AV](#)

# Datalogic Safety Light Curtains

## Accessories



### Test Pieces

TP-14 and TP-30 test pieces are used to verify if the resolution of safety light curtains is maintained inside the entire detection field. TP-14 has a diameter of 14mm [0.55 in] and TP-30 has a diameter of 30mm [1.18 in]. Both models have an overall length of 300mm [11.81 in].

| Safety Light Curtains Test Pieces |         |                                                                                      |
|-----------------------------------|---------|--------------------------------------------------------------------------------------|
| Part Number                       | Price   | Description                                                                          |
| <u><b>TP-14</b></u>               | \$23.50 | Test rod for 14mm resolution finger detection light curtains, plastic, 14mm diameter |
| <u><b>TP-30</b></u>               | \$25.50 | Test rod for 30mm resolution hand detection light curtains, plastic, 30mm diameter   |



**TP-14**



**TP-30**

# Safety Products



*Warning: Safety products sold by AutomationDirect are Safety components only. The purchaser/installer is solely responsible for the application of these components and ensuring all necessary steps have been taken to assure each application and use meets all performance and applicable safety requirements and/or local, national and/or international safety codes as required by the application. AutomationDirect cannot certify that our products, used solely or in conjunction with other AutomationDirect or other vendors' products, will assure safety for any application. Any person using or applying any products sold by AutomationDirect is responsible for learning the safety requirements for their individual application and applying them, and therefore assumes all risks, and accepts full and complete responsibility, for the selection and suitability of the product for their respective application.*

*AutomationDirect does not provide design or consulting services, and cannot advise whether any specific application or use of our products would ensure compliance with the safety requirements for any application.*