

# DINnectors® Accessories

## Steel DIN Rail (One-Meter Length)


### Features

#### 35mm wide

- 7.5 mm-high rails primarily used to mount terminal blocks, relays, timers and small PLCs such as the BRX, CLICK, DirectLogic and Productivity series. 15mm-high rails for mounting larger and heavier components such as contactors and larger PLCs

#### 15mm wide

- DN-R15S1 exclusively for mounting mini terminal blocks such as the DN-M10-A




### Steel DIN Rails Specifications

	Part Number	Qty	Price	Part Number	Qty	Price	Part Number	Qty	Price
DIN Rail	<a href="#"><u>DN-R35S1</u></a>	10	\$39.00	<a href="#"><u>DN-R35HS1</u></a>	10	\$68.00	<a href="#"><u>DN-R15S1</u></a>	10	\$36.00
	<a href="#"><u>DN-R35S1-2</u></a>	2	\$11.00	<a href="#"><u>DN-R35HS1-2</u></a>	2	\$16.50	<a href="#"><u>DN-R15S1-2</u></a>	2	\$10.00
Description	DINnector DIN rail, slotted, 35mm width, 7.5mm height, 1m (39.37in) length, plated steel. Package of 10.			DINnector DIN rail, slotted, 35mm width, 15mm height, 1m (39.37in) length, plated steel. Package of 10.			DINnector DIN rail, slotted, 15mm width, 5.5mm height, 1m (39.37in) length, plated steel. Package of 10.		
Plating	Zinc-plated and chromated								
International Standards	EN 60715, RoHs								
Suggested Mounting Screw Type	M6			M6			M4		


### Dimensions

mm [inches]


**DN-R35S1**



**DN-R35HS1**



**DN-R15S1**



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings

# **DINnectors** Accessories

## Aluminum DIN Rail (One-Meter Length)


### Features

#### 35mm wide

- Non-anodized finish
- Terminal blocks only
- Maximum mounting screw #10-32 or M5
- Available in 1-meter standard length
- Quantity per pack: 2 or 10

### Dimensions

mm [inches]




**DN-R35SAL1**  
**DN-R35SAL1-2**


### Features

#### 35mm wide raised

- Non-anodized finish
- Enables users to raise terminal blocks 2¼" above the back panel
- Terminal blocks only
- Available in 1-meter standard length
- Bushing or grommet recommended for wire access hole (example Heyco UB-875 not sold by ADC)
- Quantity per pack: 2



**DN-R35SAL2-2**



## Aluminum DIN Rails Specifications (One-Meter Length)

	Part Number	Qty	Price	Part Number	Qty	Price
DIN Rail	<u>DN-R35SAL1</u>	10	\$60.00	<u>DN-R35SAL2-2</u>	2	\$38.00
	<u>DN-R35SAL1-2</u>	2	\$16.00			
Description	DINector DIN rail, slotted, 35mm width, 10mm height, 1m (39.37in) length, aluminum. Package of 10.			DINector DIN rail, slotted, 2in raised 35mm width, 7.5mm height, 1m (39.37in) length, aluminum. Package of 2.		
International Standards	DIN 50960, RoHs					
Suggested Mounting Screw Type	#10-32 or M5					



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings

# **DINnectors® Accessories**

## Aluminum DIN Rail (Pre-Cut Lengths)

### Features


#### 35mm wide

- Non-anodized finish
- Terminal blocks only
- Maximum mounting screw #10-32 or M5
- Available in variable lengths (see chart)
- Quantity per pack: 5




### Dimensions

mm [inches]



### Aluminum DIN Rails Specifications (Pre-Cut Lengths)

Part Number	Length mm [in]	Number of Slots	Price
<a href="#"><u>DN-R35SAL1-072-5</u></a>	72 [2.83]	2	\$9.75
<a href="#"><u>DN-R35SAL1-143-5</u></a>	143 [5.63]	4	\$12.00
<a href="#"><u>DN-R35SAL1-215-5</u></a>	215 [8.46]	6	\$14.00
<a href="#"><u>DN-R35SAL1-286-5</u></a>	286 [11.26]	8	\$16.50
<a href="#"><u>DN-R35SAL1-358-5</u></a>	358 [14.09]	10	\$19.00
<a href="#"><u>DN-R35SAL1-429-5</u></a>	429 [16.89]	12	\$20.50
<a href="#"><u>DN-R35SAL1-500-5</u></a>	500 [19.69]	14	\$22.00
<a href="#"><u>DN-R35SAL1-572-5</u></a>	572 [22.52]	16	\$24.50
<a href="#"><u>DN-R35SAL1-644-5</u></a>	644 [25.35]	18	\$26.00
<a href="#"><u>DN-R35SAL1-715-5</u></a>	715 [28.15]	20	\$27.00
<a href="#"><u>DN-R35SAL1-787-5</u></a>	787 [30.98]	22	\$28.50
<a href="#"><u>DN-R35SAL1-858-5</u></a>	858 [33.78]	24	\$30.50



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings

# **DINnectors** Accessories

## DIN rail support brackets

- Angled support brackets raise and tilt mounting rails 30 degrees from mounting surface for easier wiring
- [DN-ASB1](#) plated steel support bracket
- [DN-ASB2-10](#) cold-rolled steel treated with galvanic zinc plating and passivation

## DIN rail mounting clips

- Snap small devices not made for mounting onto 35mm DIN rails
- Zinc-plated steel

DIN Rail Support Brackets and Mounting Clips			
Part Number	Description	Qty	Price
<a href="#">DN-ASB1</a>	30° angled DIN rail support bracket (M6-1.0 screws not included)	50	\$107.00
<a href="#">DN-ASB2-10</a>	30° angled DIN rail support bracket (M6-1.0 screws included)	10	\$18.00
<a href="#">DN-SSB25-10</a>	1" (25mm) DIN rail support bracket (M6-1.0 screws included)	10	\$24.50
<a href="#">DN-SSB50-10</a>	2" (50mm) DIN rail support bracket (M6-1.0 screws included)	10	\$25.50
<a href="#">DN-SSB70-10</a>	2.75" (70mm) DIN rail support bracket (M6-1.0 screws included)	10	\$32.00
<a href="#">DN-SSB90-10</a>	3.5" (90mm) DIN rail support bracket (M6-1.0 screws included)	10	\$34.50
<a href="#">DN-CLIP-FM4</a>	DIN rail mounting clip with M4 x 0.7 mm threaded hole (Screws not included)	40	\$66.00
<a href="#">DN-CLIP-FM4-5</a>		5	\$9.50
<a href="#">DN-CLIP-FM5</a>	DIN rail mounting clip with M5 x 0.8 mm threaded hole (Screws not included)	40	\$66.00
<a href="#">DN-CLIP-FM5-5</a>		5	\$9.50



[DN-ASB1](#)[DN-ASB2-10](#)[DN-SSB25-10](#)[DN-SSB50-10](#)[DN-SSB70-10](#)[DN-SSB90-10](#)
[DN-CLIP-FM4](#)  
[DN-CLIP-FM4-5](#)

[DN-CLIP-FM5](#)  
[DN-CLIP-FM5-5](#)


# DINnectors® Accessories

## Dimensions



mm [inches]

**DN-ASB1****DN-ASB2-10**

**DN-SSB25-10**  
**DN-SSB50-10**  
**DN-SSB70-10**  
**DN-SSB90-10**

**DIN Rail Support Brackets**

Part Number	DIM A mm [inches]	DIM B mm [inches]
<b>DN-SSB25-10</b>	15.0 [0.59]	25.0 [0.98]
<b>DN-SSB50-10</b>	40.0 [1.58]	50.0 [1.97]
<b>DN-SSB70-10</b>	60.0 [2.36]	70.0 [2.76]
<b>DN-SSB90-10</b>	80.0 [3.15]	90.0 [3.54]

**DN-CLIP-FM4****DN-CLIP-FM5**See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings