

**DINnectors**



Triple-level and Sensor Terminal Blocks

Triple-level terminal blocks enable high-density wiring or simplified, low-cost sensor wiring.


When wiring space is at a premium, use the [DN-TL14-A](#) to connect three separate circuits in only 5mm of linear DIN-rail space. The rest of our family of triple-level blocks will allow you to wire one terminal block per sensor, vs. the traditional method, which requires three different single-level blocks per sensor.

The [DN-TL14S-A](#) is the standard sensor terminal block, and the [DN-TL14SLP-A](#) and [DN-TL14SLN-A](#) provide LED indication at the terminal block when voltage is present.

- Screw connection terminal
- 35mm DIN-rail mountable
- LVD 2006/95/EC



DN-TL14-A
Series: EURO W 2.5/35



DN-TL14S-A
Series: EURO Z 2.5/35

Ordering Information

Color	Part Number	Qty	Price	Part Number	Qty	Price
Gray	DN-TL14-A	25	\$69.00	DN-TL14S-A	25	\$61.00

Technical Specifications

Stripping Length	10 mm [0.39 in]			10 mm [0.39 in]		
Tightening Torque	0.5 N·m [4.5 lb·in]			0.5 N·m [4.5 lb·in]		
Density	200/m [57 pcs/ft]			200/m [57 pcs/ft]		
UL Approval*	300V	10A	26-14 AWG	300V	10A	26-14 AWG
VDE Approval	300V	10A	2.5 mm²	300V	10A	2.5 mm²
Operating Temperature	Ambient air temperature: -20 to 105°C [-4 to 221°F] Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F]					
SCCR Rating	10kA per Table SB4.1, 2009, UL 508A, Maximum short circuit current rating for unmarked components					
CE Conformity	CE (EN 60947-1 / EN 60947-7-1)					
Agency File #	UL E179129					

Accessories


End Covers		DN-EC14	25	\$18.00	DN-EC14S	25	\$15.00
Jumpers	2-pole Blue	DN-2JL14B-A	100	\$67.00	DN-2JL14B-A	100	\$67.00
		DN-2JL14B-AMN	25	\$15.00	DN-2JL14B-AMN	25	\$15.00
	3-pole Blue	DN-3JL14B-A	100	\$99.00	DN-3JL14B-A	100	\$99.00
		DN-3JL14B-AMN	25	\$23.00	DN-3JL14B-AMN	25	\$23.00
	12-pole Blue	DN-12JL14B-A	10	\$26.50	DN-12JL14B-A	10	\$26.50
	2-pole Red	DN-2JL14-A	100	\$67.00	DN-2JL14-A	100	\$67.00
		DN-2JL14-AMN	25	\$15.00	DN-2JL14-AMN	25	\$15.00
	3-pole Red	DN-3JL14-A	100	\$99.00	DN-3JL14-A	100	\$99.00
		DN-3JL14-AMN	25	\$23.00	DN-3JL14-AMN	25	\$23.00
	12-pole Red	DN-12JL14-A	10	\$26.50	DN-12JL14-A	10	\$26.50
Jumper Cutting Tool		DN-JL14CUT	1	\$112.00	DN-JL14CUT	1	\$112.00
35mm DIN Rail	7.5 mm high	DN-R35S1	10	\$39.00	DN-R35S1	10	\$39.00
		DN-R35S1-2	2	\$11.00	DN-R35S1-2	2	\$11.00
	15mm high	DN-R35HS1	10	\$68.00	DN-R35HS1	10	\$68.00
		DN-R35HS1-2	2	\$16.50	DN-R35HS1-2	2	\$16.50
End Brackets		DN-EB35	50	\$67.00	DN-EB35	50	\$67.00
		DN-EB35MN	20	\$31.50	DN-EB35MN	20	\$31.50
		DN-EB35-A	50	\$47.50	DN-EB35-A	50	\$47.50
		DN-EB35-A-10	10	\$12.00	DN-EB35-A-10	10	\$12.00
		DN-QEB35	50	\$42.50	DN-QEB35	50	\$42.50
		DN-QEB35-10	10	\$11.50	DN-QEB35-10	10	\$11.50
Angled Support Bracket		DN-ASB1	50	\$107.00	DN-ASB1	50	\$107.00
Marking Tags		DN-LAT-A series	500	various	DN-LAT-A series	500	various

*Copper wire only


For more information on accessories, see the [DINnectors Accessories](#) section of this chapter.

Dimensions

DN-TL14-A



DN-TL14S-A





DINnectors®

Triple-level and Sensor Terminal Blocks

Sensor wiring has never been this simple.

- **A** Wire the bottom two levels of one [DN-TL14-A](#) to connect your power supply to what will become a sensor +V and -V power bus.
- **B** Mount the triple-level sensor blocks next to the [DN-TL14-A](#). The [DN-TL14S-A](#) is our standard sensor terminal block. The [DN-TL14SLP-A](#) gives you LED indication for PNP sensors, and the [DN-TL14SLN-A](#) gives you LED indication for NPN sensors.
- **C** Use the top level to connect the first sensor signal line to the PLC.
- **D** Connect the power supply terminals of the [DN-TL14-A](#) to the LED sensor terminal blocks by installing jumpers. This will create a +V and -V power bus on the two bottom levels of the terminals. Use an external wire to connect a group of 12 [DN-TL14-A](#)s to another group.
- **E** Wire the sensor signal lines through the top levels of the blocks to your PLC or controller. Remember to use the appropriate end covers for safety purposes.





Note: Wiring schematic is for reference only. See individual I/O modules for correct wiring connections.



Triple-level and Sensor Terminal Blocks with LED


- Screw connection terminal
- 35mm DIN-rail mountable
- LVD 2006/95/EC



DN-TL14SLP-A
Series: EURO Z 2.5 LP/35



DN-TL14SLN-A
Series: EURO Z 2.5 LN/35



Ordering Information

Color	Part Number	Qty	Price	Part Number	Qty	Price
Gray	DN-TL14SLP-A	25	\$120.00	DN-TL14SLN-A	25	\$120.00

Technical Specifications

Stripping Length	10 mm [0.39 in]			10 mm [0.39 in]		
Tightening Torque	0.5 N·m [4.5 lb·in]			0.5 N·m [4.5 lb·in]		
Density	200/m [57 pcs/ft]			200/m [57 pcs/ft]		
Leakage Current	25mA@5V			25mA@5V		
LED Voltage/Resistance	12 – 24V AC/DC. 3.4 kΩ			12 – 24V AC/DC. 3.4 kΩ		
UL Approval*	300V	10A	26-14 AWG	300V	10A	26-14 AWG
VDE Approval	300V	10A	2.5 mm²	300V	10A	2.5 mm²
Operating Temperature	Ambient air temperature: -20 to 105°C [-4 to 221°F] Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F]					
SCCR Rating	10kA per Table SB4.1, 2009, UL 508A, Maximum short circuit current rating for unmarked components					
CE Conformity	CE (EN 60947-1 / EN 60947-7-1)					
Agency File #	UL E179129					

Accessories


End Cover		DN-EC14S		25	\$15.00	DN-EC14S		25	\$15.00	
Jumpers	2-pole Blue	DN-2JL14B-A		100	\$67.00	DN-2JL14B-A		100	\$67.00	
		DN-2JL14B-AMN		25	\$15.00	DN-2JL14B-AMN		25	\$15.00	
	3-pole Blue	DN-3JL14B-A		100	\$99.00	DN-3JL14B-A		100	\$99.00	
		DN-3JL14B-AMN		25	\$23.00	DN-3JL14B-AMN		25	\$23.00	
	12-pole Blue		DN-12JL14B-A		10	\$26.50	DN-12JL14B-A		10	\$26.50
	2-pole Red	DN-2JL14-A		100	\$67.00	DN-2JL14-A		100	\$67.00	
		DN-2JL14-AMN		25	\$15.00	DN-2JL14-AMN		25	\$15.00	
	3-pole Red	DN-3JL14-A		100	\$99.00	DN-3JL14-A		100	\$99.00	
		DN-3JL14-AMN		25	\$23.00	DN-3JL14-AMN		25	\$23.00	
12-pole Red		DN-12JL14-A		10	\$26.50	DN-12JL14-A		10	\$26.50	
Jumper Cutting Tool		DN-JL14CUT		1	\$112.00	DN-JL14CUT		1	\$112.00	
35mm DIN Rail	7.5 mm high	DN-R35S1		10	\$39.00	DN-R35S1		10	\$39.00	
		DN-R35S1-2		2	\$11.00	DN-R35S1-2		2	\$11.00	
	15mm high	DN-R35HS1		10	\$68.00	DN-R35HS1		10	\$68.00	
		DN-R35HS1-2		2	\$16.50	DN-R35HS1-2		2	\$16.50	
End Brackets		DN-EB35		50	\$67.00	DN-EB35		50	\$67.00	
		DN-EB35MN		20	\$31.50	DN-EB35MN		20	\$31.50	
		DN-EB35-A		50	\$47.50	DN-EB35-A		50	\$47.50	
		DN-EB35-A-10		10	\$12.00	DN-EB35-A-10		10	\$12.00	
		DN-QEB35		50	\$42.50	DN-QEB35		50	\$42.50	
		DN-QEB35-10		10	\$11.50	DN-QEB35-10		10	\$11.50	
Angled Support Bracket		DN-ASB1		50	\$107.00	DN-ASB1		50	\$107.00	
Marking Tags		DN-LAT-A series		500	various	DN-LAT-A series		500	various	

*Copper wire only


For more information on accessories, see the DINnectors Accessories section of this chapter.

Dimensions

DN-TL14SLP-A



DN-TL14SLN-A



 DINnectors® Accessories

Marking Tags Cross Reference Charts - Screw-type

DINector Marking Tags Cross Reference - Screw-type					
<i>Block Type</i>	<i>DN-L</i>	<i>DN-LA</i>	<i>DN-LT</i>	<i>DN-LAT</i>	<i>DN-EMLBL</i>
DN-T12	–	X	X	–	–
DN-T10	X	–	X	–	–
DN-T8	X	–	X	–	–
DN-T6	X	–	X	–	–
DN-T4	X	–	X	–	–
DN-T1/0	X	–	X	–	–
<u>DN-T3/0</u>	X	–	X	–	–
DN-D10	X	–	X	–	–
DN-D10X	X	–	X	–	–
DN-D10LED	X	–	X	–	–
DN-D10DR	X	–	X	–	–
DN-TL14	–	–	–	X	–
DN-THERM	X	–	X	–	–
DN-EMXM1	–	X	X	–	X
DN-EMXDV	–	X	X	–	X
DN-M10	–	–	X	–	–
<u>DN-MG10</u>	–	–	X	–	–
DN-G10	X	–	X	–	–
DN-G8	X	–	X	–	–
DN-G6	X	–	X	–	–
DN-G4	X	–	X	–	–
DN-G1/0	X	–	X	–	–
DN-F6	X	–	X	–	–
DN-F10	X	–	X	–	–
DN-DIS2	–	X	X	–	–
DN-DIS4	X	–	X	–	–
DN-FE2	–	X	X	–	–
DN-FE4	X	–	X	–	–
DN-DIS10	X	–	X	–	–
DN-KBD12	–	X	X	–	–

Continued on next page


DINnectors® Accessories

Marking Tags

Marking Tags DN-L Series

Part Number	Marking Sequence	Qty	Price
<u>DN-L50</u>	1-50	500	\$56.00
<u>DN-L100</u>	51-100	500	\$56.00
<u>DN-L150</u>	101-150	500	\$56.00
<u>DN-L200</u>	151-200	500	\$56.00
<u>DN-L250</u>	201-250	500	\$56.00
<u>DN-L300</u>	251-300	500	\$56.00
<u>DN-L350</u>	301-350	500	\$56.00
<u>DN-L400</u>	351-400	500	\$56.00
<u>DN-L450</u>	401-450	500	\$56.00
<u>DN-LB</u>	Blank	500	\$38.00
<u>DN-LS</u>	L1, L2, L3, L, N, GND, +, -, COM, COM*	500	\$56.00

Dimensions




- The marking sequence of 50 tags (i.e. 101-150) is printed 10 times in each package of 500.
- The DN-L tags fit all DINnectors 6mm wide and wider.
- There will be a gap between tags on blocks wider than 6mm.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-LA Series

Part Number	Marking Sequence	Qty	Price
<u>DN-LA100</u>	1-100	500	\$56.00
<u>DN-LA200</u>	101-200	500	\$56.00
<u>DN-LA300</u>	201-300	500	\$56.00
<u>DN-LA400</u>	301-400	500	\$56.00
<u>DN-LAB</u>	Blank Tags	500	\$56.00
<u>DN-LAS</u>	L1, L2, L3, L, N, GND, +, -, COM, COM*	500	\$56.00

Dimensions




- The marking sequence of 100 tags (i.e. 1-100) is printed five times in each package of 500.
- The DN-LA tags fit all DINnectors 5mm wide and wider. There will be a gap between tags on blocks wider than 5mm.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-LAT Series

Part Number	Marking Sequence	Qty	Price
<u>DN-LAT100-A</u>	1-100	500	\$49.00
<u>DN-LAT200-A</u>	101-200	500	\$49.00
<u>DN-LAT300-A</u>	201-300	500	\$49.00
<u>DN-LAT400-A</u>	301-400	500	\$49.00
<u>DN-LAT500-A</u>	401-500	500	\$49.00
<u>DN-LAT600-A</u>	501-600	500	\$49.00
<u>DN-LATB-A</u>	Blank Tags	500	\$35.50
<u>DN-LATS-A</u>	L1, L2, L3, L, N, +, -, COM, COM*	500	\$49.00

Dimensions




- The marking sequence of 500 tags (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-QL Series

Part Number	Marking Sequence	Qty	Price
<u>DN-QL100</u>	1-100	500	\$42.50
<u>DN-QL200</u>	101-200	500	\$42.50
<u>DN-QL300</u>	201-300	500	\$42.50
<u>DN-QL400</u>	301-400	500	\$42.50
<u>DN-QL500</u>	401-500	500	\$42.50
<u>DN-QLB</u>	Blank Tags	500	\$36.00
<u>DN-QLS</u>	L1, L2, L3, L, N, +, -, COM, COM*	500	\$49.00

Dimensions



- The marking sequence of 500 (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

DINnectors® Accessories

Terminal Marking Accessories

**DN-EMLBL1****DN-EMLBL2****DN-EMLBL3**

Part Number	Description	For Use With	Qty	Price
DN-EMLBL1	Blank labels	DN-EMPEG1 pin protectors for DN-xEMXxx plug-in terminal blocks	100	\$9.25
DN-EMLBL2	Labels printed 1 – 12		100	\$13.00
DN-EMLBL3	Labels printed 13 – 24		100	\$13.00

Marking Pen – for terminal and wire marking tags

- Permanent
- Smudge-proof
- Waterproof
- Weatherproof
- Lightfast (won't fade)
- Dries in seconds (excellent for left-handed users)
- Dry-safe (pen can be left uncapped for days without drying out)
- Low odor ink

Part Number	Description	Qty	Price
DN-MP	Staedtler-Mars marking pen, for use with blank marking tags. Permanent Ink, fine tip.	1	\$4.50

**Marking pen**

Wire Marking Accessories

**DN-WMTAG1 wire tags &
DN-WM-x wire tag holders**

Part Number	Description	For Use With	Qty	Price
DN-WMTAG1	Wire tag – blank	all DN-WM-x wire tag holders	525	\$60.00
DN-WM-1	Wire tag holder, clear, 12mm length, 0.051–0.118 in diameter; for 22–16 AWG wire	DN-WMTAG1	200	\$12.50
DN-WM-2	Wire tag holder, clear, 12mm length, 0.098–0.196 in diameter; for 16–11 AWG wire		200	\$12.50
DN-WM-3	Wire tag holder, clear, 12mm length, 0.157–0.393 in diameter; for 13–5 AWG wire		100	\$8.25
DN-WM-4	Wire tag holder, clear, 12mm length, 0.314–0.629 in diameter; for 5AWG wire		100	\$7.75