


Flexible Portable Cord - Type SOOW, SJOOW, SEOOW & SJEOWW Type W



Overview

Use AutomationDirect's Flexible Portable Cord for temporary or portable power applications in industrial, OEM, utility, and commercial environments. Portable cord is a great solution for ceiling drops, mobile machinery power supplies, pendants, and lighting. Applications include factory floor, mining, and heavy construction. Our cord is highly flexible and suitable for harsh conditions, including temperature extremes, and is resistant to oil and chemicals that are common in the industrial environment.

AutomationDirect offers a wide range of portable cord types with jacket materials like CPE (chlorinated polyethylene elastomers), thermoset rubber or TPE (thermoplastic elastomer), and insulation types of Ethylene propylene rubber (EPR) or Ethylene Propylene Diene Monomer (EPDM) rubber. The combinations of these jackets and insulation types meet the requirement for "Extra-Hard Use" (SOOW & SEOOW) or "Hard Use" (SJOOW & SJEOWW) applications and carry the appropriate UL, CSA or MSHA ratings so they can be trusted to work in the harshest environments.

You should feel confident that AutomationDirect's Portable Cord meets or exceeds all the requirements to make it UL & CSA Listed and complies with NFPA 70 Articles 400 & 501.140 (Haz-Loc) and the Mine Safety and Health Administration.

Portable Cord Letter Codes Definitions:

- S** = Service cord - 600 Volt
- J** = Junior service - 300 Volt
- E** = Elastomer - thermoplastic elastomer that looks and feels like rubber
- OO** = Oil-resistant outer jacket and oil-resistant interior insulation
- W** = Moisture and sunlight resistant (approved for indoor and outdoor use)

Features

- 18AWG to 6AWG
- 2, 3, 4 & 5 conductors
- Cut to length in 1-foot increments
- As low as 10-foot minimum length
- 600V & 300V versions, Type W 2000V
- Multiple ratings and approvals
- Wide operating temperature range
- Thermoset rubber or thermoplastic jackets
- Suitable for outdoor use
- Excellent abrasion resistance



Click on the above thumbnail or go to <https://www.automationdirect.com/VID-WD-0016> for a short introduction on our cut to length cable

Conductor Colors:

- 2 Conductor** ● ●
- 3 Conductor** ● ● ●
- 4 Conductor** ● ● ● ●
- 5 Conductor** ● ● ● ● ●


DiRECT WIRE 8AWG SOOW Portable Cord

8AWG SOOW Portable Cord Specifications			
Conductor Gauge	8AWG	Conductor Color	3 conductor - Black, White, Green
Conductor Stranding	182/30 bare copper		4 conductor - Black, White, Red, Green
Voltage Rating	600V		
Outer Jacket Material	CPE (chlorinated polyethylene elastomers) thermoset rubber	Temperature Rating	-40°C (-40°F) to 90°C (194 °F)
Outer Jacket Color	Black with white print	Applicable Standards*	FT5 Flame Tested
Outer Jacket Thickness	0.060 in [1.52 mm] nominal		NEC (NFPA 70) Article 400
Overall Diameter	See table below		NEC (NFPA 70) 501.140 Class 1 Div 2
Cold Bend	-40°C (-40°F) per UL 1277		MSHA
Minimum Bend Radius	4x diameter		Sample Print Legend
Operating Temperature	-40°C to 90°C (-40°F to 194°F)		
Conductor Insulation	Low-smoke, halogen-free EPDM compound		
Conductor Nominal Insulation Thickness	0.030 in [0.76 mm]		

* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com

8AWG SOOW Portable Cord						
Part Number	AWG/# of Conductors	Nominal Overall Diameter in [mm]	Ampacity*	Minimum Cut Length (ft)**	Approximate Weight (lb/ft)	Price per foot
<u>SOOW-8-3BK-1</u>	8/3	17.86	40A	10ft	0.314	\$3.98
<u>SOOW-8-4BK-1</u>	8/4	19.56	35A		0.406	\$5.11

* Per NFPA 70 NEC Table 400.5 (A)(1)
** See web store for maximum cut lengths



Please Note: Our prices on flexible cord are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.


DiRECT WIRE 6AWG SOOW Portable Cord

6AWG SOOW Portable Cord Specifications			
Conductor Gauge	6AWG	Conductor Color	3 conductor - Black, White, Green
Conductor Stranding	260/30 bare copper		4 conductor - Black, White, Red, Green
Voltage Rating	600V		
Outer Jacket Material	CPE (chlorinated polyethylene elastomers) thermoset rubber	Temperature Rating	-40°C (-40°F) to 90°C (194 °F)
Outer Jacket Color	Black with white print	Applicable Standards	FT5 Flame Tested
Outer Jacket Thickness	0.060 in [1.52 mm] nominal		NEC (NFPA 70) Article 400
Overall Diameter	See table below		NEC (NFPA 70) 501.140 Class 1 Div 2
Cold Bend	-40°C (-40°F) per UL 1277		MSHA
Minimum Bend Radius	4x diameter	Sample Print Legend	Direct Wire [AWG]/[COND] SOOW 600V FT5 -40°C - 90°C P-07-KA190007- MSHA 30-CFR-S-7.407
Operating Temperature	-40°C to 90°C (-40°F to 194°F)		
Conductor Insulation	Low-smoke, halogen-free EPDM compound		
Conductor Nominal Insulation Thickness	0.030 in [0.76 mm]		

* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com

6AWG SOOW Portable Cord						
Part Number	AWG/# of Conductors	Nominal Overall Diameter in [mm]	Ampacity*	Minimum Cut Length (ft)**	Approximate Weight (lb/ft)	Price per foot
<u>SOOW-6-3BK-1</u>	6/3	19.33	55A	10ft	0.398	\$5.61
<u>SOOW-6-4BK-1</u>	6/4	21.21	45A		0.519	\$7.57

* Per NFPA 70 NEC Table 400.5 (A)(1)
** See web store for maximum cut lengths



Please Note: Our prices on flexible cord are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.