



# Tools – Drill and Tap Combinations


## Drill and Tap Combinations

Metric and fractional drill and tap combination bits.

- High-speed steel
- Relief-ground
- 1/4" (6.35 mm) hexagonal shank
- Thread deburring
- For use with mild steel. 1.5x diameter max material thickness
- Approximate thread percentage - 75%



**US270014**



| RUKO High-Speed Steel Metric Drill and Tap Combos |                 |             |         |                |                                 |                            |                          |                          |                           |                                      |
|---------------------------------------------------|-----------------|-------------|---------|----------------|---------------------------------|----------------------------|--------------------------|--------------------------|---------------------------|--------------------------------------|
| Coarse Thread                                     | Part Number     | Pcs/<br>Pkg | Price   | Thread<br>Size | Overall<br>Length<br>L1<br>(mm) | Drill Length<br>S1<br>(mm) | Tap Length<br>L2<br>(mm) | Drill Dia.<br>D1<br>(mm) | Collar Dia.<br>D2<br>(mm) | Max<br>Material<br>Thickness<br>(mm) |
|                                                   | <b>US270014</b> | 1           | \$10.00 | M3x0.5         | 51.0                            | 5.0                        | 7.0                      | 2.5                      | 7.0                       | 3.75                                 |