


Modular Fuse Holders for Class J Fuses



Description

- Choice of LED indicator or non-indicating fuse holder
- Comes in standard 1-, 2- and 3-Pole ganged assemblies where all fuses are extracted simultaneously
- Meets requirements of IEC 60529 for IP-20 finger safe rating
- 35mm DIN rail and chassis (6-32 UNC Pan Head recommended) mounting features
- Fuseholder wire ports dual wire rated from 18 to 3 AWG

Specifications

Construction: Thermoplastic, with tin-plated copper clip
 UL Flammability: 94V-0

Voltage Ratings: 600 Volts AC/DC (or less)

Ampere Ratings: 1 - 60 Amps

Interrupting Rating: 200,000 RMS Symmetrical Amps

Minimum Indicating Voltage (neon lamp): 90 Volts

Nominal Operating Current (neon lamp): 34 mA (460 VAC)

Agency Approvals

- Listed UL 512, Guide IZLT, File E14853
- CSA Certified per C22.2 Nos. 39 Class 6225-01, File LR47235
- CE compliance for the European Union Low Voltage Directive

| CH Series Modular Fuse Holders for Class J Fuses | | | | | | | | |
|--|-------------|-----------|----------------|-------|--|---------|---------------|----------|
| Amp Rating | Part Number | Amps | Type | Poles | Maximum Wire Size | Pcs/Pkg | Weight (lbs.) | Price |
| 30A | CH30J1 | 0.5 to 30 | Easy ID window | 1 | 18 -1 AWG Single 18 -3 AWG Dual 75°C | 6 | 2.8 | \$247.00 |
| | CH30J2 | | Easy ID window | 2 | | 3 | | \$344.00 |
| | CH30J3 | | Easy ID window | 3 | | 2 | | \$340.00 |
| | CH30J1I | | Neon indicator | 1 | | 6 | | \$286.00 |
| | CH30J2I | | Neon indicator | 2 | | 3 | | \$392.00 |
| | CH30J3I | | Neon indicator | 3 | | 2 | | \$373.00 |
| 60A | CH60J1 | 31 to 60 | Easy ID window | 1 | 18 -1 AWG Single 18 -3 AWG Dual 75°C | 6 | 3.4 | \$330.00 |
| | CH60J2 | | Easy ID window | 2 | | 3 | | \$386.00 |
| | CH60J3 | | Easy ID window | 3 | | 2 | | \$391.00 |
| | CH60J1I | | Neon indicator | 1 | | 6 | | \$369.00 |
| | CH60J2I | | Neon indicator | 2 | | 3 | | \$459.00 |
| | CH60J3I | | Neon indicator | 3 | | 2 | | \$420.00 |

Dimensions

| Dimension | CH30J in (mm) | CH60J in (mm) |
|-----------|---------------|---------------|
| A | 1.28 (32.5) | 1.58 (40.0) |
| B | 2.56 (65.0) | 3.16 (80.0) |
| C | 3.84 (97.5) | 4.72 (120.0) |
| D | 4.59 (116.6) | 4.88 (124.0) |
| E | 2.83 (71.8) | 3.31 (84.1) |
| F | 3.56 (90.4) | 3.85 (97.9) |
| G | 1.28 (32.5) | 1.58 (40.0) |
| H | 0.18 (4.44) | 0.18 (4.44) |

