

# Medium Duty Absolute Encoders (Metric Dimension Encoders)

## TRD-NA series


### Features

Why use an absolute encoder?  
Absolute encoders provide their exact position at all times, allowing monitoring equipment to read the correct position, even when power cycles. Features include:

- Small body with 50mm diameter and 35mm depth
- Splash proof (IP65 rating)
- 8mm solid shaft
- Absolute resolution available from 32 pulses per revolution to 2048 pulses per revolution
- Open collector output
- Up to 20kHz response frequency



Standard shaft (TRD-NA) model



\* Cable shield is not connected to the encoder body;

Absolute Medium Duty Solid Shaft Encoders					
Part Number	Price	Resolution	Input Voltage	Output	Body Dia.
<a href="#">TRD-NA32NWD</a>	\$366.00	5 bit gray code, 32 pulses per revolution	10-26 VDC	NPN open collector	50 mm
<a href="#">TRD-NA64NWD</a>	\$366.00	6 bit gray code, 64 pulses per revolution			
<a href="#">TRD-NA128NWD</a>	\$366.00	7 bit gray code, 128 pulses per revolution			
<a href="#">TRD-NA180NWD</a>	\$366.00	8 bit gray code, 180 pulses per revolution			
<a href="#">TRD-NA256NWD</a>	\$366.00	8 bit gray code, 256 pulses per revolution			
<a href="#">TRD-NA360NWD</a>	\$366.00	9 bit gray code, 360 pulses per revolution			
<a href="#">TRD-NA512NWD</a>	\$366.00	9 bit gray code, 512 pulses per revolution			
<a href="#">TRD-NA720NWD</a>	\$366.00	10 bit gray code, 720 pulses per revolution			
<a href="#">TRD-NA1024NWD</a>	\$366.00	10 bit gray code, 1024 pulses per revolution			
<a href="#">TRD-NA2048NWD</a>	\$366.00	11 bit gray code, 2048 pulses per revolution			

Wiring Connections								
Wire color	Connector Pin No.	Resolution						
		2048	1024 / 720	512 / 360	256 / 180	128	64	32
Blue	1	0V						
Brown	2	12/24V						
Black	3	bit 0 (20) *	bit 0 (20) *	no connection				
Red	4	bit 1 (21) *	bit 1 (21) *	bit 0 (20) *	no connection			
Orange	5	bit 2 (22) *	bit 2 (22) *	bit 1 (21) *	bit 0 (20) *	no connection		
Yellow	6	bit 3 (23) *	bit 3 (23) *	bit 2 (22) *	bit 1 (21) *	bit 0 (20) *	no connection	
Green	7	bit 4 (24) *	bit 4 (24) *	bit 3 (23) *	bit 2 (22) *	bit 1 (21) *	bit 0 (20) *	no connection
Purple	8	bit 5 (25) *	bit 5 (25) *	bit 4 (24) *	bit 3 (23) *	bit 2 (22) *	bit 1 (21) *	bit 0 (20) *
Gray	9	bit 6 (26) *	bit 6 (26) *	bit 5 (25) *	bit 4 (24) *	bit 3 (23) *	bit 2 (22) *	bit 1 (21) *
White	10	bit 7 (27) *	bit 7 (27) *	bit 6 (26) *	bit 5 (25) *	bit 4 (24) *	bit 3 (23) *	bit 2 (22) *
Black / White	11	bit 8 (28) *	bit 8 (28) *	bit 7 (27) *	bit 6 (26) *	bit 5 (25) *	bit 4 (24) *	bit 3 (23) *
Red / White	12	bit 9 (29) *	bit 9 (29) * (MSB)	bit 8 (28) * (MSB)	bit 7 (27) * (MSB)	bit 6 (26) * (MSB)	bit 5 (25) * (MSB)	bit 4 (24) * (MSB)
Orange / White	13	bit 10 (210) * (MSB)	no connection					
Shield	-	GND **						

\* Numbers in parentheses ( ) are the bits corresponding to binary code.  
 \*\* GND (cable shield) is not connected to encoder body; the enclosure is grounded through the 0VDC line.  
 Note: Numbers in parentheses ( ) are the bits corresponding to binary code.

# Medium Duty Absolute Encoders (Metric Dimension Encoders)

## Specifications – TRD-NA series

Electrical Specifications		
<b>Model</b>	<b>TRD-NAxxxx-NWD</b>	
<b>Power Supply</b>	<b>Operating Voltage *</b>	12–24 VDC (nominal) * Range: 10.8–26.4 VDC
	<b>Allowable Ripple</b>	3% rms max.
	<b>Current Consumption</b>	70mA max.
<b>Output Code</b>	Gray binary (38 gray codes at 180 resolution, 76 at 360 resolution, and 152 at 720 resolution)	
<b>Max. Response Frequency</b>	20kHz (Maximum revolution speed = (max. response frequency / resolution) x 60). (The encoder does not respond to revolution faster than the maximum speed.)	
<b>Accuracy</b>	$\frac{360}{\text{Resolution}} = \text{degree of accuracy}$	
<b>Direction of Rotation</b>	Normal (CW) or reversed (CCW) (When viewed from the shaft, CW is clockwise direction, and CCW is counterclockwise direction)	
<b>Rise/Fall Time</b>	2µs max. (at 1kW load resistance and when cable length is 2m or less)	
<b>Output</b>	<b>Output Type</b>	NPN open collector
	<b>Output Logic</b>	Negative logic (active low)
	<b>Sinking Current</b>	32mA max.
	<b>Residual Voltage</b>	16mA or less: 0.4 V max. 16mA → 32mA: 1.5 V max.
	<b>Load Power Voltage</b>	35VDC max.
* To be supplied by Class II source		
Mechanical Specifications		
<b>Starting Torque</b>	0.03 N·m [0.02 lb-ft]	
<b>Max. Allowable Shaft Load</b>	Radial: 50N [11.24 lbs]; Axial: 30N [6.74 lbs]	
<b>Max. Allowable Speed</b>	Continuous: 3000 rpm, instantaneous: 5000 rpm; (highest speed that can support the mechanical integrity of encoder)	
<b>Wire Size</b>	26 AWG	
<b>Weight</b>	Approx. 300g (10.58 oz) with 2m cable	
Environmental Specifications		
<b>Ambient Temperature</b>	-10 to 60 °C [14 to 140 °F]	
<b>Storage Temperature</b>	-25 to 85 °C [-13 to 185 °F]	
<b>Operating Humidity</b>	25–85% RH (with no condensation)	
<b>Insulation Resistance</b>	10MΩ min.	
<b>Vibration Resistance</b>	Durable for one hour along three axes at 10 to 55 Hz with 0.75 mm amplitude	
<b>Shock Resistance</b>	11ms with 980m/s <sup>2</sup> applied three times along three axes	
<b>Mounting Orientation</b>	Can be mounted in any orientation	
<b>Protection</b>	IP65	
<b>Agency Approvals</b>	cUL <sub>US</sub> (E189395)	

## Accessories


### Couplings

For encoders with a solid shaft, please select a coupling that fits your encoder. All couplings are typically in stock, ready to ship.

See the “Encoder Couplings” section for more information.

### Mounting Bracket & Clamps

Mounting Accessories		
Part #	Price	Description
<b>JT-035D</b>	\$18.00	Mounting Bracket: Metal; for use with all TRD-N/NH/NA encoders
<b>NM-9D*</b>	\$8.00	Mounting Clamp: Metal; for use with all TRD-N/NA encoders *
<b>NF-55D*</b>	\$20.00	Mounting Flange Kit: includes aluminum flange & NM-9D clamp; for use with all TRD-N/NA encoders *
* Order NF-55D (flange & clamp) for new installations. Order NM-9D (clamp) for replacement parts only.		




# Medium Duty Absolute and Incremental Encoders (Metric Dimension Encoders)


## Dimensions – TRD-N(H) & TRD-NA series

The following are the external dimensions of both incremental and absolute medium duty encoders and optional mounting accessories.

### Solid Shaft Incremental and Absolute Encoders (TRD-N, TRD-NA)




### Hollow Shaft Incremental Encoders only (TRD-NH)




### Optional Mounting Flange and Brackets for Medium Duty Encoders

NOTE: NF-55D flange & included NM-9D bracket: Requires (3) M4 x 0.7 tapped holes equally spaced on a 64mm bolt circle in the mounting surface.


#### JT-035D (bracket)




#### NF-55D (flange)



#### NM-9D (clamp)(included with NF-55D)



#### TRD-NH-BKT (bracket)




# Encoder Accessories – Couplings

## Encoder Couplings

Couplings provide a connection between solid-shaft encoders and solid shafts. We offer aluminum, fiberglass, and polymer couplings for metric, S.A.E. and metric-to-S.A.E. applications.

Misalignment compensation




Couplings Selection Guide and Dimensions																
Type	Part Number	Price	Applicable Encoders (shaft size)	Shaft Diameter		D	L	F	C	M	a	E	S	Working Torque (N-m)	Torsional Rigidity	Material
				d1	d2	( mm [in] )					max					
				( mm [in] )												
Fiberglass (metric)	<a href="#">GJ-4D</a>	\$12.00	TRD-MX (4mm)	4mm	4mm	13 [0.51]	21 [0.83]	5.3 [0.21]	3 [0.12]	M3 set screw	5°	0.4 [0.02]	0.4 [0.02]	0.6 N-m	6 N-m/rad	Glass-fiber reinforced resin
	<a href="#">GJ-6D</a>	\$9.25	TRD-S/SR (6mm)	6mm	6mm	15 [0.59]	22 [0.87]	5.2 [0.20]	3 [0.12]	M3 set screw	6°	0.5 [0.02]	0.12 [0.005]	0.8 N-m	10 N-m/rad	
	<a href="#">GJ-8D</a>	\$11.00	TRD-N/NA (8mm)	8mm	8mm	19 [0.75]	24 [0.94]	6.8 [0.27]	3.5 [0.14]	M4 set screw	5°	0.5 [0.02]	0.4 [0.016]	1.5 N-m	20 N-m/rad	
	<a href="#">GJ-10D</a>	\$12.00	TRD-GK (10 mm)	10 mm	10 mm	22 [0.87]	26 [1.02]	7.1 [0.28]	4 [0.16]	M4 set screw	5°	0.5 [0.02]	0.12 [0.005]	2.0 N-m	32 N-m/rad	
Fiberglass (SAE)	<a href="#">GJ-635D</a>	\$22.00	TRDA-2E (0.25 in)	0.25 in	0.25 in	15 [0.59]	22 [0.87]	5.2 [0.20]	3 [0.12]	M3 set screw	5°	0.5 [0.02]	0.12 [0.005]	0.8 N-m	10 N-m/rad	Glass-fiber reinforced resin
	<a href="#">GJK-953D</a>	\$27.00	TRDA-20/25 (0.375 in)	0.375 in	0.375 in	25 [0.98]	32 [1.26]	7.3 [0.29]	3.5 [0.14]	M4 set screw	5°	0.5 [0.02]	0.12 [0.005]	2.0 N-m	32 N-m/rad	
Polymer (SAE)	<a href="#">STP-MTRA-SC-1412</a>	\$30.00	TRDA-2E (0.25 in)	0.25 in	0.50 in	25 [0.98]	38 [1.50]	9.9 [0.39]	5.4 [0.21]	M3 cap screw	5°	0.3 [0.01]	0.12 [0.005]	3.7 N-m	0.36 °/lb-in	Engineered polymer
	<a href="#">STP-MTRA-SC-3812</a>	\$30.00	TRDA-20/25 (0.375 in)	0.375 in	0.50 in	25 [0.98]	38 [1.50]	9.9 [0.39]	5.4 [0.21]	M3 cap screw	5°	0.3 [0.01]	0.12 [0.005]	3.7 N-m	0.36 °/lb-in	
Aluminum (metric)	<a href="#">ARM-075-5-4D</a>	\$51.50	TRD-MX (4mm)	4mm	5mm	19.1 [0.75]	19.1 [0.75]	4.6 [0.18]	2.4 [0.09]	M3 set screw	5°	0.25 [0.01]	0.25 [0.01]	2.3 N-m	8.2 N-m/rad	Aluminum alloy
	<a href="#">RU-075D</a>	\$58.00	TRD-S/SR (6mm)	6mm	6mm	19.1 [0.75]	19.1 [0.75]	4.6 [0.18]	2.4 [0.09]	M3 set screw	5°	0.25 [0.01]	0.12 [0.005]	1.0 N-m	8.2 N-m/rad	
	<a href="#">JU-100D</a>	\$51.50	TRD-N/NA (8mm)	8mm	8mm	25.4 [1.00]	25.4 [1.00]	6.6 [0.26]	3.8 [0.15]	M5 set screw	5°	0.25 [0.01]	0.25 [0.01]	1.6 N-m	14.3 N-m/rad	
	<a href="#">RU-100D</a>	\$60.00	TRD-GK (10 mm)	10 mm	10 mm	25.4 [1.00]	25.4 [1.00]	6.6 [0.26]	3.8 [0.15]	M5 set screw	5°	0.25 [0.01]	0.12 [0.005]	1.6 N-m	14.3 N-m/rad	
Aluminum (metric-to-SAE)	<a href="#">ML13P-4-476D</a>	\$51.50	TRD-MX (4mm)	4mm	0.1875 in	13 [0.51]	19 [0.75]	5.5 [0.22]	2.5 [0.10]	M2 set screw	5°	0.4 [0.02]	0.2 [0.01]	0.25 N-m	44 N-m/rad	Aluminum alloy (Bent plate: Polyimide)
	<a href="#">ML16P-4-635D</a>	\$51.50	TRD-MX (4mm) TRDA-2E (0.25 in)	4mm	0.25 in	16 [0.63]	23 [0.91]	7 [0.28]	3 [0.12]	M3 set screw	5°	0.6 [0.02]	0.3 [0.01]	0.4 N-m	70 N-m/rad	
	<a href="#">MCGL16-6-635</a>	\$33.00	TRD-S/SR (6mm) TRDA-2E (0.25 in)	6mm	0.25 in	16 [0.63]	23.2 [0.91]	7 [0.28]	3 [0.12]	M3 set screw	3.5°	0.3 [0.01]	0.3 [0.01]	0.4 N-m	70 N-m/rad	
	<a href="#">MCGL20-8-635</a>	\$43.00	TRD-N/NA (8mm) TRDA-2E (0.25 in)	8mm	0.25 in	20 [0.79]	26 [1.02]	7.5 [0.30]	3.7 [0.15]	M3 set screw	3.5°	0.3 [0.01]	0.4 [0.02]	0.6 N-m	130 N-m/rad	
	<a href="#">MCGL20-8-952</a>	\$44.00	TRD-N/NA (8mm) TRDA-20/25 (0.375 in)	8mm	0.375 in	20 [0.79]	26 [1.02]	7.5 [0.30]	3.7 [0.15]	M3 set screw	3.5°	0.3 [0.01]	0.4 [0.02]	0.6 N-m	130 N-m/rad	
	<a href="#">MCGL25-10-635</a>	\$54.00	TRD-GK (10 mm) TRDA-2E (0.25 in)	10 mm	0.25 in	25 [0.98]	30.2 [1.19]	9 [0.35]	4 [0.16]	M4 set screw	3.5°	0.3 [0.01]	0.5 [0.02]	1.4 N-m	240 N-m/rad	
	<a href="#">MCGL25-10-952</a>	\$55.00	TRD-GK (10 mm) TRDA-20/25 (0.375 in)	10 mm	0.375 in	25 [0.98]	30.2 [1.19]	9 [0.35]	4 [0.16]	M4 set screw	3.5°	0.3 [0.01]	0.5 [0.02]	1.4 N-m	240 N-m/rad	
Aluminum (SAE)	<a href="#">ARM-075-635-635D</a>	\$52.00	TRDA-2E (0.25 in)	0.25 in	0.25 in	19.1 [0.75]	19.1 [0.75]	4.6 [0.18]	2.4 [0.09]	M3 set screw	5°	0.25 [0.01]	0.25 [0.01]	1.0 N-m	8.2 N-m/rad	Aluminum alloy
	<a href="#">ARM-100-9525-9525D</a>	\$50.00	TRDA-20/25 (0.375 in)	0.375 in	0.375 in	25.4 [1.00]	25.4 [1.00]	6.6 [0.26]	3.8 [0.15]	M5 set screw	5°	0.25 [0.01]	0.25 [0.01]	1.6 N-m	14.3 N-m/rad	

\* mm ÷ 25.4 = inches


# Encoder Accessories – Couplings

## Encoder Couplings – Dimensions


**GJ-xxD Fiberglass Couplings (metric) & GJx-xxxD Fiberglass Couplings (SAE)**




**STP-MTRA-SC-xxxx Polymer Couplings**




**ARM-xxxxxxD Aluminum Couplings (metric & SAE)**



**MCGLxx Aluminum Couplings & ML1xP-4-xxxD Aluminum Couplings**



**RU-075D, RU-100D, and JU-100D Aluminum Couplings**




Max Radial Load (N)	Max Axial Load (N)	Available Resolutions (PPR)	Brand
NA*	NA*	Programmable Up to 4096	<b>same sky</b>
NA*	NA*	400, 1000	<b>Sure-step</b>
20	10	100, 200, 360, 500, 600, 1000, 1024, 2000, 2500	<b>JTEKT</b>
20	20	100, 200, 360, 500, 1000, 1024, 200, 2048, 3600, 4096	<b>lika</b>
20	20	360, 1000, 1024, 2048	
30	30	1024	
100	100	Programmable from 1 to 16,384 (default 1024)	
50	50	250 (linear res: 0.36 deg/cts) 1250 (linear res: 0.072 deg/cts)	
50	30	100, 360, 500, 1000, 1024, 2500	<b>JTEKT</b>
50	30	100, 360, 500, 1000, 1024, 2500	
50	30	3, 4, 5, 10, 30, 40, 50, 60, 100, 120, 200, 240, 250, 300, 360, 400, 480, 500, 600, 750, 1000, 1024, 1200, 2000, 2500	
100	50	30, 100, 120, 200, 240, 250, 300, 360, 400, 500, 600, 1000, 1200, 2000, 2500, 3600, 5000	
50	30	32, 64, 128, 180, 256, 360, 512, 720, 1024 (gray code)	

\*Dular/Kit encoders are direct mount, there are no load ratings

## Mounting Brackets

Simplify your installation with a ready-to-use right-angle mounting bracket for light, medium and heavy-duty encoders.




## Flanges

Flanges are available to ease encoder mounting to round or square faces along with miscellaneous mounting options.




## Learn more about encoders



Click above or go to <http://go2adc.com/encoder> to view

## Need a Measuring Wheel Encoder?



AR01 Series (Priced at \$299.00)

Medium-duty measuring wheels ride directly on the product (above or below) or a conveyor to measure or provide speed control feedback. These can also be used for cut-to-length and positioning applications.

- Metric and US/imperial wheel sizes
  - Standard 4" wheel (12.5" circumference)
  - Optional 80mm wheel (250mm circumference)
- Spring loaded arm with up to 30mm deflection
- IP65 environmental rating