

# Contrinex Extended Slim Safety Light Curtains (30mm Beam Resolution)



## Features

- No blind zone
- Beam coding, EDM, start and restart interlock configurable functions
- Protective height: 170 to 1610 mm [6.69 to 63.39 in]
- Operating range: 0.25 to 5 m [0.82 to 16.4 ft]
- Type 4 according to IEC 61496-1/2
- SIL 3 according to IEC 61508
- Category 4, PL e according to EN/ISO 13849-1
- Permanent autocontrol and optical sync
- Wireless configuration through Bluetooth®




**Contrinex 30mm [1.18 in] Resolution Extended Slim Safety Light Curtains Selection Chart (Sender/Receiver Pair)**


| Part Number                         | Price      | Description          | Protective Height (Hs) mm [in] | Total Height Ht mm [in] | Number of Beams | Current Consumption (mA max) | Response Time (ms) | MTTFd (years) | DCavg (%) | Weight g [lb] |
|-------------------------------------|------------|----------------------|--------------------------------|-------------------------|-----------------|------------------------------|--------------------|---------------|-----------|---------------|
| <a href="#">YBES-30K4-0170-P012</a> | \$540.00   | Sender/Receiver Pair | 170 [6.69]                     | 170 [6.69]              | 8               | 30 (S), 35 (R)               | 7.8                | 3049          | 96.80     | 300 [0.66]    |
| <a href="#">YBES-30K4-0330-P012</a> | \$626.00   | Sender/Receiver Pair | 330 [12.99]                    | 330 [12.99]             | 16              | 30 (S), 35 (R)               | 9.6                | 2780          | 96.99     | 520 [1.14]    |
| <a href="#">YBES-30K4-0490-P012</a> | \$751.00   | Sender/Receiver Pair | 490 [19.29]                    | 490 [19.29]             | 24              | 30 (S), 35 (R)               | 11.4               | 2555          | 97.16     | 740 [1.63]    |
| <a href="#">YBES-30K4-0650-P012</a> | \$993.00   | Sender/Receiver Pair | 650 [25.59]                    | 650 [25.59]             | 32              | 30 (S), 35 (R)               | 13.2               | 2364          | 97.29     | 980 [2.16]    |
| <a href="#">YBES-30K4-0810-P012</a> | \$1,088.00 | Sender/Receiver Pair | 810 [31.89]                    | 810 [31.89]             | 40              | 30 (S), 35 (R)               | 15                 | 2199          | 97.41     | 1200 [2.65]   |
| <a href="#">YBES-30K4-0970-P012</a> | \$1,195.00 | Sender/Receiver Pair | 970 [38.19]                    | 970 [38.19]             | 48              | 30 (S), 35 (R)               | 16.8               | 2055          | 97.52     | 1420 [3.13]   |
| <a href="#">YBES-30K4-1130-P012</a> | \$1,301.00 | Sender/Receiver Pair | 1130 [44.49]                   | 1130 [44.49]            | 56              | 30 (S), 35 (R)               | 18.6               | 1930          | 97.61     | 1640 [3.62]   |
| <a href="#">YBES-30K4-1290-P012</a> | \$1,340.00 | Sender/Receiver Pair | 1290 [50.79]                   | 1290 [50.79]            | 64              | 30 (S), 35 (R)               | 20.4               | 1818          | 97.69     | 1860 [4.10]   |
| <a href="#">YBES-30K4-1450-P012</a> | \$1,475.00 | Sender/Receiver Pair | 1450 [57.09]                   | 1450 [57.09]            | 72              | 30 (S), 35 (R)               | 22.2               | 1719          | 97.76     | 2080 [4.59]   |
| <a href="#">YBES-30K4-1610-P012</a> | \$1,629.00 | Sender/Receiver Pair | 1610 [63.39]                   | 1610 [63.39]            | 80              | 30 (S), 35 (R)               | 24                 | 1630          | 97.82     | 2300 [5.07]   |

## Dimensions


mm [in]



| Assignment        | Function                               | Pins/Wires On Sender |       | Pins/Wires On Receiver |           |           |
|-------------------|----------------------------------------|----------------------|-------|------------------------|-----------|-----------|
|                   |                                        | M12                  | Cable | M12                    | 292 Cable | 295 Cable |
| Supply Voltage    | 24VDC                                  | 1                    | Brown | 2                      | Brown     | White     |
| Supply Voltage    | 0V                                     | 3                    | Blue  | 7                      | Blue      | Violet    |
| Test Mode         | 24V: Test Inactive; 0V: Test Active    | 4                    | Black | —                      | —         | —         |
| Output            | OSSD1 (Output Single Switching Device) | —                    | —     | 5                      | Gray      | Gray      |
| Output            | OSSD2 (Output Single Switching Device) | —                    | —     | 6                      | Pink      | Pink      |
| Earth Ground      | Shield (Ground)                        | FE                   | Gray  | FE                     | Red       | Orange    |
| EDM               | EDM Input                              | —                    | —     | 4                      | Yellow    | Black     |
| Restart Interlock | Input For Restart Button               | —                    | —     | 1                      | White     | Brown     |
| Not Used          | —                                      | 2                    | White | 3                      | Green     | Blue      |



M12 pigtail, 0.3 m, 5 pins



M12 pigtail, 0.3 m, 8 pins


Note: Cable color represents standard industrial pinout. Confirm the specific color and pinout during installation.

# Contrinex Extended Slim Safety Light Curtains (30mm Beam Resolution)

| Contrinex Extended Slim Safety Light Curtains YBES-30x4-xxxx-P012 Specifications                                                                               |                   |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| Resolution                                                                                                                                                     |                   |
| 30mm [1.18 in]                                                                                                                                                 |                   |
| Beam Axis Interval                                                                                                                                             |                   |
| 20mm [0.79 in]                                                                                                                                                 |                   |
| Effective Aperture Angle                                                                                                                                       |                   |
| < ± 2.5° (when operating distance ≥ 3 m [9.84 ft])                                                                                                             |                   |
| Operating Range                                                                                                                                                |                   |
| 0.25-5 m [0.82-16.4 ft]                                                                                                                                        |                   |
| Supply Voltage                                                                                                                                                 |                   |
| 24VDC ± 20%                                                                                                                                                    |                   |
| Polarity                                                                                                                                                       |                   |
| 2 PNP outputs                                                                                                                                                  |                   |
| Output Protection                                                                                                                                              |                   |
| Short-circuit, overload protected                                                                                                                              |                   |
| Output Monitoring                                                                                                                                              |                   |
| Cross-circuit monitored                                                                                                                                        |                   |
| Output Current                                                                                                                                                 |                   |
| Maximum 400mA per output (at 55°C [131°F])                                                                                                                     |                   |
| Output Voltage ON Minimum                                                                                                                                      |                   |
| -2V @ 400mA of the operating voltage                                                                                                                           |                   |
| Output Voltage OFF Maximum                                                                                                                                     |                   |
| 1.0 V                                                                                                                                                          |                   |
| Output Monitoring Frequency                                                                                                                                    |                   |
| 5Hz                                                                                                                                                            |                   |
| Leakage Current In OFF State                                                                                                                                   |                   |
| < 2mA                                                                                                                                                          |                   |
| Maximum Load Inductance                                                                                                                                        |                   |
| 100mH                                                                                                                                                          |                   |
| Sender Wavelength                                                                                                                                              |                   |
| IR 850nm                                                                                                                                                       |                   |
| Safety Level                                                                                                                                                   |                   |
| Cat. 4, PLe (EN/ISO 13849-1), Type 4 (IEC 61496-1/-2), SIL 3 (IEC 61508-1/-2/-3), SILCL3 (IEC 62061:A2)                                                        |                   |
| Electrical Protection Class                                                                                                                                    |                   |
| III (IEC 61140)                                                                                                                                                |                   |
| Startup Delay                                                                                                                                                  |                   |
| < 3s                                                                                                                                                           |                   |
| Vibration Resistance                                                                                                                                           |                   |
| 10 to 55 Hz, 0.35 mm amplitude, 1 octave/min, 20 sweeps for each axis                                                                                          |                   |
| Shock Resistance                                                                                                                                               |                   |
| 10g during 16ms, 1000 times for each axis                                                                                                                      |                   |
| Light Immunity                                                                                                                                                 |                   |
| Incandescent lamp: 3000 lx max. (light intensity on receiver surface); xenon flash tube: flash duration 1.2 ms max. with a frequency of 2Hz max. (IEC 61496-2) |                   |
| Ambient Temperature Range                                                                                                                                      |                   |
| 0 to +55°C (32 to 131°F)                                                                                                                                       |                   |
| Storage Temperature Range                                                                                                                                      |                   |
| -25 to +70°C (-13 to +158°F)                                                                                                                                   |                   |
| Air Humidity                                                                                                                                                   |                   |
| 15-95% (non-condensing)                                                                                                                                        |                   |
| Enclosure Rating                                                                                                                                               |                   |
| IP65 (EN 60529/A1)                                                                                                                                             |                   |
| Housing Material                                                                                                                                               |                   |
| Aluminum profile, PC front screen, upper and lower cover PA + 30% fiberglass                                                                                   |                   |
| Cable Runs                                                                                                                                                     |                   |
| 100m [328 ft]max. (at 10nF capacitive load)                                                                                                                    |                   |
| Reference Standards                                                                                                                                            | Safety            |
|                                                                                                                                                                | Environment       |
|                                                                                                                                                                | EMC               |
|                                                                                                                                                                | Radio Disturbance |
|                                                                                                                                                                | Bluetooth®        |
| EDM (External Device Monitoring)                                                                                                                               |                   |
| Start and Restart Interlock                                                                                                                                    |                   |
| Beam Coding                                                                                                                                                    |                   |
| Configuration                                                                                                                                                  |                   |
| Connection                                                                                                                                                     |                   |

# Contrinex Safety Light Curtains YBxS Accessories

| Contrinex Safety Light Curtains YBxS Accessories |         |                                           |                                  |                      |                            |
|--------------------------------------------------|---------|-------------------------------------------|----------------------------------|----------------------|----------------------------|
| Part Number                                      | Price   | Description                               | Material                         | Mounting             | Use With                   |
| <a href="#"><u>YXW-0005-000</u></a>              | \$11.00 | Contrinex mounting bracket. Package of 2. | Glass fiber reinforced polyamide | Top and bottom mount | YBxS series light curtains |
| <a href="#"><u>YXW-0006-000</u></a>              | \$23.00 | Contrinex mounting bracket. Package of 2. | Stainless steel                  | Side mount           | YBxS series light curtains |
| <a href="#"><u>YXW-0007-000</u></a>              | \$21.00 | Contrinex mounting bracket. Package of 2. | Stainless steel                  | Side or end mount    | YBxS series light curtains |

**YXW-0005-000****YXW-0006-000****YXW-0007-000**

**Warning:** Safety products sold by AutomationDirect are Safety components only.

The purchaser/installer is solely responsible for the application of these components and ensuring all necessary steps have been taken to assure each application and use meets all performance and applicable safety requirements and/or local, national and/or international safety codes as required by the application. AutomationDirect cannot certify that our products used solely or in conjunction with other AutomationDirect or other vendors' products will assure safety for any application.

Any person using or applying any products sold by AutomationDirect is responsible for learning the safety requirements for their individual application and applying them, and therefore assumes all risks, and accepts full and complete responsibility for the selection and suitability of the product for their respective application. AutomationDirect does not provide design or consulting services, and cannot advise whether any specific application or use of our products would ensure compliance with the safety requirements for any application.