

# Rack Mount Fan Trays



Fan Tray p/n [019310-00](#)

## Applications

Compact high performance fan tray for forced circulation of air in switch and server enclosures and for concerted cooling of 19in. rack mounted component groups. Natural convection is improved and the formation of localized hot pockets is avoided.

## Features

- High air output
- Long service life
- Ball bearing fans
- Ready for connection. Plug included, cable required.
- Optical function indicator
- 115VAC Operating Voltage
- UL Recognized File: E234324



General Specifications	
<b>Axial fans, ball bearing</b>	Service life 50,000 hr at 25°C (77°F), 65 % RH
<b>Material</b>	Front panel: aluminum, bright anodized; casing: steel sheet, electro-galvanized
<b>Optical indicator</b>	Integrated in front panel
<b>Connection</b>	Appliance power inlet on rear of casing, plug included
<b>Fitting position</b>	Vertical airflow (air outlet up)
<b>Operating/Storage temperature</b>	-10 to 60°C (14 to 140°F) / -40 to 70°C (-40 to 158°F)
<b>Operating/Storage humidity</b>	Max. 90 % RH (non-condensing)
<b>Protection type</b>	IP20

Rack Mount Fan Trays			
Part Number	Price	Airflow (CFM)	Drawing Links
<a href="#">019310-00</a>	\$211.00	339	<a href="#">PDF</a>
<a href="#">019510-00</a>	\$653.00	1016	<a href="#">PDF</a>