



Switch-Tek™ LU10 Ultrasonic Level Switches

Overview

CSA approved for hazardous environments, the intrinsically safe ultrasonic point level switch provides reliable liquid level detection of chemical, solvent, hydrocarbon and petroleum based liquids with a 1A relay output. The submersible polypropylene (PP) liquid level sensor is universally mounted through the tank wall or inside the tank as a high level alarm or low level alarm.

Features

- CSA approved intrinsically safe for use in hazardous environments
- Submersible polypropylene (PP) sensor and cable
- 60VA relay selectable NO or NC via power supply wiring polarity
- Compatible with Switch-Pak installation fittings
- Able to mount through the side wall or top wall of tank
- 2-year warranty



Part No. LU10-1305Part No. LU10-1405

Switch-Tek™ LU10 Technical Specifications		
Model	LU10-1305	LU10-1405
Price	\$330.00	\$350.00
Weight (lb)	0.7	0.7
Insertion Length	0.7 in [17.8 mm]	2.1 in [53.3 mm]
Orientation	Universal	
Accuracy	±1mm [0.04 in] in water	
Repeatability	±0.5 mm [0.02 in] in water	
Supply Voltage	12-36 VDC	
Consumption	25mA maximum	
Contact Type	(1) SPST relay	
Contact Rating	General purpose: 60VA @ 1A (125VAC max) Intrinsically safe: 32VDC @ 0.5 A	
Contact Output	Selectable NO / NC	
Process Temp.	-40°F to 176°F [-40°C to 80°C]	
Pressure	150psi [10bar] @ 25°C, derated @ 1.667 psi [0.113 bar] per °C above 25°C	
Sensor Rating	NEMA 6 (IP68)	
Sensor Material	PP (polypropylene)	
Cable Jacket Material	PP (polypropylene)	
Cable Type	4-conductor, #22AWG, shielded	
Cable Length	10ft (3m)	
Process Mount	3/4" NPT	
Classification	Intrinsically safe (Haz-Loc)	
Agency Approvals*	CSA: Class 1, Groups A, B, C, & D; Class II Groups E, F & G; Class III EEx: Class 1, Division 1, Groups A, B, C, & D; EEx ib IIC T6	
Intrinsically Safe (I.S.) Parameters	CSA: Vmax = 32V, Imax = 300mA, Pmax = 1.3 W; Ci = 0μF, Li = 0μH EEx: Ui = 32V; li = 300mA; Pi = 1.3 W; Ci = 0μF; Li = 0μH	
Certificates*	CSA: LR 79326; EEx: LCIE 01.E6048 X	
Compliance*	CE (EN61326, EN61010-1)	



Dimensions

inches [mm]

Part No. LU10-1305Part No. LU10-1405

See our website www.AutomationDirect.com for complete Engineering drawings.

Compatible Products

Switch-Pro™
Remote Level Controllers



LCXX

Switch-Pro™
Junction Box and Strobe



LC06-1001

LC06-1001
with LC09-1004
and LM90-1001

Switch-Pak™
Installation Fittings



LM45-7001-0000

LM45-1001-12

See the Switch-Pro® LCXX and Accessories pages at the end of the section for further details and pricing.

* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com



Switch-Tek™ LU10 Ultrasonic Level Switches

Intrinsically Safe (Haz-Loc) Wiring Information

Models LU10:

The LU10 level switch has been approved for use in Class I, Groups A, B, C & D; UNDER CERTIFICATE NUMBER LR 79326-

4. The Entity parameter for the LU10 are:

$$V_{\max} = 32 \text{ VDC}$$


$$I_{\max} = 0.5 \text{ A}$$

$$C_i = 0 \mu\text{F}$$

$$L_i = 0 \text{ mH}$$

Intrinsically Safe Control Drawing:

NON-HAZARDOUS LOCATION




Red Wire

Black Wire

Shield

HAZARDOUS LOCATION

Class I, Groups A, B, C & D
Class II, Groups E, F & G
Class III



Notes:

1. CSA certified associated equipment with entity parameters.
2. $V_{\max} \geq V_{oc}$, $I_{\max} \geq I_{sc}$, $C_i + C_{\text{cable}} \leq C_a$, $L_i + L_{\text{cable}} \leq L_a$.
3. Installation should be in accordance with CEC Part I, or NFPA 70.
4. Associated equipment must be installed per manufacturers instructions

Sensor Drawing: LSD1
Rev. B 10-01-02



Switch-Tek™ LU10 Ultrasonic Level Switches

Intrinsically Safe (Haz-Loc) Wiring Information

Models LU10:

The LU10 level switch has been approved for use in Class I, Division 1, Groups A, B, C & D; EEx ib IIC T6; UNDER CERTIFICATE NUMBER LCIE 01.E6048X.

The Entity parameter for the LU10 are:

North America	Europe
$V_{max} = 32 \text{ VDC}$	$U_i = 32 \text{ VDC}$
$I_{max} = 0.5 \text{ A}$	$I_i = 0.5 \text{ A}$
$P_{max} = 1.3 \text{ W}$	$P_i = 1.3 \text{ W}$
$C_i = 0 \mu\text{F}$	$C_i = 0 \mu\text{F}$
$L_i = 0 \mu\text{H}$	$L_i = 0 \mu\text{H}$

Intrinsically Safe Control Drawing:

NON-HAZARDOUS LOCATION

Entity Parameters: North America $V_{oc} \leq V_{max}$ $I_{sc} \leq I_{max}$ $C_a \geq C_i + C_{cable}$ $L_a \geq L_i + L_{cable}$ Europe $U_o \leq U_i$ $I_o \leq I_i$ $C_o \geq C_i + C_{cable}$ $L_o \geq L_i + L_{cable}$	
--	--

Red Wire
Black Wire
Shield

HAZARDOUS LOCATION

Class I, Division1,
Groups A,B,C,D
EEx ib IIC T6

Sensor Models LU10-__5 Entity Parameters: North America $V_{max} = 32\text{V}$ $I_{max} = 300 \text{ mA}$ $P_{max} = 1.3 \text{ W}$ $C_i = 0 \mu\text{F}$ $L_i = 0 \mu\text{H}$ Europe $U_i = 32\text{V}$ $I_i = 300 \text{ mA}$ $P_i = 1.3 \text{ W}$ $C_i = 0 \mu\text{F}$ $L_i = 0 \mu\text{H}$	
--	--

Sensor Drawing: U10900
Sheet 1 of 2
Rev. B 4-02-01

NON-HAZARDOUS LOCATION

Entity Parameters for 12-32 Lines: $V_{oc} \leq V_{max}$, $U_o \leq U_i$ $I_{sc} \leq I_{max}$, $I_o \leq I_i$ $C_a \geq C_i + C_{cable}$, $C_o \geq C_i + C_{cable}$ $L_a \geq L_i + L_{cable}$, $L_o \geq L_i + L_{cable}$ Entity Parameters for Switch Outputs: $V_{oc} \leq V_{max}$, $U_o \leq U_i$ $I_{sc} \leq I_{max}$, $I_o \leq I_i$ $C_a \geq C_i + C_{cable}$, $C_o \geq C_i + C_{cable}$ $L_a \geq L_i + L_{cable}$, $L_o \geq L_i + L_{cable}$	
---	--

Red Wire
Black Wire
Shield
Green Wire
White Wire

HAZARDOUS LOCATION

Class I, Division1,
Groups A,B,C,D
EEx ib IIC T6

Sensor Models LU10-__5 Entity Parameters for 12-32 Lines: $V_{max} = 32\text{V}$, $U_i = 32\text{V}$ $I_{max} = 300 \text{ mA}$, $I_i = 300 \text{ mA}$ $P_{max} = 1.3 \text{ W}$, $P_i = 1.3 \text{ W}$ $C_i = 0 \mu\text{F}$, $C_i = 0 \mu\text{F}$ $L_i = 0 \mu\text{H}$, $L_i = 0 \mu\text{H}$ Entity Parameters for Switch Outputs: $V_{max} = 32\text{V}$, $U_i = 32\text{V}$ $I_{max} = 500 \text{ mA}$, $I_i = 500 \text{ mA}$ $P_{max} = 1.3 \text{ W}$, $P_i = 1.3 \text{ W}$ $C_i = 0 \mu\text{F}$, $C_i = 0 \mu\text{F}$ $L_i = 0 \mu\text{H}$, $L_i = 0 \mu\text{H}$	
---	--

Notes: PARAMETERS DEPEND ON OUTPUT TYPE

1. Installation should be in accordance with CEC Part 1, or NFPA 70.
2. Associated Equipment shall be CSA certified with entity parameters connected in accordance with manufacturers instructions.

Sensor Drawing: U10900
Sheet 2 of 2
Rev. B 4-02-01



Switch-Pro™ Remote Level Controllers

Overview

CSA approved, the Switch-Pro general purpose level controllers are offered in three configurations for alarms, pump and valve control. The LC40 accepts one level sensor input and provides one 10A relay for high level or low level alarm. The LC41 accepts two level sensor inputs and provides one latching 10A relay for automatic fill or empty control. The LC42 accepts three level sensor inputs with one latching 10A relay output for automatic fill or empty control, and a second non-latching 10A relay for high level or low level alarm.

Part No. [LC40-1001](#)Part No. [LC41-1001](#)Part No. [LC42-1001](#)

Features

- Fail-safe relay control of pumps or valves with 0-60 second delay
- Easy setup with LED indicators for sensor, power and relay status
- 35mm DIN rail mount or panel mount polypropylene (PP) enclosure with removable terminal strips
- Invert switch changes relay state from NO to NC without rewiring
- Mounts easily in control panel
- Connects to any Flowline level switch
- Interfaces directly with any horn, buzzer, valve, etc...
- Use LC41, LC42 version for automatic fill/empty operations
- 2-year warranty



Switch-Pro LC Series Technical Specifications

Model	LC40-1001	LC41-1001	LC42-1001
Price	\$275.00	\$325.00	\$385.00
Weight (lb)	1.9	1.9	1.9
Supply Voltage	120VAC @ 50-60 Hz (can be field configured for 240VAC)		
Consumption	5W maximum		
Sensor Inputs	(1) two wire level switch	(2) two wire level switches	(3) two wire level switches
Sensor Supply	13.5 VDC @ 27mA		
LED Indication	Sensor (green), power (green) & relay (red)		
Contact Type	(1) SPDT relay (non-latching)	(1) SPDT relay (latching)	(2) SPDT relays, (one non-latching, one latching)
Contact Rating	250VAC @ 10A		
Contact Output	Selectable NO / NC		
Contact Latch	N/A	Selectable ON / OFF	Selectable ON / OFF
Contact Delay	0-60 seconds		
Ambient Temperature	-40°F to 158°F [-40°C to 70°C]		
Enclosure Mounting	35mm DIN rail or thru-hole panel mount		
Enclosure Material	PP (polypropylene), UL94VO		
Classification	General purpose		
Compliance*	CSA LR 79326		

* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com



Switch-Pro™ Remote Level Controllers

Wiring

LC40 series: 1 sensor input, 1 relay output.

Typical Application:

High level or low level alarm



LC41 series: 2 sensor inputs, 1 relay output. The relay included is a latching relay.

Typical Application:

Automatic fill or empty




LC42 series: 3 sensor input, 2 relay outputs. One relay is latching and the other is a single input relay.

Typical Application:


Automatic fill or empty with high level or low level alarm




Low Level Alarm Output Wiring Example (One level sensor input required):




Automatic Fill Output Wiring Example (Two level sensor inputs required):



High Level Alarm Output Wiring Example (One level sensor input required):




Automatic Empty Output Wiring Example (Two level sensor inputs required):



Symbol Key:



Level Sensor Input Wiring Example:





LV10 series can be wired using the White and Black wires for NO operations or the Red and Black wires for NC operations.

Dimensions

inches [mm]

MODEL LC42



See our website www.AutomationDirect.com for complete Engineering drawings.

Compatible Products

ProSense Float Level Switches







Switch-Tek™ Level Switch Sensors





Level Switch Accessories

Level Sensor Accessories					
Part No.	Item Photo	Description	Quantity	Weight (lb)	Price
<u>LM45-1001-12</u>		Flowline Switch-Pak level sensor extension installation fitting, polypropylene (PP) construction, 12 inch insertion length, 2 inch NPT male process connection, 3/4 inch NPT female sensor threads, 3/4 inch NPT male electrical junction box threads	1	1.1	\$72.00
<u>LM45-7001-0000</u>		Flowline Switch-Pak level sensor extension installation fitting kit, polyvinyl chloride (PVC) construction, includes (1) fitting with 2 inch NPT male process connection, 3/4 inch NPT male electrical junction box threads and 3/4 inch PVC pipe socket; (1) fitting with 3/4 inch NPT female sensor threads and 3/4 inch female PVC pipe socket. Purchase 3/4 inch schedule 40 PVC pipe separately, cut to desired length and solvent weld to fittings in this kit.	1	0.7	\$52.00
<u>LC06-1001</u>		Flowline Switch-Pro compact electrical junction box, polypropylene (PP) construction, screw cover with O-ring gasket, NEMA 4X rated, 3/4 inch NPT female mounting threads with 300 degree swivel base, 1/2 inch NPT female conduit entrance, removable 6-pole terminal strip	1	0.7	\$85.00
<u>LM90-1001</u>		Cable gland, 1/2 inch NPT male thread, Buna N sealing gland accommodates a cable diameter range of 0.180 to 0.400 inches (4.6 to 10.2 mm), nylon housing, IP68 protection level	1	0.4	\$10.00

Accessory Field Assembly Example



Order the following parts for field assembly: (1)

[LC06-1001](#) - Junction box

(1) [LM90-1001](#) - Cable gland

(1) LU10 Series ultrasonic level switch





Level Switch Accessory Drawings



Dimensions

inches [mm]




LM45-1001-12



LM45-7001-0000



LC06-1001



See our website www.AutomationDirect.com for complete Engineering drawings.




Level Switch Accessory Drawings

Dimensions

inches [mm]

LM90-1001



See our website www.AutomationDirect.com for complete Engineering drawings.