



Motor Controller Communication

Drive / Motor Controller (GS/DuraPulse/SureServo/SureStep/Stellar) ZIPLink Selector										
Drive / Motor Controller		Communications			ZIPLink Cable					
Controller	Comm Port Type	Network/Protocol	Connects to	Comm Port Type	Cable (2 meter length)	Cable Connectors	Other Hardware Required			
GS1	RJ12	RS-485 Modbus RTU	BRX MPUs	RS-485, 3-Pin	ZL-RJ12-CBL-2P	RJ12 to pigtail	N/A			
			P2-550							
			P3-530							
			P3-550							
			P3-550E	RS-485, 4-Pin						
			P2-SCM							
			P3-SCM							
			DL06 PLCs	Port 2 (HD15)				GS-485HD15-CBL-2	RJ12 to HD15	
			D2-262 CPU	RJ12				GS-EDRV-CBL-2	RJ12 to RJ12	
			GS-EDRV100					GS-485RJ12-CBL-2		
ZL-CDM-RJ12Xxx *	RJ12	GS-485RJ12-CBL-2	RJ12 to RJ12							
FA-ISOCON	5-pin Connector	GS-ISOCON-CBL-2	RJ12 to 5-pin plug							
GS2	RJ12	RS-232 Modbus RTU	BRX MPUs	RS-232/485, 3-Pin	ZL-RJ12-CBL-2P	RJ12 to pigtail	N/A			
			P2-550	RS-485, 4-Pin						
			P3-530							
			P3-550							
			P3-550E							
			P2-SCM	Ports 1, 2 & 3						
			P3-SCM	Ports 1 to 4						
			CLICK PLCs	Port 2 (RJ12)				GS-RJ12-CBL-2	RJ12 to RJ12	FA-15HD
			DL05 PLCs							
			DL06 PLCs	Port 2 (HD15)						
		D2-262 CPU								
		D4-454 CPU	Port 3 (25-pin)	FA-CABKIT						
		RS-485 Modbus RTU	BRX MPUs	RS-232/485, 3-Pin	ZL-RJ12-CBL-2P	RJ12 to pigtail	N/A			
			P2-550	RS-485, 3-Pin						
			P3-530							
			P3-550							
			P3-550E							
			P2-SCM							
			P3-SCM							
			DL06 PLCs	Port 2 (HD15)				GS-485HD15-CBL-2	RJ12 to HD15	
D2-262 CPU	RJ12		GS-EDRV-CBL-2	RJ12 to RJ12						
GS-EDRV100			GS-485RJ12-CBL-2							
ZL-CDM-RJ12Xxx *	RJ12	GS-485RJ12-CBL-2	RJ12 to RJ12							
FA-ISOCON	5-pin Connector	GS-ISOCON-CBL-2	RJ12 to 5-pin plug							
Stellar (Soft Starter) SR44 Series	RJ45 **	RS-485 Modbus RTU	DL06 PLCs	Port 2 (HD15)	SR44-485HD15-CBL-2	RJ45 to HD15	SR44-RS485			
			D2-262 CPU							
			ZL-CDM-RJ12Xxx *	RJ12				SR44-485RJ45-CBL-2	RJ45 to RJ12	

* When using the ZL-CDM-RJ12Xxx ZIPLink Communication Distribution Module, replace the lowercase xx with the number of RJ12 ports, i.e. 4 for four ports or 10 for ten ports. (ex: ZL-CDM-RJ12X4 or ZL-CDM-RJ12X10)

** The [SR44-RS485](#) Communications Adapter must be installed for RS-485 communications with the Stellar soft starters.



Motor Controller Communication

Drive / Motor Controller (GS/DuraPulse/SureServo/SureStep/Stellar) ZIPLink Selector							
Drive / Motor Controller		Communications			ZIPLink Cable		
Controller	Comm Port Type	Network/Protocol	Connects to	Comm Port Type	Cable (2 meter length)	Cable Connectors	Other Hardware Required
DuraPulse (GS3)	RJ12	RS-485 Modbus RTU	BRX MPUs	RS-485, 3-Pin	ZL-RJ12-CBL-2P	RJ12 to pigtail	N/A
			P2-550	RS-485, 3-Pin			
			P3-530				
			P3-550				
			P3-550E	RS-485, 4-Pin			
			P2-SCM				
			P3-SCM	Port 2 (HD15)	GS-485HD15-CBL-2	RJ12 to HD15	
			DL06 PLCs		RJ12	GS-EDRV-CBL-2	
			D2-262 CPU				
			GS-EDRV100	RJ12	GS-485RJ12-CBL-2	RJ12 to 5-pin plug	
ZL-CDM-RJ12Xxx *	RJ12	GS-ISOCON-CBL-2	RJ12 to 5-pin plug				
SureServo	IEEE1394 (CN3)	RS-232 Modbus RTU	CLICK PLCs	Port 2 (RJ12)	SVC-232RJ12-CBL-2	6-pin IEEE to RJ12	N/A
			DL05 PLCs	Port 2 (HD15)			FA-15HD
			DL06 PLCs				
			D2-262 CPU		RS232		
			P2-550	SVC-232RJ12-CBL-2		6-pin IEEE to RJ12	
			P3-530				
		P3-550					
		P3-550E					
		P2-SCM	Ports 1, 2 & 3				
		P3-SCM					
RS-485 Modbus RTU	DL06 PLCs	Port 2 (HD15)	SVC-485HD15-CBL-2	6-pin IEEE to HD15			
	D2-262 CPU	RJ12	SVC-485RJ12-CBL-2	6-pin IEEE to RJ12			
	ZL-CDM-RJ12Xxx *	RJ45	SVC-485CFG-CBL-2	6-pin IEEE to RJ45			
	USB-485M						
SureStep	RJ12	RS-232 ASCII	BRX MPUs	3-Pin	ZL-RJ12-CBL-2P	RJ12 to pigtail	N/A
			P2-550	RS-485, 3-Pin			
			P3-530				
			P3-550				
			P3-550E	RS-485, 4-Pin			
			P2-SCM				
			P3-SCM	Port 2 (HD15)	STP-232HD15-CBL-2	HD15-pin to RJ12	
			DL06 PLCs		RJ12	STP-232RJ12-CBL-2	
			D2-262 CPU (Port2)				
			DL05 PLCs				
CLICK PLCs							

* When using the ZL-CDM-RJ12Xxx ZIPLink Communication Distribution Module, replace the lowercase xx with the number of RJ12 ports, i.e. 4 for four ports or 10 for ten ports. (ex: ZL-CDM-RJ12X4or ZL-CDM-RJ12X10)
 ** The SR44-RS485 Communications Adapter must be installed for RS-485 communications with the Stellar soft starters.

ZIPLINK™ Wiring Solutions

AUTOMATIONDIRECT®

Wiring Solutions using the ZIPLink Wiring System

ZIPLinks eliminate the normally tedious process of wiring between devices by utilizing pre-wired cables and DIN rail mount connector modules. It's as simple as plugging in a cable connector at either end or terminating wires at only one end. Pre-wired cables keep installation clean and efficient, using half the space at a fraction of the cost of standard terminal blocks. There are several wiring solutions available when using the **ZIPLink** System ranging from PLC I/O-to-**ZIPLink** Connector

Modules that are ready for field termination, options for connecting to third party devices, GS, DuraPulse and SureServo Drives, as well as special relay, transorb and communications modules. Pre-printed I/O-specific adhesive label strips for quick marking of **ZIPLink** modules are provided with **ZIPLink** cables. See the following solutions to help determine the best **ZIPLink** system for your application.

Solution 1: Do-more, DirectLOGIC, CLICK and Productivity Series I/O Modules to ZIPLink Connector Modules

When looking for quick and easy I/O-to-field termination, a **ZIPLink** connector module used in conjunction with a prewired **ZIPLink** cable, consisting of an I/O terminal block at one end and a multi-pin connector at the other end, is the best solution.



Using the PLC I/O Modules to **ZIPLink** Connector Modules selector tables located in this section,

1. Locate your I/O module/PLC
2. Select a **ZIPLink** Module
3. Select a corresponding **ZIPLink** Cable.

Solution 2: Do-more, DirectLOGIC, CLICK and Productivity Series I/O Modules to 3rd Party Devices

When wanting to connect I/O to another device within proximity of the I/O modules, no extra terminal blocks are necessary when using the **ZIPLink** Pigtail Cables. **ZIPLink** Pigtail Cables are prewired to an I/O terminal block with color-coded pigtail with soldered-tip wires on the other end.



Using the I/O Modules to 3rd Party Devices selector tables located in this section,

1. Locate your PLC I/O module
2. Select a **ZIPLink** Pigtail Cable that is compatible with your 3rd party device.

Solution 3: GS Series and DuraPulse Drives Communication Cables

Need to communicate via Modbus RTU to a drive or a network of drives?

ZIPLink cables are available in a wide range of configurations for connecting to PLCs and SureServo, SureStep, Stellar Soft Starter and AC drives. Add a **ZIPLink** communications module to quickly and easily set up a multi-device network.

Using the Drives Communication selector tables located in this section,

1. Locate your Drive and type of communications
2. Select a **ZIPLink** cable and other associated hardware.



ZIP LINK™ Wiring Solutions

AUTOMATIONDIRECT

Solution 4: Serial Communications Cables

ZIPLink offers communications cables for use with DirectLOGIC, CLICK, and Productivity CPUs, that can also be used with other communications devices. Connections include a 6-pin RJ12 or 9-pin, 15-pin and 25-pin D-sub connectors which can be used in conjunction with the RJ12 or D-Sub feedthrough modules.

Using the Serial Communications Cables selector table located in this section,

1. Locate your connector type
2. Select a cable.



Solution 5: Specialty ZIPLink Modules

For additional application solutions, ZIPLink modules are available in a variety of configurations including stand-alone relays, 24VDC and 120VAC transorb modules, D-sub, RJ12 and RJ45 feedthrough modules, communication port adapter and distribution modules, and SureServo 50-pin I/O interface connection.

Using the ZIPLink Specialty Modules selector table located in this section,

1. Locate the type of application
2. Select a ZIPLink module.



Solution 6: ZIPLink Connector Modules to 3rd Party Devices

If you need a way to connect your device to terminal blocks without all that wiring time, then our pigtail cables with color coded soldered tip wires are a good solution. Used in conjunction with any compatible ZIPLink Connector Modules, a pigtail cable keeps wiring clean and easy and reduces troubleshooting time.

Using the Universal Connector Modules and Pigtail Cables table located in this section,

1. Select module type
2. Select the number of pins
3. Select cable.






Specialty Modules

ZIPLink Specialty Modules Selector			
ZIPLink			
Module	Type	Module Part No.	Cable Part No. (optional)
24VDC Stand-Alone Relay	Single-Socket Relay	ZL-RLS1-24	N/A
	Four Socket-Relay	ZL-RLS4-24	
120VAC Stand-Alone Relay	Single-Socket Relay	ZL-RLS1-120	
	Four-Socket Relay	ZL-RLS4-120	
250V AC/DC Max.	16-point, Fused Block	ZL-FUSE-16	
24VDC Transorb	8-Channel	ZL-TSD8-24	
120VAC Transorb	8-Channel	ZL-TSD8-24	
240V AC/DC Max.	40-Point Power/Common	ZL-RTB-COM	
D-Sub Feedthrough	9-pin Male & Female D-Subs to Terminal Blocks	ZL-RTB-DB09	ZL-DB9-CBL-2
	15-pin Male & Female D-Subs to Terminal Blocks	ZL-RTB-DB15	ZL-DB15-CBL-2
	25-pin Male & Female D-Subs to Terminal Blocks	ZL-RTB-DB25	ZL-DB25-CBL-2
RJ12 Feedthrough	6-pin RJ12 to Terminal Block	ZL-RTB-RJ12	ZL-RJ12-CBL-2
RJ45 Feedthrough	8-pin RJ45 to Terminal Block	ZL-RTB-RJ45	N/A
Comm Port Adapters	15-pin HD D-Sub to Terminal Block	ZL-CMA15	
	15-pin HD D-Sub to Terminal Block with LED Indicators	ZL-CMA15L	
Comm Distribution	4-Port RJ12 to Terminal Block	ZL-CDM-RJ12X4	
	10-Port RJ12 to Terminal Block	ZL-CDM-RJ12X10	
Feedthrough Module (SureServo I/O)	50-pin to Terminal Blocks	ZL-RTB50	ZL-SVC-50CBL *

* Select the cable length by replacing the * with: Blank = 0.5m, -1 = 1.0m, or -2 = 2.0m





Connector Modules to 3rd Party Devices

ZIPLink Connector Modules to 3rd Party Devices Selector			
ZIPLink			
Module	Type	Module Part No.	Pigtail Cable Part No. (optional)
Feedthrough Connector	24-pin to Terminal Blocks	ZL-RTB20 ZL-RTB20-1	ZL-CBL24-1P ZL-CBL24-2P
	40-pin to Terminal Blocks	ZL-RTB40 ZL-RTB40-1	ZL-CBL40-1P ZL-CBL40-2P
	50-pin to Terminal Blocks	ZL-RTB50	ZL-CBL50-1P ZL-CBL50-2P
Fuse	16-Fuse, 24-pin	ZL-RFU20	ZL-CBL24-1P ZL-CBL24-2P
	32-Fuse, 40-pin	ZL-RFU40	ZL-CBL40-1P ZL-CBL40-2P
24VDC Powered Relay	16-Relay, Sinking, 24-pin	ZL-RRL16-24-1 ZL-RRL16F-24-1 ZL-RRL16W-24-1	ZL-CBL24-1P ZL-CBL24-2P
	16-Relay, Sourcing, 24-pin	ZL-RRL16-24-2 ZL-RRL16F-24-2 ZL-RRL16W-24-2	ZL-CBL24-1P ZL-CBL24-2P
Sensor Input	16-Point with LEDs	ZL-LTB16-24-1	ZL-CBL24-1P ZL-CBL24-2P
	32-Point with LEDs	ZL-LTB32-24-1	ZL-CBL40-1P ZL-CBL40-2P
D-Sub Feedthrough	9-pin D-Sub to Terminal Block	ZL-RTB-DB09	ZL-DB9F-CBL-2P
			ZL-DB9F-CBL-5P

