


# Fuji Duo Series Manual Motor Starters Accessories

## Optional accessories


- All accessories can be used with BM3R (45 mm wide) and BM3V (55 mm wide) frames
- Accessories are easily mounted
- Internally-mountable auxiliary contact blocks and alarm contact blocks can be front mounted
- Side-mountable auxiliary contact blocks can be mounted on the left side
- Shunt trip and undervoltage trip devices are available in a wide operating coil voltage range and mount on the right side
- Standard and emergency external handles are available
- IP20 terminal cover helps prevent accidental contact with electrically charged parts
- Optional front mounted contact and alarm blocks eliminate horizontal space needed with the DIN rail



### Installation of optional contact blocks and trip devices



### Auxiliary contact blocks



Auxiliary Contact Blocks						
Part Number	Price	Description	Starter Type	Mounting	Contact Arrangement	Weight (g/lb)
<b>BZ0WIA</b>	\$8.75	These contact blocks do not discriminate between OFF, overload, phase-loss, or short circuit. The blocks are linked to the ON/OFF operation of the MMS, and also operate in the event of an overload, phase-loss, or short circuit. Up to two contact blocks can be mounted to the right/left front, and up to two contact blocks can be mounted to the left sides.	BM3RHB-xxx BM3VHB-xxx	Front	1NO	9/0.02
<b>BZ0WIB</b>	\$8.75				1NC	
<b>BZ0WUABL</b>	\$12.50			Left side	2NO	45/0.1
<b>BZ0WUABL</b>	\$12.50				1NO + 1NC	
<b>BZ0WUBBL</b>	\$12.50				2NC	

# Fuji Duo Series Manual Motor Starters Accessories




## Accessories (continued)

### Alarm contact blocks




Alarm Contact Blocks						
Part Number	Price	Description	Starter Type	Mounting	Contact Arrangement	Weight (g/lb)
<b>BZ0KIA</b>	\$8.75	This block operates when the MMS trips due to overload, phase-loss, or short-circuit. It is not linked to the ON/OFF operation of the MMS. Note: Operation can be checked with the test trip function.	BM3RHB-xxx BM3VHB-xxx	Front (Right side only)	1NO	9/0.02
<b>BZ0KIB</b>	\$8.75				1NC	

### Auxiliary and alarm contact blocks



Combination Auxiliary/Alarm Contact Blocks						
Part Number	Price	Description	Starter Type	Mounting	Contact Arrangement	Weight (g/lb)
<b>BZ0WKUAA</b>	\$15.50	<ul style="list-style-type: none"> <li>This contact block combines an auxiliary contact and an alarm contact that operates in the event of an overload, phase loss, or short-circuit. Alarm contact is not linked to the ON/OFF operation of the MMS.</li> <li>An alarm is displayed in the contact block's indicator when the alarm contact operates.</li> <li>Note: Operation can be checked with the test trip function.</li> </ul>	BM3RHB-xxx BM3VHB-xxx	Left	1NO (Aux.) + 1NO (Alarm)	45/0.1

### Short-circuit alarm contact blocks




Note 1: Required when using MMS in a UL Type E application.  
Note 2: Do not configure this with an auxiliary contact block; the contact will only close when a short circuit occurs.

Short-Circuit Alarm Contact Block						
Part Number	Price	Description	Starter Type	Mounting	Contact Arrangement	Weight (g/lb)
<b>BZ0TKUAB</b>	\$19.50	<ul style="list-style-type: none"> <li>The contacts operate only when the MMS has tripped due to a short-circuit (cannot be checked with trip test function).</li> <li>When these contacts operate, the blue reset button extends out, and a trip indication is displayed.</li> <li>The power to the MMS can be turned ON after pressing the reset button.</li> <li>Note: Be sure to press the reset button before mounting to the MMS.</li> </ul>	BM3RHB-xxx BM3VHB-xxx	Left	1NO + 1NC	45/0.1

Contact Status					
Contact Type		Device Condition			
		OFF	ON	Tripped	
				Overload or Phase-loss	Short Circuit
AUX CONTACT, <b>BZ0WIA, BZ0WIB, BZ0WUAA, BZ0WUBBL, BZ0WUABL</b>	NO	Open	Closed	Opens	
	NC	Closed	Open	Closes	
ALARM CONTACT <b>BZ0KIA, BZ0KIB</b>	NO	Open (no change)	Open (no change)	Closes	
	NC	Closed (no change)	Closed (no change)	Opens	
AUX & ALARM CONTACT <b>BZ0WKUAA</b>	NO (AUX)	Open	Closed	Opens	
	NO (ALM)	Open (no change)	Open (no change)	Closes	
SHORT-CIRCUIT CONTACT <b>BZ0TKUAB</b>	NO	Open (no change)	Open (no change)	Open (no change)	Closes
	NC	Closed (no change)	Closed (no change)	Closed (no change)	Opens


# Fuji Duo Series Manual Motor Starters Accessories

## Accessories (continued)



### Shunt trip devices

Shunt Trip Devices						
Part Number	Price	Description	Starter Type	Mounting	Contact Arrangement	Weight (g/lb)
<a href="#"><u>BZ0FAZU</u></a> <a href="#"><u>BZ0FDZU</u></a>	\$26.00	This device is used to remotely trip the MMS.	BM3RHB-xxx BM3VHB-xxx	Right	110-127V 50Hz/120V 60Hz	115/0.25
<a href="#"><u>BZ0FKZUD</u></a>	\$26.00	Notes: • This device cannot be used together with an undervoltage trip device. • When the MMS has been tripped with the shunt trip device, press the reset button before turning ON the power.			24-60VDC (time rating of coil is 5s)	



### Undervoltage trip devices

Undervoltage Trip Devices						
Part Number	Price	Description	Starter Type	Mounting	Contact Arrangement	Weight (g/lb)
<a href="#"><u>BZ0RDZU</u></a>	\$26.00	This device automatically trips the MMS when the control circuit voltage drops below the specified value.	BM3RHB-xxx BM3VHB-xxx	Right	110-127V 50Hz/120V 60Hz	115/0.25
<a href="#"><u>BZ0R4ZU</u></a>	\$26.00	Notes: This device cannot be used together with a shunt trip device. When the MMS has been tripped with the undervoltage trip device, press the reset button before turning ON the power.			415-440V 50Hz/460-480V 60Hz	



### Push-in lug

Push-in Lug				
Part Number	Price	Description	Starter type	Weight (g/lb)
<a href="#"><u>BZ0SET</u></a>	\$8.75	Push-in mounting lug. Required for screw mounting of MMS; qty: 10/pkg	BM3RHB-xxx	2.0/.004

Note: See page MRC-tMRC-73 for installation instructions



### Terminal Cover

Terminal Cover			
Part Number	Price	Description	Starter Type
<a href="#"><u>BZ0TCRE</u></a>	\$15.00	Line side terminal cover.	BM3RHB-xxx

Notes: BZ0TCRE required only when using BM3RHB-xxx MMS in a UL Type E application (along with short circuit alarm contact block [BZ0TKUAB](#)).  
If using BZ0TCRE terminal cover with BM3R series MMS, the busbar system and front mounted contacts cannot be used.

# Fuji Duo Series Manual Motor Starters Accessories

## Accessories (continued)

### External operating handles



**BZ0VBBL**

**BZ0VYRL**

External Operating Handles					
Part Number	Price	Description	Starter Type	Handle Type	Weight (g/lb)
<a href="#"><u>BZ0VBBL</u></a>	\$38.00	<ul style="list-style-type: none"> <li>Used to operate an MMS installed inside a panel, from the outside of the panel.</li> <li>Equipped with an interlock mechanism that prevents someone from mistakenly opening the panel door when the MMS is in the ON state.</li> <li>The shaft can be cut to match the distance between the MMS and the panel door.</li> <li>Door interlock function</li> <li>OFF lock function</li> <li>Can be locked OFF with up to three padlocks. Note: Padlocks are to be provided by the customer.</li> <li>Release screw allows the door to be opened with the handle in the ON position.</li> <li>IP54 enclosure</li> </ul>	BM3RHB-xxx	Standard (black)	160/0.35
<a href="#"><u>BZ0VYRL</u></a>	\$39.50			Emergency (red/yellow)	160/0.35
<a href="#"><u>BZ0VBBM</u></a>	\$38.00		BM3VHB-xxx	Standard (black)	160/0.35
<a href="#"><u>BZ0VYRM</u></a>	\$39.50			Emergency (red/yellow)	160/0.35

NOTE: Premade MMS enclosures are currently not available.

## Accessory Specifications

Trip Device Specifications			
Accessory Type and Part Number		Shunt trip device	Undervoltage device
		BZ0Fxxx	BZ0Rxxx
<b>Standard</b>		IEC 60947-1, UL 508	
<b>Rated Insulation Voltage (VAC)</b>	IEC 60947	690	
	UL 508	600	
<b>No. of ON-OFF Operations</b>		5000	
<b>Operating Time (ms)</b>		20	
<b>Power Consumption</b>	Inrush (VA/W)	21/12	
	Sealed (VA/W)	8/1.2	
<b>Voltage Range</b>	Tripping Voltage (V)	0.7 to 1.1 Ue	0.35 to 0.7 Ue
	Closing Voltage (V)	-	0.85 to 1.1 Ue
<b>Time Rating of Coil (s)</b>	AC: Continuous		AC: Continuous
	DC: 5		

# Fuji Duo Series Manual Motor Starters Accessories

## Accessory specifications (continued)

Contact Block Specifications						
Accessory Type and Part Number		Auxiliary contact block/front	Auxiliary contact block/side	Alarm contact block	Aux. and alarm contact block	Short-circuit alarm contact block
		<u>BZOWIA, BZOWIB</u> (note 3)	<u>BZOWUAA</u> <u>BZOWUABL</u> <u>BZOWUBBL</u>	<u>BZOKIA, BZOKIB</u> (note 3)	<u>BZOWKUA</u>	<u>BZOTKUAB</u>
<b>Standard</b>		IEC 60947-5-1, UL 508				
<b>Rated Operational Current (A)</b>	<b>48VAC AC-15</b> (note 2)	5	6	5	6	6
	<b>125VAC</b>	3	4	3	4	4
	<b>230VAC</b>	1.5	4	1.5	4	4
	<b>400VAC</b>	(note 3)	2.2	(note 3)	2.2	2.2
	<b>500VAC</b>		1.5		1.5	
	<b>690VAC</b>		0.6		0.6	
	<b>48VDC DC-13</b> (note 2)	1.38	5	1.38	5	5
	<b>110VDC</b>	0.55	1.3	0.55	1.3	1.3
<b>220VDC</b>	0.27	0.5	0.27	0.5	0.5	
<b>Contact Rating Code UL 508</b> (note 1)	<b>AC</b>	B300	A600	B300	A600	A600
	<b>DC</b>	Q300	P300	Q300	P300	P300
<b>Min. Voltage and Current</b>		17V / 5mA				

Note 1: NEMA ICS 5-2000. For more information, refer to Control Circuit Contact Electrical Ratings, page MRC-tMRC-130.


Note 2: IEC utilization category. For more information, refer to page MRC-tMRC-131.

Note 3: The indicated contacts should not be used in control circuits higher than 300V.


## Dimensions [mm]

### Manual motor starters

Rotary handle types **BM3RHB-xxx**



Rotary handle types **BM3VHB-xxx**




# Fuji Duo Series Manual Motor Starters Accessories

## Dimensions (continued) [mm]




### Accessories


**Auxiliary contact blocks, front mounting  
BZ0WIA, BZ0WIB**




**Auxiliary contact blocks, side mounting  
BZ0WUAAL, BZ0WUABL, BZ0WUBBL**




**Alarm contact blocks, front mounting  
BZ0KIA, BZ0KIB**




**Auxiliary and alarm contact blocks  
BZ0WKUAA**



**Short-circuit alarm contact block  
BZ0TKUAB**




**Shunt trip devices BZ0Fxxxx  
Undervoltage trip devices BZ0Rxxxx**




### MMS with accessories

**BM3RHB-xxx + BZ0xxxxx**



**BM3VHB-xxx + BZ0xxxxx**



# Fuji Duo Series Manual Motor Starters Accessories




## Dimensions (continued)



[mm]

### Accessories

#### External operation handle BZ0Vxxx




#### Panel drilling




Type	X min.	X max.
BZ0VBBL, BZ0VYRL	139 ± 2	289 ± 2
BZ0VBMM, BZ0VYRM	156 ± 2	306 ± 2

## Wiring Diagrams

### MMS




### Auxiliary and alarm contact blocks BZ0WKUAA




### Alarm contact blocks

#### Front mounting

#### BZ0KIA



#### BZ0KIB




For control circuit design, see design standards such as NEC 430 "Electrical Arrangement of control Circuits" or UL508A Section 38 "Wiring methods, wire routing, and separation of circuits for internal wiring of a control circuit."

# Fuji Duo Series Manual Motor Starters Accessories


## Wiring Diagrams (continued)

### Auxiliary contact blocks Front mounting


**BZ0WIA**




**BZ0WIB**




### Side mounting BZ0WUAAAL



**BZ0WUABL**




**BZ0WUBBL**




### Short-circuit alarm contact blocks

**BZ0TKUAB**




### Shunt trip devices

**BZ0Fxxxx**



### Undervoltage trip devices

**BZ0Rxxxx**



For control circuit design, see design standards such as NEC 430 "Electrical Arrangement of control Circuits" or UL508A section 38 "Wiring methods, wire routing, and separation of circuits for internal wiring of a control circuit."





# Fuji Duo Series Manual Motor Starters Accessories

## Busbar system

### Features

- The busbar system reduces wiring time and saves floor space.
- The busbar makes it easy to power from 2 to 5 manual motor starters, with no wiring needed.
- The 3-phase feed-in terminals are used to connect the wire for the power supply circuit.
- The busbar cover guards against accidental touching of nonconnected busbar terminals (charged parts).
- If using BZ0TCRE terminal cover with BM3R series MMS, the busbar system can not be used.



Note: Busbar photos continued on next page.



BZ0BFRA



BZ0BFVA



BZ0BCRA



BZ0BCVA

Busbar System Components and Ratings								
Part Number	Price	Description	Used with	Specifications	Weight (g)			
<a href="#">BZ0BR02A</a>	\$23.00	Busbar	BM3R	Continuous current: 64A max. pin connection	2-BM3R, modular space: 45mm	30		
<a href="#">BZ0BR03A</a>	\$20.50				3-BM3R, modular space: 45mm	50		
<a href="#">BZ0BR04A</a>	\$24.50				4-BM3R, modular space: 45mm	70		
<a href="#">BZ0BR05A</a>	\$26.00				5-BM3R, modular space: 45mm	90		
<a href="#">BZ0BR12A</a>	\$19.50				2-BM3R, modular space: 54mm	30		
<a href="#">BZ0BR13A</a>	\$23.50		BM3R+ 1 external accessory, 9mm wide	Continuous current: 126A max. pin connection	3-BM3R, modular space: 54mm	55		
<a href="#">BZ0BR14A</a>	\$26.00				4-BM3R, modular space: 54mm	80		
<a href="#">BZ0BR15A</a>	\$27.50				5-BM3R, modular space: 54mm	105		
<a href="#">BZ0BV02A</a>	\$37.00				BM3V	Continuous current: 126A max. pin connection	2-BM3V, modular space: 55mm	140
<a href="#">BZ0BV03A</a>	Retired						3-BM3V, modular space: 55mm	240
<a href="#">BZ0BV04A</a>	\$55.00		4-BM3V, modular space: 55mm	340				
<a href="#">BZ0BV12A</a>	\$39.50		BM3V + 1 external accessory, 9mm wide	2-BM3V, modular space: 64mm			150	
<a href="#">BZ0BV13A</a>	Retired			3-BM3V, modular space: 64mm			270	
<a href="#">BZ0BV14A</a>	Retired			4-BM3V, modular space: 64mm	380			
<a href="#">BZ0BFRA</a>	\$20.50		3-phase feed-in terminal	BM3R	Continuous current: 64A max. Applicable cable size: 25mm <sup>2</sup> max.	40		
<a href="#">BZ0BFVA</a>	\$41.50	BM3V		Continuous current: 126A max. Applicable cable size: 50mm <sup>2</sup> max.	170			
<a href="#">BZ0BCRA</a>	\$5.50	Busbar cover	BZ0BR	For pin connection	10			
<a href="#">BZ0BCVA</a>	Retired		BZ0BV	NOTE: Some fine tuning and fitting adjustments may be needed.	5			

# Fuji Duo Series Manual Motor Starters

## Accessories

### Busbar system (continued)

### Dimensions

(mm)




**BZ0BV04A**



**BZ0BV12A**




**BZ0BV13A**



**BZ0BV14A**

**For BM3RHB-xxx**


**BZ0BR0xx Without external accessory**



- BZ0BR02A: 80 mm
- BZ0BR03A: 125 mm
- BZ0BR04A: 170 mm
- BZ0BR05A: 215 mm


**For BM3VHB-xxx**

**BZ0BV0xx Without external accessory**




- BZ0BV02A: 97 mm
- BZ0BV03A: 151 mm
- BZ0BV04A: 205 mm

**BZ0BR1xx With 1 external accessory**




- BZ0BR12A: 89 mm
- BZ0BR13A: 143mm
- BZ0BR14A: 197 mm
- BZ0BR15A: 251 mm

**BZ0BV1xx With 1 external accessory, 9mm wide**



- BZ0BV12A: 106 mm
- BZ0BV13A: 169 mm
- BZ0BV14A: 232 mm

**BZ0BFRA 3-phase feed-in terminals**



**BZ0BFVA**

