

2-Post Open-Frame Knockdown Rack



Features

- Automated tapping process provides 10-32 tapped rails only on the front to ensure ease of mounting rack mount equipment.
 - Includes marked rack unit dividers to aid in equipment mounting.
- To keep the rack upright when it is loaded with equipment, we've included a large base for freestanding support. Optionally, the base can be caster mounted when you need to move your rack.

Construction

- 12-gauge steel
- Three-stage paint process which includes a coat of premium smooth black powder coat.
- In order to prevent any damage that may occur during transportation, rails and base are protected by a thick cardboard carton.
- Tested to nearly double the suggested static load rating of 800 lb [363 kg].

Listings

- TAA compliant for GSA Schedule purchases.
- EIA compliant
- RoHS



2-Post Open-Frame Knockdown Rack

Part Number	Price	Rack Units	Drawing Link
DNRR1942LDK	Retired	24U	PDF
DNRR1963LDK	Retired	36U	PDF
DNRR1970LDK	Retired	40U	PDF
DNRR1977LDK	Retired	44U	PDF