

# 2-Post Open Frame 19-Inch and 23-Inch Welded Rack



## Features

- Automated tapping process provides threaded rails on both the front and back to ensure flexibility when mounting equipment.
  - Includes marked rack unit dividers to aid in equipment mounting.
- For connecting multiple racks together: numerous holes for mounting power distribution, cable management and other accessories are provided.
- Bonding is possible two pairs of integrated 10-32 ground studs, spaced 0.63in [16 mm] apart. Stud pairs are conveniently located across from each other inside the rail channel. For added convenience, a pair of studs is located near the top of the rack, while another pair is located at the lower side.

## Construction

- 10-gauge steel
- Three-stage paint process which includes a coat of premium smooth black powder coat.
- In order to prevent any damage that may occur during transportation, rails and base are protected with a thick layer of cardboard.
- UL Listed 2416 load rated for up to 1,500 lb [680 kg]. Static Load tested to 6,000 lb [2,721 kg].

## Listings

- TAA compliant for GSA Schedule purchases.
- EIA compliant
- RoHS
- cULus File E474597



2-Post Open Frame 19-Inch and 23-Inch Welded Rack				
Part Number	Price	Rack Units	Rack Width	Drawing Link
<a href="#">DNRR63HDW</a>	\$487.00	36U	19.0 [483]	<a href="#">PDF</a>
<a href="#">DNRR70HDW</a>	\$443.00	40U	19.0 [483]	<a href="#">PDF</a>
<a href="#">DNRR77HDW</a>	\$531.00	44U	19.0 [483]	<a href="#">PDF</a>
<a href="#">DNRR84HDW</a>	\$575.00	48U	19.0 [483]	<a href="#">PDF</a>
<a href="#">DNRR2377HDWB</a>	\$531.00	44U	23.0 [584]	<a href="#">PDF</a>
<a href="#">DNRR2384HDWB</a>	\$566.00	48U	23.0 [584]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].