


# NEMA 3R, 4X, 12, and 13 Stainless Steel Two-Door Freestanding



## Features

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

## Construction

- Formed 12-gauge 304 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Heavy-duty stainless steel lifting eye-bolts are provided with reinforcing support angles.
- Doors are supported with heavy gauge continuous hinges.
- 3-point padlocking door handle.
- Seamless poured-in-place gasket.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.
- Center post is removable for easy installation of the subpanel.

## Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

## Listings


- UL 508A Type 3R, 4X, and 12 [File E65324]
- Complies with:
  - NEMA Type 3R, 4X, 12, and 13
  - IEC 60529, IP66
  - CSA Type 3R, 4X and 12 [File LR21001]



| NEMA 3R, 4X, 12, and 13 Stainless Steel Two-Door Freestanding |             |                                           |                        |            |                     |
|---------------------------------------------------------------|-------------|-------------------------------------------|------------------------|------------|---------------------|
| Part Number                                                   | Price       | Enclosure Size HxWxD                      | Optional Subpanel      | Price      | Drawing Link        |
| <a href="#">HN4FS604818SS</a>                                 | \$6,543.00  | 60.06 x 48.06 x 19.25 [1526 x 1221 x 489] | <a href="#">60AWFW</a> | \$787.00   | <a href="#">PDF</a> |
| <a href="#">HN4FS724818SS</a>                                 | \$7,157.00  | 72.06 x 48.06 x 19.25 [1830 x 1221 x 489] | <a href="#">72ZWFW</a> | \$892.00   | <a href="#">PDF</a> |
| <a href="#">HN4FS724824SS</a>                                 | \$7,806.00  | 72.06 x 48.06 x 25.25 [1830 x 1221 x 641] | <a href="#">72ZWFW</a> | \$892.00   | <a href="#">PDF</a> |
| <a href="#">HN4FS726018SS</a>                                 | \$8,064.00  | 72.06 x 60.06 x 19.25 [1830 x 1526 x 489] | <a href="#">72ZXFW</a> | \$1,035.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS726024SS</a>                                 | \$8,756.00  | 72.06 x 60.06 x 25.25 [1830 x 1526 x 641] | <a href="#">72ZXFW</a> | \$1,035.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS726036SS</a>                                 | \$10,090.00 | 72.06 x 60.06 x 37.25 [1830 x 1526 x 946] | <a href="#">72ZXFW</a> | \$1,035.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS727218SS</a>                                 | \$8,955.00  | 72.06 x 72.06 x 19.25 [1830 x 1830 x 489] | <a href="#">72ZYFW</a> | \$1,175.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS727224SS</a>                                 | \$9,681.00  | 72.06 x 72.06 x 25.25 [1830 x 1830 x 641] | <a href="#">72ZYFW</a> | \$1,175.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS904820SS</a>                                 | \$8,381.00  | 90.06 x 48.06 x 21.25 [2288 x 1221 x 540] | <a href="#">90BWFW</a> | \$1,048.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS907220SS</a>                                 | \$10,573.00 | 90.06 x 72.06 x 21.25 [2288 x 1830 x 540] | <a href="#">90BYFW</a> | \$1,417.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS907224SS</a>                                 | \$11,113.00 | 90.06 x 72.06 x 25.25 [2288 x 1830 x 641] | <a href="#">90BYFW</a> | \$1,417.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS907236SS</a>                                 | \$12,786.00 | 90.06 x 72.06 x 37.25 [2288 x 1830 x 946] | <a href="#">90BYFW</a> | \$1,417.00 | <a href="#">PDF</a> |

Note: Dimensions in inches [millimeters].

# NEMA 3R, 4X, 12, and 13 Stainless Steel Two-Door Freestanding Dual Access



## Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

## Construction

- Formed 12-gauge 304 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Heavy-duty stainless steel lifting eyebolts are provided with reinforcing support angles.
- Doors are supported with heavy gauge continuous hinges
- Dual Access versions have doors front and back.
- 3-point 316 stainless steel padlocking door handle.
- Uses 1/4 turn latch handles.
- Seamless poured-in-place gasket.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.
- Center post is removable for easy installation of the subpanel.

## Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

## Listings

- UL 508A Type 3R, 4X, and 12
- CSA Type 3R, 4, 4X, and 12 [File LR21001]
- Complies with:
  - NEMA Type 3R, 4X, 12, and 13
  - IEC 60529, IP66



## NEMA 3R, 4X, 12, and 13 Stainless Steel Freestanding Two-Door Dual Access

| Part Number                     | Price       | Enclosure Size HxWxD                      | Subpanel               | Price      | Drawing Link        |
|---------------------------------|-------------|-------------------------------------------|------------------------|------------|---------------------|
| <a href="#">HN4FS724824DASS</a> | \$8,765.00  | 72.06 x 48.06 x 26.43 [1830 x 1221 x 671] | <a href="#">72ZWFW</a> | \$892.00   | <a href="#">PDF</a> |
| <a href="#">HN4FS726024DASS</a> | \$9,865.00  | 72.06 x 60.06 x 26.43 [1830 x 1526 x 671] | <a href="#">72ZXFW</a> | \$1,035.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS726036DASS</a> | \$11,341.00 | 72.06 x 60.06 x 38.43 [1830 x 1526 x 976] | <a href="#">72ZXFW</a> | \$1,035.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS727224DASS</a> | \$10,937.00 | 72.06 x 72.06 x 26.43 [1830 x 1830 x 671] | <a href="#">72ZYFW</a> | \$1,175.00 | <a href="#">PDF</a> |
| <a href="#">HN4FS907224DASS</a> | \$12,556.00 | 90.06 x 72.06 x 26.43 [2288 x 1830 x 671] | <a href="#">90BYFW</a> | \$1,417.00 | <a href="#">PDF</a> |

Note: Dimensions in inches [millimeters].

# NEMA 3R, 4X, 12, and 13 Stainless Steel Two-Door Freestanding with Slope Top



powder coating.



## Features

- Designed to enclose electrical and/or electronic equipment and protect against harsh, industrial environments for larger free-standing applications.
- Sloped top prevents water from resting on top as well as providing potential for controls mounting.

## Construction

- Formed 12-gauge 304 or 316L stainless steel.
- Continuously welded seams are ground smooth.
- Flange trough collar around door opening excludes flowing liquids and contaminants.
- Heavy-duty lifting eyes are anchored into reinforced top corners.
- Removable doors are secured with bullet style, heavy-duty, lift off hinges.
- Panel supports are provided.
- Center post is removable, providing easy panel installation.
- Heavy-duty three point latching mechanism with heavy-duty roller ends is provided for ease of door closing.
- Uses 1/4 turn latch handles.
- Seamless poured-in-place gasket
- Stainless steel door handles are complete with padlock hasp.
- A provision for mounting fluorescent lighting is provided.
- A bonding stud is provided in the door and a grounding stud is provided in the enclosure for each door.
- A literature pocket is provided for the inside of the door.
- Cover and enclosure are natural stainless steel with a smooth, brushed finish.
- Subpanel is finished in white

## Listings

- UL 508A Type 3R, 4, and 4X [UL File E65324]
- Complies with
  - NEMA Type 3R, 4, 4X, and 12
  - IEC 60529, IP66



| NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Freestanding with Slope Top |             |                                |             |                                           |                     |
|---------------------------------------------------------------------------------|-------------|--------------------------------|-------------|-------------------------------------------|---------------------|
| 304 Stainless Steel                                                             | Price       | 316 Stainless Steel            | Price       | Enclosure Size HxWxD                      | Drawing Link        |
| <a href="#">2STFS747512SS</a>                                                   | \$15,226.00 | <a href="#">2STFS747512S16</a> | \$17,019.00 | 78.54 x 75.13 x 15.58 [1995 x 1908 x 396] | <a href="#">PDF</a> |
| <a href="#">2STFS747518SS</a>                                                   | \$16,595.00 | <a href="#">2STFS747518S16</a> | \$18,554.00 | 80.72 x 75.13 x 22.38 [2050 x 1908 x 568] | <a href="#">PDF</a> |
| <a href="#">2STFS747524SS</a>                                                   | \$17,872.00 | <a href="#">2STFS747524S16</a> | \$19,986.00 | 82.91 x 75.13 x 29.17 [2106 x 1908 x 741] | <a href="#">PDF</a> |

Note: Dimensions in inches [millimeters].

# Enclosure Accessories

## Locks and Latches



### 1/4-Turn Latch Handles



#### Features

- Durable zinc diecast or stainless steel.
- Removable handle stop for clockwise / counter-clockwise operation.
- Textured powder coat Black finish on zinc cast handle.
- Maintains NEMA rating of enclosure.
- Padlock "trigger" design for security requirements.
- Optional key lock or defeater available. Key lock versions include two keys.

| 1/4-Turn Latch Handles  |          |                                       |              |                     |             |                                            |                     |
|-------------------------|----------|---------------------------------------|--------------|---------------------|-------------|--------------------------------------------|---------------------|
| Part Number             | Price    | Security Type                         | Latch Points | Material            | Finish      | For Use With These Hammond Enclosures Only | Drawing Link        |
| <a href="#">MHK1</a>    | \$127.00 | padlocking                            | 1            | die-cast zinc       | black matte | single-door NEMA 4 and NEMA 12             | <a href="#">PDF</a> |
| <a href="#">MHKD1</a>   | \$133.00 | padlocking with defeater              |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHKL1</a>   | \$144.00 | combination keylocking/<br>padlocking |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHK2</a>    | \$217.00 | padlocking                            | 3            | die-cast zinc       | black matte | less than 60in (H) NEMA 4 and NEMA 12      | <a href="#">PDF</a> |
| <a href="#">MHKD2</a>   | \$228.00 | padlocking with defeater              |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHKL2</a>   | \$246.00 | combination keylocking/<br>padlocking |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHK3</a>    | \$221.00 | padlocking                            | 3            | die-cast zinc       | black matte | 60in (H) or greater NEMA 4 and NEMA 12     | <a href="#">PDF</a> |
| <a href="#">MHKD3</a>   | \$232.00 | padlocking with defeater              |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHKL3</a>   | \$251.00 | combination keylocking/<br>padlocking |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHK1SS</a>  | \$234.00 | padlocking                            | 1            | 316 stainless steel | #4 brush    | single-door NEMA 4X                        | <a href="#">PDF</a> |
| <a href="#">MHKD1SS</a> | \$258.00 | padlocking with defeater              |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHKL1SS</a> | \$258.00 | combination keylocking/<br>padlocking |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHK2SS</a>  | \$249.00 | padlocking                            | 3            | 316 stainless steel | #4 brush    | less than 60in (H) NEMA 4X                 | <a href="#">PDF</a> |
| <a href="#">MHKD2SS</a> | \$274.00 | padlocking with defeater              |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHKL2SS</a> | \$274.00 | combination keylocking/<br>padlocking |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHK3SS</a>  | \$362.00 | padlocking                            | 3            | 316 stainless steel | #4 brush    | 60in (H) or greater NEMA 4X                | <a href="#">PDF</a> |
| <a href="#">MHKD3SS</a> | \$398.00 | padlocking with defeater              |              |                     |             |                                            | <a href="#">PDF</a> |
| <a href="#">MHKL3SS</a> | \$398.00 | combination keylocking/<br>padlocking |              |                     |             |                                            | <a href="#">PDF</a> |