

NEMA 4 and 4X Extra Deep Stainless Steel Pushbutton



Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Provides protection from dirt, dust, oil, and water.

Construction

- Smooth continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Captive cover screws fasten into threaded, sealed wells.
- Larger enclosures provide internally hinged removable covers, designed to hold the cover open during wiring (see drawings).
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

Finish

- Natural stainless steel with a #4 smooth brushed finish.

Listings

- UL 508A Type 4 and 4X [UL File E65324]
- CSA Type 4 and 4X [CSA File LR21001]
- Complies with
 - NEMA Type 4 and 4X
 - IEC 60529, IP66
- All appropriate components are required to maintain these standards.



NEMA 4 and 4X Extra Deep Stainless Steel Pushbutton


304 Stainless Steel		316 Stainless Steel				Console Size HxWxD	Drawing Link	# Holes	Steel Gauge	Hinged		
22 mm	Price	30 mm	Price	22 mm	Price						30 mm	Price
1437MSSA	\$216.00	1437SSA	\$211.00	1437MS16A	\$281.00	1437S16A	\$260.00	4.31 x 4.31 x 4.91 [109 x 109 x 125]	PDF	1	16	No
1437MSSB	\$265.00	1437SSB	\$258.00	1437MS16B	\$345.00	1437S16B	\$319.00	6.31 x 4.31 x 4.92 [160 x 109 x 125]	PDF	2	14	Yes
1437MSSC	\$307.00	1437SSC	\$299.00	1437MS16C	\$400.00	1437S16C	\$370.00	8.31 x 4.31 x 4.92 [211 x 109 x 125]	PDF	3		
1437MSSD	\$345.00	1437SSD	\$336.00	1437MS16D	\$451.00	1437S16D	\$416.00	10.31 x 4.31 x 4.92 [262 x 109 x 125]	PDF	4		
—	—	1437SSS	\$659.00	—	—	1437S16S	\$787.00	12.06 x 11.06 x 4.92 [306 x 281 x 125]	PDF	16		

Note: Dimensions in inches [millimeters].


NEMA 4 and 4X Extra Deep Stainless Steel Pushbutton



Dimensions



22 mm [0.87in] Hole Placement



30 mm [1.18in] Hole Placement

