


HydroMode™ Lead Free Brass Adapter Fittings

HydroMode lead free brass fittings are designed for use in potable water and beverage applications. These hose barb adapters work well with PVC hose and stainless steel hose clamps.

Note: Actual product dimensions and appearance may vary



NLBHB-316-18N



HydroMode™ Lead Free Brass Straight Barb Fitting								
Inch Sizes - dimensions in inches [mm]								
Part No.	Price	Description	Parts Per Pkg	Weight	T	L	ØD	C Hex
<u>NLBHB-316-18N</u>	\$14.00	Straight barb, 3/16 inch hose to 1/8 inch male NPT	3	0.1	1/8	1.27 [32.1]	0.20 [5.1]	0.44 [11.1]
<u>NLBHB-14-18N</u>	\$14.00	Straight barb, 1/4 inch hose to 1/8 inch male NPT	3	0.1	1/8	1.43 [36.3]	0.24 [6.1]	0.44 [11.1]
<u>NLBHB-14-14N</u>	\$8.50	Straight barb, 1/4 inch hose to 1/4 inch male NPT	3	0.1	1/4	1.69 [42.9]	0.24 [6.1]	0.56 [14.3]
<u>NLBHB-516-18N</u>	\$17.50	Straight barb, 5/16 inch hose to 1/8 inch male NPT	3	0.1	1/8	1.40 [35.6]	0.29 [7.4]	0.44 [11.1]
<u>NLBHB-516-14N</u>	\$19.00	Straight barb, 5/16 inch hose to 1/4 inch male NPT	3	0.1	1/4	1.43 [36.3]	0.29 [7.4]	0.56 [14.3]
<u>NLBHB-38-14N</u>	\$17.00	Straight barb, 3/8 inch hose to 1/4 inch male NPT	3	0.1	1/4	1.63 [41.5]	0.36 [9.2]	0.56 [14.3]
<u>NLBHB-38-38N</u>	\$25.00	Straight barb, 3/8 inch hose to 3/8 inch male NPT	3	0.2	3/8	1.52 [38.6]	0.36 [9.2]	0.69 [17.5]
<u>NLBHB-38-12N</u>	\$46.00	Straight barb, 3/8 inch hose to 1/2 inch male NPT	3	0.2	1/2	1.61 [40.9]	0.36 [9.2]	0.88 [22.2]
<u>NLBHB-12-14N</u>	\$29.00	Straight barb, 1/2 inch hose to 1/4 inch male NPT	3	0.2	1/4	1.64 [41.8]	0.48 [12.3]	0.56 [14.3]
<u>NLBHB-12-38N</u>	\$27.50	Straight barb, 1/2 inch hose to 3/8 inch male NPT	3	0.2	3/8	1.74 [44.1]	0.48 [12.3]	0.69 [17.5]
<u>NLBHB-12-12N</u>	\$37.00	Straight barb, 1/2 inch hose to 1/2 inch male NPT	3	0.3	1/2	1.80 [45.7]	0.48 [12.3]	0.88 [22.2]
<u>NLBHB-34-12N</u>	\$55.00	Straight barb, 3/4 inch hose to 1/2 inch male NPT	3	0.3	1/2	1.78 [45.2]	0.73 [18.5]	0.88 [22.2]
<u>NLBHB-34-34N</u>	\$78.00	Straight barb, 3/4 inch hose to 3/4 inch male NPT	3	0.4	3/4	1.90 [48.3]	0.73 [18.5]	1.06 [27.0]