

HY-TECH Hydraulic Threaded Adapters



Part No. 8MJ-6MB

Overview

Hydraulic threaded adapters are used to connect hoses to valves, actuators or manifolds.

Features

- Plated steel body
- All Requirements as per SAE J514 & 6149-3

HY-TECH Hydraulic JIC to O-ring Boss Straight Adapters Selection							
Part No.	Connection 1 (Male JIC)	Connection 2 (Male O-ring boss)	Max. Temp.	Max. Pressure	Qty./pack	Weight (lbs)	Price
<u>4MJ-4MB</u>	-4	-4	212°F (100°C)	5,000 psi	2	0.10	\$3.75
<u>4MJ-6MB</u>		-6			2	0.14	\$4.75
<u>4MJ-8MB</u>		-8			2	0.23	\$6.50
<u>6MJ-4MB</u>	-6	-4			2	0.12	\$4.50
<u>6MJ-6MB</u>		-6			2	0.14	\$4.25
<u>6MJ-8MB</u>		-8			2	0.24	\$6.25
<u>6MJ-10MB</u>		-10		2	0.36	\$8.50	
<u>8MJ-6MB</u>	-8	-6		4,500 psi	2	0.22	\$6.00
<u>8MJ-8MB</u>		-8			2	0.27	\$6.50
<u>8MJ-10MB</u>		-10			2	0.36	\$8.75
<u>8MJ-12MB</u>		-12			2	0.60	\$11.00
<u>10MJ-8MB</u>	-10	-8		3,500 psi	2	0.38	\$8.50
<u>10MJ-10MB</u>		-10			2	0.40	\$9.00
<u>12MJ-8MB</u>	-12	-8			2	0.60	\$12.00
<u>12MJ-10MB</u>		-10			2	0.56	\$12.00
<u>12MJ-12MB</u>		-12	2		0.67	\$12.00	
<u>12MJ-16MB</u>		-16	2		0.93	\$19.00	

HY-TECH Hydraulic Threaded Adapters



Part No. 8MJ-6MB90

Overview

Hydraulic threaded adapters are used to connect hoses to valves, actuators or manifolds.

Features

- Plated steel body
- All Requirements as per SAE J514 & 6149-3

HY-TECH Hydraulic JIC to O-ring Boss Elbow Adapters Selection							
Part No.	Connection 1 (Male JIC)	Connection 2 (Male O-ring boss)	Max. Temp.	Max. Pressure	Qty./pack	Weight (lbs)	Price
<u>4MJ-4MB90</u>	-4	-4	212°F (100°C)	5,000 psi	2	0.14	\$8.25
<u>4MJ-6MB90</u>		-6			2	0.24	\$9.25
<u>4MJ-8MB90</u>		-8			2	0.45	\$14.50
<u>6MJ-4MB90</u>	-6	-4			2	0.23	\$10.00
<u>6MJ-6MB90</u>		-6			2	0.23	\$8.00
<u>6MJ-8MB90</u>		-8			2	0.45	\$12.50
<u>6MJ-10MB90</u>		-10			2	0.68	\$18.00
<u>8MJ-6MB90</u>	-8	-6		4,500 psi	2	0.41	\$11.50
<u>8MJ-8MB90</u>		-8			2	0.48	\$13.00
<u>8MJ-10MB90</u>		-10			2	0.72	\$16.00
<u>8MJ-12MB90</u>		-12			2	1.16	\$24.50
<u>10MJ-8MB90</u>	-10	-8		3,500 psi	2	0.66	\$17.00
<u>10MJ-10MB90</u>		-10			2	0.75	\$17.00
<u>10MJ-12MB90</u>		-12			2	1.19	\$28.00
<u>12MJ-8MB90</u>	-12	-8		3,500 psi	2	1.02	\$32.50
<u>12MJ-10MB90</u>		-10	2		1.07	\$24.50	
<u>12MJ-12MB90</u>		-12	2		1.21	\$22.50	

HY-TECH Hydraulic Threaded Adapters



Part No. 8MJ-8FJX90

Overview

Hydraulic threaded adapters are used to connect hoses to valves, actuators or manifolds.

Features

- Plated steel body
- All Requirements as per SAE J514 & 6149-3

HY-TECH Hydraulic Elbow JIC to JIC Adapters Selection							
Part No.	Connection 1 (Male JIC)	Connection 2 (Female JIC)	Max. Temp.	Max. Pressure	Qty./pack	Weight (lbs)	Price
<u>4MJ-4FJX90</u>	-4	-4	250°F (121.1°C)	5,000 psi	2	0.14	\$9.50
<u>6MJ-6FJX90</u>	-6	-6			2	0.23	\$11.00
<u>8MJ-8FJX90</u>	-8	-8		2	0.44	\$13.00	
<u>10MJ-10FJX90</u>	-10	-10		3,500 psi	2	0.64	\$17.50
<u>12MJ-12FJX90</u>	-12	-12			2	1.05	\$26.50

HY-TECH Hydraulic Threaded Adapters

Part No. 8MB-6FBPart No. 6MB-6FB90

Overview

Hydraulic threaded adapters are used to connect hoses to valves, actuators or manifolds.

Features

- Plated steel body
- All Requirements as per SAE J514 & 6149-3

Part No. 8MJ-8FFORX

HY-TECH Hydraulic O-ring Boss Straight Reducer Adapters Selection							
Part No.	Connection 1	Connection 2	Max. Temp.	Max. Pressure	Qty./pack	Weight (lbs)	Price
<u>8MB-4FB</u>	-8 male o-ring boss	-4 female o-ring boss	212°F (100°C)	6,000 psi	2	0.28	\$15.50
<u>8MB-6FB</u>		-6 female o-ring boss			2	0.26	\$7.50
<u>10MB-8FB</u>	-10 male o-ring boss	-8 female o-ring boss		5,000 psi	2	0.41	\$9.00
<u>12MB-8FB</u>	-12 male o-ring boss				2	0.42	\$14.50
<u>12MB-10FB</u>					-10 female o-ring boss	2	0.63
HY-TECH Hydraulic O-ring Boss Elbow Adapters Selection							
<u>4MB-4FB90</u>	-4 male o-ring boss	-4 female o-ring boss	212°F (100°C)	6,000 psi	2	0.30	\$17.50
<u>6MB-6FB90</u>	-6 male o-ring boss	-6 female o-ring boss			2	0.56	\$24.50
HY-TECH Hydraulic JIC to Flat Face Adapters Selection							
<u>6MJ-6FFORX</u>	-6 male JIC 37 deg	-6 female flat face o-ring	212°F (100°C)	6,000 psi	2	0.28	\$13.50
<u>8MJ-8FFORX</u>	-8 male JIC 37 deg	-8 female flat face o-ring			2	0.48	\$18.00