

Non-Insulated Connector Crimping Tool

The DN-CT-ID1 series crimping tools are for non-insulated connectors, available up to AWG4, side feeded, Indent-Crimp. For connectors to DIN 46234.


- High-strength, through hardened alloy steel construction
- Unique mechanism significantly reduces hand force requirement over competing crimping tools
- Versatile and easy to customize for right hand or left hand users.
- Non-slip pad holds tool in place when leveraging on a work surface
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear miscrimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- Hole in handle allows attachment of safety strap
- Each tool has a unique serial number for traceability




DN-CT-ID1

Non-Insulated Connector Crimping Tool		
Part Number	Description	Price
<u>DN-CT-ID1</u>	AutomationDirect wire crimping tool, indent profile, 8-4 AWG capacity, compatible with non-insulated connectors.	\$283.00

Non-Insulated Connector Crimping Tool Specifications	
Length	10.08 in [256mm]
Width	0.87 in [22mm]
Height	3.15 in [80mm]
Weight	1.23 lb [559g]
Capacity	10 - 25 mm ² / AWG 8-4
Crimp Profile	Indent
Crimp Dimensions	AWG 8/AWG 6/AWG 4 [10 mm ² /16 mm ² /25 mm ²]
Connector	Non-insulated connectors
Lifespan	Tested to 50,000 cycles



Die Profile



Crimp Profile

DN-CT-ID1