



Miniature Feed-Through Terminal Blocks





Dimensions: mm [in]

KN-M12xxx

KN-MG12

- Screw connection terminal
- PE snap-on connection DIN rail
- UL E179129
(For copper wire only.
One conductor in
terminal only.)
- CE (EN 60947-7-1/
EN 60947-7-2)



See our website: www.AutomationDirect.com for complete engineering drawings

Ordering Information

Color	Part Number	Qty	Price	Part Number	Qty	Price
Gray	<u>KN-M12GRY</u>	100	\$59.00	—	—	—
	<u>KN-M12GRY-25</u>	25	\$14.50	—	—	—
Blue	<u>KN-M12BLU</u>	100	\$59.00	—	—	—
	<u>KN-M12BLU-25</u>	25	\$14.50	—	—	—
Yellow/ Green	—	—	—	<u>KN-MG12</u>	50	\$144.00
	—	—	—	<u>KN-MG12-10</u>	10	\$30.00

Technical Specifications

Model	KN-M12xxx			KN-MG12		
Width	5mm [0.20 in]			5mm [0.20 in]		
Stripping Length	10mm [0.39 in]			10mm [0.39 in]		
Tightening Torque	0.4 N·m [3.5 lb·in]			0.4 N·m [3.5 lb·in]		
Density	200/m [60 pcs/ft]			200/m [60 pcs/ft]		
UL/CSA Approval	300V	20A	26-12 AWG	—	—	26-12 AWG
CE Conformity	400V	24A	2.5 mm²	—	—	2.5 mm²
SCCR Rating	100kA			100kA per Table SB4.1, 2009, UL 508A.		
Operating Temperature	Ambient air temperature: -67 to 185°F [-55 to 85°C] Relative humidity: 50% max at 104°F [40°C] and 90% max at 68°F [20°C]					
Material	Current Bar: Copper Alloy / Housing: Polyamide 66 / Screws: Zinc Plated Steel					
DIN Rail Width	15mm					

Accessories

End Covers (International colors)	Gray	<u>KN-ECMGRY-10</u>	10/pkg	\$6.00	—	—	—
		<u>KN-ECMGRY</u>	100/pkg	\$55.00	—	—	—
	Blue	<u>KN-ECMBLU</u>	10/pkg	\$6.00	—	—	—
	Green/ Yellow	—	—	—	<u>KN-ECMGRN</u>	10/pkg	\$6.00
Jumpers	2-pole	<u>KN-2JM12</u>	25/pkg	\$10.50	—	—	—
	3-pole	<u>KN-3JM12</u>	20/pkg	\$12.00	—	—	—
	4-pole	<u>KN-4JM12</u>	15/pkg	\$12.00	—	—	—
	10-pole	<u>KN-10JM12</u>	5/pkg	\$13.50	—	—	—
Marking Tags	KN-L5 Series			KN-L5 Series			



Miniature Feed-Through Terminal Blocks





Dimensions: mm [in]

KN-M10xxx

KN-MG10

- Screw connection terminal
- PE snap-on connection DIN rail
- UL E179129
(For copper wire only.
One conductor in terminal only.)
- CE (EN 60947-7-1)



See our website: www.AutomationDirect.com for complete engineering drawings

Ordering Information

Color	Part Number	Qty	Price	Part Number	Qty	Price
Gray	<u>KN-M10GRY</u>	100	\$73.00	—	—	—
	<u>KN-M10GRY-25</u>	25	\$17.00	—	—	—
Blue	<u>KN-M10BLU</u>	100	\$73.00	—	—	—
	<u>KN-M10BLU-25</u>	25	\$17.00	—	—	—
Green/ Yellow	—	—	—	<u>KN-MG10</u>	50	\$112.00
	—	—	—	<u>KN-MG10-10</u>	10	\$33.00

Technical Specifications

Technical Specifications						
Model	KN-M10xxx			KN-MG10		
Width	6mm [0.24 in]			6mm [0.24 in]		
Stripping Length	10mm [0.39 in]			10mm [0.39 in]		
Tightening Torque	0.5 N·m [4.4 lb·in]			0.5 N·m [4.4 lb·in]		
Density	166/m [50 pcs/ft]			166/m [50 pcs/ft]		
UL/CSA Approval	300V	30A	26-10 AWG	—	—	26-10 AWG
CE Conformity	400V	32A	4mm²	—	—	4mm²
SCCR Rating	100kA			10kA per Table SB4.1, 2009, UL 508A.		
Operating Temperature	Ambient air temperature: -67 to 185°F [-55 to 85°C] Relative humidity: 50% max at 104°F [40°C] and 90% max at 68°F [20°C]					
Material	Current Bar: Copper Alloy / Housing: Polyamide 66 / Screws: Zinc Plated Steel					
DIN Rail Width	15mm					

Accessories

End Covers	Gray	<u>KN-ECMGRY-10</u>	10/pkg	\$6.00	—	—	—
		<u>KN-ECMGRY</u>	100/pkg	\$55.00	—	—	—
	Blue	<u>KN-ECMBLU</u>	10/pkg	\$6.00	—	—	—
	Green/ Yellow	—	—	—	<u>KN-ECMGRN</u>	10/pkg	\$6.00
Jumpers	2-pole	<u>KN-2JM10</u>	25/pkg	\$11.00	—	—	—
	3-pole	<u>KN-3JM10</u>	20/pkg	\$13.50	—	—	—
	4-pole	<u>KN-4JM10</u>	15/pkg	\$15.50	—	—	—
	10-pole	<u>KN-10JM10</u>	5/pkg	\$14.50	—	—	—
Marking Tags	KN-L5 Series				KN-L5 Series		



100kA Terminal Block

Short-Circuit Current

Rating Data

Short-Circuit Current Rating Data										
Part Number	Suitable Copper Conductor Range (AWG)		Fuse Class Maximum Amperage						SCCR Rating	Volts Max
	Line	Load	Class J	Class T	Class RK1	Class RK5	Class G	Class CC		
KN-T12 ²	26-12	26-12	20	20	—	—	20	20	100 kA	600
KN-T10 ²	26-10	26-10	30	30	—	—	30	30	100 kA	600
KN-T8 ²	26-8	26-8	50	50	30	—	45	30	100 kA	600
KN-T6 ²	16-6	16-6	80	80	60	30	60	30	100 kA	600
KN-T4 ²	12-4	12-4	80	80	60	30	60	30	100 kA	600
KN-T2 ²	12-2	12-2	125	125	100	30	60	30	100 kA	600
KN-T1/0 ³	6-1/0	6-1/0	150	150	100	30	60	30	100 kA	600
KN-T2/0 ³	6-2/0	6-2/0	225	225	100	60	60	30	100 kA	600
KN-D12 ^{1 2}	26-12	26-12	20	20	—	—	20	20	100 kA	600
KN-D10 ^{1 2}	26-10	26-10	30	30	—	—	30	30	100 kA	600
KN-TL14 ²	24-12	24-12	30	30	—	—	30	30	100 kA	600
KN-TG12 ²	24-12	24-12	30	30	—	—	30	30	100 kA	600
KN-M12 ²	26-12	26-12	30	30	—	—	30	30	100 kA	600
KN-M10 ²	14-12	14-12	30	30	—	—	30	30	100 kA	600

Note: ¹ KN-D12 and KN-D10 have optional short circuit rating evaluated for use with copper conductors only. Must be protected by the max ampere and Class of overcurrent protective device noted above.

² The terminal block short-circuit rating for KN-D12 and KN-D10 were determined based on testing in a minimum size enclosure measuring 4x4x6 inches. The suitability of smaller enclosures shall be determined in the end-use investigation.

³ The terminal block short-circuit rating for KN-T1/0 and KN-T2/0 were determined based on testing in a minimum size enclosure measuring 12x12x6 inches. The suitability of smaller enclosures shall be determined in the end-use investigation.



KONNECT-IT Accessories

Multi-Pole Jumper Bars

Multi-pole jumper bars provide terminal block connection flexibility. Screw-down connection jumpers feature all-metal construction and can be installed quickly just by tightening the screws. Screwless comb-style jumpers are also available. See next page for the larger J1/O jumper installation instructions.

KN-10J12



KN-2JM12



KN-2JCC8



Multi-Pole Jumper Bars Ordering Information

Type	Part Number	Price	Qty	Number of Poles	Rating		Tightening Torque	Dimensions - mm [in]			Fig.	Works With
					(V)	(A)		Height	Length	Width		
Screw-down connection	KN-2J12	\$12.00	25	2	750	24	0.4–0.6 Nm [3.5–5.3 lb-in]	15.8 [0.62]	10.1 [0.40]	4.4 [0.17]	1	KN-T12xx KN-D12xx KN-D12X KN-D12DR1 KN-D12LEDxx
	KN-3J12	\$14.50	20	3	750	24			15.3 [0.60]			
	KN-4J12	\$18.00	15	4	750	24			20.4 [0.80]			
	KN-10J12	\$12.00	5	10	750	24			51.1 [2.01]			
	KN-2J10	\$17.00	25	2	750	32	0.6–0.8 Nm [5.3–7.1 lb-in]	15.5 [0.61]	10.8 [0.43]	6.0 [0.24]	1	KN-T10xx KN-D10xx KN-D10X KN-D10DR1 KN-D10LEDxx
	KN-3J10	\$20.50	20	3	750	32			17.0 [0.67]			
	KN-4J10	\$20.50	15	4	750	32			23.0 [0.91]			
	KN-10J10	\$14.50	5	10	750	32			59.0 [2.32]			
	KN-2J8	\$18.00	25	2	630	41	0.6–0.8 Nm [5.3–7.1 lb-in]	15.5 [0.61]	14.3 [0.56]	6.0 [0.24]	1	KN-T8xx
	KN-3J8	\$22.00	20	3	630	41			22.3 [0.88]			
	KN-4J8	\$21.50	15	4	630	41			30.3 [1.19]			
	KN-10J8	\$17.00	5	10	630	41			78.3 [3.08]			
	KN-2J6	\$22.50	25	2	630	57	0.6–0.8 Nm [5.3–7.1 lb-in]	15.5 [0.61]	18.0 [0.71]	6.0 [0.24]	1	KN-T6xx
	KN-3J6	\$23.50	20	3	630	57			28.0 [1.10]			
	KN-4J6	\$23.50	15	4	630	57			38.0 [1.50]			
	KN-10J6	\$18.50	5	10	630	57			98.0 [3.86]			
	KN-2J4	\$35.50	25	2	750	76	0.6–0.8 Nm [5.3–7.1 lb-in]	23.0 [0.91]	21.0 [0.83]	6.0 [0.24]	1	KN-T4xx
	KN-3J4	\$37.00	20	3	750	76			33.0 [1.30]			
	KN-4J4	\$37.00	15	4	750	76			45.0 [1.77]			
	KN-10J4	\$29.50	5	10	750	76			117.0 [4.61]			
	KN-2J2	\$36.00	25	2	750	125	1.2–1.4 Nm [10.6–12.4 lb-in]	21.0 [0.83]	29.0 [1.14]	8.0 [0.31]	1	KN-T2xx
	KN-3J2	\$39.00	20	3	750	125			45.0 [1.77]			
	KN-4J2	\$39.00	15	4	750	125			61.0 [2.40]			
	KN-10J2	\$29.50	5	10	750	125			157.0 [6.18]			
	KN-2J1/O	\$11.00	5	2	1000	150	2.5–3.5 Nm [22.1–31.0 lb-in]	22.3 [0.88]	36.0 [1.42]	12.0 [0.47]	2	KN-T1/Oxx
	KN-3J1/O	\$18.50	5	3	1000	150			56.0 [2.20]			
	KN-4J1/O	\$23.50	5	4	1000	150			76.0 [2.99]			
	KN-2JTL12	\$18.50	25	2	440	24	0.4–0.6 Nm [3.5–5.3 lb-in]	15.5 [0.61]	11.0 [0.43]	4.4 [0.17]	1	KN-DG12 KN-TG12 KN-TL14 KN-TL14S KN-TL14SLN KN-TL14SLP
	KN-3JTL12	\$23.00	20	3	440	24			17.0 [0.67]			
	KN-4JTL12	\$21.50	15	4	440	24			23.0 [0.91]			
	KN-10JTL12	\$18.50	5	10	440	24			59.0 [2.32]			
Push-in Connection	KN-2JM10	\$11.00	25	2	750	32	–	23.2 [0.91]	9.5 [0.37]	2.7 [0.11]	3	KN-M10xx KN-KBD10
	KN-3JM10	\$13.50	20	3	750	32			15.5 [0.61]			
	KN-4JM10	\$15.50	15	4	750	32			21.5 [0.85]			
	KN-10JM10	\$14.50	5	10	750	32			57.5 [2.26]			
	KN-2JM12	\$10.50	25	2	750	24	–	21.7 [0.85]	8.0 [0.31]	2.3 [0.09]	3	KN-M12xx KN-T12SP4
	KN-3JM12	\$12.00	20	3	750	24			13.0 [0.51]			
	KN-4JM12	\$12.00	15	4	750	24			18.0 [0.71]			
	KN-10JM12	\$13.50	5	10	750	24			48.0 [1.89]			
Screwless Comb-style	KN-2JCC12	\$15.50	25	2	750	24	–	23.7 [0.93]	8.0 [0.31]	2.8 [0.11]	4	KN-T12xx
	KN-2JCC10	\$31.00	25		750	32	–	24.7 [0.97]	9.5 [0.37]			KN-T10xx
	KN-2JCC8	\$32.50	25		630	41	–	25.6 [1.01]	13.5 [0.53]			KN-T8xx
	KN-2JCC6	\$36.00	25		630	57	–	26.7 [1.05]	16.0 [0.63]			KN-T6xx

Screwless Comb-Style jumpers are designed to be connected under the conductor clamp.

Figure 1




Figure 2




Figure 3





Figure 4



Please visit our website
www.automationdirect.com
for complete engineering drawings.







KONNECT-IT® Accessories

End Brackets

End brackets prevent terminal blocks and other DIN rail mount components and devices from moving laterally on the rail. They are constructed from polyamide 66 and available in configurations for 35mm and 15mm DIN rails.

Dimensions mm [in]



End Brackets Ordering Information

Gray End Brackets	KN-EB3	100/pkg	\$48.00	KN-EB4	100/pkg	\$50.00	KN-EB5	100/pkg	\$73.00	KN-EB7	50/pkg	\$50.00
	KN-EB3-10	10/pkg	\$6.00	KN-EB4-10	10/pkg	\$4.75	KN-EB5-10	10/pkg	\$8.50	KN-EB7-10	10/pkg	\$9.75

Technical Specifications

Description	Screw-type end bracket	Screwless end bracket	Screwless end bracket	Screw-type end bracket
Bracket Width	8 mm [0.31 in]	8 mm [0.31 in]	8 mm [0.31 in]	10 mm [0.39 in]
DIN Rail Width	35 mm	35 mm	15 mm	35 mm
Material	Housing: Polyamide 66 / Clamping Connector: Zinc Plated Steel			


End Bracket Accessories

Label Holder	—	—	—	KN-MA-1	25/pkg	\$21.50	—	—	—	KN-MA-2	50/pkg	\$54.00
	—	—	—	KN-MA-1-10	10/pkg	\$9.75	—	—	—	KN-MA-2-10	10/pkg	\$12.50
Marking Tags	KN-L5 Series or KN-L6P5 Series											

End Covers

End covers are used to cover the open side of sectional DIN rail mount terminal blocks. They should be used at the end of an assembly of identical terminal blocks or whenever there is a change in the physical size of the terminal block.

Material: Polyamide 66



End Covers Ordering Information

Part Number	Color	Dimensions H x L x W mm [in]	Works With	Qty	Price	Part Number	Color	Dimensions H x L x W mm [in]	Works With	Qty	Price
KN-ECT6GRY	gray	34.0x42.7x1.3 [1.34x1.68x0.05]	KN-T12 KN-T10 KN-T8 KN-T6	100	\$26.50	KN-ECDORG	orange	48.2x63.2x1.3 [1.90x2.49x0.05]	KN-D10 KN-D12	10	\$6.00
KN-ECT6GRY-25	gray			25	\$6.00	KN-ECDRED	red				\$6.00
KN-ECT6BLU	blue				\$3.00	KN-ECDYEL	yellow				\$6.00
KN-ECT6BLK	black				\$3.00	KN-ECTL	gray	54.7x87.1x1.3 [2.15x3.43x0.05]	KN-TL14	10	\$3.75
KN-ECT6BRN	brown				\$3.00	KN-ECTLS	gray	54.7x72.8x1.2 [2.15x2.87x0.05]	KN-TL14S	10	\$4.75
KN-ECT6GRN	green			10	\$3.00	KN-ECDG12	gray	48.0x71.4x1.2 [1.89x2.81x0.05]	KN-DG12	10	\$4.75
KN-ECT6ORG	orange				\$3.00	KN-ECTG12	gray	62.5x87.5x1.2 [2.46x3.44x0.05]	KN-TG12	10	\$4.75
KN-ECT6RED	red				\$3.00	KN-ECMGRY	gray	28.1x27.0x3.0 [1.11x1.06x0.12]	KN-M12 KN-M10	100	\$55.00
KN-ECT6WHT	white				\$3.00	KN-ECMGRY-10	gray			10	\$6.00
KN-ECT6YEL	yellow				\$3.00	KN-ECMBLU	blue				\$6.00
KN-ECT4GRY	gray	45.7x52.8x1.2 [1.80x2.08x0.05]	KN-T4	25	\$12.50	KN-ECMGRN	green/ yellow	28.1x27.0x3.0 [1.11x1.06x0.12]	KN-MG12 KN-MG10	10	\$6.00
KN-ECT4BLU	blue			10	\$5.25	KN-ECG12SP4	green/ yellow	39.7x57.1x1.2 [1.56x2.25x0.05]	KN-G12SP4	10	\$4.75
KN-ECDGRY	gray	48.2x63.2x1.3 [1.90x2.49x0.05]	KN-D10 KN-D12	25	\$13.50	KN-ECT12SP4	gray	39.7x57.1x1.2 [1.56x2.25x0.05]	KN-T12SP4	25	\$12.00
KN-ECDBLU	blue			10	\$6.00	KN-ECF10	gray	27.3x59.6x1.2 [1.07x2.35x0.05]	KN-F10	25	\$14.50
KN-ECDBLK	black				\$6.00	KN-ECKBD	gray	37.1x53.5x1.2 [1.46x2.11x0.05]	KN-KDB10	10	\$6.00
KN-ECDGRN	green				\$6.00						



KONNECT-IT® Accessories

Separators

Separators are used to segment banks of terminal blocks. Allows you to maintain a single row of terminal blocks, but have separate power source clusters.

Separators Ordering Information								
Part Number	Color	Works With	Dimensions - mm [in]			Qty	Price	
			Height	Length	Thickness			
KN-ST1GRY	Gray	KN-T12 KN-T10 KN-T8 KN-T6	39.0 [1.54]	42.5 [1.67]	1.2 [0.05]	25	\$12.50	
KN-ST1BLU	Blue					10	\$4.75	
KN-ST1BLK	Black						\$4.75	
KN-ST1BRN	Brown						\$4.75	
KN-ST1GRN	Green						\$4.75	
KN-ST1ORG	Orange						\$4.75	
KN-ST1RED	Red						\$4.75	
KN-ST1WHT	White						\$4.75	
KN-ST1YEL	Yellow						\$4.75	
KN-ST2GRY	Gray	KN-T4	52.5 [2.07]	50.5 [1.99]	1.5 [0.06]	25	\$16.00	
KN-ST2BLU	Blue					10	\$16.00	
KN-ST3GRY	Gray	KN-T2	62.6 [2.46]	53.1 [2.09]	1.5 [0.06]		\$8.00	
KN-ST3BLU	Blue						\$8.00	

KN-ST1GRY



Top Covers and Label Holders

Top Covers and Label Holders Ordering Information							
Part Number	Description	Works With	Dimensions - mm [in]			Qty	Price
			Height	Length	Width		
KN-TC-1	Top cover for Konnect-It terminal block, blank, white	KN-T12 KN-T10 KN-T8 KN-T6	6.8 [0.27]	29.0 [1.14]	5.8 [0.23]	25	\$9.75
KN-TC-1S	Top cover for Konnect-It terminal block, printed electric symbol, white					25	\$14.00
KN-TC-2	Top cover for Konnect-It terminal block, blank, white	KN-T4 KN-T2	7.3 [0.29]	35.8 [1.41]	9.0 [0.35]	25	\$25.00
KN-TC-2S	Top cover for Konnect-It terminal block, printed electric symbol, white					25	\$25.00
KN-MA-1	Label holder for terminal block group. Label media not included. Adhesive label: Apply on top.	KN-EB4	46.2 [1.82]	46.0 [1.81]	11.4 [0.45]	25	\$21.50
KN-MA-1-10	Max label dimensions: 7 x 44 mm (0.28 x 1.73 in).					10	\$9.75
KN-MA-2	Label holder for terminal block group. Label media not included. Adhesive label: Apply on top.	KN-EB7	37.5 [1.48]	46.2 [1.82]	9.5 [0.37]	50	\$54.00
KN-MA-2-10	Max label dimensions: 7 x 44 mm (0.28 x 1.73 in).					10	\$12.50
KN-MA-3	Top mounting marking tag adapter for terminal block. Holds up to (4) L5x5 tags	KN-T4 KN-T2	9.3 [0.36]	36.0 [1.42]	9.0 [0.35]	25	\$14.00
KN-MA-4	Top mounting marking tag adapter for terminal block. Holds up to (4) L5x5 tags	KN-T12 KN-T10 KN-T8 KN-T6	9.0 [0.35]	29.0 [1.14]	5.7 [0.22]	25	\$12.50
KN-MA-5	Label holder for terminal block group. Label media included.	Attaches to any 35mm DIN rail	46.4 [1.83]	44.5 [1.75]	10.0 [0.39]	50	\$44.00
KN-MA-5-25	Max label dimensions: 10 x 38mm (0.39 x 1.50 in). Thickness 0.30 mm (0.01 in)					25	\$27.00

KN-MA-1



KN-MA-2



KN-MA-5



KN-TC-1 / KN-TC-2



KN-TC-1S / KN-TC-2S



KN-MA-3



KN-MA-4






KONNECT-IT® Accessories

Marking Tags 5 x 5mm

Use with any KONNECT-IT series terminal blocks.



5 x 5mm Marking Tags Ordering Information

250 Pieces per Package						500 Pieces per Package					
Part Number	Imprint	Price	Part Number	Imprint	Price	Part Number	Imprint	Price	Part Number	Imprint	Price
<u>KN-L5-BLANK-250</u>	Blank	\$11.50	<u>KN-L5-A-250</u>	A	\$11.50	<u>KN-L5-BLANK</u>	Blank	\$18.00	<u>KN-L5-A</u>	A	\$22.00
<u>KN-L5-0-250</u>	0	\$11.50	<u>KN-L5-B-250</u>	B	\$11.50	<u>KN-L5-0</u>	0	\$22.00	<u>KN-L5-B</u>	B	\$22.00
<u>KN-L5-1-250</u>	1	\$11.50	<u>KN-L5-C-250</u>	C	\$11.50	<u>KN-L5-1</u>	1	\$22.00	<u>KN-L5-C</u>	C	\$22.00
<u>KN-L5-2-250</u>	2	\$11.50	<u>KN-L5-D-250</u>	D	\$11.50	<u>KN-L5-2</u>	2	\$22.00	<u>KN-L5-D</u>	D	\$22.00
<u>KN-L5-3-250</u>	3	\$11.50	<u>KN-L5-E-250</u>	E	\$11.50	<u>KN-L5-3</u>	3	\$22.00	<u>KN-L5-E</u>	E	\$22.00
<u>KN-L5-4-250</u>	4	\$11.50	<u>KN-L5-F-250</u>	F	\$11.50	<u>KN-L5-4</u>	4	\$22.00	<u>KN-L5-F</u>	F	\$22.00
<u>KN-L5-5-250</u>	5	\$11.50	<u>KN-L5-G-250</u>	G	\$11.50	<u>KN-L5-5</u>	5	\$22.00	<u>KN-L5-G</u>	G	\$22.00
<u>KN-L5-6-250</u>	6	\$11.50	<u>KN-L5-H-250</u>	H	\$11.50	<u>KN-L5-6</u>	6	\$22.00	<u>KN-L5-H</u>	H	\$22.00
<u>KN-L5-7-250</u>	7	\$11.50	<u>KN-L5-I-250</u>	I	\$11.50	<u>KN-L5-7</u>	7	\$22.00	<u>KN-L5-I</u>	I	\$22.00
<u>KN-L5-8-250</u>	8	\$11.50	<u>KN-L5-J-250</u>	J	\$12.00	<u>KN-L5-8</u>	8	\$22.00	<u>KN-L5-J</u>	J	\$22.50
<u>KN-L5-9-250</u>	9	\$11.50	<u>KN-L5-K-250</u>	K	\$12.00	<u>KN-L5-9</u>	9	\$22.00	<u>KN-L5-K</u>	K	\$22.50
<u>KN-L5-10-250</u>	10	\$11.50	<u>KN-L5-L-250</u>	L	\$11.50	<u>KN-L5-10</u>	10	\$22.00	<u>KN-L5-L</u>	L	\$22.00
<u>KN-L5-1-10-250</u>	1-10	\$11.50	<u>KN-L5-M-250</u>	M	\$12.00	<u>KN-L5-1-10</u>	1-10	\$22.00	<u>KN-L5-M</u>	M	\$22.50
<u>KN-L5-11-20-250</u>	11-20	\$11.50	<u>KN-L5-N-250</u>	N	\$11.50	<u>KN-L5-11-20</u>	11-20	\$22.00	<u>KN-L5-N</u>	N	\$22.00
<u>KN-L5-21-30-250</u>	21-30	\$11.50	<u>KN-L5-O-250</u>	O	\$11.50	<u>KN-L5-21-30</u>	21-30	\$22.00	<u>KN-L5-O</u>	O	\$22.00
<u>KN-L5-31-40-250</u>	31-40	\$11.50	<u>KN-L5-P-250</u>	P	\$12.00	<u>KN-L5-31-40</u>	31-40	\$22.00	<u>KN-L5-P</u>	P	\$22.50
<u>KN-L5-41-50-250</u>	41-50	\$11.50	<u>KN-L5-Q-250</u>	Q	\$12.00	<u>KN-L5-41-50</u>	41-50	\$22.00	<u>KN-L5-Q</u>	Q	\$22.50
<u>KN-L5-1-50-250</u>	1-50	\$11.50	<u>KN-L5-R-250</u>	R	\$11.50	<u>KN-L5-1-50</u>	1-50	\$22.00	<u>KN-L5-R</u>	R	\$22.00
<u>KN-L5-51-100-250</u>	51-100	\$11.50	<u>KN-L5-S-250</u>	S	\$11.50	<u>KN-L5-51-100</u>	51-100	\$22.00	<u>KN-L5-S</u>	S	\$22.00
<u>KN-L5-101-150-250</u>	101-150	\$11.50	<u>KN-L5-T-250</u>	T	\$11.50	<u>KN-L5-101-150</u>	101-150	\$22.00	<u>KN-L5-T</u>	T	\$22.00
<u>KN-L5-151-200-250</u>	151-200	\$11.50	<u>KN-L5-U-250</u>	U	\$12.00	<u>KN-L5-151-200</u>	151-200	\$22.00	<u>KN-L5-U</u>	U	\$22.50
<u>KN-L5-201-250-250</u>	201-250	\$11.50	<u>KN-L5-V-250</u>	V	\$11.50	<u>KN-L5-201-250</u>	201-250	\$22.00	<u>KN-L5-V</u>	V	\$22.00
<u>KN-L5-251-300-250</u>	251-300	\$11.50	<u>KN-L5-W-250</u>	W	\$12.00	<u>KN-L5-251-300</u>	251-300	\$22.00	<u>KN-L5-W</u>	W	\$22.50
<u>KN-L5-301-350-250</u>	301-350	\$11.50	<u>KN-L5-X-250</u>	X	\$11.50	<u>KN-L5-301-350</u>	301-350	\$22.00	<u>KN-L5-X</u>	X	\$22.00
<u>KN-L5-351-400-250</u>	351-400	\$11.50	<u>KN-L5-Y-250</u>	Y	\$11.50	<u>KN-L5-351-400</u>	351-400	\$22.00	<u>KN-L5-Y</u>	Y	\$22.00
<u>KN-L5-401-450-250</u>	401-450	\$11.50	<u>KN-L5-Z-250</u>	Z	\$12.00	<u>KN-L5-401-450</u>	401-450	\$22.00	<u>KN-L5-Z</u>	Z	\$22.50
<u>KN-L5-451-500-250</u>	451-500	\$11.50	<u>KN-L5-POS-250</u>	+	\$11.50	<u>KN-L5-451-500</u>	451-500	\$22.00	<u>KN-L5-POS</u>	+	\$22.00
<u>KN-L5-L1-250</u>	L1	\$11.50	<u>KN-L5-NEG-250</u>	-	\$11.50	<u>KN-L5-L1</u>	L1	\$22.00	<u>KN-L5-NEG</u>	-	\$22.00
<u>KN-L5-L2-250</u>	L2	\$11.50	<u>KN-L5-GND-250</u>	GND	\$11.50	<u>KN-L5-L2</u>	L2	\$22.00	<u>KN-L5-GND</u>	GND	\$22.00
<u>KN-L5-L3-250</u>	L3	\$11.50				<u>KN-L5-L3</u>	L3	\$22.00			



KONNECT-IT Accessories


Marking Tags 6 x 11.5 mm

Use with Konnect-It series terminal blocks
6.5mm or wider.



Marking Tags 5 x 10mm, 6 x 10mm, 10 x 10mm

Use with Konnect-It series terminal blocks
5 x 10mm, 6 x 10mm, and 10 x 10mm.



Marking Tags 6 x 11.5mm			
Part Number	Description	Qty	Price
<u>KN-L6P5-BLNK</u>	Blank	500	\$56.00
<u>KN-L6P5-BLNK-250</u>	Blank	250	\$30.00
<u>KN-L6P5-BLNK-300</u>	Blank	300	\$15.00
<u>KN-L6P5-1-10</u>	Numbered 1-10	500	\$57.00
<u>KN-L6P5-1-10-250</u>	Numbered 1-10	250	\$31.50
<u>KN-L6P5-1-10-300</u>	Numbered 1-10	300	\$34.00
<u>KN-L6P5-11-20</u>	Numbered 11-20	500	\$57.00
<u>KN-L6P5-11-20-250</u>	Numbered 11-20	250	\$31.50
<u>KN-L6P5-11-20-300</u>	Numbered 11-20	300	\$34.00
<u>KN-L6P5-21-30</u>	Numbered 21-30	500	\$57.00
<u>KN-L6P5-21-30-250</u>	Numbered 21-30	250	\$31.50
<u>KN-L6P5-21-30-300</u>	Numbered 21-30	300	\$34.00
<u>KN-L6P5-31-40</u>	Numbered 31-40	500	\$57.00
<u>KN-L6P5-31-40-250</u>	Numbered 31-40	250	\$31.50
<u>KN-L6P5-31-40-300</u>	Numbered 31-40	300	\$34.00
<u>KN-L6P5-41-50</u>	Numbered 41-50	500	\$57.00
<u>KN-L6P5-41-50-250</u>	Numbered 41-50	250	\$31.50
<u>KN-L6P5-41-50-300</u>	Numbered 41-50	300	\$34.00
<u>KN-L6P5-51-60</u>	Numbered 51-60	500	\$57.00
<u>KN-L6P5-51-60-250</u>	Numbered 51-60	250	\$31.50
<u>KN-L6P5-51-60-300</u>	Numbered 51-60	300	\$34.00
<u>KN-L6P5-61-70</u>	Numbered 61-70	500	\$57.00
<u>KN-L6P5-61-70-250</u>	Numbered 61-70	250	\$31.50
<u>KN-L6P5-61-70-300</u>	Numbered 61-70	300	\$34.00
<u>KN-L6P5-71-80</u>	Numbered 71-80	500	\$57.00
<u>KN-L6P5-71-80-250</u>	Numbered 71-80	250	\$31.50
<u>KN-L6P5-71-80-300</u>	Numbered 71-80	300	\$34.00
<u>KN-L6P5-81-90</u>	Numbered 81-90	500	\$58.00
<u>KN-L6P5-81-90-250</u>	Numbered 81-90	250	\$32.00
<u>KN-L6P5-91-100</u>	Numbered 91-100	500	\$58.00
<u>KN-L6P5-91-100-250</u>	Numbered 91-100	250	\$32.00

Marking Tags			
Part Number*	Description	Qty	Price
<u>KN-L5X-BLNK</u>	Blank marking tag, 5 x 10mm, use with any Konnect-It terminal block series	440	\$19.50
<u>KN-L5X-BLNK-220</u>	Blank marking tag, 5 x 10mm, use with any Konnect-It terminal block series	220	\$10.50
<u>KN-L6X-BLNK</u>	Blank marking tag, 6 x 10mm, use with any Konnect-It terminal block 6mm or wider	360	\$18.50
<u>KN-L6X-BLNK-180</u>	Blank marking tag, 6 x 10mm, use with any Konnect-It terminal block 6mm or wider	180	\$9.75
<u>KN-L10X-BLNK</u>	Blank marking tag, 10 x 10mm, use with any Konnect-It terminal block 10mm or wider	200	\$26.50
<u>KN-L10X-BLNK-100</u>	Blank marking tag, 10 x 10mm, use with any Konnect-It terminal block 10mm or wider	100	\$14.50

*Does not fit any KN-T1/0xx or [KN-G1/0](#) series block

DINnectors® Accessories

Steel DIN Rail (One-Meter Length)


Features

35mm wide

- 7.5 mm-high rails primarily used to mount terminal blocks, relays, timers and small PLCs such as the BRX, CLICK, DirectLogic and Productivity series. 15mm-high rails for mounting larger and heavier components such as contactors and larger PLCs

15mm wide

- [DN-R15S1](#) exclusively for mounting mini terminal blocks such as the [DN-M10-A](#)




Steel DIN Rails Specifications

	Part Number	Qty	Price	Part Number	Qty	Price	Part Number	Qty	Price
DIN Rail	<u>DN-R35S1</u>	10	\$39.00	<u>DN-R35HS1</u>	10	\$68.00	<u>DN-R15S1</u>	10	\$36.00
	<u>DN-R35S1-2</u>	2	\$11.00	<u>DN-R35HS1-2</u>	2	\$16.50	<u>DN-R15S1-2</u>	2	\$10.00
Description	DINnector DIN rail, slotted, 35mm width, 7.5mm height, 1m length, plated steel. Package of 10.			DINnector DIN rail, slotted, 35mm width, 15mm height, 1m length, plated steel. Package of 10.			DINnector DIN rail, slotted, 15mm width, 5.5mm height, 1m length, plated steel. Package of 2.		
Plating	Zinc-plated and chromated								
International Standards	EN 60715, RoHs								
Suggested Mounting Screw Type	M6			M6			M4		


Dimensions

mm [inches]


[DN-R35S1](#)



[DN-R35HS1](#)



[DN-R15S1](#)



See our website: www.AutomationDirect.com for complete engineering drawings

DINnectors Accessories

Aluminum DIN Rail (One-Meter Length)


Features

35mm wide

- Non-anodized finish
- Terminal blocks only
- Maximum mounting screw #10-32 or M5
- Available in 1-meter standard length
- Quantity per pack: 2 or 10

Dimensions

mm [inches]




DN-R35SAL1
DN-R35SAL1-2


Features

35mm wide raised

- Non-anodized finish
- Enables users to raise terminal blocks 2¼" above the back panel
- Terminal blocks only
- Available in 1-meter standard length
- Bushing or grommet recommended for wire access hole (example Heyco UB-875 not sold by ADC)
- Quantity per pack: 2




DN-R35SAL2-2



Aluminum DIN Rails Specifications (One-Meter Length)

	Part Number	Qty	Price	Part Number	Qty	Price
DIN Rail	<u>DN-R35SAL1</u>	10	\$60.00	<u>DN-R35SAL2-2</u>	2	\$38.00
	<u>DN-R35SAL1-2</u>	2	\$16.00			
Description	DINector DIN rail, slotted, 35mm width, 10mm height, 1m length, aluminum. Package of 10.			DINector DIN rail, slotted, 2in raised 35mm width, 7.5mm height, 1m length, aluminum. Package of 2.		
International Standards	DIN 50960, RoHs					
Suggested Mounting Screw Type	#10-32 or M5					



See our website: www.AutomationDirect.com for complete engineering drawings


DINnectors® Accessories

Aluminum DIN Rail (Pre-Cut Lengths)

Features


35mm wide

- Non-anodized finish
- Terminal blocks only
- Maximum mounting screw #10-32 or M5
- Available in variable lengths (see chart)
- Quantity per pack: 5




Dimensions

mm [inches]



Aluminum DIN Rails Specifications (Pre-Cut Lengths)

Part Number	Length mm [in]	Number of Slots	Price
<u>DN-R35SAL1-072-5</u>	72 [2.83]	2	\$9.75
<u>DN-R35SAL1-143-5</u>	143 [5.63]	4	\$12.00
<u>DN-R35SAL1-215-5</u>	215 [8.46]	6	\$14.00
<u>DN-R35SAL1-286-5</u>	286 [11.26]	8	\$16.50
<u>DN-R35SAL1-358-5</u>	358 [14.09]	10	\$19.00
<u>DN-R35SAL1-429-5</u>	429 [16.89]	12	\$20.50
<u>DN-R35SAL1-500-5</u>	500 [19.69]	14	\$22.00
<u>DN-R35SAL1-572-5</u>	572 [22.52]	16	\$24.50
<u>DN-R35SAL1-644-5</u>	644 [25.35]	18	\$26.00
<u>DN-R35SAL1-715-5</u>	715 [28.15]	20	\$27.00
<u>DN-R35SAL1-787-5</u>	787 [30.98]	22	\$28.50
<u>DN-R35SAL1-858-5</u>	858 [33.78]	24	\$30.50



See our website: www.AutomationDirect.com for complete engineering drawings

 DINnectors Accessories


DIN rail support brackets

- Angled support brackets raise and tilt mounting rails 30 degrees from mounting surface for easier wiring
- [DN-ASB1](#) plated steel support bracket
- [DN-ASB2-10](#) cold-rolled steel treated with galvanic zinc plating and passivation

DIN rail mounting clips

- Snap small devices not made for mounting onto 35mm DIN rails
- Zinc-plated steel

DIN Rail Support Brackets and Mounting Clips			
Part Number	Description	Qty	Price
DN-ASB1	30° angled DIN rail support bracket (M6-1.0 screws not included)	50	\$107.00
DN-ASB2-10	30° angled DIN rail support bracket (M6-1.0 screws included)	10	\$18.00
DN-SSB25-10	1" (25mm) DIN rail support bracket (M6-1.0 screws included)	10	\$24.50
DN-SSB50-10	2" (50mm) DIN rail support bracket (M6-1.0 screws included)	10	\$25.50
DN-SSB70-10	2.75" (70mm) DIN rail support bracket (M6-1.0 screws included)	10	\$32.00
DN-SSB90-10	3.5" (90mm) DIN rail support bracket (M6-1.0 screws included)	10	\$34.50
DN-CLIP-FM4	DIN rail mounting clip with M4 x 0.7 mm threaded hole (Screws not included)	40	\$66.00
DN-CLIP-FM4-5		5	\$9.50
DN-CLIP-FM5	DIN rail mounting clip with M5 x 0.8 mm threaded hole (Screws not included)	40	\$66.00
DN-CLIP-FM5-5		5	\$9.50

[DN-ASB1](#)[DN-ASB2-10](#)[DN-SSB25-10](#)[DN-SSB50-10](#)[DN-SSB70-10](#)[DN-SSB90-10](#)
[DN-CLIP-FM4](#)
[DN-CLIP-FM4-5](#)

[DN-CLIP-FM5](#)
[DN-CLIP-FM5-5](#)