




Precision Limit Switches

High Precision Touch Limit Switches






Features

- 0.5 micron (μm) repeat accuracy
- No movement differential
- No temperature drift
- Dustproof / water-resistant (IP67)
- LED indicator
- Stainless steel housing

P085DB-AL
P10DB-A
P10DA-AL
P10DB-AL
P10DLB-AL



O indicates correct target approach and orientation.
 X indicates approach and orientation that should be avoided.



P10DHA-TML
P10DHB-TML
P10DHLTB-TML

High Precision Touch Limit Switches Selection Chart

Part Number	Price	Drawing Link	Actuator/Head Type*	Barrel Type	Barrel Diameter/Thread	Stroke	Switching Output	Contact Force	Connection Type
Straight Touch									
P085DB-AL	\$148.00	PDF	Ø 5.5mm plunger, 2mm round	Threaded	M8×0.5	3mm	(1) N.C.	1N	Cable 3m [9.8ft]
P10DB-A	\$129.00	PDF	Ø8.5mm plunger, 2mm round	Threaded	M10×0.5	3mm	(1) N.C.	1N	
P10DB-AL	\$148.00	PDF	Ø 8.5mm plunger, 2mm round	Threaded	M10×0.5	3mm	(1) N.C.	1N	
P10DA-AL	\$148.00	PDF	Ø 8.5mm plunger, 2mm round	Threaded	M10×0.5	3mm	(1) N.O.	1N	
P10DLB-AL	\$149.00	PDF	Ø 8.5mm plunger, 2mm round	Threaded	M10×0.5	10mm	(1) N.C.	1N	
Straight Touch With Ball Bearing									
P10DHA-TML	\$312.00	PDF	Ø 2.5mm plunger, 8mm roller	Threaded	M14×0.5	3mm	(1) N.O.	1N	Cable 3m [9.8ft]
P10DHB-TML	\$312.00	PDF	Ø 2.5mm plunger, 8mm roller	Threaded	M14×0.5	3mm	(1) N.C.	1N	
P10DHLTB-TML	\$343.00	PDF	Ø 2.5mm plunger, 8mm roller	Threaded	M14×0.5	10mm	(1) N.C.	1N	

* Ø = diameter, SR = surface radius

-xL: LED indicator (mounted in cable 120mm from the switch)



P085DB-AL



P10DB-A



P10DB-AL



P10DA-AL



P10DLB-AL



P10DHA-TML



P10DHB-TML



P10DHLTB-TML



Precision Limit Switches

High Precision Touch Limit Switches

High Precision Touch Limit Switches Specifications				
Series	P08	P10	P10DH	P10DHL
Environmental				
Degree of Protection	IP67			
Temperature Range	Operating: 0 to 80°C [32 to 176°F] (Ice-free)			
Mechanical Ratings				
Enclosure Material	303 Stainless Steel			
Pretravel	0*	P10DA / P10DHA: 0.2 mm P10DB / P10DHB: 0*		0*
Torque (for nuts on threaded barrels, set screws on smooth barrels)	4 N•m (2.95 lb•ft)	8 N•m (5.90 lb•ft)	10 N•m (7.38 lb•ft)	
Vibration	10–55Hz total amplitude 1.5 for X, Y, Z each direction			
Shock	300 m/s² for X, Y, Z each direction			
Repeat Accuracy	Both On–Off, Off–On: 0.0005 mm (range)**			
Recommended Minimum Operating Speed	50mm/minute			
Electrical Ratings				
Contact Life	3 million operations			
Contact Voltage	5–24VDC			
Steady Current Rating	10mA or less			
Max In-rush Current Rating	20mA without LED indicator, 10mA with LED indicator			
Connection Type	Cable: 3m Oil resistant Ø5/2 cores (P08: Ø4/2 cores), tensile strength 30N, minimum bending R7, 20AWG			
Indicating	-AL: LED indicator (mounted in cable 120mm from the switch)			

* Adjust the installed location of the switch by the signal switching point.

** At operating speed 50-200 mm/minute. Operating speed slower than 10 mm/min is not recommended.

Circuit Diagrams

Without LED	With LED (-AL models)
Normally open (N.O.)	Normally open (N.O.)
Normally closed (N.C.)	Normally closed (N.C.)