



LZE19-100A-00-10S

The LZ19 Series of LVIT (Linear Variable Inductance Transducer) position sensors are contactless devices designed for use in factory automation or assembly machinery applications where space is a premium, as well as for external mounting on pneumatic cylinders to sense rod position. The LVIT is offered in nominal full scale ranges from 2.5 to 375 mm [0.10 to 15 in] with an excellent stroke to-body-length ratio. The sensor has a 19mm [3/4 in] outside diameter stainless steel body with a 1m [3.2 ft] axial cable for I/O connections. The 6mm [0.236 in] diameter through-bore of an LZ-19 provides clearance for its 5.2 mm [0.200 in] diameter, PVDF-sheathed moving rod, which is made of the same material as its housing. This through-bore feature also means that the sensor is not subject to damage from typical mechanical overstroking.

## Features

- LVIT Technology™ (Linear Variable Inductance Transducer)
- Contactless operation prevents internal wearout from dithering or rapid cycling
- Full-scale ranges from 2.5 to 375 mm [0.10 to 15 in]
- Through-bore design eliminates mechanical overstroking
- DC in / DC out operation with built in electronics
- For applications requiring superior stroke-to-body-length ratio
- Proprietary SenSet™ field adjustable range scaling



## LZE19/LZI19 LVIT Inductive Linear Position Sensors

| Part Number                        | Price    | Drawing Link        | Stroke<br>mm [in] | Body Length<br>mm [in] | Output   | Connection<br>m [ft] | Housing Material |
|------------------------------------|----------|---------------------|-------------------|------------------------|----------|----------------------|------------------|
| <b>0-10 VDC models</b>             |          |                     |                   |                        |          |                      |                  |
| <a href="#">LZE19-2.5A-00-10S</a>  | \$333.00 | <a href="#">PDF</a> | 2.5 [0.10]        | 35.0 [1.38]            | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <a href="#">LZE19-6.4A-00-10S</a>  | \$338.00 | <a href="#">PDF</a> | 6.4 [0.25]        | 35.0 [1.38]            | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <a href="#">LZE19-12.7A-00-10S</a> | \$343.00 | <a href="#">PDF</a> | 12.7 [0.50]       | 35.0 [1.38]            | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <a href="#">LZE19-025A-00-10S</a>  | \$353.00 | <a href="#">PDF</a> | 25 [1.0]          | 35.0 [1.38]            | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <a href="#">LZE19-050A-00-10S</a>  | \$373.00 | <a href="#">PDF</a> | 50 [2.0]          | 60.5 [2.38]            | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <a href="#">LZE19-100A-00-10S</a>  | \$398.00 | <a href="#">PDF</a> | 100 [4.0]         | 111.1 [4.38]           | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <a href="#">LZE19-150A-00-10S</a>  | \$423.00 | <a href="#">PDF</a> | 150 [6.0]         | 165.1 [6.50]           | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <a href="#">LZE19-200A-00-10S</a>  | \$448.00 | <a href="#">PDF</a> | 200 [8.0]         | 215.9 [8.50]           | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <a href="#">LZE19-250A-00-10S</a>  | \$473.00 | <a href="#">PDF</a> | 250 [10.0]        | 266.7 [10.50]          | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <a href="#">LZE19-300A-00-10S</a>  | \$498.00 | <a href="#">PDF</a> | 300 [12.0]        | 317.5 [12.50]          | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <a href="#">LZE19-375A-00-10S</a>  | \$548.00 | <a href="#">PDF</a> | 375 [15.0]        | 400.0 [15.75]          | 0-10 VDC | 1 [3.2]              | Stainless steel  |
| <b>4-20 mA models</b>              |          |                     |                   |                        |          |                      |                  |
| <a href="#">LZI19-2.5A-00-20S</a>  | \$333.00 | <a href="#">PDF</a> | 2.5 [0.10]        | 35.0 [1.38]            | 4-20 mA  | 1 [3.2]              | Stainless steel  |
| <a href="#">LZI19-6.4A-00-20S</a>  | \$338.00 | <a href="#">PDF</a> | 6.4 [0.25]        | 35.0 [1.38]            | 4-20 mA  | 1 [3.2]              | Stainless steel  |
| <a href="#">LZI19-12.7A-00-20S</a> | \$343.00 | <a href="#">PDF</a> | 12.7 [0.50]       | 35.0 [1.38]            | 4-20 mA  | 1 [3.2]              | Stainless steel  |
| <a href="#">LZI19-025A-00-20S</a>  | \$353.00 | <a href="#">PDF</a> | 25 [1.0]          | 35.0 [1.38]            | 4-20 mA  | 1 [3.2]              | Stainless steel  |
| <a href="#">LZI19-050A-00-20S</a>  | \$373.00 | <a href="#">PDF</a> | 50 [2.0]          | 60.5 [2.38]            | 4-20 mA  | 1 [3.2]              | Stainless steel  |
| <a href="#">LZI19-100A-00-20S</a>  | \$398.00 | <a href="#">PDF</a> | 100 [4.0]         | 111.1 [4.38]           | 4-20 mA  | 1 [3.2]              | Stainless steel  |
| <a href="#">LZI19-150A-00-20S</a>  | \$423.00 | <a href="#">PDF</a> | 150 [6.0]         | 165.1 [6.50]           | 4-20 mA  | 1 [3.2]              | Stainless steel  |
| <a href="#">LZI19-200A-00-20S</a>  | \$448.00 | <a href="#">PDF</a> | 200 [8.0]         | 215.9 [8.50]           | 4-20 mA  | 1 [3.2]              | Stainless steel  |
| <a href="#">LZI19-250A-00-20S</a>  | \$473.00 | <a href="#">PDF</a> | 250 [10.0]        | 266.7 [10.50]          | 4-20 mA  | 1 [3.2]              | Stainless steel  |
| <a href="#">LZI19-300A-00-20S</a>  | \$498.00 | <a href="#">PDF</a> | 300 [12.0]        | 317.5 [12.50]          | 4-20 mA  | 1 [3.2]              | Stainless steel  |
| <a href="#">LZI19-375A-00-20S</a>  | \$548.00 | <a href="#">PDF</a> | 375 [15.0]        | 400.0 [15.75]          | 4-20 mA  | 1 [3.2]              | Stainless steel  |


# LZE19/LZI19 LVIT Inductive Linear Position Sensors

## LZE19/LZI19 LVIT Inductive Linear Position Sensor Specifications

|                                |   |
|--------------------------------|---|
| <b>Analog I/Os</b>             | 0–10 VDC output; 12–30V input, 35 mA max<br>4 – 20 mA (3-wire) output; 18–30V input, 60 mA max. [75° C max] |
| <b>Measuring Ranges</b>        | 2.5 to 750 mm [0.100 to 30 in] full scale   |
| <b>Linearity Error</b>         | $\leq \pm 0.15\%$ of Full Scale Output (FSO) typical, $\pm 0.25\%$ max                                      |
| <b>Resolution</b>              | 0.025% of FS  |
| <b>Update Rate</b>             | 300Hz nominal   |
| <b>Operating Temperature</b>   | Current output: -20 to +85°C; [-40 to +185°F]; Voltage output: -40 to 105°C [-40 to 221°F]                  |
| <b>Temperature Coefficient</b> | $\leq \pm 0.015\%$ of FS/C  |
| <b>Vibration</b>               | 5-20 Hz, 0.5 in peak-to-peak; 20-2000 Hz, 4.2 g peak-to-peak  |
| <b>Shock</b>                   | 1000g, 11ms   |
| <b>Terminations</b>            | IEC IP-67   |
| <b>Humidity</b>                | 95% RH, non-condensing  |
| <b>Connection</b>              | 1m [3.2 ft] cable, PUR, 28AWG   |
| <b>Mounting</b>                | M5 x 0.8 [mount for target rod]   |
| <b>Agency Approval *</b>       | CE  |

\*To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

## Wiring Diagram



## Wiring Table

| I/O Function   | Cable Color |
|----------------|-------------|
| + Power Input  | Red         |
| Ground         | Black       |
| Analog Output  | Green       |
| SenSet™        | White       |
| Shield/Drain * | Shield      |

\*Shield not connected internally