

## Smart Link I/O System

The Smart Link I/O system is a breakout wiring system used for high density I/O modules in the LS Electric XGB PLC series. The system is required for all modules with a 40-pin connection, and consists of a Smart Link cable with an XTB-40H terminal block.



Download module specific XTB-40H Terminal Label Printouts here: [Terminal Printouts](#)



Part Number	Price	Description	Length	Compatible With
<a href="#"><u>XTB-40H</u></a>	\$20.00	LS Electric XGB terminal block, 40-pin screw type. For use with LS Electric XGB series high-density modules.	n/a	All LS XGB series PLCs and modules with 40-pin connectors
<a href="#"><u>XTB-40H-LABEL</u></a>	\$3.00	AutomationDirect terminal label sheet, printed with terminal names for LS Electric XGB series modules. Package of 8. For use with XTB-40H terminal block.	n/a	
<a href="#"><u>C40HH-05SB-XBI</u></a>	\$22.00	LS Electric XGB PLC I/O cable, 1.6ft/0.5m cable length, 40-pin connector to 40-pin connector. For use with LS Electric XGB series high-density modules.	0.5 m	
<a href="#"><u>C40HH-10SB-XBI</u></a>	\$25.00	LS Electric XGB PLC I/O cable, 3.2ft/1m cable length, 40-pin connector to 40-pin connector. For use with LS Electric XGB series high-density modules.	1m	
<a href="#"><u>C40HH-15SB-XBI</u></a>	\$29.00	LS Electric XGB PLC I/O cable, 4.9ft/1.5m cable length, 40-pin connector to 40-pin connector. For use with LS Electric XGB series high-density modules.	1.5 m	
<a href="#"><u>C40HH-20SB-XBI</u></a>	\$36.00	LS Electric XGB PLC I/O cable, 6.5ft/2m cable length, 40-pin connector to 40-pin connector. For use with LS Electric XGB series high-density modules.	2m	
<a href="#"><u>C40HH-30SB-XBI</u></a>	\$42.00	LS Electric XGB PLC I/O cable, 9.8ft/3m cable length, 40-pin connector to 40-pin connector. For use with LS Electric XGB series high-density modules.	3m	

XTB-40H Specifications			
Number of Pins		40 pin	
Terminal Pitch		7.0 mm	
Connector Type		MIL-C-83503 (50P polarity guide: 2EA)	
Applicable Wires		AWG22-16 (1.5mm <sup>2</sup> /MAX)	
Insulation Resistance		100MΩ (500VDC)	
Dielectric Strength		500VAC 1 minute	
Screw		M3 x 8L	
Screw Torque		1.2N•m (12kgf•cm)	
Ambient Temperature		-10°C to +50°C (no freezing)	
Material	Case	Modified PPO	
	Protective Cover	Polycarbonate	
	PCB	Epoxy 1.6t	

## Smart Link I/O System, Terminals and Cable Connections

Module to Cable to Terminal Pinouts		
Module Pins	C40HH-xxSB-XBI	XTB-40H Terminal
B20	 <p>HIROSE HIF3BA-40D-2.54R</p> <p>HIROSE HIF3BA-40D-2.54R</p>	A1
B19		B1
B18		A2
B17		B2
B16		A3
B15		B3
B14		A4
B13		B4
B12		A5
B11		B5
B10		A6
B09		B6
B08		A7
B07		B7
B06		A8
B05		B8
B04		A9
B03		B9
B02		A10
B01		B10
A20	 <p>39 40</p> <p>1 2</p> <p>FRONT VIEW</p> <p>2 1</p> <p>40 39</p> <p>FRONT VIEW</p>	A11
A19		B11
A18		A12
A17		B12
A16		A13
A15		B13
A14		A14
A13		B14
A12		A15
A11		B15
A10		A16
A09		B16
A08		A17
A07		B17
A06		A18
A05		B18
A04		A19
A03		B19
A02		A20
A01		B20