

# Dold Relay Timers

## On-Delay Relay Timers MK Series

### Features

- 8 time ranges from 0.05 sec to 300 hr selectable via rotational switch
- Voltage range 12-240 VAC/VDC for auxiliary supply and control input
- Adjustment aid for quick setting of long time values
- Input for interruption of timing
- LED indicators for operation, contact position, and time delay
- 2 changeover contacts



**MK9906N-82-61**

### On-Delay Relay Timers MK Series

Part Number	Price	Timer Type	Timing Range	Voltage	Output Type	Drawing Link
<a href="#">MK9906N-82-61</a>	\$60.00	On-delay	0.05 seconds to 300 hours selectable	12-240 VAC/VDC	2 changeover contacts one programmable as instantaneous	<a href="#">PDF</a>

### On-Delay Relay Timers Specifications

Input Specifications	
Nominal Voltage	12-240 VAC/VDC
Nominal Consumption	12VAC ~ 1.5 VA 24VAC ~ 2VA 240VAC ~ 3VA 12VDC ~ 1W 24VDC ~ 1W 240VDC ~ 1W
Contact Specifications	
Type	2 changeover contacts one programmable as instantaneous
Contact Material	AgNi
Measured Nominal Voltage	250VAC
Switching Capacity (according to AC 15)	N.O. Contact 3A / 230VAC N.C. Contact 1A / 230VAC
Electrical Lifetime	1.5 x 10 <sup>5</sup> switching cycle (to AC 15 at 1A, 230VAC)
Switching Frequency	36,000 switching cycle / hr
Max Fuse Rating	4A
Mechanical Lifetime	≥ 30 x 10 <sup>6</sup> switching cycles
Time Circuit Specifications	
Time Ranges	8 time ranges in one unit, selectable via rotational switch 0.05 ~ 1 sec, 0.06 ~ 6 sec, 0.3 ~ 30 sec 0.03 ~ 3 min, 0.3 ~ 30 min, 3 ~ 300 min 0.3 ~ 30 hr, 3 ~ 300 hr
Time Setting	Continuous, 1:100 on relative scale
Recovery Time	24VDC 15ms 240VDC 50ms 230VAC 80ms
Repeat Accuracy	± 0.5% of selected end of scale value + 20ms
Voltage and Temperature Influence	≤ 1% with the complete operating range

### On-Delay Relay Timers Specifications

General Specifications	
Connection (cage clamp terminal)	1 x 4mm <sup>2</sup> / 12AWG solid or 1 x 2.5 mm <sup>2</sup> / 14 AWG stranded ferruled or 2 x 1.5 mm <sup>2</sup> / 16 AWG stranded ferruled or 2 x 2.5 mm <sup>2</sup> / 14 AWG solid
Tightening Torque	0.8 N·m
Ambient Temperature	-4 to +60°C [-40 to +140°F]
Storage Temperature	-40 to +70°C [-40 to +158°F]
Relative Air Humidity	93% at 40°C
Protection Rating	Housing IP40 / Terminals IP20
Vibration Resistance	Amplitude 0.35mm frequency 10 – 55Hz
Mounting	35mm Din-rail
Relay Indicator	Green LED: On, when voltage connected Yellow LED "R/t": Shows status of output relay and time delay: - Flashing (long on, short off) output relay not active; time delay - Continuously on: output relay active after time delay
Weight (g [oz])	150.0 [5.29]
Agency Approvals and Standards *	cULus, CE
UL Data	
Switching Capacity	Ambient temperature 60°C: Pilot duty B300 5A 250VAC G.P.
UL Specified Wire Connection	60°C / 75°C copper conductors only Screw terminals fixed: AWG 20 – 12 solid or stranded Torque 0.8 Nm

\*To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.