




Power Supplies - Switching CPS Ultra Series - 1-Phase



CPS2B1-240-24

Overview

The Compact Ultra series power supplies are approximately 50% smaller than standard industrial power supplies. These power supplies provide maximum efficiency to 93% in housings even smaller than the ECO line.

Features

- Compact footprint
- Aluminum housing
- 35mm DIN rail mount
- IP20 rated
- Power Boost - 150% for 5s
- 5 year warranty



Power Supplies - Switching CPS Ultra Series 1-Phase Selection Chart

Part Number	Price	Output Voltage	Output Current	Output Power	Input Voltage	Power Boost	Dimensions (W x H x D)	Drawing Link
CPS2B1-120-24	\$155.00	24VDC	5A	120W	120/240 VAC	150% for 5s	35 x 103 x 126mm [1.37 x 4.05 x 4.96 in]	PDF
CPS2B1-240-24	\$210.00		10A	240W			40 x 115 x 133mm [1.57 x 4.52 x 5.23 in]	PDF
CPS2B1-480-24	\$335.00		20A	480W			56 x 140 x 139mm [2.20 x 5.51 x 5.57 in]	PDF

Power Supplies - Switching CPS Ultra Series 1 - Phase Input Specifications

Part Number	CPS2B1-120-24	CPS2B1-240-24	CPS2B1-480-24
Operation Voltage Range	90-264 VAC 110-345 VDC		
Frequency Range	47-63Hz		
Rated Current	1.4 A @ 120VAC 0.7 A @ 240VAC	2.4 A @ 120VAC 1.2 A @ 240VAC	4.8 A @ 120VAC 2.4 A @ 240 VAC
Inrush Current	≤ 32A / 0.49 A ² s	≤ 34A / 0.66 A ² s	≤ 23A / 0.56 A ² s
Power Factor Correction	> 0.90 enabled		
Recommended Circuit Breaker	C-curve 4A	C-curve 10A	

Power Supplies - Switching CPS Ultra Series 1-Phase Output Specifications

Part Number	CPS2B1-120-24	CPS2B1-240-24	CPS2B1-480-24
Overload Limit In Constant Current Mode	7.5 A	11A	21A
Maximum Output Current	7.5 A 5s @ Hiccup mode	15A 5s @ Hiccup mode	30A 5s @ Hiccup mode 21A CC mode
Power Dissipation	< 13.5 W	< 19W	< 36.5 W
Setting Range	11.5-29 VDC	22-29 VDC	22-29 VDC
Load Regulation	≤ 1%	≤ 1%	< 1.5%
Ripple And Noise	60mV pp	≤ 260mV pp	< 150mV pp
Hold-Up Time	≥ 20ms @ 120VAC ≥ 30ms @ 240VAC	≥ 20ms @ 240VAC	> 25ms @ 240VAC
Parallel / Redundant Mode	Yes, via external decoupling diode		
Efficiency (Typical)	> 90% @ 240VAC	> 93% @ 240VAC	> 93% @ 240VAC
Short-Circuit	Hiccup mode/ Current limit	Hiccup mode/ Constant current	Adjustable, Hiccup, Constant Current
MTBF	500,000h @ 25°C ambient full load	600,000h @ 25°C ambient full load	600,000h @ 25°C ambient full load

Power Supplies - Switching

CPS Series

Power Supplies - Switching CPS 3-Phase Series General Specifications

Series	ECO Series 1-Phase	Ultra Series 1-Phase	Universal Series - 1/2/3 Phase	3-Phase Series
Overvoltage Protection	≤ 33VDC			CPSB3-120-24 <32V CPSB3-240-24 <32V CPSB3-960-24 <33VDC
Overtemperature Protection	Yes			
Status Indicators	DC ON LED (green): ≥ 21.6 V DC LOW LED (red): ≤ 21.6 V		CPSB-123-240-24 DC ON LED (green): ≥ 21.6 V DC LOW LED (red): ≥ 21.6 V CPSB-123-480-24 DC ON LED (green): ≥ 21.6 V DC LOW LED (red): $I_{out} > 1.1 I_n$	CPSB3-120-24 CPSB3-240-24 DC OK LED (green) ON $U_{out} > 95\% U_{set}$ OFF $U_{out} > 90\% U_{se}$ CPSB3-960-24 DC ON LED (green): ≥ 21.6 V DC LOW LED (red): ≥ 21.6 V
Humidity	5 to 95%, non-condensing			
Vibration	IEC 60068-2-6			
Shock	IEC 60068-2-27			
Protection Rating	IP20			
Mounting	35mm DIN rail (vertical)			
Housing Material	Aluminum (enclosed)			
Agency Approval	CE, UKCA, cULus E249179			

Additional Data

Part Number	Weight kg [lb]	Operating Temperature	Storage Temperature	Terminal Type	Solid Wire Size*		Tightening Torque
					Output	Input	
CPSB1-120-24E	0.45 [0.99]	-40 to 70°C [-40 to 158°F]	-40 to 80°C [-40 to 176°F]	Screw	0.20 – 2.5 mm ² [AWG 24-14]	0.20 – 2.5 mm ² [AWG 24-14]	0.5 – 0.6 N•m [4.42 – 5.30 lb•ft]
CPSB1-240-24E	0.75 [1.65]						
CPSB1-480-24E	1 [2.20]						
CPS2B1-120-24	0.45 [0.99]	-35 to 70°C [-31 to 158°F]	-40 to 80°C [-40 to 176°F]	Screw	0.20 – 2.5 mm ² [AWG 24-14]	0.20 – 2.5 mm ² [AWG 24-14]	0.5 – 0.6 N•m [4.42 – 5.30 lb•ft]
CPS2B1-240-24	0.75 [1.65]						
CPS2B1-480-24	1.1 [2.42]						
CPSB-123-240-24	0.65 [1.43]	-40 to 70°C [-40 to 158°F]	-40 to 80°C [-40 to 176°F]	Screw	0.20 – 2.5 mm ² [AWG 30-12]	0.20 – 2.5 mm ² [AWG 30-12]	0.5 – 0.6 N•m [4.42 – 5.30 lb•ft]
CPSB-123-480-24	1 [2.20]				0.20 – 2.5 mm ² [AWG 24-14]	0.20 – 2.5 mm ² [AWG 24-14]	
CPSB3-120-24	0.66 [1.45]	-25 to 70°C [-13 to 158°F]	-40 to 85°C [-40 to 185°F]	Push-in	0.20 – 2.5 mm ²	0.20 – 2.5 mm ²	–
CPSB3-240-24	0.78 [1.71]				0.20 – 2.5 mm ²	0.20 – 2.5 mm ²	–
CPSB3-960-24	1.3 [2.86]	-40 to 70°C [-40 to 158°F]	-40 to 80°C [-40 to 176°F]	Screw	0.20 – 10mm ² [AWG 24-14]	0.20 – 10mm ² [AWG 24-14]	max. 62 N•m

* For other types of wire please see the insert.