

Disconnect Handle Applications for Disconnect Enclosures

Designed to house the following available at AutomationDirect.com

- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F_S0_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C**
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft)
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9F0CA-15A, BW9F0CA-20A, BW9F0GA-15A, BW9F0GA-20A, BW9F0HA-15A, BW9F0HA-20A, BW9F0JA-15A, and BW9F0JA-20A.**
- Gladiator Molded Case Circuit Breakers (MCCBs) flange mounted cable operator and handles. See Gladiator sections for handles and cable options. **GCBX1-FHC-N3R4-M, GCBX1-FHC-N4X-M, GCBX5-FHC-N3R4-M, and GCBX5-FHC-N4X-M**

Available at AutomationDirect.com

Disconnect Enclosure Series	AutomationDirect F_S0_C Series	Socomec 37299002 and 37299003	Fuji BW9F series	Gladiator GCBX
N412_CD Series	✓	✓	✓	✓
N412_CDSS Series	✓	✓	✓	✓
N412_CDSSA Series	✓	✓	✓	✓
N412_CSTD Series	✓	✓	✓	✓
N412_CSSSTD Series	✓	✓	✓	✓
SDN_PL Series	✓	✓	✓	✓
SN4 Series	✓	✓	✓	✓
ABN12 Series	✗	✗	✗	✗
SSN4X Series	✓	✓	✓	✓
SSN4X_A Series	✓	✓	✓	✓
WRD-XM_FS4 Series	✓	✓	✓	✓
WRD-XM_FSD4 Series	✓	✓	✓	✓

Designed to house other brands

- Allen-Bradley** Bulletin 1494V and 140U disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. These enclosures will not accept Allen-Bradley Bulletin 1494F disconnect devices or Bulletin 1494D circuit breaker operators
- ABB Controls** flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable depth
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers
- General Electric** Type STDA flange handles and variable depth operating
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices.

Other Brands

Disconnect Enclosures Series	Square D 9422 series	Allen-Bradley 1494F and 1494D series	Allen-Bradley 1494V, 1494C, 140U, 194RC series	ABB Controls	Eaton/Cutler-Hammer C361 and C371 series	General Electric STDA series	Siemens I-T-E Max-Flex Series
N412_CD Series	✓	✗	✓	✓	✓	✓	✓
N412_CDSS Series	✓	✗	✓	✓	✓	✓	✓
N412_CDSSA Series	✓	✗	✓	✓	✓	✓	✓
N412_CSTD Series	✓	✗	✓	✓	✓	✓	✓
N412_CSSSTD Series	✓	✗	✓	✓	✓	✓	✓
SDN_PL Series	✓	✗	✓	✓	✓	✓	✓
SN4 Series	✓	✗	✓	✓	✓	✓	✓
ABN12 Series	✗	✓	✗	✗	✗	✗	✗
SSN4X Series	✓	✗	✓	✓	✓	✓	✓
SSN4X_A Series	✓	✗	✓	✓	✓	✓	✓
WRD-XM_FS4 Series	✓	✗	✓	✓	✓	✓	✓
WRD-XM_FSD4 Series	✓	✗	✓	✓	✓	✓	✓

NEMA 12 and 13 Single-Door Wall-Mount Right-Flanged Disconnect with Handle



Construction

- 14-gauge steel bodies and doors
- Plasma welded seams
- Rolled lip around all sides of opening keeps out liquids and contaminants
- Remove doors easily by pulling continuous hinge pin
- Polyurethane poured-in-place gasket
- External mounting feet
- Collar studs for mounting optional subpanel
- Ground stud in door
- Instructions provided for locating and installing disconnect switches, circuit breakers and operating mechanisms
- Enclosures provided with padlocking, defeater handle and latching system

Finish


- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized panels are a conductive finish (unpainted)

Listings

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13



Dimensions



Notes: Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

4.50in [114mm] Handle and latching hardware are included.

Make sure the disconnect device you are using will fit the enclosure size you choose.

NOTES:

1. SUBPANELS ARE MADE FROM 12 GA STEEL.
2. SUBPANELS HAVE FLANGES ALONG ALL SIDES WHEN EITHER DIMENSION EXCEEDS 17".
3. CATALOG NUMBER SDN12603812A HAS A LARGER CUTOUT IN THE ENCLOSURE FLANGE TO ACCOMMODATE ALLEN-BRADLEY 1494V-H2 AND I-T-E FHOHN OPERATING HANDLES.

NEMA 12 and 13 Single-Door Wall-Mount Right-Flanged Disconnect with Handle



NEMA 12 and 13 Single-Door Wall-Mount Right-Flanged Disconnect with Handle

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Stainless Steel Subpanel
<u>SDN12202108PL</u>	\$662.00	20.00 x 21.38 x 8.88 [508 x 543 x 226]	<u>NP2020</u>	<u>NP2020SS</u>
<u>SDN12242108PL</u>	\$701.00	24.00 x 21.38 x 8.88 [610 x 543 x 226]	<u>NP2420</u>	<u>NP2420SS</u>
<u>SDN12242510PL</u>	\$782.00	24.00 x 25.38 x 10.88 [610 x 645 x 276]	<u>NP2424</u>	<u>NP2420SS</u>
<u>SDN12302510PL</u>	\$855.00	30.00 x 25.38 x 10.88 [762 x 645 x 276]	<u>NP3024</u>	<u>NP3024SS</u>
<u>SDN12302612PL</u>	\$894.00	30.00 x 25.38 x 12.88 [762 x 645 x 327]	<u>NP3024</u>	<u>NP3024SS</u>
<u>SDN12362508PL</u>	\$860.00	36.00 x 25.38 x 8.88 [914 x 645 x 226]	<u>NP3624</u>	<u>NP3624SS</u>
<u>SDN12362510PL</u>	\$928.00	36.00 x 25.38 x 10.88 [914 x 645 x 276]	<u>NP3624</u>	<u>NP3624SS</u>
<u>SDN12363108PL</u>	\$980.00	36.00 x 31.38 x 8.88 [914 x 797 x 226]	<u>NP3630</u>	<u>NP3630SS</u>
<u>SDN12363212PL</u>	\$1,075.00	36.00 x 31.37 x 12.88 [914 x 797 x 327]	<u>NP3630</u>	<u>NP3630SS</u>
<u>SDN12423108PL</u>	\$1,062.00	42.00 x 31.38 x 8.88 [1067 x 797 x 226]	<u>NP4230</u>	<u>NP4230SS</u>
<u>SDN12423110PL</u>	\$1,112.00	42.00 x 31.38 x 10.88 [1067 x 797 x 276]	<u>NP4230</u>	<u>NP4230SS</u>
<u>SDN12423708PL</u>	\$1,123.00	42.00 x 37.37 x 8.88 [1067 x 949 x 226]	<u>NP4236</u>	<u>NP4236SS</u>
<u>SDN12423812PL</u>	\$1,283.00	42.00 x 37.37 x 12.88 [1067 x 949 x 327]	<u>NP4236</u>	<u>NP4236SS</u>
<u>SDN12483710PL</u> **	\$1,325.00	48.00 x 37.38 x 10.88 [1219 x 949 x 276]	<u>NP4836</u>	<u>NP4836SS</u>
<u>SDN12483812PL</u> **	\$1,389.00	48.00 x 37.38 x 12.88 [1219 x 949 x 327]	<u>NP4836</u>	<u>NP4836SS</u>
<u>SDN12483816PL</u> **	\$1,511.00	48.00 x 37.38 x 16.88 [1219 x 949 x 429]	<u>NP4836</u>	<u>NP4836SS</u>
<u>SDN12603710PL</u> **	\$1,456.00	60.00 x 37.38 x 10.88 [1524 x 949 x 276]	<u>NP6036</u>	<u>NP6036SS</u>
<u>SDN12603808PL</u> **	\$1,501.00	60.00 x 37.38 x 8.88 [1524 x 949 x 226]	<u>NP6036</u>	<u>NP6036SS</u>
<u>SDN12603812PL</u> **	\$1,594.00	60.00 x 37.38 x 12.88 [1524 x 949 x 327]	<u>NP6036</u>	<u>NP6036SS</u>

Note: Subpanels must be ordered separately.

Dimensions in inches [millimeters].

**These enclosures have a closed-cell neoprene gasket, not poured-in-place.

Note: Enclosures 12 in [305 mm] and 16 in [152 mm] deep can be modified to accept I-T-E Siemens 800 amp and 1200 amp circuit breakers. (When using an I-T-E Siemens circuit breaker and an enclosure with an "H" dimension of 30", 36 in [914 mm] or 42 in [1067 mm], verify the amount of wire bend space required for both the line and load sides.)

Enclosure Subpanels




Subpanels for NEMA 1, 12, 4 and 4X Wall-Mount Enclosures and WC9 NEMA 12 Operator Consoles

- 12-gauge steel (perforated subpanels are 14-gauge)
- Subpanels with any side over 17 in [432 mm] have 0.25 in [6mm] flange on all sides
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint) Panels listed fit the following enclosures:
- NEMA 1 large (N1C, 42 in [1067 mm] width and wider)
- NEMA 12 single door wall-mount (N12)
- NEMA 12 two-door wall-mount (WA_WF)
- NEMA 12 single door flush wall-mount (WA_FM)
- NEMA 4 (N4) and 4X (SSN) single door wall-mount
- NEMA 12 operator consoles (WC9)
- NEMA 12 Wall Disconnect (SDN12_PL and ABN12)
- NEMA 4 and 4X Wall-Mount Disconnect (SSN4 and SSN4X)



Note: Use NPxxxx subpanels in NEMA 1, NEMA 4 and 4X, and NEMA 12 enclosures only. Do NOT use NPxxxx subpanels in N412 Ultimate Series enclosures with a C in the suffix.

Dimensions



NOTE:
SUBPANELS LARGER THAN
20 X 20 HAVE (2) 0.31"
GROUND HOLES.

Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25 in [6 mm] spacing.

Enclosure Subpanels



Subpanels for NEMA 1, 12, 4 and 4X Wall-Mount Enclosures and WC9 NEMA 12 Operator Consoles

<i>Painted Steel</i>	<i>Price</i>	<i>Galvanized</i>	<i>Price</i>	<i>304 Stainless Steel</i>	<i>Price</i>	<i>Nominal Enclosure Size HxW</i>	<i>Subpanel Size AxB</i>
<u>NP1212</u>	\$18.50	—	—	—	—	12 x 12	9.00 x 9.00 [229 x 229]
<u>NP1224</u>	\$45.50	—	—	—	—	24 x 12	9.00 x 21.00 [229 x 533]
<u>NP1612</u>	\$33.00	—	—	<u>NP1612SS</u>	\$87.00	12 x 16 16 x 12	13.00 x 9.00 [330 x 229]
<u>NP1616</u>	\$40.50	—	—	<u>NP1616SS</u>	\$106.00	16 x 16	13.00 x 13.00 [330 x 330]
<u>NP2012</u>	\$38.00	—	—	—	—	20 x 12	17.00 x 9.00 [432 x 229]
<u>NP2016</u>	\$48.00	—	—	<u>NP2016SS</u>	\$128.00	20 x 16	17.00 x 13.00 [432 x 330]
<u>NP2020</u>	\$58.00	—	—	<u>NP2020SS</u>	\$165.00	20 x 20	17.00 x 17.00 [432 x 432]
<u>NP2416</u>	\$56.00	—	—	<u>NP2416SS</u>	\$159.00	24 x 16	21.00 x 13.00 [533 x 330]
<u>NP2420</u>	\$75.00	—	—	<u>NP2420SS</u>	\$200.00	24 x 20	21.00 x 17.00 [533 x 432]
<u>NP2424</u>	\$86.00	—	—	<u>NP2424SS</u>	\$233.00	24 x 24	21.00 x 21.00 [533 x 533]
<u>NP3016</u>	\$75.00	—	—	—	—	30 x 16	27.00 x 13.00 [686 x 330]
<u>NP3020</u>	\$90.00	—	—	<u>NP3020SS</u>	\$268.00	30 x 20	27.00 x 17.00 [686 x 432]
<u>NP3024</u>	\$105.00	—	—	<u>NP3024SS</u>	\$283.00	24 x 30 30 x 24	27.00 x 21.00 [686 x 533]
<u>NP3030</u>	\$147.00	—	—	<u>NP3030SS</u>	\$452.00	30 x 30	27.00 x 27.00 [686 x 686]
<u>NP3624</u>	\$125.00	—	—	<u>NP3624SS</u>	\$386.00	36 x 24	33.00 x 21.00 [838 x 533]
<u>NP3630</u>	\$167.00	—	—	<u>NP3630SS</u>	\$443.00	30 x 36 36 x 30	33.00 x 27.00 [838 x 686]
<u>NP3636</u>	\$196.00	—	—	<u>NP3636SS</u>	\$535.00	36 x 36	33.00 x 33.00 [838 x 838]
<u>NP4024</u>	\$151.00	—	—	—	—	40 x 24	37.00 x 21.00 [940 x 533]
<u>NP4224</u>	\$144.00	—	—	—	—	42 x 24	39.00 x 21.00 [991 x 533]
<u>NP4230</u>	\$191.00	—	—	<u>NP4230SS</u>	\$563.00	42 x 30	39.00 x 27.00 [991 x 686]
<u>NP4236</u>	\$225.00	—	—	<u>NP4236SS</u>	\$676.00	42 x 36	39.00 x 33.00 [991 x 838]
<u>NP4824</u>	\$163.00	—	—	—	—	48 x 24	45.00 x 21.00 [1143 x 533]
<u>NP4830</u>	\$215.00	—	—	—	—	48 x 30	45.00 x 27.00 [1143 x 686]
<u>NP4836</u>	\$254.00	—	—	<u>NP4836SS</u>	\$731.00	48 x 36	45.00 x 33.00 [1143 x 838]
<u>NP6030</u>	\$263.00	—	—	—	—	60 x 30	57.00 x 27.00 [1448 x 686]
<u>NP6036</u>	\$313.00	—	—	<u>NP6036SS</u>	\$965.00	60 x 36	57.00 x 33.00 [1448 x 838]
<u>NP7230</u>	\$302.00	<u>NP7230G</u>	\$327.00	—	—	72 x 30	69.00 x 27.00 [1753 x 686]
<u>NP7236</u>	\$371.00	<u>NP7236G</u>	\$402.00	—	—	72 x 36	69.00 x 33.00 [1753 x 838]

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.

Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions in this table.