

NEMA 12 and 13 Hinged Screw Cover Wall-Mount



Applications

Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes or electrical junction boxes. Provides protection from dirt, dust, oil and water.

Construction

- Bodies and doors fabricated from 14-gauge steel
- Lids are sealed with closed-cell oil-resistant neoprene gasket
- Continuously-welded seams ground smooth, less knockouts of holes
- Captive door screws thread into sealed wells
- Grounding provisions provided
- Weldnuts are provided for mounting optional subpanel
- No mounting feet or mounting holes are provided

Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings

- UL 50, 12 and 13 [UL File E6924]
- NEMA/EEMAC 12 and 13
- JIC EL-1-71



NEMA 12 and 13 Hinged Screw Cover Wall-Mount


Part Number	Price	Enclosure SizeHxWxD	Painted Steel Subpanel
<u>WA060604GIE</u>	\$89.00	6.31 x 6.31 x 4.15 [160 x 160 x 105]	<u>N1P0606</u>
<u>WA080604GIE</u>	\$98.00	8.31 x 6.31 x 4.15 [211 x 160 x 105]	<u>N1P0608</u>
<u>WA080804GIE</u>	\$100.00	8.31 x 8.31 x 4.15 [211 x 211 x 105]	<u>N1P0808</u>
<u>WA080806GIE</u>	\$107.00	8.31 x 8.31 x 6.15 [211 x 211 x 156]	<u>N1P0808</u>
<u>WA100804GIE</u>	\$97.00	10.31 x 8.31 x 4.15 [262 x 211 x 105]	<u>N1P0810</u>
<u>WA100806GIE</u>	\$113.00	10.31 x 8.31 x 6.15 [262 x 211 x 156]	<u>N1P0810</u>
<u>WA101006GIE</u>	\$121.00	10.31 x 10.31 x 6.15 [262 x 262 x 156]	<u>N1P1010</u>
<u>WA121004GIE</u>	\$116.00	12.31 x 10.31 x 4.15 [313 x 262 x 105]	<u>N1P1012</u>
<u>WA121006GIE</u>	\$126.00	12.31 x 10.31 x 6.15 [313 x 262 x 156]	<u>N1P1012</u>
<u>WA121206GIE</u>	\$142.00	12.31 x 12.31 x 6.15 [313 x 313 x 156]	<u>N1P1212</u>
<u>WA141206GIE</u>	\$154.00	14.31 x 12.31 x 6.15 [363 x 313 x 156]	<u>N1P1214</u>

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters]
Letters in table correspond to letters on dimensional drawings.

NEMA 12 and 13 Hinged Screw Cover Wall-Mount



Dimensions



NOTES:

1. PANELS ARE 14GA STEEL.
2. PANEL SCREWS ARE #10-32 PAN HEAD.

Enclosure Subpanels




Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures

- 14-gauge
- Painted steel and perforated subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized panels have a conductive finish (no paint)
- Panels listed fit the following enclosures:
 - NEMA 1 small (N1C)
 - NEMA 3R small (RHC)
 - NEMA 12 WA_GIE



Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures			
Painted Steel	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
<u>N1P0606</u>	\$5.25	6 x 6	4.25 x 4.25 [108 x 108]
<u>N1P0608</u>	\$6.25	6 x 8	6.25 x 4.25 [159 x 108]
<u>N1P0808</u>	\$7.25	8 x 8	6.25 x 6.25 [159 x 159]
<u>N1P0810</u>	\$8.50	8 x 10	8.25 x 6.25 [210 x 159]
<u>N1P1010</u>	\$10.00	10 x 10	8.25 x 8.25 [210 x 210]
<u>N1P1012</u>	\$11.50	10 x 12	10.25 x 8.25 [260 x 210]
<u>N1P1212</u>	\$13.75	12 x 12	10.25 x 10.25 [260 x 260]
<u>N1P1214</u>	\$15.50	12 x 14	12.25 x 10.25 [311 x 260]
<u>N1P1216</u>	\$17.50	12 x 16	14.25 x 10.25 [362 x 260]
<u>N1P1220</u>	\$24.00	12 x 20	18.25 x 10.25 [464 x 260]
Notes: Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawing.			

Dimensions



Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25in [6 mm] spacing.