

# Subpanels and Swing-out Panels for NEMA 3, 3R, 4, and 12 Freestanding Single-Door Enclosures



Subpanels for NEMA 3, 3R, 4, and 12 Freestanding Single-Door Enclosures				
Enclosures	Full Height Subpanels		Half Height Subpanels	
	Painted Steel	Galvanized	Painted Steel	Galvanized
<u>WRD602418FS4</u>	<u>WA60P24F1</u>	—	<u>WA60P24F2</u>	—
<u>WRD603624FS4</u>	<u>WA60P36F1</u>	<u>WA60P36F1G</u>	<u>WA60P36F2</u>	<u>WA60P36F2G</u>
<u>WRD722418FS4</u>	<u>WA72P24F1</u>	<u>WA72P24F1G</u>	—	—
<u>WRD723018FS4</u>	<u>WA72P30F1</u>	<u>WA72P30F1G</u>	—	—
<u>WRD723618FS4</u>	<u>WA72P36F1</u>	<u>WA72P36F1G</u>	—	—
<u>WRD723630FS4</u>	<u>WA72P36F1</u>	<u>WA72P36F1G</u>	—	—
<u>WRD723636FS4</u>	<u>WA72P36F1</u>	<u>WA72P36F1G</u>	—	—
<u>WRD903620FS4</u>	<u>WA90P36F1</u>	<u>WA90P36F1G</u>	—	—
<u>WRD903636FS4</u>	<u>WA90P36F1</u>	<u>WA90P36F1G</u>	—	—


# Subpanels and Swing-out Panels for NEMA 3, 3R, 4, and 12 Freestanding Single-Door Enclosures



## Side-Mount Panels for NEMA 3, 3R, 4, and 12 Freestanding Single-Door Enclosures

Enclosures	Side-Mount Panels	
	Painted Steel	
<u><a href="#">WRD722418FS4</a></u>	<u><a href="#">WA72SMP14</a></u>	
<u><a href="#">WRD723018FS4</a></u>	<u><a href="#">WA72SMP14</a></u>	
<u><a href="#">WRD723618FS4</a></u>	<u><a href="#">WA72SMP14</a></u>	
<u><a href="#">WRD723630FS4</a></u>	<u><a href="#">WA72SMP14</a></u>	<u><a href="#">WA72SMP20</a></u>
<u><a href="#">WRD723636FS4</a></u>	<u><a href="#">WA72SMP14</a></u>	<u><a href="#">WA72SMP20</a></u>

# WA-F1/F2 Panels for Single-Door Freestanding Enclosures




## Description

- Panels for single-door single-access and single-door dual-access, freestanding NEMA 12, and freestanding NEMA 4 enclosures
- Can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with other freestanding accessories


Painted Steel	Price	Galvanized	Price	Steel Gauge	Panel Size HxW	Subpanel Type
<a href="#">WA60P24F1</a>	\$342.00	–	–	12	48.00 x 20.00 [1219 x 508]	Full
<a href="#">WA60P24F2</a>	\$246.00	–	–	10	24.88 x 20.00 [632 x 508]	Half
<a href="#">WA60P36F1</a>	\$441.00	<a href="#">WA60P36F1G</a>	\$441.00	12	48.00 x 32.00 [1219 x 813]	Full
<a href="#">WA60P36F2</a>	\$278.00	<a href="#">WA60P36F2G</a>	\$278.00	12	24.88 x 32.00 [632 x 813]	Half
<a href="#">WA72P24F1</a>	\$383.00	<a href="#">WA72P24F1G</a>	\$383.00	12	60.00 x 20.00 [1524 x 508]	Full
<a href="#">WA72P30F1</a>	\$445.00	<a href="#">WA72P30F1G</a>	\$482.00	12	60.00 x 26.00 [1524 x 660]	Full
<a href="#">WA72P36F1</a>	\$507.00	<a href="#">WA72P36F1G</a>	\$507.00	12	60.00 x 32.00 [1524 x 813]	Full
<a href="#">WA90P24F1</a>	\$445.00	<a href="#">WA90P24F1G</a>	\$445.00	12	78.00 x 20.00 [1981 x 508]	Full
<a href="#">WA90P36F1</a>	\$607.00	<a href="#">WA90P36F1G</a>	\$607.00	12	78.00 x 32.00 [1981 x 813]	Full

Notes: Dimensions in inches [millimeters].  
 Letters in table correspond to letters on dimensional drawing.  
 If used in a two-door enclosure, a center panel support must be ordered.  
 Suffix F1= full panel, F2 = half panel

## Dimensions



# WA-SMP Series Side-Mount Panels for Freestanding Enclosures



## Description

- Panels for freestanding NEMA 4 and freestanding NEMA 12 enclosures
- Panels are fabricated from 12-gauge steel
- They provide extra mounting space on the sides of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Panels attach securely to mounting channels

Painted Steel	Price	Panel Size AxB
<b>WA72SMP14</b>	\$236.00	60.00 x 14.00 [1524 x 356]
<b>WA72SMP20</b>	\$288.00	60.00 x 20.00 [1524 x 508]

Note: Dimensions in inches [millimeters].

## Dimensions

