

# Disconnect Handle Applications for Disconnect Enclosures

Designed to house the following available at AutomationDirect.com

- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F\_S0\_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C**
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft)
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9F0CA-15A, BW9F0CA-20A, BW9F0GA-15A, BW9F0GA-20A, BW9F0HA-15A, BW9F0HA-20A, BW9F0JA-15A, and BW9F0JA-20A.**
- Gladiator Molded Case Circuit Breakers (MCCBs) flange mounted cable operator and handles. See Gladiator sections for handles and cable options. **GCBX1-FHC-N3R4-M, GCBX1-FHC-N4X-M, GCBX5-FHC-N3R4-M, and GCBX5-FHC-N4X-M**

Available at AutomationDirect.com

Disconnect Enclosure Series	AutomationDirect F_S0_C Series	Socomec 37299002 and 37299003	Fuji BW9F series	Gladiator GCBX
<b>N412_CD Series</b>	✓	✓	✓	✓
<b>N412_CDSS Series</b>	✓	✓	✓	✓
<b>N412_CDSSA Series</b>	✓	✓	✓	✓
<b>N412_CSTD Series</b>	✓	✓	✓	✓
<b>N412_CSSSTD Series</b>	✓	✓	✓	✓
<b>SDN_PL Series</b>	✓	✓	✓	✓
<b>SN4 Series</b>	✓	✓	✓	✓
<b>ABN12 Series</b>	✗	✗	✗	✗
<b>SSN4X Series</b>	✓	✓	✓	✓
<b>SSN4X_A Series</b>	✓	✓	✓	✓
<b>WRD-XM_FS4 Series</b>	✓	✓	✓	✓
<b>WRD-XM_FSD4 Series</b>	✓	✓	✓	✓

## Designed to house other brands

- Allen-Bradley** Bulletin 1494V and 140U disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. These enclosures will not accept Allen-Bradley Bulletin 1494F disconnect devices or Bulletin 1494D circuit breaker operators
- ABB Controls** flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable depth
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers
- General Electric** Type STDA flange handles and variable depth operating
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices.

Disconnect Enclosures Series	Other Brands						
	Square D 9422 series	Allen-Bradley 1494F and 1494D series	Allen-Bradley 1494V, 1494C, 140U, 194RC series	ABB Controls	Eaton/Cutler-Hammer C361 and C371 series	General Electric STDA series	Siemens I-T-E Max-Flex Series
<b>N412_CD Series</b>	✓	✗	✓	✓	✓	✓	✓
<b>N412_CDSS Series</b>	✓	✗	✓	✓	✓	✓	✓
<b>N412_CDSSA Series</b>	✓	✗	✓	✓	✓	✓	✓
<b>N412_CSTD Series</b>	✓	✗	✓	✓	✓	✓	✓
<b>N412_CSSSTD Series</b>	✓	✗	✓	✓	✓	✓	✓
<b>SDN_PL Series</b>	✓	✗	✓	✓	✓	✓	✓
<b>SN4 Series</b>	✓	✗	✓	✓	✓	✓	✓
<b>ABN12 Series</b>	✗	✓	✗	✗	✗	✗	✗
<b>SSN4X Series</b>	✓	✗	✓	✓	✓	✓	✓
<b>SSN4X_A Series</b>	✓	✗	✓	✓	✓	✓	✓
<b>WRD-XM_FS4 Series</b>	✓	✗	✓	✓	✓	✓	✓
<b>WRD-XM_FSD4 Series</b>	✓	✗	✓	✓	✓	✓	✓

# Enclosure Subpanels




## Subpanels for NEMA 1, 12, 4 and 4X Wall-Mount Enclosures and WC9 NEMA 12 Operator Consoles

- 12-gauge steel (perforated subpanels are 14-gauge)
- Subpanels with any side over 17 in [432 mm] have 0.25 in [6mm] flange on all sides
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint) Panels listed fit the following enclosures:
- NEMA 1 large (N1C, 42 in [1067 mm] width and wider)
- NEMA 12 single door wall-mount (N12)
- NEMA 12 two-door wall-mount (WA\_WF)
- NEMA 12 single door flush wall-mount (WA\_FM)
- NEMA 4 (N4) and 4X (SSN) single door wall-mount
- NEMA 12 operator consoles (WC9)
- NEMA 12 Wall Disconnect (SDN12\_PL and ABN12)
- NEMA 4 and 4X Wall-Mount Disconnect (SSN4 and SSN4X)



Note: Use NPxxxx subpanels in NEMA 1, NEMA 4 and 4X, and NEMA 12 enclosures only. Do NOT use NPxxxx subpanels in N412 Ultimate Series enclosures with a C in the suffix.

## Dimensions



NOTE:  
SUBPANELS LARGER THAN  
20 X 20 HAVE (2) 0.31"  
GROUND HOLES.

Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25 in [6 mm] spacing.

# Enclosure Subpanels



Subpanels for NEMA 1, 12, 4 and 4X Wall-Mount Enclosures and WC9 NEMA 12 Operator Consoles							
<i>Painted Steel</i>	<i>Price</i>	<i>Galvanized</i>	<i>Price</i>	<i>304 Stainless Steel</i>	<i>Price</i>	<i>Nominal Enclosure Size HxW</i>	<i>Subpanel Size AxB</i>
<a href="#"><u>NP1212</u></a>	\$19.50	—	—	—	—	12 x 12	9.00 x 9.00 [229 x 229]
<a href="#"><u>NP1224</u></a>	\$48.00	—	—	—	—	24 x 12	9.00 x 21.00 [229 x 533]
<a href="#"><u>NP1612</u></a>	\$34.50	—	—	<a href="#"><u>NP1612SS</u></a>	\$80.00	12 x 16 16 x 12	13.00 x 9.00 [330 x 229]
<a href="#"><u>NP1616</u></a>	\$42.50	—	—	<a href="#"><u>NP1616SS</u></a>	\$97.00	16 x 16	13.00 x 13.00 [330 x 330]
<a href="#"><u>NP2012</u></a>	\$40.00	—	—	—	—	20 x 12	17.00 x 9.00 [432 x 229]
<a href="#"><u>NP2016</u></a>	\$51.00	—	—	<a href="#"><u>NP2016SS</u></a>	\$117.00	20 x 16	17.00 x 13.00 [432 x 330]
<a href="#"><u>NP2020</u></a>	\$61.00	—	—	<a href="#"><u>NP2020SS</u></a>	\$151.00	20 x 20	17.00 x 17.00 [432 x 432]
<a href="#"><u>NP2416</u></a>	\$59.00	—	—	<a href="#"><u>NP2416SS</u></a>	\$145.00	24 x 16	21.00 x 13.00 [533 x 330]
<a href="#"><u>NP2420</u></a>	\$79.00	—	—	<a href="#"><u>NP2420SS</u></a>	\$183.00	24 x 20	21.00 x 17.00 [533 x 432]
<a href="#"><u>NP2424</u></a>	\$91.00	—	—	<a href="#"><u>NP2424SS</u></a>	\$213.00	24 x 24	21.00 x 21.00 [533 x 533]
<a href="#"><u>NP3016</u></a>	\$78.00	—	—	—	—	30 x 16	27.00 x 13.00 [686 x 330]
<a href="#"><u>NP3020</u></a>	\$95.00	—	—	<a href="#"><u>NP3020SS</u></a>	\$245.00	30 x 20	27.00 x 17.00 [686 x 432]
<a href="#"><u>NP3024</u></a>	\$110.00	—	—	<a href="#"><u>NP3024SS</u></a>	\$258.00	24 x 30 30 x 24	27.00 x 21.00 [686 x 533]
<a href="#"><u>NP3030</u></a>	\$155.00	—	—	<a href="#"><u>NP3030SS</u></a>	\$414.00	30 x 30	27.00 x 27.00 [686 x 686]
<a href="#"><u>NP3624</u></a>	\$132.00	—	—	<a href="#"><u>NP3624SS</u></a>	\$353.00	36 x 24	33.00 x 21.00 [838 x 533]
<a href="#"><u>NP3630</u></a>	\$175.00	—	—	<a href="#"><u>NP3630SS</u></a>	\$405.00	30 x 36 36 x 30	33.00 x 27.00 [838 x 686]
<a href="#"><u>NP3636</u></a>	\$206.00	—	—	<a href="#"><u>NP3636SS</u></a>	\$489.00	36 x 36	33.00 x 33.00 [838 x 838]
<a href="#"><u>NP4024</u></a>	\$158.00	—	—	—	—	40 x 24	37.00 x 21.00 [940 x 533]
<a href="#"><u>NP4224</u></a>	\$151.00	—	—	—	—	42 x 24	39.00 x 21.00 [991 x 533]
<a href="#"><u>NP4230</u></a>	\$201.00	—	—	<a href="#"><u>NP4230SS</u></a>	\$515.00	42 x 30	39.00 x 27.00 [991 x 686]
<a href="#"><u>NP4236</u></a>	\$236.00	—	—	<a href="#"><u>NP4236SS</u></a>	\$618.00	42 x 36	39.00 x 33.00 [991 x 838]
<a href="#"><u>NP4824</u></a>	\$171.00	—	—	—	—	48 x 24	45.00 x 21.00 [1143 x 533]
<a href="#"><u>NP4830</u></a>	\$225.00	—	—	—	—	48 x 30	45.00 x 27.00 [1143 x 686]
<a href="#"><u>NP4836</u></a>	\$267.00	—	—	<a href="#"><u>NP4836SS</u></a>	\$669.00	48 x 36	45.00 x 33.00 [1143 x 838]
<a href="#"><u>NP6030</u></a>	\$276.00	—	—	—	—	60 x 30	57.00 x 27.00 [1448 x 686]
<a href="#"><u>NP6036</u></a>	\$328.00	—	—	<a href="#"><u>NP6036SS</u></a>	\$883.00	60 x 36	57.00 x 33.00 [1448 x 838]
<a href="#"><u>NP7230</u></a>	\$318.00	<a href="#"><u>NP7230G</u></a>	\$344.00	—	—	72 x 30	69.00 x 27.00 [1753 x 686]
<a href="#"><u>NP7236</u></a>	\$389.00	<a href="#"><u>NP7236G</u></a>	\$422.00	—	—	72 x 36	69.00 x 33.00 [1753 x 838]
Notes: Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawing. Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions in this table.							