



Inline Manual Shutoff Valves - 2-Way/ 3-Way Locking/Non-Locking



Non-Locking Valve




Locking Valve




NITRA pneumatic push-to-connect in-line hand valves have a technopolymer body and nickel-plated brass valve insert, with a range of 0 to 150 psi. Both 2-way and 3-way valves are available with or without locking capability. 3-way valves relieve pressure downstream when in the closed position.

Features

- Works with flexible pneumatic tubing
- Easily added to existing circuits
- 2-way and 3-way valves available
- Lockable valves keep valve in closed position during maintenance (Note: Valve can only be locked in closed position)
- Two-year warranty



2-Way Valve



3-Way Valve

NITRA Inline Manual Shutoff Valves

Inch Sizes - dimensions in inches (in.)

Part No.	Price	Tube Size	Position	A	B	C	D	E	H	I	Max Pressure (psi)	Flow Rate (scfm)*	Package Weight (lbs)
<u>HVU14-2</u>	\$14.00	1/4 in. x 1/4 in.	2-way (non-locking)	1.85	1.61	0.58	0.79	0.45	M15x1	0.55	145	9.9	0.1
<u>HVU14-3</u>	\$14.00	1/4 in. x 1/4 in.	3-way (non-locking)										0.1
<u>HVU516-2</u>	\$15.50	5/16 in. [8mm] x 5/16 in. [8mm]	2-way (non-locking)	2.18	1.81	0.74	0.94	0.54	M15x1	0.59	145	16.6	0.1
<u>HVU516-3</u>	\$15.50	5/16 in. [8mm] x 5/16 in. [8mm]	3-way (non-locking)										0.1
<u>HVU14-2L</u>	\$23.50	1/4 in. x 1/4 in.	2-way (locking)	1.85	1.61	0.58	0.79	0.45	M15x1	0.55	145	9.9	0.1
<u>HVU14-3L</u>	\$30.50	1/4 in. x 1/4 in.	3-way (locking)										0.1
<u>HVU516-2L</u>	\$25.00	5/16 in. [8mm] x 5/16 in. [8mm]	2-way (locking)	2.18	1.81	0.74	0.94	0.54	M15x1	0.59	145	16.6	0.2
<u>HVU516-3L</u>	\$24.50	5/16 in. [8mm] x 5/16 in. [8mm]	3-way (locking)										0.2

*Flow conditions: 90psi inlet pressure, 14.5 psi ΔP

See our website www.AutomationDirect.com for complete Engineering drawings.



Special Purpose Push-to-Connect Pneumatic Fittings

NITRA pneumatic inline fittings are special purpose products mounted inline with pneumatic circuits. With these small, highly efficient components it is possible to perform many pneumatic functions at any point in a circuit.

- Ultra-modular
- Components can be connected in parallel
- Push-to-Connect: No tools required!
- Made of lightweight technopolymer
- Stem adapters connect push-to-connect fittings to NPT ports



(Fasteners shown not included)



Inline Pressure Regulators
from \$20.25



Inline Pressure Gauges
from \$17.75



Inline Pressure Indicators
from \$11.75



Inline Manual Shutoff Valves
from \$11.25



Inline Quick Exhaust Valves
from \$8.75



Stem Adapters
from \$3.25