

# Shields

## P1AM-ETH

## \$55.00

### Ethernet Communications Shield

The P1AM-ETH is a housed Arduino Compatible Ethernet Shield based on the Wiznet W5500 Ethernet Controller. It interfaces to the left side

of the [P1AM-100](#) CPU and most Arduino MKR form factor shields.



### General Specifications

<b>Operating Temperature</b>	0° to 60°C (32° to 140°F)
<b>Storage Temperature</b>	-20° to 70°C (-4° to 158°F)
<b>Humidity</b>	5 to 95% (non-condensing)
<b>Environmental Air</b>	No corrosive gases permitted
<b>Vibration</b>	IEC60068-2-6 (Test Fc)
<b>Shock</b>	IEC60068-2-27 (Test Ea)
<b>Heat Dissipation</b>	750mW
<b>Enclosure Type</b>	Open Equipment
<b>Power Budget</b>	150mA/5V
<b>Recommended Library</b>	Arduino Ethernet
<b>Module Location</b>	Connects to the left side of the <a href="#">P1AM-100</a> CPU.
<b>Weight</b>	20g (0.8 oz.)
<b>Agency Approvals</b>	UL 61010-1 and UL 61010-2-201 File E139594, Canada & USA CE


### Ethernet Features

Supports Hardwired TCP Protocols:

- TCP, UDP, ICMP, IPV4, ARP, IGMP, PPPOE
- Supports 8 independent sockets simultaneously
- Supports Power Down Mode
- Supports Wake on LAN over UDP
- Supports High Speed Serial Peripheral Interface (SPI MODE 0, 3)
- Internal 32K bytes of Memory for TX/RX Buffers
- 10BaseT / 100BaseTX Ethernet PHY embedded
- Supports Auto Negotiation (Full and Half Duplex, 10 and 100-based)
- Does Not Support IP Fragmentation
- 3.3 V operation with 5V I/O signal tolerance
- LED outputs (Full / Half duplex, Link, Speed, Active)

### !WARNING!

Do not add or remove modules with field power applied!



### MKR Expansion Bus Pins

<b>GPIO</b>	A0–A6, 0–14
<b>Analog Input Pins</b>	A0–A6
<b>Analog Output Pins</b>	A0
<b>PWM Pins</b>	0–8, 10, A3, A4
<b>Interrupt Pins</b>	0, 1, 4–8, A1, A2
<b>5V</b>	5V supply output
<b>Vin</b>	5V regulated supply
<b>VCC</b>	3.3 V supply output
<b>GND</b>	Ground
<b>RST</b>	Reset
<b>AREF</b>	Analog Input Reference

#### Critical Notes:

Pins A3, A4, and 8–10 are used for the base controller.  
Do not exceed 46mA combined from pins 0, 1, and 4–10.  
Do not exceed 3.3 V on any I/O pin.  
Do not exceed 7mA on any I/O pin.  
Do not apply power to 5V or VCC

### Header Pins Used for Ethernet Shield

Pins Used	Function	Description
5	ETH SS	
8	MOSI	SPI pins are shared with other devices on SPI bus
9	SCK	
10	MISO	