




Pneumatic Air Preparation - AC Series Coalescing Filters

**AC-444-AD****AC-334-N****AC-224****AC-214***Mounting bracket included.***Coalescing
Filter**

Typical installation example shows AF series particulate filter (left), AR series pressure regulator (center) and AC series coalescing filter (right).

NITRA[®] pneumatic coalescing air filters are available with 1/8", 1/4", 3/8" or 1/2" NPT female port sizes to meet pneumatic air supply filtration applications that require oil mist and moisture removal to provide the best performance of modern pneumatic system components. Available with either a semi-automatic/manual or automatic drain. All-metal bowls with sight gauge are available on 3xx and 4xx sizes. Polycarbonate or nylon bowls with metal bowl guards available on all sizes. Replaceable 0.3-micron filter elements are standard. An optional 0.01-micron filter element (purchased separately and customer installable) is available when stricter filtration is required. Provided with a mounting bracket for stand-alone applications, the modular design also enables easy field assembly for combining with NITRA pneumatic particulate filters and regulators (using modular assembly brackets purchased separately).

Features

- 1/8", 1/4", 3/8" and 1/2" NPT female port sizes
- 0.3-micron replaceable filter element standard; for stricter filtration an optional 0.01-micron filter element purchased separately is easily customer installable
- Polycarbonate and Nylon bowls with metal bowl guards available on all sizes. Metal bowls with sight gauge on 3xx and 4xx sizes.
- Semi-automatic/manual and automatic drains available
- Mounting bracket provided for stand-alone applications
- Modular design enables easy field assembly for combining with NITRA particulate filters and regulators
- 2-year warranty



See www.AutomationDirect.com for a wide variety of fitting options






Pneumatic Air Preparation - AC Series Filters

AC Series Filters Cont.												
Part No.	Price	Weight (lbs)	Port Size (FNPT)	Drain Bowl	Drain Type	Fluid	Temperature	Filtering Grade	Operating Pressure	Maximum Pressure	Proof Pressure	
<u>AC-214</u>	\$90.00	0.7	1/8"	19cc Polycarbonate with metal bowl guard	Manual/Semi-Automatic	Air	23~140°F (-4~60°C)	0.3μ, 99.9% efficiency (0.01μ, 99.9% efficiency element may be ordered separately and field installed)	20~145psi (0.14~1.0MPa) (1.4~10.0 bar)	145psi (1.0MPa) (10.0 bar)	215psi (1.5MPa) (15 bar)	
<u>AC-214-N</u>	\$91.00	0.7		19cc Nylon with metal bowl guard								
<u>AC-224</u>	\$90.00	0.7	1/4"	19cc Polycarbonate with metal bowl guard								
<u>AC-224-N</u>	\$91.00	0.7		19cc Nylon with metal bowl guard								
<u>AC-324</u>	\$95.00	1.15		54.5cc Polycarbonate with metal bowl guard								
<u>AC-324-N</u>	\$98.00	1.15		54.5cc Nylon with metal bowl guard								
<u>AC-324-D</u>	\$99.00	1.2		54.5cc metal with sight gauge								
<u>AC-324-A</u>	\$125.00	1.15		54.5cc Polycarbonate with metal bowl guard								Automatic
<u>AC-324-AN</u>	\$128.00	1.15		54.5cc Nylon with metal bowl guard								
<u>AC-324-AD</u>	\$130.00	1.2		54.5cc metal with sight gauge								
<u>AC-334</u>	\$95.00	1.15	3/8"	54.5cc Polycarbonate with metal bowl guard	Manual/Semi-Automatic							
<u>AC-334-N</u>	\$98.00	1.15		54.5cc Nylon with metal bowl guard								
<u>AC-334-D</u>	\$99.00	1.2		54.5cc metal with sight gauge								
<u>AC-334-A</u>	\$125.00	1.15		54.5cc Polycarbonate with metal bowl guard	Automatic							
<u>AC-334-AN</u>	\$128.00	1.15		54.5cc Nylon with metal bowl guard								
<u>AC-334-AD</u>	\$130.00	1.2		54.5cc metal with sight gauge								
<u>AC-444</u>	\$129.00	1.8	1/2"	89cc Polycarbonate with metal bowl guard	Manual/Semi-Automatic							
<u>AC-444-N</u>	\$133.00	1.8		89cc Nylon with metal bowl guard								
<u>AC-444-D</u>	\$133.00	1.8		89cc metal with sight gauge								
<u>AC-444-A</u>	\$159.00	1.8		89cc Polycarbonate with metal bowl guard	Automatic							
<u>AC-444-AN</u>	\$164.00	1.8		89cc Nylon with metal bowl guard								
<u>AC-444-AD</u>	\$142.00	1.8		89cc metal with sight gauge								



Pneumatic Air Preparation - AC Series Filters




Performance Charts - .01μ Coalescing Filters





Pneumatic Air Preparation - AC Series Filters

Performance Charts - .3μ Coalescing Filters






Pneumatic Air Preparation - AC Series Filters

AC Series Filter Dimensions - mm (inches)

Part No.	A	B	C	D	ØE	ØF
AC-214	137.0 [5.39]	33.0 [1.30]	52.5 [2.07]	54.5 [2.15]	36.1 [1.42]	1/8
AC-214-N	137.0 [5.39]	33.0 [1.30]	52.5 [2.07]	54.5 [2.15]	36.1 [1.42]	1/8
AC-224	137.0 [5.39]	33.0 [1.30]	52.5 [2.07]	54.5 [2.15]	36.1 [1.42]	1/4
AC-224-N	137.0 [5.39]	33.0 [1.30]	52.5 [2.07]	54.5 [2.15]	36.1 [1.42]	1/4
AC-324	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	1/4
AC-324-N	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	1/4
AC-324-D	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	1/4
AC-324-A	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	1/4
AC-324-AN	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	1/4
AC-324-AD	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	1/4
AC-334	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	3/8
AC-334-N	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	3/8
AC-334-D	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	3/8
AC-334-A	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	3/8
AC-334-AN	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	3/8
AC-334-AD	179.0 [7.05]	41.0 [1.61]	62.5 [2.46]	67.8 [2.67]	46.5 [1.83]	3/8
AC-444	202.4 [7.97]	50.0 [1.97]	80.0 [3.15]	84.0 [3.31]	58.0 [2.28]	1/2
AC-444-N	202.4 [7.97]	50.0 [1.97]	80.0 [3.15]	84.0 [3.31]	58.0 [2.28]	1/2
AC-444-D	202.4 [7.97]	50.0 [1.97]	80.0 [3.15]	84.0 [3.31]	58.0 [2.28]	1/2
AC-444-A	202.4 [7.97]	50.0 [1.97]	80.0 [3.15]	84.0 [3.31]	58.0 [2.28]	1/2
AC-444-AN	202.4 [7.97]	50.0 [1.97]	80.0 [3.15]	84.0 [3.31]	58.0 [2.28]	1/2
AC-444-AD	202.4 [7.97]	50.0 [1.97]	80.0 [3.15]	84.0 [3.31]	58.0 [2.28]	1/2



Note: Unit dimensions are the same for listed models; port NPT varies based on model.

See our Web site
www.AutomationDirect.com
 for complete Engineering drawings.



Pneumatic Air Preparation Accessories



Part No. [ADB-21](#)



Part No. [AB-4T](#)



Part No. [AB-4L](#)



Part No. [AB-4U](#)

Pneumatic Air Preparation Accessories			
Part No.	Price	Description	Weight (lbs)
ADB-21	\$19.00	NITRA pneumatic distribution block, 1/8in female NPT inlet(s), (3) 1/8in female NPT outlet(s). For use with Ax-21 series air prep components.	0.1
ADB-22	\$19.00	NITRA pneumatic distribution block, 1/4in female NPT inlet(s), (3) 1/4in female NPT outlet(s). For use with Ax-22 series air prep components.	0.1
ADB-32	\$26.50	NITRA pneumatic distribution block, 1/4in female NPT inlet(s), (3) 1/4in female NPT outlet(s). For use with Ax-32 series air prep components.	0.2
ADB-33	\$26.50	NITRA pneumatic distribution block, 3/8in female NPT inlet(s), (3) 3/8in female NPT outlet(s). For use with Ax-33 series air prep components.	0.2
ADB-44	\$28.50	NITRA pneumatic distribution block, 1/2in female NPT inlet(s), (3) 1/2in female NPT outlet(s). For use with Ax-44 series air prep components.	0.4
AB-2T	\$17.50	NITRA modular T-bracket, for use with Ax-2 series air prep components.	0.2
AB-2L	\$17.50	NITRA modular L-bracket, for use with Ax-2 series air prep components.	0.2
AB-2U	\$17.50	NITRA modular U-bracket, for use with Ax-2 series air prep components.	0.1
AB-3T	\$19.00	NITRA modular T-bracket, for use with Ax-3 series air prep components.	0.3
AB-3L	\$19.00	NITRA modular L-bracket, for use with Ax-3 series air prep components.	0.3
AB-3U	\$19.00	NITRA modular U-bracket, for use with Ax-3 series air prep components.	0.2
AB-4T	\$23.00	NITRA modular T-bracket, for use with Ax-4 series air prep components.	0.5
AB-4L	\$23.00	NITRA modular L-bracket, for use with Ax-4 series air prep components.	0.5
AB-4U	\$23.00	NITRA modular U-bracket, for use with Ax-4 series air prep components.	0.4
AB-6T	\$33.50	NITRA modular T-bracket, for use with Ax-6 series air prep components.	1.3
AB-6L	\$31.50	NITRA modular L-bracket, for use with Ax-6 series air prep components.	1.2
AB-6U	\$30.00	NITRA modular U-bracket, for use with Ax-6 series air prep components.	0.8



Pneumatic Air Preparation Accessories



Part No. [AFE2-43](#)



Part No. [AFE2-41](#)



Part No. [AFE-24](#)



Part No. [AFE-35](#)

Pneumatic Air Preparation Accessories			
Part No.	Price	Description	Weight (lbs)
NITRA Gen 2 Particulate Filters			
AFE2-23	\$1.50	NITRA particulate filter element, replacement, 40 micron particles, high-density polyethylene (HDPE). For use with AF-2 series filters or AFR-2 series filter regulators.	0.01
AFE2-33	\$3.25	NITRA particulate filter element, replacement, 40 micron particles, high-density polyethylene (HDPE). For use with AF-3 series filters or AFR-3 series filter regulators.	0.01
AFE2-43	\$4.50	NITRA particulate filter element, replacement, 40 micron particles, high-density polyethylene (HDPE). For use with AF-4 series filters or AFR-4 series filter regulators.	0.01
AFE2-63	\$11.50	NITRA particulate filter element, replacement, 40 micron particles, high-density polyethylene (HDPE). For use with AF-6 series filters or AFR-6 series filter regulators.	0.04
AFE2-21	\$1.50	NITRA particulate filter element, replacement, 5 micron particles, high-density polyethylene (HDPE). For use with AF-2 series filters or AFR-2 series filter regulators.	0.01
AFE2-31	\$3.25	NITRA particulate filter element, replacement, 5 micron particles, high-density polyethylene (HDPE). For use with AF-3 series filters or AFR-3 series filter regulators.	0.01
AFE2-41	\$4.50	NITRA particulate filter element, replacement, 5 micron particles, high-density polyethylene (HDPE). For use with AF-4 series filters or AFR-4 series filter regulators.	0.01
AFE2-61	\$11.50	NITRA particulate filter element, replacement, 5 micron particles, high-density polyethylene (HDPE). For use with AF-6 series filters or AFR-6 series filter regulators.	0.04
NITRA Coalescing Filters			
AFE-24	\$21.50	NITRA coalescing oil removal filter element, replacement, 0.3 micron particles, borosilicate glass microfiber. For use with AC-2 series coalescing filters.	0.05
AFE-34	\$26.50	NITRA coalescing oil removal filter element, replacement, 0.3 micron particles, borosilicate glass microfiber. For use with AC-3 series coalescing filters.	0.05
AFE-44	\$42.50	NITRA coalescing oil removal filter element, replacement, 0.3 micron particles, borosilicate glass microfiber. For use with AC-4 series coalescing filters.	0.1
AFE-25	\$21.50	NITRA coalescing oil removal filter element, replacement, 0.01 micron particles, borosilicate glass microfiber. For use with AC-2 series coalescing filters.	0.04
AFE-35	\$26.50	NITRA coalescing oil removal filter element, replacement, 0.01 micron particles, borosilicate glass microfiber. For use with AC-3 series coalescing filters.	0.05
AFE-45	\$42.50	NITRA coalescing oil removal filter element, replacement, 0.01 micron particles, borosilicate glass microfiber. For use with AC-4 series coalescing filters.	0.1




Pneumatic Air Preparation Accessories

Dimensions

mm [inches]

ADB-x

PART NO.	A NPT	DIM B	DIM C	DIM D	DIM E
ADB-21	1/8	30.0 [1.18]	36.0 [1.42]	19.5 [0.77]	28.5 [1.12]
ADB-22	1/4	30.0 [1.18]	36.0 [1.42]	19.5 [0.77]	28.5 [1.12]
ADB-32	1/4	38.0 [1.50]	44.0 [1.73]	26.0 [1.02]	35.0 [1.38]
ADB-33	3/8	38.0 [1.50]	44.0 [1.73]	26.0 [1.02]	35.0 [1.38]
ADB-44	1/2	52.0 [2.05]	52.0 [2.05]	30.0 [1.18]	42.0 [1.65]



See our Web site www.AutomationDirect.com for complete Engineering drawings.



Pneumatic Air Preparation Accessories

Dimensions

mm [inches]

AB-xT




TABLE 1									
PART NUMBER	DIM "A"	DIM "B"	DIM "C"	DIM "D"	DIM "E"	DIM "F"	DIM "G"	DIM "H"	DIM "J"
AB-2T	66.0 [2.60]	45.0 [1.77]	38.3 [1.51]	30.0 [1.18]	5.0 [0.20]	50.0 [1.97]	11.5 [0.45]	8.5 [0.33]	5.5 [0.22]
AB-3T	88.0 [3.46]	60.5 [2.38]	49.3 [1.94]	41.5 [1.63]	7.0 [0.28]	70.0 [2.76]	12.5 [0.49]	9.0 [0.35]	6.5 [0.26]
AB-4T	104.0 [4.09]	76.0 [2.99]	58.5 [2.30]	50.0 [1.97]	7.0 [0.28]	80.0 [3.15]	15.5 [0.61]	12.0 [0.47]	8.6 [0.34]
AB-6T	128.0 [5.04]	104.0 [4.09]	79.5 [3.13]	70.0 [2.76]	10.0 [0.39]	100.0 [3.94]	19.5 [0.77]	16.0 [0.63]	11.0 [0.43]

AB-xL




TABLE 1									
PART NUMBER	DIM "A"	DIM "B"	DIM "C"	DIM "D"	DIM "E"	DIM "F"	DIM "G"	DIM "H"	DIM "J"
AB-2L	51.3 [2.02]	45.0 [1.77]	38.3 [1.51]	30.0 [1.18]	5.0 [0.20]	25.0 [0.98]	11.5 [0.45]	8.5 [0.33]	5.5 [0.22]
AB-3L	68.6 [2.70]	60.5 [2.38]	49.3 [1.94]	41.5 [1.63]	7.0 [0.28]	35.0 [1.38]	12.5 [0.49]	9.0 [0.35]	6.5 [0.26]
AB-4L	79.5 [3.13]	76.0 [2.99]	58.5 [2.30]	50.0 [1.97]	7.0 [0.28]	40.0 [1.57]	15.5 [0.61]	12.0 [0.47]	8.6 [0.34]
AB-6L	103.5 [4.07]	104.0 [4.09]	79.5 [3.13]	70.0 [2.76]	10.0 [0.39]	50.0 [1.97]	19.5 [0.77]	16.0 [0.63]	11.0 [0.43]

See our Web site www.AutomationDirect.com for complete Engineering drawings.



Pneumatic Air Preparation Accessories

Dimensions

mm [inches]

AB-xU




TABLE 1

PART NUMBER	DIM "A"	DIM "B"	DIM "C"	DIM "D"	DIM "E"
AB-2U	35.5 [1.39]	30.0 [1.18]	38.3 [1.51]	15.0 [0.59]	11.5 [0.45]
AB-3U	43.8 [1.72]	38.0 [1.50]	49.3 [1.94]	19.5 [0.75]	12.5 [0.49]
AB-4U	52.5 [2.07]	52.0 [2.05]	58.5 [2.30]	26.0 [1.02]	15.5 [0.61]
AB-6U	76.5 [3.01]	68.0 [2.68]	79.5 [3.13]	34.0 [1.34]	19.5 [0.77]

See our Web site www.AutomationDirect.com for complete Engineering drawings.