



# Process Pipeline Solenoid Valves

## DVP-2D & DVP-3D Series

Part No. **DVP-2DC1D-24D**

The Nitra DVP-2D and DVP-3D Series valves are composite body solenoid valves offered in both 2-way and 3-way normally closed styles in three orifice sizes. Features include a direct acting solenoid utilizing a long-life spring compensated poppet at the heart of an all stainless solenoid operator. Body construction is glass filled nylon with Viton seals, making the valves compatible with air, oil, inert gas, water and caustics\*. Operating voltages of 24VDC, 24VAC or 120VAC are available.

### Features

- 2-way and 3-way poppet style valves
- 1/8, 1/4 or 3/8" FNPT ports
- 2-position, normally closed, spring return
- 24VDC, 24VAC or 120VAC solenoids
- DIN style wiring connector

Valve Symbols



2-way, 2-pos, NC

See [www.AutomationDirect.com](http://www.AutomationDirect.com)

for a wide variety of fitting and cable options



| DVP-2D Series Solenoid Valve Specifications |                                                                |                      |                       |                      |                      |                       |                                              |                      |                           |
|---------------------------------------------|----------------------------------------------------------------|----------------------|-----------------------|----------------------|----------------------|-----------------------|----------------------------------------------|----------------------|---------------------------|
| Model                                       | <u>DVP-2DC1D-24D</u>                                           | <u>DVP-2DC1D-24A</u> | <u>DVP-2DC1D-120A</u> | <u>DVP-2DC2E-24D</u> | <u>DVP-2DC2E-24A</u> | <u>DVP-2DC2E-120A</u> | <u>DVP-2DC3F-24D</u>                         | <u>DVP-2DC3F-24A</u> | <u>DVP-2DC3F-120A</u>     |
| Price                                       | \$50.00                                                        | \$50.00              | \$50.00               | \$50.00              | \$50.00              | \$50.00               | \$50.00                                      | \$50.00              | \$50.00                   |
| Weight (lbs)                                | 0.6                                                            | 0.6                  | 0.6                   | 0.6                  | 0.6                  | 0.6                   | 0.6                                          | 0.6                  | 0.6                       |
| Valve Type                                  | 2-way, 2-position                                              |                      |                       |                      |                      |                       |                                              |                      |                           |
| Acting                                      | Poppet valve, normally closed, spring return                   |                      |                       |                      |                      |                       | Poppet valve, normally closed, spring return |                      |                           |
| Port Size                                   | 1/8" FNPT                                                      |                      |                       | 1/4" FNPT            |                      |                       | 3/8" FNPT                                    |                      |                           |
| Orifice Size                                | 0.062" [1.6 mm]                                                |                      |                       | 0.094" [2.4 mm]      |                      |                       | 0.118" [3.0 mm]                              |                      |                           |
| Cv                                          | 0.12                                                           |                      |                       | 0.245                |                      |                       | 0.315                                        |                      |                           |
| Media                                       | Air, oil, inert gas, water, caustics*                          |                      |                       |                      |                      |                       |                                              |                      |                           |
| Pressure Range                              | 0-250 psi<br>[0-17.2 bar]                                      |                      |                       |                      |                      |                       | 0-150 psi<br>[0-10.3 bar]                    |                      | 0-250 psi<br>[0-17.2 bar] |
| Voltage<br>(± 10%)                          | 24VDC                                                          | 24VAC<br>50/60 Hz    | 120VAC<br>50/60 Hz    | 24VDC                | 24VAC<br>50/60 Hz    | 120VAC<br>50/60 Hz    | 24VDC                                        | 24VAC<br>50/60 Hz    | 120VAC<br>50/60 Hz        |
| Inrush AC                                   | -                                                              | 26VA                 |                       | -                    | 26VA                 |                       | -                                            | 26VA                 |                           |
| Power Consumption                           | 10W                                                            | 11.5 VA              |                       | 10W                  | 11.5 VA              |                       | 10W                                          | 11.5 VA              |                           |
| Max Freq                                    | 25Hz                                                           |                      |                       |                      |                      |                       |                                              |                      |                           |
| Insulation                                  | Class F (continuous duty)                                      |                      |                       |                      |                      |                       |                                              |                      |                           |
| Min Response                                | 16-40 ms                                                       |                      |                       |                      |                      |                       |                                              |                      |                           |
| Temperature                                 | 14°F to 122°F [-10°C to 50°C]                                  |                      |                       |                      |                      |                       |                                              |                      |                           |
| Lubrication                                 | Not Required                                                   |                      |                       |                      |                      |                       |                                              |                      |                           |
| Protection                                  | NEMA Type 4                                                    |                      |                       |                      |                      |                       |                                              |                      |                           |
| Connection                                  | 18mm DIN terminal                                              |                      |                       |                      |                      |                       |                                              |                      |                           |
| Construction                                | Glass filled nylon body; Viton seals; Operator Stainless Steel |                      |                       |                      |                      |                       |                                              |                      |                           |
| Life Cycle                                  | 10 million                                                     |                      |                       |                      |                      |                       |                                              |                      |                           |
| Agency Approvals                            | CE                                                             |                      |                       |                      |                      |                       |                                              |                      |                           |


\* Check the chemical compatibility of the valve materials with the process media being used.




# Process Pipeline Solenoid Valves

## DVP-2D & DVP-3D Series

### Valve Symbols



3-way, 2-pos, NC



3-way, 2-pos, Mixing



3-way, 2-pos, Diverting

| DVP-3D Series Solenoid Valve Specifications |                                                      |                   |                    |                           |                   |                           |                           |                   |                         |
|---------------------------------------------|------------------------------------------------------|-------------------|--------------------|---------------------------|-------------------|---------------------------|---------------------------|-------------------|-------------------------|
| Model                                       | DVP-3DC1D-24D                                        | DVP-3DC1D-24A     | DVP-3DC1D-120A     | DVP-3DC2E-24D             | DVP-3DC2E-24A     | DVP-3DC2E-120A            | DVP-3DC3F-24D             | DVP-3DC3F-24A     | DVP-3DC3F-120A          |
| Price                                       | \$50.00                                              | \$50.00           | \$50.00            | \$50.00                   | \$50.00           | \$50.00                   | \$50.00                   | \$50.00           | \$50.00                 |
| Weight (lbs)                                | 0.6                                                  | 0.6               | 0.6                | 0.6                       | 0.6               | 0.6                       | 0.6                       | 0.6               | 0.6                     |
| Valve Type                                  | 3-way, 2-position                                    |                   |                    |                           |                   |                           |                           |                   |                         |
| Acting                                      | Poppet valve, normally closed, spring return         |                   |                    |                           |                   |                           |                           |                   |                         |
| Port Size                                   | 1/8" FNPT                                            |                   |                    | 1/4" FNPT                 |                   |                           | 3/8" FNPT                 |                   |                         |
| Orifice Size                                | 0.062" [1.6 mm]                                      |                   |                    | 0.094" [2.4 mm]           |                   |                           | 0.118" [3.0 mm]           |                   |                         |
| Cv                                          | 0.12 (exhaust port 0.08)                             |                   |                    | 0.245 (exhaust port 0.08) |                   |                           | 0.315 (exhaust port 0.08) |                   |                         |
| Media                                       | Air, oil, inert gas, water, caustics*                |                   |                    |                           |                   |                           |                           |                   |                         |
| Pressure Range                              | 0–220 psi<br>[0–15.2 bar]                            |                   |                    | 1–120 psi<br>[0–8.3 bar]  |                   | 1–150 psi<br>[0–10.3 bar] | 1–82 psi<br>[0–5.7 bar]   |                   | 1–90 psi<br>[0–6.2 bar] |
| Voltage<br>(±10%)                           | 24VDC                                                | 24VAC<br>50/60 Hz | 120VAC<br>50/60 Hz | 24VDC                     | 24VAC<br>50/60 Hz | 120VAC<br>50/60 Hz        | 24VDC                     | 24VAC<br>50/60 Hz | 120VAC<br>50/60 Hz      |
| Inrush AC                                   | –                                                    | 26VA              |                    | –                         | 26VA              |                           | –                         | 26VA              |                         |
| Power Consumption                           | 10W                                                  | 11.5 VA           |                    | 10W                       | 11.5 VA           |                           | 10W                       | 11.5 VA           |                         |
| Max Freq                                    | 25Hz                                                 |                   |                    |                           |                   |                           |                           |                   |                         |
| Insulation                                  | Class F (continuous duty)                            |                   |                    |                           |                   |                           |                           |                   |                         |
| Min Response                                | 16–40 ms                                             |                   |                    |                           |                   |                           |                           |                   |                         |
| Temperature                                 | 14°F to 122°F [-10°C to 50°C]                        |                   |                    |                           |                   |                           |                           |                   |                         |
| Lubrication                                 | Not Required                                         |                   |                    |                           |                   |                           |                           |                   |                         |
| Protection                                  | NEMA Type 4                                          |                   |                    |                           |                   |                           |                           |                   |                         |
| Connection                                  | 18mm DIN terminal                                    |                   |                    |                           |                   |                           |                           |                   |                         |
| Construction                                | Glass filled nylon body; Viton seals; Operator Brass |                   |                    |                           |                   |                           |                           |                   |                         |
| Life Cycle                                  | 10 million                                           |                   |                    |                           |                   |                           |                           |                   |                         |
| Agency Approvals                            | CE                                                   |                   |                    |                           |                   |                           |                           |                   |                         |

\* Check the chemical compatibility of the valve materials with the process media being used.




# Process Pipeline Solenoid Valves

## DVP-2D & DVP-3D Series

### Dimensions

inches [mm]



| PORT SIZES       |          |
|------------------|----------|
| PART NO.         | DIM A    |
| DVP-2DC1D-24/120 | 1/8 FNPT |
| DVP-2DC2E-24/120 | 1/4 FNPT |
| DVP-2DC3F-24/120 | 3/8 FNPT |
| DVP-3DC1D-24/120 | 1/8 FNPT |
| DVP-3DC2E-24/120 | 1/4 FNPT |
| DVP-3DC3F-24/120 | 3/8 FNPT |

FNPT = FEMALE NATIONAL PIPE THREAD

See our website [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete Engineering drawings.

# Solenoid Valve Cables and Connectors



## 8mm Connectors


Dimensions shown  
mm [inches]



These high quality connectors and over-molded cables help reduce wiring time. The lower voltage models, 24V or 110V AC/DC, include built-in surge suppression, Yellow LED indicator and are rated for connecting with electronics. The 230V AC/DC models are rated for straight wired products. All models are available in five sizes based on DIN 43650.


## Features

- 8mm, 9.4mm, 10mm, 11mm and 18mm square DIN styles
- Fits most popular solenoid valves and sensors
- Suppression and LED indication available in 24V or 110V AC/DC models
- PVC jacketed cables in 1, 3 or 5 meter lengths on select connectors
- Field wireable connectors on select models
- Polarity insensitive (follow solenoid, sensor, or other devices wiring diagram)



Height = 25mm [0.98in]

Connector with Cable



Height = 26mm [1.02]


Field Wireable Connector

| 8mm (3-pole) Connectors (per DIN 43650 Form C) |         |                 |                |           |                                               |                                        |     |                                |               |                                    |              |                    |
|------------------------------------------------|---------|-----------------|----------------|-----------|-----------------------------------------------|----------------------------------------|-----|--------------------------------|---------------|------------------------------------|--------------|--------------------|
| Part No.                                       | Price   | Voltage (AC/DC) | Current Rating | IP Rating | Wire Size                                     | Cable Dia. (in.)                       | LED | Surge Protection               | Wiring Figure | Screw Size/ Torque                 | Weight (lbs) | Agency Approval    |
| <a href="#">SC8-LS24-3</a>                     | \$15.50 | 24 ±20%         | max 4A         | 67        | 18 AWG                                        | 0.23                                   | yes | zener diode (D-Z DO-15 47V 2W) | 1             | m2.5-0.45x25mm/ 0.4 Nm (3.5 in lb) | 0.40         | CSA (080128-0-000) |
| <a href="#">SC8-LS24-5</a>                     | \$18.50 |                 |                |           |                                               |                                        |     |                                | 0.65          |                                    |              |                    |
| <a href="#">SC8-LS110-3</a>                    | \$19.00 |                 |                |           |                                               |                                        |     |                                | 0.41          |                                    |              |                    |
| <a href="#">SC8-LS110-5</a>                    | \$22.00 |                 |                |           |                                               |                                        |     |                                | 0.63          |                                    |              |                    |
| <a href="#">SC8-3</a>                          | \$12.50 | 230             | max 6A         | 65        | Solid 12 AWG Stranded 14 AWG w/Ferrule 16 AWG | field wireable gland size 0.20 to 0.24 | no  | none                           | 2             | m2.5-0.45x25mm/ 0.5 Nm (4.4 in lb) | 0.39         | none               |
| <a href="#">SC8-0</a>                          | \$8.25  |                 |                |           |                                               |                                        |     |                                | 9             |                                    | 0.10         |                    |
| <a href="#">SC8-1</a>                          | \$16.50 |                 |                |           |                                               |                                        |     |                                | 2             |                                    | 0.10         |                    |
| <a href="#">SC8-5</a>                          | \$17.50 |                 |                |           |                                               |                                        |     |                                |               |                                    | 0.68         |                    |

Last digit in part number denotes cable length in meters, a 0 indicates field termination.

## 8mm Transmitter Connector

Dimensions shown  
mm [inches]



Height = 25mm [0.98in]

Connector with Cable


| 8mm (4-pole) Connectors (per DIN 43650 Form C) |         |                 |                |           |           |                  |     |                  |               |                                |              |                    |
|------------------------------------------------|---------|-----------------|----------------|-----------|-----------|------------------|-----|------------------|---------------|--------------------------------|--------------|--------------------|
| Part No.                                       | Price   | Voltage (AC/DC) | Current Rating | IP Rating | Wire Size | Cable Dia. (in.) | LED | Surge Protection | Wiring Figure | Screw Size/Torque              | Weight (lbs) | Agency Approval    |
| SC8-5T                                         | \$23.50 | 230             | max 6A         | 67        | 18 AWG    | 0.26             | yes | none             | 8             | m3-0.5x42mm/0.5 Nm (4.4 in lb) | 0.80         | CSA (080128-0-000) |

Last numeric digit in part number denotes cable length in meters, a 0 indicates field termination.

# Solenoid Valve Cables and Connectors

## 9.4mm Connectors


Dimensions shown  
mm [inches]



| 9.4mm (3-pole) Connectors (DIN Style, Form C Industrial) |         |                 |                |           |           |                  |        |                                |               |                                 |                                  |                    |                                 |      |      |
|----------------------------------------------------------|---------|-----------------|----------------|-----------|-----------|------------------|--------|--------------------------------|---------------|---------------------------------|----------------------------------|--------------------|---------------------------------|------|------|
| Part No.                                                 | Price   | Voltage (AC/DC) | Current Rating | IP Rating | Wire Size | Cable Dia. (in.) | LED    | Surge Protection               | Wiring Figure | Screw Size/ Torque              | Weight (lbs)                     | Agency Approval    |                                 |      |      |
| <a href="#">SC9-LS24-3</a>                               | \$15.50 | 24 ±20%         | max 4A         | 67        | 18 AWG    | 0.23             | yes    | zener diode (D-Z DO-15 47V 2W) | 1             | m3-0.5x26mm/ 0.4 Nm (3.5 in lb) | 0.40                             | CSA (080128-0-000) |                                 |      |      |
| <a href="#">SC9-LS24-5</a>                               | \$18.50 |                 |                |           |           |                  |        |                                |               |                                 | 0.64                             |                    |                                 |      |      |
| <a href="#">SC9-LS110-3</a>                              | \$19.00 | 110 ±10%        |                |           |           |                  | max 6A |                                |               |                                 | zener diode (D-Z DO-41 ZY200 2W) |                    | 7                               | 0.40 |      |
| <a href="#">SC9-LS110-5</a>                              | \$22.00 |                 |                |           |           |                  |        |                                |               |                                 |                                  |                    |                                 | 0.64 |      |
| <a href="#">SC9-3</a>                                    | \$12.50 | 230             | max 6A         |           |           |                  | no     |                                |               |                                 | none                             | 2                  | m3-0.5x26mm/ 0.5 Nm (4.4 in lb) | 0.40 | none |
| <a href="#">SC9-5</a>                                    | \$17.50 |                 |                |           |           |                  |        |                                |               |                                 |                                  |                    |                                 |      |      |

## 9.4mm Connectors

Dimensions shown  
mm [inches]




Height = 25mm [0.98in]  
Connector with Cable

| 9.4mm (4-pole) Connectors (DIN Style, Form C Industrial) |         |                 |                |           |           |            |              |     |                  |               |                                       |              |                             |
|----------------------------------------------------------|---------|-----------------|----------------|-----------|-----------|------------|--------------|-----|------------------|---------------|---------------------------------------|--------------|-----------------------------|
| Part No.                                                 | Price   | Voltage (AC/DC) | Current Rating | IP Rating | Wire Size | Cable Dia. | Cable Length | LED | Surge Protection | Wiring Figure | Screw Size/Torque                     | Weight (lbs) | Agency Approval             |
| <a href="#">7000-94141-6270300</a>                       | \$18.00 | 230 VAC/<br>VDC | max 6A         | IP67      | 18 AWG    | 5.6–6.2 mm | 9.8ft/3m     | no  | none             | 8             | m3-0.5x26mm/<br>0.4 Nm<br>(3.5 in lb) | 0.50         | CSA (080128-0-000)/<br>RoHS |
| <a href="#">7000-94141-6270500</a>                       | \$24.00 |                 |                |           |           |            | 16.4ft/5m    |     |                  |               |                                       | 0.79         |                             |

# Solenoid Valve Cables and Connectors


## 10mm Connectors

Dimensions shown  
mm [inches]



Height = 30mm [1.18in]

Connector with Cable



Height = 41mm [1.61in]

Field Wireable Connector


### 10mm (3-pole) Connectors (per DIN 43650 Form B)

| Part No.                     | Price   | Voltage<br>(AC/DC)                  | Current<br>Rating | IP<br>Rating | Wire Size                                                 | Cable Dia.<br>(in.)                                | LED  | Surge Protection                    | Wiring<br>Figure | Screw Size/<br>Torque                 | Weight<br>(lbs) | Agency<br>Approval    |
|------------------------------|---------|-------------------------------------|-------------------|--------------|-----------------------------------------------------------|----------------------------------------------------|------|-------------------------------------|------------------|---------------------------------------|-----------------|-----------------------|
| <a href="#">SC10-LS24-3</a>  | \$15.50 | 24 ±20%                             | max 4A            | 67           | 18 AWG                                                    | 0.23                                               | yes  | zener diode<br>(D-Z DO-15 47V 2W)   | 10               | m3-0.5x30mm/<br>0.4 Nm<br>(3.5 in lb) | 0.43            | CSA<br>(080128-0-000) |
| <a href="#">SC10-LS24-5</a>  | \$18.50 |                                     |                   |              |                                                           |                                                    |      | zener diode<br>(D-Z DO-41 ZY200 2W) | 6                |                                       | 0.68            |                       |
| <a href="#">SC10-LS110-3</a> | \$19.00 | zener diode<br>(D-Z DO-41 ZY200 2W) | 6                 |              |                                                           |                                                    |      | 0.43                                |                  |                                       |                 |                       |
| <a href="#">SC10-LS110-5</a> | \$22.00 |                                     |                   |              |                                                           |                                                    | 0.68 |                                     |                  |                                       |                 |                       |
| <a href="#">SC10-3</a>       | \$12.50 | 230                                 | max 10A           |              |                                                           |                                                    | no   | none                                | 3                |                                       | 0.43            |                       |
| <a href="#">SC10-5</a>       | \$17.50 |                                     |                   |              |                                                           |                                                    |      |                                     |                  |                                       |                 |                       |
| <a href="#">SC10-LS24-0</a>  | \$12.50 | 24 ±20%                             | max 4A            | 65           | Solid 12 AWG<br>Stranded 14<br>AWG<br>w/Ferrule<br>16 AWG | field<br>wireable<br>gland size<br>0.24 to<br>0.32 | yes  | zener diode<br>(D-Z DO-15 47V 2W)   | 4                | m3-0.5x42mm/<br>0.5 Nm<br>(4.4 in lb) | 0.07            | none                  |
| <a href="#">SC10-LS110-0</a> | \$14.00 | 110 ±10%                            | max 1A            |              |                                                           |                                                    |      | mov<br>(SIOV S10 K130)              | 5                |                                       | 0.07            |                       |

Last digit in part number denotes cable length in meters, a 0 indicates field termination.


## 11mm Connectors

Dimensions shown  
mm [inches]




Height = 30mm [1.18in]

Connector with Cable



Height = 30mm [1.18in]

Reverse Connector with Cable



Height = 41mm [1.61in]











Field Wireable Connector

### 11mm (3-pole) Connectors (DIN Style, Form B Industrial)

| Part No.                      | Price   | Voltage (AC/DC) | Current Rating | IP Rating | Wire Size                                     | Cable Dia. (in)                        | LED | Surge Protection                 | Wiring Figure | Screw Size/ Torque              | Weight (lbs) | Agency Approval    |
|-------------------------------|---------|-----------------|----------------|-----------|-----------------------------------------------|----------------------------------------|-----|----------------------------------|---------------|---------------------------------|--------------|--------------------|
| <a href="#">SC11-LS24-3</a>   | \$15.50 | 24 ±20%         | max 4A         | 67        | 18 AWG                                        | 0.23                                   | yes | zener diode (D-Z DO-15 47V 2W)   | 10            | m3-0.5x30mm/ 0.4 Nm (3.5 in lb) | 0.44         | CSA (080128-0-000) |
| <a href="#">SC11-LS24-5</a>   | \$18.50 |                 |                |           |                                               |                                        |     | zener diode (D-Z DO-41 ZY200 2W) | 6             |                                 | 0.67         |                    |
| <a href="#">SC11-LS110-3</a>  | \$19.00 | 110 ±10%        | max 1A         |           |                                               |                                        |     | zener diode (D-Z DO-15 47V 2W)   | 10            |                                 | 0.44         |                    |
| <a href="#">SC11-LS110-5</a>  | \$22.00 |                 |                |           |                                               |                                        |     | zener diode (D-Z DO-41 ZY200 2W) | 6             |                                 | 0.67         |                    |
| <a href="#">SC11-LS24-3R</a>  | \$15.50 | 24 ±20%         | max 4A         |           |                                               |                                        |     | zener diode (D-Z DO-15 47V 2W)   | 10            |                                 | 0.44         |                    |
| <a href="#">SC11-LS24-5R</a>  | \$18.50 |                 |                |           |                                               |                                        |     | zener diode (D-Z DO-41 ZY200 2W) | 6             |                                 | 0.67         |                    |
| <a href="#">SC11-LS110-3R</a> | \$19.00 | 110 ±10%        | max 1A         |           |                                               |                                        | no  | none                             | 3             |                                 | 0.44         |                    |
| <a href="#">SC11-LS110-5R</a> | \$22.00 |                 |                |           |                                               |                                        |     |                                  |               |                                 | 0.67         |                    |
| <a href="#">SC11-3</a>        | \$12.50 | 230             | max 10A        |           |                                               |                                        | no  | none                             | 3             |                                 | 0.44         |                    |
| <a href="#">SC11-5</a>        | \$17.50 |                 |                |           |                                               |                                        |     |                                  |               |                                 | 0.67         |                    |
| <a href="#">SC11-LS24-0</a>   | \$12.50 | 24 ±20%         | max 4A         | 65        | Solid 12 AWG Stranded 14 AWG w/Ferrule 16 AWG | field wireable gland size 0.24 to 0.32 | yes | zener diode (D-Z DO-15 47V 2W)   | 4             | m3-0.5x42mm/ 0.5 Nm (4.4 in lb) | 0.07         | none               |
| <a href="#">SC11-LS110-0</a>  | \$14.00 | 110 ±10%        | max 1A         |           |                                               |                                        |     | mov (SIOV S10 K130)              | 5             |                                 | 0.07         |                    |
| <a href="#">SC11-0</a>        | \$10.50 | 230             | max 10A        |           |                                               |                                        | no  | none                             | 9             |                                 | 0.07         |                    |

Last numeric digit in part number denotes cable length in meters, a 0 indicates field termination.

# Solenoid Valve Cables and Connectors Wiring Diagrams

**Figure No. 1****Figure No. 2****Figure No. 3****Figure No. 4****Figure No. 5****Figure No. 6****Figure No. 7****Figure No. 8****Figure No. 9****Figure No. 10**