

# Input Simulator & Filler Module

## P2-08SIM \$67.00

### Input Simulator Module

The P2-08SIM Input Simulator module provides 8 toggle switches to simulate input devices.



### Input Specifications

|                           |                       |
|---------------------------|-----------------------|
| <b>Inputs per Module</b>  | 8 Internal switches   |
| <b>OFF to ON Response</b> | Max. 20ms             |
| <b>ON to OFF Response</b> | Max. 20ms             |
| <b>Status Indicators</b>  | Logic Side (8 points) |

### General Specifications

|                              |                                                                                                                        |
|------------------------------|------------------------------------------------------------------------------------------------------------------------|
| <b>Operating Temperature</b> | 0° to 60°C (32° to 140°F)                                                                                              |
| <b>Storage Temperature</b>   | -20° to 70°C (-4° to 158°F)                                                                                            |
| <b>Humidity</b>              | 5 to 95% (non-condensing)                                                                                              |
| <b>Environmental Air</b>     | No corrosive gases permitted                                                                                           |
| <b>Vibration</b>             | IEC60068-2-6 (Test Fc)                                                                                                 |
| <b>Shock</b>                 | IEC60068-2-27 (Test Ea)                                                                                                |
| <b>Heat Dissipation</b>      | 200mW                                                                                                                  |
| <b>Enclosure Type</b>        | Open equipment                                                                                                         |
| <b>Module Location</b>       | Any I/O slot in a Productivity2000 system.                                                                             |
| <b>Weight</b>                | 90g (3.2 oz.)                                                                                                          |
| <b>Agency Approvals**</b>    | UL 61010-1 and UL 61010-2-201 File E139594, Canada & USA<br>CE (EN 61131-2 EMC, EN 61010-1 and EN 61010-2-201 Safety)* |

\* Meets EMC and Safety requirements. See the D.O.C. for details.

\*\*For complete system limits, please refer to the "Hardware and Communication Limits" table in the Productivity Suite online "Help" file "Hardware Configuration", topic P050.

## P2-FILL \$15.50

### Filler Module

The P2-FILL filler module protects unused I/O module slots in the base.

