



Electrical Tape

Overview

Plymouth Rubber develops and manufactures adhesive tapes and solutions for electrical insulation. Their vast experience in the industry allows them to be one of the more prominent companies in the global industry of electrical tape, highlighting vinyl tapes, rubber tapes, and much more.

Our offering includes solutions for primary insulation, insulating and jacketing splices, and color-coded vinyl tape for quick identification of electrical circuits. This is accomplished with a selection of tapes that include vinyl electrical tape, silicone rubber tape, glass tape, and self-amalgamating and self-fusing mastics.



Electrical Tape						
Part Number	Series	Description	Thickness	Size	Color	Compare With Scotch®
PR-1101-1	61	Fabric Electrical Tape	7.1 mil	0.75in x 60ft	Yellow	2510
PR-1121-1	61A	Fabric Electrical Tape w/ Adhesive	7.9 mil			2520
PR-2006-1	150 ASTM	Rubber Electrical Tape	30 mil	0.75in x 30ft	Gray	n/a
PR-2104-1	17 Plyshield	Semi-conducting Rubber Electrical Tape		0.75in x 15ft	Black	13
PR-2117-1	W963	Rubber Electrical Tape		0.75in x 30ft		23
PR-2211-1	L969	Rubber Electrical Tape		1in x 30ft		130C
PR-2212-1				1.5in x 30ft		
PR-2213-1				2in x 30ft		
PR-2214-1						
PR-2609-1	VM	Vinyl-backed Mastic Electrical Tape		47 mil	4in x 10ft	n/a
PR-2626-1	10 Plyseal	Mastic Electrical Tape		126 mil	3.75in x 10ft	
PR-3455-1	20 Plysil	Silicone Rubber Electrical Tape	20 mil	1in x 30ft	Gray	70
PR-3456-1	77 PLYGLAS	Glass Cloth Electrical Tape	7 mil	0.75in x 66ft	White	27
PR-3702-1	Premium 37	Vinyl Electrical Tape	7 mil		Green	35
PR-3703-1					Yellow	
PR-3704-1					Red	
PR-3705-1					Blue	
PR-3706-1					White	
PR-3707-1					Brown	
PR-3708-1					Orange	
PR-3709-1					Gray	
PR-3711-1					Violet	
PR-3119-5	Revere	Vinyl Electrical Tape		0.75in x 60ft	Black	Temflex 1700
PR-4275-1	Slipknot Platinum 8.5	Vinyl Electrical Tape	8.5 mil	0.75in x 66ft		Super 88
PR-4454-1	Slipknot Platinum 7.0	Vinyl Electrical Tape	7 mil	0.75in x 66ft		Super 33+



Vinyl Electrical Tape

Premium 37 Vinyl Electrical Tape

A 7 mil professional grade available in 9 colors for color coding with an excellent elasticity and insulating properties. High resistance against abrasion, water, oil, alkalis, acids, and corrosive chemicals. Use for quick identification of electrical circuits, containers, and conduit systems as well as primary insulation for splices not more than 600V.

Features

- Cold and weather resistant
- Flame retardant
- High dielectric strength
- Highly elastic
- Highly conformable
- High UV resistance
- Highly resistant to sun, water, oil, acids, alkalis, corrosive chemicals
- Meets ASTM D-3005, Type I; EN 60454-3-1, Type 11; UL 510; CSA C 22.2 no. 197
- Meets 2000/53/EC and RoHS 2011/65/EU directives
- Temperature range:
 - UL510: -10°C – 105°C (14°F – 221°F)
 - CSA C 22.2 no.197: -18°C – 105°C (-0.4°F – 221°F)



Vinyl Electrical Tape										
Part Number	Color	Description	Duty Grade	Size	Thickness	Elongation at Break	Dielectric Strength	Adhesion to Steel	Voltage	Price
<u>PR-3702-1</u>	Green	Premium 37 vinyl electrical tape	professional	0.75in x 66ft	7 mil	260%	1150 V/mil	<u>20 oz/in</u>	600V	\$5.00
<u>PR-3703-1</u>	Yellow									\$5.00
<u>PR-3704-1</u>	Red									\$5.00
<u>PR-3705-1</u>	Blue									\$5.00
<u>PR-3706-1</u>	White									\$5.00
<u>PR-3707-1</u>	Brown									\$5.00
<u>PR-3708-1</u>	Orange									\$5.00
<u>PR-3709-1</u>	Gray									\$5.00
<u>PR-3711-1</u>	Violet									\$5.00

Note: Values are typical data.



Vinyl Electrical Tape

Revere Vinyl Electrical Tape

A 7.0 mil general purpose grade characterized by its excellent performance and high durability, with good elasticity, level of adhesion, and insulating properties. Resists abrasion, water, oil, alkalis, acids, and corrosive chemicals. Great for use in harnessing, protective jacketing, as well as primary insulation for splices not more than 600V.

Features

- Meets EN 60454-3-1 and UL-510 standards.
- Meets 2000/53/EC and RoHS 2011/65/EU directives
- Temperature range:
 - UL510: -10°C – 80°C (14°F – 176°F)
 - CSA C 22.2 no.197: -10°C – 105°C (14°F – 221°F)
- Sold in quantity of 5



Slipknot Platinum 7.0

A 7.0 mil premium vinyl electrical tape included in our new Slipknot Vinyl series. A professional grade vinyl electrical tape specially designed for professional use with excellent elasticity even in cold weather applications. Primary insulation for splices up to 600V, protective outer jacket over splices and for all low temperature applications.



Slipknot Platinum 8.5

An 8.5 mil premium vinyl electrical tape included in our new Slipknot Vinyl series. A heavy-duty grade vinyl electrical tape specially designed for professional use with excellent elasticity even in cold weather applications. Primary insulation for splices up to 600V, protective outer jacket over splices and for all low temperature applications.



Slipknot Platinum 7.0 / 8.5 Features

- Cold and weather resistant. All-weather performance.
- Flame retardant
- High dielectric strength
- Highly elastic and conformable
- High UV resistance
- Cold & weather resistant
- High resistant to sun, water, oil, acids, alkalis, and corrosive chemicals
- Meets 2000/53/EC and RoHS 2 2011/65/EU directives
- Meets ASTM D-3005, Type I; EN 60454-3-1, Type 11; UL 510; CSA C 22.2 no. 197
- Temperature range:
 - UL510: -10°C – 80°C (14°F – 176°F)
 - CSA C 22.2 no.197: -18°C – 105°C (0°F – 221°F)

Platinum Vinyl Electrical Tape											
Part Number	Description	Duty Grade	Size	Thickness	Elongation at Break	Voltage	Dielectric Strength	Adhesion to Steel	Color	Quantity	Price
PR-3119-5	Revere	general purpose	0.75in x 60ft	7 mil	220%	600V	1200 V/mil	20 oz/in	Black	5	\$9.75
PR-4454-1	Slipknot Platinum 7.0	Professional	0.75in x 66ft		300%		1200 V/mil	27 oz/in		1	\$4.75
PR-4275-1	Slipknot Platinum 8.5	heavy duty		8.5 mil			1150 V/mil				\$5.50

Note: Values are typical data.



Insulating and Splicing Tape

150 ASTM Low Voltage Rubber Splicing Tape

A 30 mil self-amalgamating tape which can be used for insulating cables splices through 2kV, in conjunction with a jacketing tape. Meets ASTM D4388, Communications Industry Specification 6746.

Features

- Self-amalgamating
- Good electrical properties
- Effective moisture seal
- Good conformability



W963 Plysafe Rubber Tape w/ Liner

A 30 mil EPR, self-bonding, high voltage tape for insulating and jacketing splices through 69kV. W963 amalgamates quickly, yielding a void-free, electrically stable build-up and it's ideal for waterproofing. Meets ASTM D-4388, HH-I-553C/Grade A, MIL-I3825B standards.

Features

- Self-amalgamating
- Outstanding corona and ozone resistance
- UV resistance
- Excellent moisture, corrosion and chemical resistance



L969 Plyvolt Linerless Rubber Tape

A 30mil EPR, self-bonding, thermally conductive tape for insulating and jacketing splices through 69kV. L969 Plyvolt is linerless, allowing an easier application and a void-free build-up. This rubber tape provides excellent corona, ozone, and chemical resistance. It can also be used for building stress-cones on power cable through 35kV.

Features

- Linerless
- Self-amalgamating
- Outstanding corona and ozone resistance
- High thermal conductivity
- Excellent moisture, corrosion chemical resistance, and UV resistance
- Lead free



Insulating and Splicing Tape									
Part Number	Description	Size	Thickness	Voltage	Elongation at Break	Dielectric Strength	Maximum Temperature	Color	Price
PR-2006-1	150 ASTM rubber electrical tape	0.75in x 30ft	30 mil	2 kV	500%	508 V/mil	176 deg F (80 deg C)	Gray	\$7.25
PR-2117-1	W963 rubber electrical tape	0.75in x 30ft		69 kV	950%	1000 V/mil	194 deg F (90 deg C)	Black	\$11.00
PR-2211-1	L969 rubber Electrical Tape	0.75in x 30ft		69 kV	890%	990 V/mil			\$14.00
PR-2212-1		1in x 30ft		69 kV					\$18.00
PR-2213-1		1.5in x 30ft		69 kV					\$26.00
PR-2214-1		2in x 30ft		69 kV					\$33.00

Note: Values are typical data.



Insulating and Splicing Tape

20 Physil Silicone Rubber Tape

A 20 mil triangular cross-section, self-fusing tape, arc and track resistance, used for jacketing high voltage terminations on solid dielectric cable through 69kV.

Features

- Unique triangular cross-section
- Self-amalgamating
- -50°C to 200°C (-60°F to 400°F) operating temperature.
- UV resistant
- Oil resistant
- Center line for half-lapping guide



61/61A Varnished Dacron Glass Tape

A fine weave of Dacron and fiber glass threads, impregnated with a fully cured polyester coating which provides excellent electrical and mechanical protection. Available without adhesive (61/7 mil) and with adhesive (61A/8 mil).

Features

- Straight weave with bias characteristics
- Exceptionally high dielectric strength
- Retains dielectric strength on heat aging
- Excellent flexibility and conforms well to irregular shapes
- High tensile and edge-tear strength
- Meet requirements for Class F insulation



17 Plyshield Semi-Conducting Electrical Tape

An ethylene propylene rubber based, self-amalgamating and conducting tape. Its unsupported construction makes it ideal for use on power cable where accommodation of expansion and contraction due to load cycling is important. Use this semi-conducting tape for shielding cable from EMI, at termination points, and for providing a ground path for dissipating a charge resulting from EMI. The excellent stretch of 17 Plyshield allows conformability to complex shapes. Meets ASTM D-4388 Type IV standard.

Features

- Self-amalgamating retains good conducting properties
- Easy to apply
- UV resistance



Insulating and Splicing Tape - Cont'd											
Part Number	Description	Size	Thickness	Voltage	Adhesion to Steel	Elongation at Break	Dielectric Strength	Maximum Temperature	Color	Special	Price
<u>PR-3455-1</u>	20 Physil silicone rubber tape	1in x 30ft	20 mil	69 kV	n/a	300%	610 V/mil	400 deg F (204 deg C)	Gray	n/a	\$29.00
<u>PR-1101-1</u>	61 Fabric electrical tape	0.75in x 60ft	7.1 mil	n/a		n/a	1270 V/mil	311 deg F (155 deg C)	Yellow	w/o adhesive	\$57.00
<u>PR-1121-1</u>	61A Fabric electrical tape		7.9 mil		w/ adhesive					\$60.00	
<u>PR-2104-1</u>	17 Plyshield semi-conducting rubber electrical tape	0.75in x 15ft	30 mil			n/a	750%	n/a	194 deg F (90 deg C)	Black	n/a

Note: Values are typical data.



Mastics and Specialty Tapes

Vinyl Mastic

A self-fusing mastic compound with an all weather vinyl backing that adds UV protection. It can be used for insulating and water sealing electrical connections through 600V. Excellent electrical properties, superior adhesion, moisture and chemical resistance.

10 Plyseal Insulating Mastic

A self-amalgamating insulating mastic for insulating and sealing all types of overhead and direct buried electrical connections up to 600V. Excellent adhesion to metals, cable insulations and jackets. For water-sealing duct work cable ends and all types of splices.

77 Plyglas Glass Cloth Tape

A 7 mil woven glass fabric tape with a thermosetting rubber based adhesive used for protecting and insulating high temperature connections (130°C/266°F), such as motor leads, and transformed windings. High tensile strength for splice reinforcement. Excellent tear and abrasion resistance.



PR-2609-1



PR-2626-1



PR-3456-1

Sealing and Insulating Mastics									
Part Number	Style	Size	Thickness	Voltage	Dielectric Strength	Adhesion to Steel	Maximum Temperature	Color	Price
PR-2609-1	VM Mastic electrical tape	4in x 10ft	47 mil	600V	330 V/mil	200 oz/in	194 deg F (90 deg C)	Black	\$24.00
PR-2626-1	10 Plyseal Mastic electrical tape	3.75in x 10ft	126 mil		508 V/mil	n/a*			\$34.50
PR-3456-1	77 Plyglas Cloth Electrical Tape	0.75in x 66ft	7 mil		350V/mil	16 oz/in	266 deg F (130 deg C)	White	\$18.00

Note: Values are typical data.

*Excellent adhesion to metals, cable insulations, and jackets.