

pro^{sense}® Differential Pressure Gauges

Accessories

Applications




- **DGA-T Static Pressure Tip:**
Use the **DGA-T** to sense static pressure in ducts, across filters, coils, fans, etc. The angled tip is brass, has a 4" insertion depth and four radial 0.04" sensing holes. The tip also has a compression fitting for use with 1/4" OD metal or plastic tubing.
- **DGA-B Surface Mount Bracket:**
Mount the DGA gauge to the pre-drilled holes in the metal **DGA-B** mounting bracket and then mount the bracket to any vertical flat surface.
- **DGA-R Panel Mount Flange:**
Secure the plastic flange to the DGA gauge with the three set screws in the flange. The DGA can now be mounted to a panel using the three mounting holes in the flange and the included mounting screws.

Part No. **DGA-B**Part No. **DGA-R**Part No. **DGA-T**Part **DGA-B** shown with
DGA Differential Pressure
GaugePart **DGA-R** shown with
DGA Differential Pressure
Gauge

ProSense Differential Pressure Gauges Accessories				
Part Number	Description	Pcs/Pkg	Wt(lb)	Price
DGA-T	ProSense static pressure tip with compression fitting, brass, for use with DGA series differential pressure gauges or DPTA series differential pressure transmitters.	1	0.07	\$18.00
DGA-B	ProSense surface mount bracket, aluminum, for use with DGA series differential pressure gauges. Hardware included.	1	0.1	\$11.50
DGA-R	ProSense panel mount flange, ABS plastic, for use with DGA series differential pressure gauges. Hardware included.	1	0.15	\$12.00

Dimensions

inches [mm]

Part No. **DGA-R**Part No. **DGA-B**Part No. **DGA-T**See our website www.AutomationDirect.com for complete Engineering drawings.