

PMW Series Inductive Proximity Sensors



M12 (12mm) Stainless Steel – DC

- Low cost/high performance
- LED status indicators are visible at a wide angle.
- Axial cable or M12 quick-disconnect models
- Purchase cable separately (for quick-disconnect models).
- Lifetime warranty



PMW Series M12 DC Inductive Proximity Selection Chart

| Part Number | Price | Sensing Range | Mounting | Output State | Logic | Connection | Wiring | Dimensions |
|---------------------------|----------|----------------|-----------|--------------|-------|-------------------------|-----------|------------|
| Standard Distance | | | | | | | | |
| PMW-0N-1H | \$46.50 | 2mm [0.08 in] | Flush | N.O./N.C. | NPN | M12 [12mm] connector | Diagram 3 | Figure 1 |
| PMW-0P-1H | \$46.50 | | | | PNP | M12 [12mm] connector | Diagram 4 | Figure 1 |
| PMW-0N-2H | \$46.50 | 4mm [0.157 in] | Non-flush | N.O./N.C. | NPN | M12 [12mm] connector | Diagram 3 | Figure 1 |
| PMW-0P-2H | \$46.50 | | | | PNP | M12 [12mm] connector | Diagram 4 | Figure 1 |
| Triple Distance | | | | | | | | |
| PMW-AN-5A | \$111.00 | 6mm [0.236 in] | Flush | N.O. | NPN | 2m [6.5 ft] axial cable | Diagram 1 | Figure 2 |
| PMW-AP-5A | \$111.00 | | | | PNP | 2m [6.5 ft] axial cable | Diagram 2 | Figure 2 |
| PMW-AN-5H | \$111.00 | | | | NPN | M12 [12mm] connector | Diagram 1 | Figure 3 |
| PMW-AP-5H | \$111.00 | | | | PNP | M12 [12mm] connector | Diagram 2 | Figure 3 |

Wiring Diagrams

Diagram 1
NPN Output






Diagram 2
PNP Output



Connector
M12 connector



Note: Pin 2 is not present on some models.

Diagram 3
NPN Output





Diagram 4
PNP Output



PMW Series Inductive Proximity Sensors

PMW Series M12 DC Inductive Proximity Specifications

| Models | Standard Distance | Triple Distance |
|---|--|--|
| Mounting Type | Flush | Flush |
| Nominal Sensing Distance | 2mm [0.08 in] ¹ | 6mm [0.236 in] |
| Operating Distance | NA | |
| Material Correction Factors | See the Material influence table | |
| Output Type | NPN or PNP and N.O./N.C. complementary | NPN or PNP, N.O. only |
| Operating Voltage | 10 to 30 VDC | |
| No-load Supply Current | ≤15 mA | ≤10 mA |
| Operating (Load) Current | ≤100 mA | ≤ 00 mA |
| Off-state (Leakage) Current | ≤1 0μA | ≤100μA |
| Voltage Drop | ≤1.2 V | ≤2.0 V |
| Switching Frequency | 2kHz | 400Hz |
| Differential Travel (% of Nominal Distance) | 2 to 10% | ≤ 15% |
| Repeat Accuracy | ≤5% | |
| Ripple | ≤10% | ≤ 20% |
| Time Delay Before Availability (tv) | 100ms | ≤10 ms |
| Reverse Polarity Protection | Yes | |
| Short-circuit Protection | Yes | |
| Operating Temperature / Temperature Drift | -25 to 70°C [-13 to 158°F] / 10%Sr | |
| Protection Degree (DIN 40050) | IEC IP67/68 | IEC IP67 ² (connector/IP68 ² cable) |
| Indication/Switch Status | Yellow (N.O. output energized) | |
| Housing Material | Stainless steel | Stainless steel |
| Sensing Face Material | PPS | Stainless steel |
| Shock/Vibration | See Proximity Sensor Terminology | |
| Tightening Torque | 10Nm [7.25 lb-in] | |
| Weight | 35g [1.23 oz] | 89g [3.14 oz] |
| Connections | M12 connector with gold-plated contacts | |
| Agency Approvals | NA | UL file E328811, RoHS |

Notes: ¹With 12 x 12mm FE360 target

²Fully submersible to 290 psi.

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Dimensions

mm[inches]

Figure 1




Figure 2




Figure 3





Figure 4



Note: Pin 2 is not present on some models.

Accessories for 12mm Sensors

Axial Mounting Bracket

Mounting bracket, axial, available in zinc-plated steel or 316L stainless steel. For use with 12mm sensors. Has two mounting holes (use 3mm screws) and allows the rotation of an optical axis for right-angle adapter sensors. Hexagonal nuts not included.

| Accessories for 12mm Sensors | | | | |
|--------------------------------|--------|--|----------------------------|---------------|
| Part Number | Price | Description | Drawing Link | Weight lb [g] |
| <u>ST12A</u> | \$2.00 | Micro Detectors mounting bracket, axial, zinc plated steel. For use with 12mm sensors. | <u>PDF</u> | 0.03 [13.6] |
| <u>ST12A7W</u> | \$7.25 | Micro Detectors mounting bracket, axial, 316L stainless steel. For use with 12mm sensors. | <u>PDF</u> | 0.03 [13.6] |



[ST12A](#)

Right-angle Mounting Bracket

Mounting bracket, right-angle, zinc-plated steel or 316L stainless steel. For use with 12mm sensors. Has two mounting holes (use 3mm screws) and allows the rotation of an optical axis for axial sensors. Hexagonal screws not included.

| Accessories for 12mm Sensors | | | | |
|--------------------------------|--------|--|----------------------------|---------------|
| Part Number | Price | Description | Drawing Link | Weight lb [g] |
| <u>ST12C</u> | \$2.00 | Micro Detectors mounting bracket, right-angle, zinc plated steel. For use with 12mm sensors. | <u>PDF</u> | 0.03 [13.6] |
| <u>ST12C7W</u> | \$7.25 | Micro Detectors mounting bracket, right-angle, 316L stainless steel. For use with 12mm sensors. | <u>PDF</u> | 0.03 [13.6] |



[ST12C](#)

Accessories for 12mm Sensors

Right-angle Mounting Brackets

Mounting bracket, right-angle, fixed insertion stop adjustment, plastic. For use with 12mm sensors. Available with or without fixed insertion stop.

| Accessories for 12mm Sensors | | | | |
|--------------------------------|--------|---|----------------------------|---------------|
| Part Number | Price | Description | Drawing Link | Weight lb [g] |
| <u>OPT2102</u> | \$8.00 | Wenglor mounting bracket, right-angle, fixed insertion stop adjustment, plastic. For use with 12mm sensors. | <u>PDF</u> | 0.05 [22.7] |
| <u>OPT2103</u> | \$8.00 | Wenglor mounting bracket, right-angle, plastic. For use with 12mm sensors. | <u>PDF</u> | 0.05 [22.7] |



[OPT2102](#), [OPT2103](#)

Right-angle Swivel Mounting Systems

Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 12mm rod mount. For use with 12mm sensors. Available in all stainless steel or with an aluminum head and stainless steel mounting plate.

| Accessories for 12mm Sensors | | | | | | |
|--------------------------------|---------|--|---------------------|---------------------|----------------------------|---------------|
| Part Number | Price | Description | Mounting Head | Mounting Plate | Drawing Link | Weight lb [g] |
| <u>OPT2114</u> | \$11.50 | Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with 12mm sensors. | Aluminum | Stainless steel | <u>PDF</u> | 0.14 [63.5] |
| <u>OPT2115</u> | \$21.00 | Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with 12mm sensors. | 304 Stainless steel | 304 Stainless steel | <u>PDF</u> | 0.27 [122.5] |

Note: 304 stainless steel mounting rods sold separately: [OPT2109](#) (200mm [7.87 in] length), [OPT2110](#) (300mm [11.81 in] length), and [OPT2111](#) (500mm [19.69 in] length).



[OPT2114](#), [OPT2115](#)

Mounting Rods and Brackets

Mounting Rods

304 Stainless steel rods for mounting swivel brackets [OPT2112](#) - [OPT2127](#). Available in three lengths: 200mm, 300mm, and 500mm. 12mm diameter.

| Mounting Rods for OPT2112-2127 Swivel Mounting Brackets | | | | |
|---|---------|---|---------------------|------------------|
| Part Number | Price | Description | Drawing Link | Weight lb (g) |
| OPT2109 | \$13.00 | Wenglor mounting rod, 12mm diameter, 200mm length, 304 stainless steel. | PDF | 0.41 [185.97] |
| OPT2110 | \$16.00 | Wenglor mounting rod, 12mm diameter, 300mm length, 304 stainless steel. | PDF | 0.60 [272.16] |
| OPT2111 | \$21.00 | Wenglor mounting rod, 12mm diameter, 500mm length, 304 stainless steel. | PDF | 0.98 [444.52] |



Right-angle Mounting Bracket

Mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods [OPT2109](#), [OPT2110](#) & [OPT2111](#).

| Right-angle Mounting Brackets for 12mm Sensors | | | | |
|--|---------|---|---------------------|----------------|
| Part Number | Price | Description | Drawing Link | Weight lb [g] |
| OPT2108 | \$16.00 | Wenglor mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods OPT2109, OPT2110 & OPT2111. | PDF | 0.07 [31.8] |

