



prosense® Thermocouple Probes with Connection Head

Overview

THMJ & K - CXX-01 & 04



THMJ & K - CXX-02



- Probe
 - Type J or K thermocouple elements to meet many temperature sensing applications
 - 1/4" diameter, 316 SS or Inconel Alloy 600 sealed sheath to protect against harsh environments
 - Magnesium Oxide (MgO) insulation provides vibration dampening and protection against thermal shock
 - Bendable to adapt to installation requirements
 - 6", 12" or 18" probe length
- Connection Head
 - Cast aluminum NEMA 4X, IP66 screw cover head with captive gasket
 - One turn cover removal & installation eliminates cross threading and saves time
 - 3/4" NPT conduit opening with internal stop to prevent overtightening and installation damage
 - Gripping ribs on cover edge
 - Stainless steel cover chain
- Wiring
 - Ceramic terminal base
 - Brass terminals with stainless steel screws eliminate the need to wrap connections around screws
 - Elevated terminal block for easy wire termination
- Made in the USA

Thermocouple Probes with Connection Head - Types J and K

Part Number	Pcs/Pkg	Wt (lb)	Price	Type	Probe Diameter (O.D.)	Probe Length	Probe Material	Temperature Sensing Range	Mounting
THMJ-C06-01	1	1.3	\$72.00	J	1/4"	6"	316 stainless steel	0 to 720°C (32 to 1330°F)	Integral 1/2" x 1/2" NPT Hex Nipple, 316 SS
THMJ-C12-01			\$77.00	J		12"			
THMJ-C18-01			\$80.00	J		18"			
THMK-C06-01			\$72.00	K		6"			
THMK-C12-01			\$77.00	K		12			
THMK-C18-01			\$80.00	K		18"			
THMJ-C06-02			\$69.00	J		6"		0 to 927°C (32 to 1700°F)	
THMJ-C12-02			\$70.00	J		12"			
THMJ-C18-02			\$71.00	J		18"			
THMK-C06-02			\$69.00	K		6"			ProSense compression fitting (see accessories - purchased separately)
THMK-C12-02			\$70.00	K		12"			
THMK-C18-02			\$71.00	K		18"			
THMK-C06-04			\$75.00	K		6"	Inconel Alloy 600	0 to 1149°C (32 to 2100°F)	Integral 1/2" x 1/2" NPT Hex Nipple, 316 SS
THMK-C12-04			\$85.00	K		12"			
THMK-C18-04			\$93.00	K		18"			

Technical Specifications

Junction Type	Ungrounded
ASTM E230 Standard Limits of Error	±2.2°C (±4.0°F) or 0.75%, whichever is greater
Probe	4", 316 stainless steel or Inconel Alloy 600 sheath, single thermocouple element is embedded in MgO powder
Probe Minimum Bend Radius	2 x sheath diameter
Minimum Installation Depth	3" (76 mm)
Connection Head	Die-cast aluminum, screw cover with stainless steel chain, compressed graphite gasket, NEMA 4X, IP66, 3/4" NPT conduit opening, max temp. 400°F (204°C)
Response Time	2.9 seconds, 63.2% of a 25-77°C step change per method ASTM E839
Wiring	Ceramic terminal base with brass terminals and stainless steel screws (Recommended tightening torque 3-4 lb-in)




Note: Check the chemical compatibility of the sensor's wetted parts with the medium to be measured. Not designed for use in a thermowell. Use spring-loaded probe when installing in a thermowell.

prosense® Thermocouple Probes with Connection Head

Dimensions


inches [mm]

THMJ & K - CXX-01 & 04



PART NUMBER	DIM "A"	DIM "B"
THMJ-C06-01	6.00[152.4]	11.33[287.8]
THMJ-C12-01	12.00[304.8]	17.33[440.2]
THMJ-C18-01	18.00[457.2]	23.33[592.6]
THMK-C06-01	6.00[152.4]	11.33[287.8]
THMK-C12-01	12.00[304.8]	17.33[440.2]
THMK-C18-01	18.00[457.2]	23.33[592.6]
THMK-C06-04	6.00[152.4]	11.33[287.8]
THMK-C12-04	12.00[304.8]	17.33[440.2]
THMK-C18-04	18.00[457.2]	23.33[592.6]


Wiring Information




Type J: (+) white (-) red
Type K: (+) yellow (-) red

- Must use thermocouple extension lead wire
- Observe polarity when making connections
- Do not use standard wire nuts
- Recommended screw terminal tightening torque 3-4 lb-in

THMJ & K - CXX-02



PART NUMBER	DIM "A"	DIM "B"
THMJ-C06-02	6.00[152.4]	10.64[270.3]
THMJ-C12-02	12.00[304.8]	16.64[422.7]
THMJ-C18-02	18.00[457.2]	22.64[575.1]
THMK-C06-02	6.00[152.4]	10.64[270.3]
THMK-C12-02	12.00[304.8]	16.64[422.7]
THMK-C18-02	18.00[457.2]	22.64[575.1]



Accessories

Part No.	Description	Pcs/Pkg	Price
BCF14-125N	Compression fitting, brass, for 1/4 inch diameter temperature probes, 1/8 inch male thread	1	\$3.25
BCF14-25N	Compression fitting, brass, for 1/4 inch diameter temperature probes, 1/4 inch male thread	1	\$4.25
BCF14-50N	Compression fitting, brass, for 1/4 inch diameter temperature probes, 1/2 inch male thread	1	\$6.50
CF14-125N	Compression fitting, 316 stainless steel, for 1/4 inch diameter temperature probes, 1/8 inch male thread	1	\$8.00
CF14-25N	Compression fitting, 316 stainless steel, for 1/4 inch diameter temperature probes, 1/4 inch male thread	1	\$9.25
CF14-50N	Compression fitting, 316 stainless steel, for 1/4 inch diameter temperature probes, 1/2 inch male thread	1	\$14.00
CFTE-14	Teflon ferrule for brass or stainless steel compression fittings and 1/4 inch diameter temperature probes	5	\$7.75

Note: Full listing of accessories available at the end of this section. Thermocouple extension lead wire available at www.automationdirect.com.