


# proense® RTD Bolt-On Ring Sensors



## Overview

- Ideal for many surface mount sensing applications
- 100 ohm platinum RTD 3-wire element
- Class A accuracy
- Brass ring construction
- 6-foot lead wires with Kapton insulation and stainless steel overbraid
- Made in the USA

RTD Probes with Leadwire Transition							
Part Number	Pcs/Pkg	Wt (lb)	Price	Type	Ring Material	Temperature Sensing Range	Mounting
<b>RTD1-B01L06-01</b>	1	0.4	\$72.00	PT 100, 3-wire	Brass	-50 to 300°C (-58 to 572°F)	Bolt on #6-#10 (4mm-5mm) screw or bolt size
<b>RTD1-B02L06-01</b>	1	0.4	\$76.00	PT 100, 3-wire	Brass	-50 to 300°C (-58 to 572°F)	Bolt on #12, 1/4 to 5/16 inch (5mm - 8mm) screw or bolt size


Technical Specifications	
<b>Sensing Element</b>	Single 100Ω platinum (Pt 100), 3-wire; TCR = 0.00385 Ω/Ω/°C
<b>Initial Accuracy</b>	Class A ±[0.15 + 0.002  t ] °C
<b>Response Time</b>	7 seconds, 63% of a 25 to 77°C step change (ASTM E1137)
<b>Wiring</b>	6 foot stranded 24 AWG wire leads with stripped ends, Kapton insulation and stainless steel overbraid




Note: Check the chemical compatibility of the sensor's wetted parts with the medium to be measured.

## Dimensions

inches [mm]



## Wiring Information



PART NUMBER	DIM "A"	DIM "B"	DIM "C"
RTD1-B01L06-01	0.63[15.9]	0.38[9.5]	0.20[5.2]
RTD1-B02L06-01	0.88[22.2]	0.63[15.9]	0.33[8.3]

## Accessories

Part No.	Description	Pcs/Pkg	Price
<b>RTD-SP</b>	RTD 3-pin connector, standard round pin plug, maximum continuous temperature 400°F (200°C), white body, copper pins, 14 AWG maximum (2.0 mm) wire size	1	\$9.00
<b>RTD-SJ</b>	RTD 3-pin connector, standard round pin jack, maximum continuous temperature 400°F (200°C), white body, copper pins, 14 AWG maximum (2.0 mm) wire size	1	\$11.50
<b>WCB-S</b>	Wire / cable clamp bracket for use with standard thermocouple and RTD connectors.	4	\$7.00

Note: Full listing of accessories and dimension information available at the end of this section. RTD extension lead wire available at [www.automationdirect.com](http://www.automationdirect.com)