



Cat5e Ethernet

Q5943-1 Cable Specifications

		Part Number	Wire/Cable Type	Flexibility	Minimum Cut Length (ft)*	Approximate Weight (lb/ft)	Price per foot
		Q5943-1	Cat5e Ethernet	Semi-flexible	20	0.03	\$0.64
Physical Properties							
Conductor Gauge		24 AWG	Conductor Stranding		Solid Bare Copper		
Conductor Material		Bare Copper	Conductor Insulation Wall Thickness		0.008 in, nominal		
Conductor Assembly		4 twisted pairs	Bare Conductor Diameter		0.022 in, nominal		
Color Code	Pair 1	Blue, White/Blue	Insulated Conductor Diameter		0.038 in, nominal		
	Pair 2	Orange, White/Orange	Twisted Conductor Diameter		0.076 in, nominal		
	Pair 3	Green, White/Green	Overall Cable Diameter		0.230 in, nominal		
	Pair 4	Brown, White/Brown	Jacket Color		Black		
Voltage Rating		300V	Jacket Thickness		0.033 in, nominal		
Temperature Rating		-40 to 75 °C (-40 to 167 °F)	Jacket Material		PVC		
Plenum		No	Sunlight Resistant		Yes		
Shield		Unshielded	Oil Resistance		No		
Drain		No	Flame Retardant		No		
Conductor Insulation Material		Polyethylene	Sample Print Legend		QUABBIN DATAMAX 5E 350 MHZ ISO 11801 PATCH CORD P/N xxxx--(UL) TYPE CMR 24 AWG 75C --CSA LL51726 TYPE CMG 60C --ETL VERIF. TIA-568-C.2 CAT 5e --RoHS --(LOT DESIGNATOR) (SEQUENTIAL FOOTAGE)		
Minimum Bend Radius		2.30in					
Cabled Core Diameter		0.164 in					
Electrical Characteristics (for 100 meters of cable)							
Impedance		100 ± 200 Ω (1 - 200 MHz)	UL Classification		(UL) Type CMR, & CMX		
Capacitance		13.5 pF/ft @ 1MHz; Nominal	Approvals**		cULus, ETL, RoHS		
Resistance, Max.		26.2 Ω DC per 1000ft	Attenuation Crosstalk Ratio, Far End (ACRF)		1 ≤ f ≤ 200 MHz: 23.8 - 20 LOG(f/100) dB MIN		
Dielectric Withstanding, Min.		1500V RMS	Insertion Loss		1 ≤ f ≤ 200 MHz: 1.967 √f + 0.023(f) + 0.050/√f dB MAX		
Return Loss		1 ≤ f < 10 MHz: 20 + 5 LOG(f) dB MIN 10 ≤ f < 20 MHz: 25 dB MIN 20 ≤ f ≤ 200 MHz: 25 - 7 LOG(f/20) dB MIN	Power Sum Attenuation to Crosstalk Ratio, Far End (PSACRF)		1 ≤ f ≤ 200 MHz: 20.8 - 20 LOG(f/100) dB MIN		
Near End Crosstalk (NEXT)		1 ≤ f ≤ 200 MHz: 35.3 - 15 LOG(f/100) dB MIN	Cross Section				
Power Sum Near End Crosstalk (PSNEXT)		1 ≤ f ≤ 200 MHz: 32.3 - 15 LOG(f/100) dB MIN					
TCL		N/A					
ELTCTL		N/A					
Velocity of Propagation		0.68					
Delay		1 ≤ f ≤ 200 MHz: 534 + 36/√f ns MAX					
Delay Skew		1 ≤ f ≤ 200 MHz: <25 ns					

* See web store www.AutomationDirect.com for maximum cut lengths

** To obtain the most current agency approval information, see the Agency Approval Checklist section on the part number's web page at www.AutomationDirect.com



Please Note: Our prices on Ethernet Cable are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.



DataMax® Ethernet Cables

Quabbin DataMax Ethernet Cable

The Quabbin DataMax® Category network cables are proudly made in the USA and are available in Cat5e, 6, 6a or 6e. These cables are offered in 26AWG or 24AWG stranded tinned copper or bare solid copper in shielded or unshielded constructions. Designed to be round and smooth, Quabbin DataMax® Category network cables are compatible with most popular plugs for quick termination and easy installation.

When it comes to network cable, flexibility can mean many different things. The first and most obvious is the ease with which it bends. The importance behind having a pliable cable has to do with installation and cabinet routing. Flexibility allows easy manipulation between devices while increasing the durability, which is important when considering a lifetime of "moves & changes" that can occur in a dynamic network environment. Durability is paramount in allowing these changes to take place without compromising the cable.

The Quabbin DataMax® Category network cables exceed the requirements of ANSI/TIA-568-C.2, are compatible with Cat 5e and 6 hardware, and are suitable for applications from 10 Base-T to 1000 Base-T (Gigabit Ethernet).

Also available are Quabbin DataMax® MIL-spec Cat6 cables with black low smoke PVC jacket and special conductor insulations colors.

* DataMax is a registered trademark of Quabbin Wire and Cable Corporation.

** EtherNet/IP is a trademark of ODVA, Inc.

Features

- Available in Category 5e, 6, 6e, and 6a
- In compliance with TIA 568-C.2 and TIA 1005
- Designed for use in EtherNet/IP systems **
- 4 twisted pairs
- Unshielded or overall foil shields
- UL Type CM and UL AWM Style 2463 (80°C, 600V)
- Some cables available with conductor color code for MIL spec applications
- Cut to length in 1 foot increments
- Low 20 foot minimum length
- Made in the USA



Click on the thumbnail or go to
<https://www.automationdirect.com/VID-WD-0016>
 for a short introduction on our cut to length cable

