

OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door



Description

Each OKK Series expansion bay kit contains all the components required to expand one enclosure of the same height and depth.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

[Configuration Tool](#)



View assembly guide with the link button or QR code below:

[Assembly Guide](#)



OKK Series Expansion Bay Kit – NEMA 12 Freestanding Single-Door



OKK Series Expansion Bay Kit – NEMA12 Freestanding Single-Door				
Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-X180604CSBF	\$883.50	1800 x 600 x 400 [70.87 x 23.62 x 15.75]	(1) MTK180-4, (1) OKKTB6040, (1) PNA186, (1) DBE186, (1) RPE186, (1) UTK700, (1) FUP188 and (1) TTP040	PDF
QTA-X180606CSBF	\$964.00	1800 x 600 x 600 [70.87 x 23.62 x 23.62]	(1) MTK180-4, (1) OKKTB6060, (1) PNA186, (1) DBE186, (1) RPE186, (1) UTK700, (1) FUP188 and (1) TTP060	PDF
QTA-X180608CSBF	\$1,063.75	1800 x 600 x 800 [70.87 x 23.62 x 31.50]	(1) MTK180-4, (1) OKKTB6080, (1) PNA186, (1) DBE186, (1) RPE186, (1) UTK700, (1) FUP188 and (1) TTP080	PDF
QTA-X180804CSBF	\$996.50	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (1) PNA188, (1) DBE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP040	PDF
QTA-X180806CSBF	\$1,036.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (1) PNA188, (1) DBE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP060	PDF
QTA-X180808CSBF	\$1,141.75	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (1) PNA188, (1) DBE188, (1) RPE188, (1) UTK700, (1) FUP188 and (1) TTP080	PDF
QTA-X181004CSBF	\$1,068.50	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (1) PNA18A, (1) DBE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP040	PDF
QTA-X181006CSBF	\$1,117.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (1) PNA18A, (1) DBE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP060	PDF
QTA-X181008CSBF	\$1,236.75	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (1) PNA18A, (1) DBE18A, (1) RPE18A, (1) UTK700, (1) FUP188 and (1) TTP080	PDF
QTA-X200604CSBF	\$995.50	2000 x 600 x 400 [78.74 x 23.62 x 15.75]	(1) MTK200-4, (1) OKKTB6040, (1) PNA206, (1) DBE206, (1) RPE206, (1) UTK700, (1) FUP208 and (1) TTP040	PDF
QTA-X200606CSBF	\$1,076.00	2000 x 600 x 600 [78.74 x 23.62 x 23.62]	(1) MTK200-4, (1) OKKTB6060, (1) PNA206, (1) DBE206, (1) RPE206, (1) UTK700, (1) FUP208 and (1) TTP060	PDF
QTA-X200608CSBF	\$1,175.75	2000 x 600 x 800 [78.74 x 23.62 x 31.50]	(1) MTK200-4, (1) OKKTB6080, (1) PNA206, (1) DBE206, (1) RPE206, (1) UTK700, (1) FUP208 and (1) TTP080	PDF
QTA-X200804CSBF	\$1,113.50	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (1) PNA208, (1) DBE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP040	PDF
QTA-X200806CSBF	\$1,153.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (1) PNA208, (1) DBE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP060	PDF
QTA-X200808CSBF	\$1,258.75	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (1) PNA208, (1) DBE208, (1) RPE208, (1) UTK700, (1) FUP208 and (1) TTP080	PDF
QTA-X201004CSBF	\$1,200.50	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (1) PNA20A, (1) DBE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP040	PDF
QTA-X201006CSBF	\$1,249.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (1) PNA20A, (1) DBE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP060	PDF
QTA-X201008CSBF	\$1,368.75	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (1) PNA20A, (1) DBE20A, (1) RPE20A, (1) UTK700, (1) FUP208 and (1) TTP080	PDF
Note: Dimensions in millimeters [inches].				