

Quabbin Ethernet Cable - Cat6/6a/6e

Ethernet Cat6/6a/6e Cable Selection									
Part Number	Wiring Standard	Jacket Color	Shield	No. of Pairs	Pair Colors	Description	Approximate Weight (lb/ft)	Minimum Cut Length (ft)*	Price per foot
<u>Q2034-1</u>	6a	Black	Shielded	4	Pair 1: Natural & Orange Pair 2: Gray & Brown Pair 3: Natural & Green Pair 4: Gray & Blue	shielded, 4 twisted pairs, 28 AWG, 7-stranded, tinned copper, foamed FEP conductor insulation material, PVC jacket, black, cut to length.	0.017	20	\$1.16
<u>Q2045-1</u>	6					shielded, 4 twisted pairs, 28 AWG, 7-stranded, tinned copper, foamed FEP conductor insulation material, PVC jacket, black, cut to length.	0.017		\$1.10
<u>Q2056-1</u>	6a					shielded, 4 twisted pairs, 26 AWG, 7-stranded, tinned copper, foamed FEP conductor insulation material, PVC jacket, black, cut to length.	0.022		\$1.18
<u>Q2067-1</u>	6					shielded, 4 twisted pairs, 26 AWG, 7-stranded, tinned copper, foamed FEP conductor insulation material, PVC jacket, black, cut to length.	0.022		\$0.99
<u>Q2206-1</u>	Cat6e	Blue	Unshielded		Pair 1 - Blue/White & Blue Pair 2 - Orange/White & Orange Pair 3 - Green/White & Green Pair 4 - Brown/White & Brown	unshielded, 4 twisted pairs, 24 AWG, 7-stranded, tinned copper, polyethylene conductor insulation material, PVC jacket, blue, cut to length.	0.024		\$0.49
<u>Q2936-1</u>	Cat6		Shielded			shielded, 4 twisted pairs, 26 AWG, 7-stranded, tinned copper, polyethylene conductor insulation material, PVC jacket, blue, cut to length.	0.025		\$0.72
<u>Q2948-1</u>	Cat6a					shielded, 4 twisted pairs, 26 AWG, 7-stranded, tinned copper, polyethylene conductor insulation material, PVC jacket, blue, cut to length.	0.025		\$0.76

*See web store for maximum cut lengths



Please Note: Our prices on Ethernet Cables are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.

Quabbin Ethernet Cable - Cat6a

Ethernet Cat6a Cable Specifications				
		Physical Properties		
		Q2948-1	Q2034-1	Q2056-1
Conductor Gauge and Stranding		26AWG 7/34 solid bare copper; 4 twisted pairs	28AWG 7/36 stranded tinned copper; 4 twisted pairs	26AWG 7/34 stranded tinned copper; 4 twisted pairs
Assembly		Individual conductors twisted into pairs with a central spline and polyester binder under foil shield and PVC Jacket		
Jacket		Blue Polyvinylchloride (PVC)		
Jacket Insulation Thickness		0.024 inch; Nominal		
Shield		Aluminized Polyester Foil Shield (Foil In, 100% Coverage) with 26AWG Tinned Copper Drain		
Cable Overall Diameter		0.235 inch; Nominal		
Temperature Rating		-20°C to 75°C (-4°F to 167°F)		
Plenum		No		
Sunlight Resistant		No		
Conductor Insulation		High Density Polyethylene (HDPE)		
Color Code	Pair 1	Blue/White & Blue		
	Pair 2	Orange/White & Orange		
	Pair 3	Green/White & Green		
	Pair 4	Brown/White & Brown		
Bare Conductor Diameter		0.019 inch; Nominal		
Conductor Insulation Thickness		0.009 inch; Nominal		
Insulated Conductor Diameter		0.036 inch; Nominal		
Pair Diameter		0.072 inch; Nominal		
Cabled Core Diameter		0.208 inch; Nominal		
Print Legend		QUABBIN DATAMAX 6a F/UTP 100 OHM PATCH CORD P/N xxxx -- TYPE CMR C(UL) US CMG 4 PR 26 AWG SHIELDED 75C -- FT4/IEEE 1202 -- CAT 6a TIA-568.2-D -- RoHS -- (LOT DESIGNATOR) (SEQUENTIAL FOOTAGE)		



Please Note: Our prices on Ethernet Cables are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.

Quabbin Ethernet Cable - Cat6a

Ethernet Cat6a Cable Specifications (continued)			
	Electrical Characteristics (for 100 meters of cable)		
	<u>Q2948-1</u>	<u>Q2034-1</u>	<u>Q2056-1</u>
Impedance (1-100 MHz)	100Ω ±15Ω (1-200 MHz)	100Ω ±15Ω (1 - 500MHz)	100 ± 15 Ω (1 - 100 MHz) 100 ± 20 Ω (100 - 500 MHz)
Capacitance	13.5 pF/ft @ 1MHz; Nominal		
Resistance (nom)	26.0 Ω DC per 1000ft	68.2 Ω DC per 1000ft	42.6 Ω DC per 1000ft
Voltage Rating (max)	300V		
Dielectric Withstand, Min.	1500V RMS		
Return Loss	$1 \leq f < 10 \text{ MHz}$ 20 + 5 LOG(f) dB MIN	$1 \leq f < 2 \text{ MHz}$ 17 + 9.5 LOG(f) dB MIN	$1 \leq f < 10 \text{ MHz}$ 20 + 5 LOG(f) dB MIN
	$10 \leq f < 20 \text{ MHz}$ 25 dB MIN	$2 \leq f < 10 \text{ MHz}$ 20 + 5 LOG(f) dB MIN	$10 \leq f < 20 \text{ MHz}$ 25 dB MIN
	$20 \leq f \leq 500 \text{ MHz}$ 25 – 8.6 LOG(f/20) dB MIN	$10 \leq f < 20 \text{ MHz}$ 25 dB MIN	$20 \leq f \leq 250 \text{ MHz}$ 25 - 8.6 LOG(f/20) dB MIN
	$1 \leq f \leq 500 \text{ MHz}$ 44.3 – 15 LOG(f/100) dB MIN	$20 \leq f < 500 \text{ MHz}$ 25 - 8.6 LOG(f) dB MIN	
Near End Crosstalk (NEXT)	$1 \leq f \leq 500 \text{ MHz}$ 42.3 – 15 LOG(f/100) dB MIN	$1 \leq f \leq 500 \text{ MHz}$ 44.3 - 15 LOG(f/100) dB MIN	
Power Sum Near End Crosstalk (PSNEXT)	$1 \leq f \leq 500 \text{ MHz}$ 24.8 – 20 LOG(f/100) dB MIN	$1 \leq f \leq 500 \text{ MHz}$ 42.3 - 15 LOG(f/100) dB MIN	
Power Sum Attenuation to Crosstalk Ratio, Far End (PSACRF)	N/A	$1 \leq f \leq 500 \text{ MHz}$ 24.8 - 20 LOG(f/100) dB MIN	
Attenuation Crosstalk Ratio, Far End (ACRF)	$1 \leq f \leq 500 \text{ MHz}$ 27.8 – 20 LOG(f/100) dB MIN	$1 \leq f \leq 500 \text{ MHz}$ 27.8 - 20 LOG(f/100) dB MIN	
Insertion Loss	$1 \leq f \leq 500 \text{ MHz}$ 1.5[1.82√(f) + 0.0091(f) + 0.25/√(f)] dB MAX	$1 \leq f \leq 500 \text{ MHz}$ 1.95 [1.82 √f + 0.0091(f) + 0.25/√f] dB	$1 \leq f \leq 500 \text{ MHz}$ 1.5 [1.82 √f + 0.0091(f) + 0.25/√f] dB
Delay	$1 \leq f \leq 500 \text{ MHz}$ 534 + 36/√(f) ns MAX	$1 \leq f \leq 500 \text{ MHz}$ 534 + 36/√f ns MAX	
Delay Skew	$1 \leq f \leq 500 \text{ MHz}$ <45ns MAX		
TCL	N/A	$1 \leq f \leq 500 \text{ MHz}$ 30 - 10 LOG(f/100) dB MIN	
ELTCTL	N/A	$1 \leq f \leq 30 \text{ MHz}$ 35 - 20 LOG(f) dB MIN	
Velocity Of Propagation	0.68		
UL Classification	(UL) Type CMR/CMG	NEC (ETL) TYPE CMP CEC C(ETL) TYPE CMP	
Agency Approvals	cULus, RoHS	cETLus, RoHS	

NOTE: All testing conducted off the reel.



Please Note: Our prices on Ethernet Cables are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.



DataMax® Ethernet Cables

Quabbin DataMax Ethernet Cable

The Quabbin DataMax® Category network cables are proudly made in the USA and are available in Cat5e, 6, 6a or 6e. These cables are offered in 26AWG or 24AWG stranded tinned copper or bare solid copper in shielded or unshielded constructions. Designed to be round and smooth, Quabbin DataMax® Category network cables are compatible with most popular plugs for quick termination and easy installation.

When it comes to network cable, flexibility can mean many different things. The first and most obvious is the ease with which it bends. The importance behind having a pliable cable has to do with installation and cabinet routing. Flexibility allows easy manipulation between devices while increasing the durability, which is important when considering a lifetime of "moves & changes" that can occur in a dynamic network environment. Durability is paramount in allowing these changes to take place without compromising the cable.

The Quabbin DataMax® Category network cables exceed the requirements of ANSI/TIA-568-C.2, are compatible with Cat 5e and 6 hardware, and are suitable for applications from 10 Base-T to 1000 Base-T (Gigabit Ethernet).

Also available are Quabbin DataMax® MIL-spec Cat6 cables with black low smoke PVC jacket and special conductor insulations colors.

* DataMax is a registered trademark of Quabbin Wire and Cable Corporation.

** EtherNet/IP is a trademark of ODVA, Inc.

Features

- Available in Category 5e, 6, 6e, and 6a
- In compliance with TIA 568-C.2 and TIA 1005
- Designed for use in EtherNet/IP systems **
- 4 twisted pairs
- Unshielded or overall foil shields
- UL Type CM and UL AWM Style 2463 (80°C, 600V)
- Some cables available with conductor color code for MIL spec applications
- Cut to length in 1 foot increments
- Low 20 foot minimum length
- Made in the USA



Click on the thumbnail or go to
<https://www.automationdirect.com/VID-WD-0016>
 for a short introduction on our cut to length cable

