

Dold BG5933 and BH5933 Series Two-Hand Controllers

**BH5933-48-61-110**

Designed to protect people and machines in applications with two-hand buttons or production machinery with dangerous closing movements.

- Inputs for 2 pushbuttons, each with 1 N.C. and 1 N.O. contact.
- Output options: 2 N.O. contacts and 1 N.C. contact, or 3 N.O. contacts and 1 N.C. contact
- Feedback circuit Y1 - Y2 to monitor external contactors used for reinforcement of contacts
- Overvoltage and short-circuit protection
- LED indicators for power and state of operation

Two-Hand Controllers Selection Chart

Part Number	Price	Marking Type	Voltage	Outputs
BG5933-22-61-24	\$194.00	Two-hand controller	24VDC	2 N.O. and 1 N.C.
BH5933-48-61-110	\$285.00	Two-hand controller	110VAC	3 N.O. and 1 N.C.

Note: Output contacts will be switched if both pushbuttons are operated within m0.5s. If both buttons are pressed while switching on the operating voltage (e.g. after voltage functions), the output contacts do not energize.

Safety Data – Values per EN ISO 13849-1

Category	4 according to EN 954-1
Performance level	PL _e according to EN 13849-1
MTTF _d	30.7 years
DC _{avg}	99%

Safety Data – Values per IEC/EN 62061 / IEC/EN 61508

SIL CL	3 per IEC/EN 62061
SIL	3 per IEC/EN 61508
HFT (Hardware Failure Tolerance)	1
DC _{avg}	99%
SFF	99.7%
PFH _D	7.51E ⁻⁹ h ⁻¹



Two-Hand Controllers Safety Relay Specification Table

Part Numbers	BG5933-22-61-24		BH5933-48-61-110	
General Specifications				
Temperature	Storage: -25°C to 85°C (-13°F to 185°F) Operating: -15°C to 55°C (5°F to 131°F)			
Altitude	< 2,000 meters			
Vibration Resistance	Amplitude: 0.35mm, Frequency: 10 to 55 Hz (IEC/EN 60-068-2-6)			
Degree of Protection	Per IEC/EN 60 529. Housing: IP40; Terminals IP20			
Housing	UL 94V-0 Thermoplastic; Din mount 35 mm x 7.5 mm			
Weight	200g (7.05 oz.)		400g (14.11 oz.)	
Agency Approvals and Standards	cULus file E107778, CE, RoHS, TUV			
Terminal Designation per EN 50 005 Wire Connections	1x4 mm ² solid or 1 x 2.5 mm ² stranded ferruled (isolated) or 2 x 1.5 mm ² stranded ferruled (isolated) DIN 46 228-1/-2/-3/-4 or 2 x 2.5 mm ² stranded ferruled DIN 46 228-1/-2/-3			
Wire Fixing	Terminal screws M3.5. Box terminals with self-lifting wire protection			
Input Specifications				
Nominal Voltage	24V DC		110V AC, 230V AC	
Voltage Range	At 10% residual ripple: DC: 0.9 to 1.1 UN		At 10% residual ripple: AC: 0.85 to 1.1 UN	
Maximum Consumption	DC approx. 2.3 W		AC approx. 4 VA	
Nominal Frequency			50 to 60 Hz	
Time Delay for Simultaneous Demand	0.5 sec max			
Recovery time	1 second			
Control Contacts	2 x (1 N.O. and 1 N.C. contacts)			
Current via Control Contacts with 24VDC	N.O. contact: typ. 50mA; N.C. contact: typ. 20mA			
Short Circuit Protection	Internal with PTC (Positive Temperature Coefficient resistor)			
Overvoltage Protection	Internal VDR (Voltage Dependent Resistor)			
Output Specifications				
Electrical Contact Life	To DC 13 at 2A, DC 24V: >1.5 x 10 ⁵ switching cycles To AC 15 at 2A, 230 VAC : 10 ⁵ switching cycles IEC/EN 60 947-5-1			
Mechanical Life	10 x 10 ⁶ switching cycles			
Contact Type (N.O. are safety contacts)	2 N.O. positively driven and 1 N.C. relay contacts		3 positively driven N.O. and 1 N.C. relay contacts	
Operate Time	Operate time: typ. 40ms			
Release Time	Release time: typ. 15ms			
Nominal Output Voltage	AC: 250V; DC: See continuous current limit curve in manual.			
Thermal Current (I _{th})	Max. 5A See continuous current limit curve in manual.			
Switching of Low Loads	M100 mV; (contacts with 5µ Au) M 1mA			
Short Circuit Strength	Max. fuse rating: 6 A gl (IEC/EN 60 947-5-1); line circuit breaker C 6 K			
Switching Capacity	AC 15: N.O. contacts: 3A/230V; N.C. contacts: 2A/230VAC DC 13: N.C. contacts: 2A/24VDC 2 N. O. contacts in series; 8 A/24V >105. ON: 0.4s, OFF: 9.6 s			
Switching Frequency	Max. 1800 switching cycles/hr			

Dold BG5933 and BH5933 Series Two-Hand Controllers





Wiring


BG5933 Block Diagram

BH5933 Block Diagram


Dimensions


mm [in]

BG5933

BH5933


Applications



Two-hand control



Two-hand control with contact reinforcement via external positively-driven contactors

**Note: When switching inductive loads, surge suppressors are recommended.*

Dold LG5929 Extension Module



Additional contacts for emergency-stop modules and safety gate monitors.

- 1-channel or 2-channel connection
- LED indication for operation
- Output: 5 N.O. and 1 N.C. contacts

Safety Data – Values per EN ISO 13849-1

Category	4 according to EN 954-1
Performance level	PL _e according to EN 13849-1
MTTF_d	>100 years
DC_{avg}	99%

Safety Data – Values per IEC/EN 62061 /IEC/EN 61508

SIL CL	3 per IEC/EN 62061
SIL	3 per IEC/EN 61508
HFT (Hardware Failure Tolerance)	1
DC_{avg}	99%
SFF	99.7%
PFH_D	4.68E ⁻¹⁰ h ⁻¹

Safety Relays Selection Chart

Part Number	Price	Marking Type	Voltage	Outputs
LG5929-60-100-61	\$136.00	Safety relay extension module	24 VAC/VDC	5 N.O./1 N.C.

Safety Relay Extension Module Specification Table

General Specifications	
Temperature	Storage: -25°C to 85°C (-13°F to 185°F) Operating: -15°C to 55°C (5°F to 131°F)
Altitude	< 2,000 meters
Vibration Resistance	Amplitude: 0.35mm, Frequency: 10 to 55 Hz (IEC/EN 60-068-2-6)
Degree of Protection	Per IEC/EN 60 529. Housing: IP40; Terminals IP20
Housing	UL 94V-0 Thermoplastic; Din mount 35 mm x 7.5 mm
Weight	205g (7.23 oz.)
Agency Approvals and Standards	CSA, cULus file E107778, CE, RoHS, TUV
Terminal Designation per EN 50 005 Wire Connections	1x4 mm ² solid or 1 x 2.5 mm ² stranded ferruled (isolated) or 2 x 1.5 mm ² stranded ferruled (isolated) DIN 46 228-1/-2/-3/-4 or 2 x 2.5 mm ² solid per DIN 46 228-1/-2/-3 /-4
Wire Fixing	Plus-minus terminal screws M3.5 box terminals with wire protection or cage clamp terminals.
Input Specifications	
Nominal Voltage	24V AC/DC
Voltage Range	AC: 0.85 to 1.1 U _N At 10% residual ripple: 0.9 to 1.1 U _N ; At 48% residual ripple: 0.85 to 1.1 U _N
Maximum Consumption	24VAC/DC: 1.8VA
Nominal Frequency	50 to 60 Hz
Control Current	Control current typ. at 24V over 2 relays: 75 mA
Overvoltage Protection	Internal VDR (Voltage Dependent Resistor)
Output Specifications	
Electrical Contact Life	To AC15 at 2 A,230V: 10 ⁵ switching cycles IEC/EN 60 947-5-1
Mechanical Life	20 x 10 ⁶ switching cycles
Contact Type	5 N.O. positively driven and 1 N.C. relay contacts (N.O. contacts are safety contacts)
Operate/Release Time	Operate typ at U _N : 20 ms.; Release typ at U _N : 35 ms.
Nominal Output Voltage	250VAC
Thermal Current (I_{th})	Max. 5A per contact. See continuous current limit curve in installation manual.
Short Circuit Strength	Max fuse rating:10A gl (IEC/EN 60 9470-5-1); Line circuit breaker: B6A
Switching Capacity IEC/EN 60 947-5-1	AC 15: N.O. contacts: 3A/230V; N.C. contacts: 2A/230VAC DC 13: N.O. contacts: 4A/24V; N.C. contacts: 4A/24VDC; N.O. contact: 8A/24V >25x10 ³ ON: 0.4s, OFF: 9.6s
Switching Frequency	Max. 1,200 switching cycles/hr




Dold LG5929 Extension Module




Wiring

Dimensions mm [in]

LG5929 Block Diagram



Applications



Note: This is a representative drawing. Depending on the LG5925 safety relay you select, different voltage sources may be required.

**Note: When switching inductive loads, surge suppressors are recommended.*

Safety Products



Warning: Safety products sold by AutomationDirect are Safety components only. The purchaser/installer is solely responsible for the application of these components and ensuring all necessary steps have been taken to assure each application and use meets all performance and applicable safety requirements and/or local, national and/or international safety codes as required by the application. AutomationDirect cannot certify that our products, used solely or in conjunction with other AutomationDirect or other vendors' products, will assure safety for any application. Any person using or applying any products sold by AutomationDirect is responsible for learning the safety requirements for their individual application and applying them, and therefore assumes all risks, and accepts full and complete responsibility, for the selection and suitability of the product for their respective application.

AutomationDirect does not provide design or consulting services, and cannot advise whether any specific application or use of our products would ensure compliance with the safety requirements for any application.