

# RHINO DIN Rail Power Supplies PSB Series

## Single-Phase Input Overview

AutomationDirect's RHINO PSB series of DIN rail power supplies is perfect for applications that require a basic DC voltage power supply. These low-cost power supplies offer high performance and reliability without all the additional features of higher-cost full-featured power supplies. The following models in the RHINO PSB series are available with universal single-phase input and with output voltages of 24VDC or 48VDC from 60 to 480 Watts. They feature removable terminal blocks, high efficiencies, conformal coated circuit boards, and approval for Class 1, Division 2 hazardous locations. The rugged plastic and aluminum housings easily install with integral 35mm DIN rail mounting adapters. These high-quality power supplies include overload, overvoltage and thermal protection, and are UL 508 listed, UL 60950 recognized, CSA certified, CE marked and RoHS compliant.

[PSB48-480S](#) is perfect for Stepper Drives, like our [STP-DRV-6575](#), [STP-DRV-4850](#) or [STP-DRV-80100](#)

## Features

- Universal input voltage, single-phase 120/240 VAC or 120–375 VDC
- 24VDC or 48VDC outputs, 60 to 480 Watts
- Adjustable output voltage
- Rugged plastic or aluminum housings with integral 35mm DIN rail mounting adapters
- Output voltage status LED
- NEC Class2 (Model [PSB24-100-N](#) & [PSB24-060S-P](#) only)
- Removable terminal blocks (except [PSB24-060S-P](#), [PSB24-100-N](#), [PSB24-480S](#) and [PSB48-480S](#)) with IP20 protection
- Conformal coated circuit board for protection against demanding environments
- Overload, overvoltage and thermal protection
- UL 508 listed, UL 60950 recognized, CSA certified, approved for Class I (except [PSB24-100-N](#)), Division 2 hazardous locations CE marked and RoHS compliant
- 3-year warranty



Input Specifications											
Part Number	Price	Weight kb [lb]	Housing	Input Voltage	Input Frequency Range	Max. Input Current	Inrush Current Limitation I2t @ 77°F (+25°C) typ.	Leakage Current	Recommended Circuit Breaker	Hold-Up Time at Nominal Load (Typ.) (Mains Buffering) (100% load, 25°C)	Turn-on Time
<a href="#"><u>PSB24-060S-P</u></a>	\$41.00	0.33 [0.73]	Plastic	85–264 VAC [DC input range 120–375 VDC] UL Approved for 100-240 VAC only	47–63 Hz [0Hz @ DC Input]	<1.5 A @ 100VAC	<40A @ 115VAC, <80A @ 230VAC	<0.5mA @ 240VAC	16A “B” Curve	>20ms @ 115VAC >125ms @ 230VAC	<3 sec.
<a href="#"><u>PSB24-060S</u></a>	\$49.50	0.37 [0.82]	Aluminum			<1.4 A @ 115VAC, <0.8 A @ 230VAC	<20A @ 115VAC, <35A @ 230VAC	<1mA @ 240VAC	8A “B” Curve	>20ms @ 115VAC >30ms @ 230VAC	<2 sec.
<a href="#"><u>PSB24-100-N</u></a>	\$74.00	0.60 [1.32]				<1.00A @ 115VAC, <0.53A @ 230 VAC	<30A @ 115VAC <60A @ 230VAC	<0.5mA @ 24VAC	13A “B” Curve		
<a href="#"><u>PSB24-120S</u></a>	\$88.00	0.72 [1.59]				<2.2 A @ 115VAC, <1.2 A @ 230VAC	<35A @ 115VAC, <35A @ 230VAC	<1mA @ 240VAC	10A “B” Curve	>20ms @ 115VAC >115ms @ 230VAC	<1 sec.
<a href="#"><u>PSB24-240S</u></a>	\$146.00	1.10 [2.43]				<2.5 A @ 115VAC, <1.3 A @ 230VAC			8A “B” Curve	>20ms @ 115VAC & 230VAC	
<a href="#"><u>PSB24-480S</u></a>	\$225.00	1.37 [3.02]				<5A @ 115VAC, <3A @ 230VAC		<3mA @ 240VAC	6A “B” Curve		
<a href="#"><u>PSB48-120S</u></a>	\$88.00	0.72 [1.59]				<2.2 A @ 115VAC, <1.1 A @ 230VAC		<1mA @ 240VAC	8A “B” Curve	>20ms @ 115VAC >50ms @ 230VAC	
<a href="#"><u>PSB48-240S</u></a>	\$146.00	0.97 [2.14]				<2.5 A @ 115VAC, <1.3 A @ 230VAC			8A “B” Curve	>20ms @ 115VAC & 230VAC	
<a href="#"><u>PSB48-480S</u></a>	\$199.00	1.37 [3.02]				<5A @ 115VAC, <3A @ 230VAC		<3mA @ 240VAC	10A “B” Curve	>20ms @ 115VAC & 230VAC	<1.5 sec.

# RHINO DIN Rail Power Supplies PSB Series

Output Specifications									
Part Number	Output Voltage (Vnom) / Adjustment Range	Output Power	Output Current	Ripple and Noise [20 MHz]	Startup with Capacitive Loads Max	Derating	Max. Power Dissipation Idling/Nominal Load Approx.	Efficiency [Typ @ 115VAC]	MTBF
<a href="#"><u>PSB24-060S-P</u></a>	24VDC $\pm 2\%$ /22–28 VDC [maximum power $\leq 60$ W]	60W	2.5 A	<240mVpp @ 25°C	8,000 $\mu$ F	>50°C de-rate power by 2.5%/°C >70°C de-rate power by 4%/°C	8W	88%	>800,000 hrs.
<a href="#"><u>PSB24-060S</u></a>	24VDC $\pm 2\%$ /24–28 VDC [maximum power $\leq 60$ W]					>50°C de-rate power by 2.5%/°C	7.4 W	90%	>1,000,000 hrs.
<a href="#"><u>PSB24-100-N</u></a>	24VDC $\pm 2\%$ /22–24 VDC [maximum power $\leq 91.2$ W]	91.2 W	3.80A	<150mVpp @ 25°C	8,000 $\mu$ F	>50°C de-rate power by 2.5%/°C >70°C de-rate power by 4%/°C	12.4 W	88%	>800,000 hrs.
<a href="#"><u>PSB24-120S</u></a>	24VDC $\pm 2\%$ /24–28 VDC [maximum power $\leq 120$ W]	120W	5A		10,000 $\mu$ F	>50°C de-rate power by 2.5%/°C	14.8 W	89%	
<a href="#"><u>PSB24-240S</u></a>	24VDC $\pm 2\%$ /24–28 VDC [maximum power $\leq 240$ W]	240W	10A			>50°C de-rate power by 2.5%/°C	26.5 W	90%	>500,000 hrs.
<a href="#"><u>PSB24-480S</u></a>	24VDC $\pm 2\%$ /24–28 VDC [maximum power $\leq 480$ W]	480W	20A			>50°C de-rate power by 2.5%/°C >70°C de-rate power by 5%/°C	47W	91%	
<a href="#"><u>PSB48-120S</u></a>	48VDC $\pm 1\%$ /48–56 VDC [maximum power $\leq 120$ W]	120W	2.5 A	<200mVpp @ 25°C	6,500 $\mu$ F	>50°C de-rate power by 2.5%/°C	14.8 W	90%	>800,000 hrs.
<a href="#"><u>PSB48-240S</u></a>	48VDC $\pm 1\%$ /48–56 VDC [maximum power $\leq 240$ W]	240W	5A	<200mVpp @ 85VAC to 265VAC	10,000 $\mu$ F	>50°C de-rate power by 2.5%/°C	25W	90%	>500,000 hrs.
<a href="#"><u>PSB48-480S</u></a>	48VDC $\pm 1\%$ /48–56 VDC [maximum power $\leq 480$ W]	480W	10A	<200 mVpp @ 85VAC to 264VAC		>50°C de-rate power by 2.5%/°C >70°C de-rate power by 5%/°C	46.5 W	91%	

General Specifications	
Output Line Regulation	<0.5% @ 85–264 VAC input, 100% load
Output Load Regulation	<1% @ 85–264 VAC input, 0-100% load
Parallel Operation	PSB60-REM20S / PSB60-REM40S or with ORing Diode
Case Cover	Aluminium or Plastic [Polycarbonate] for P Series
Signals	Green LED DC OK
Humidity at 25°C [77°F], no condensation	<95% RH [non-condensing]
Shock (Non-Operating)	IEC 60068-2-27, 30G [300m/S <sup>2</sup> ] for a duration of 18ms, 1 time per direction, 2 times in total
Vibration (Non-Operating)	IEC60068-2-6, 10Hz to 500Hz @ 30 m/S <sup>2</sup> [3G peak]; 60 min per axis for all X, Y, Z direction
Environmental Air	No corrosive gases permitted (PSB24-100-N ) Conformal coating on PCBA to protect against chemical and dust pollutants
Pollution Degree	2
Climatic Class	3K3 according to EN 60721

Series Certification and Standards	
Electrical Equipment of Machines	IEC60204-1 [over voltage category III]
Electronic equipment for use in electrical power installations	EN62477-1 / IEC62103
Safety Entry Low Voltage	PELV [EN60204], SELV [EN60950]
Industrial Control Equipment	UL/cUL listed to UL508 and CSA C22.2 No. 107.1-01 File no. E197592 CSA to CSA C22.2 No. 107.1-01
Hazardous Location	cCSAus to CSA C22.2 No. 213-M1987, ANSI / ISA 12.12.01:2007 Class I, Division 2, Group A,B,C,D T4, Ta = 25 to +80°C (PSB24-060S-P, PSB24-060S, PSB24-120S, PSB24-240S, PSB48-120S, PSB48-240S); 25 to +75°C (PSB24-480S, PSB48-480S) Vertical: > +50°C derating, File no. 249074
Class 2 Power Supply	UR/cUR Class 2 power supply recognized to UL1310 and CSA C22.2 No. 223 File no. E198298 (PSB24-060S-P and PSB24-100-N only)
CE	CE

To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.

# RHINO DIN Rail Power Supplies PSB Series

Safety and Protection		
<b>Transient surge voltage protection</b>	Varistor	
<b>Overvoltage</b>	PSB24-060S-P, PSB24-060S, PSB24-100-N, PSB24-120S, PSB24-240S, PSB24-480S: <32V, SELV Output, hiccup mode, non-latching [auto-recovery]	PSB48-120S, PSB48-240S, PSB48-480S: <57V, SELV Output, hiccup mode, non-latching [auto-recovery]
<b>Overload / Overcurrent</b>	PSB24-060S-P, PSB24-060S, PSB24-100-N, PSB24-120S, PSB24-240S, PSB24-480S: >150% of rated load current, hiccup mode, non-latching [auto-recovery].	
	PSB24-060S-P: 110-150% of rated load current, hiccup mode, non-latching [auto-recovery].	
<b>Isolation Voltage:</b> <b>Input/output (type test/routine test)</b> <b>Input/GND (type test/routine test)</b> <b>Output/GND (type test/routine test)</b>	4 kVAC / 3 kVAC 1.5 kVAC / 1.5 kVAC 1.5 kVAC / 500 VAC	
<b>Protection Degree</b>	IP20	
<b>Safety Class</b>	Class I with GND connection	

Additional Data						
Part Number	Wire Size / Torque*		Terminal Block Type	Ambient Operating Temperature**	Storage Temperature	Drawing Link
	Input	Output				
<a href="#"><u>PSB24-060S-P</u></a>	0.52–5.3 mm <sup>2</sup> [AWG 20–10] / 0.45 Nm [3.96 lb-in]		Fixed screw terminals	-25 to 80°C [-13 to 176°F]	-25 to 80°C [-13 to 176°F]	<a href="#">PDF</a>
<a href="#"><u>PSB24-060S</u></a>	0.52–3.3 mm <sup>2</sup> [AWG 20–12] / 0.46 Nm [4.05 lb-in]		Removable screw terminals	-25 to 80°C [-13 to 176°F] Cold start at -40°C [-40°F]	-40 to 85°C [-40 to 185°F]	<a href="#">PDF</a>
<a href="#"><u>PSB24-100-N</u></a>	0.82–3.3 mm <sup>2</sup> [AWG 18–12] / 0.91 Nm [8.1 lb-in]	0.82–3.3 mm <sup>2</sup> [AWG 18–12] / 0.61 Nm [5.4 lb in]	Fixed screw terminals			<a href="#">PDF</a>
<a href="#"><u>PSB24-120S</u></a>	0.52–3.3 mm <sup>2</sup> [AWG 20–12] / 0.46 Nm [4.05 lb-in]		Removable screw terminals			<a href="#">PDF</a>
<a href="#"><u>PSB24-240S</u></a>	1.3–2.1 mm <sup>2</sup> [AWG 16–14] / 0.46 Nm [4.05 lb-in]					<a href="#">PDF</a>
<a href="#"><u>PSB24-480S</u></a>	0.82–5.3 mm <sup>2</sup> [AWG 18–10] / 0.45 Nm [3.96 lb-in]	3.3–5.3 mm <sup>2</sup> [AWG 12–10] / 0.45 Nm [3.96 lb-in]	Fixed screw terminals	-25 to 75°C [-13 to 176°F]		<a href="#">PDF</a>
<a href="#"><u>PSB48-120S</u></a>	0.52–3.3 mm <sup>2</sup> [AWG 20–12] / 0.46 Nm [4.05 lb in]		Removable screw terminals	-25 to 80°C [-13 to 176°F]		<a href="#">PDF</a>
<a href="#"><u>PSB48-240S</u></a>					<a href="#">PDF</a>	
<a href="#"><u>PSB48-480S</u></a>	0.82–5.3 mm <sup>2</sup> [AWG 18–10] / 0.45 Nm [3.96 lb-in]	1.3–5.3 mm <sup>2</sup> [AWG 16–10] / 0.45 Nm [3.96 lb-in]	Fixed screw terminals	-25 to 75°C [-13 to 176°F]	<a href="#">PDF</a>	

\*Stripping length 7 mm [0.28 in]

\*\* See output specifications for temperature derating