Screwless Terminal Blocks Overview

Why go screwless?

Screwless clamping technology offers several benefits:

- Speed: On average, screwless connections can be made in half the time of screw type connections, cutting installation labor costs in half.
- Ease: No need for twisting and turning screws, so screwless terminal blocks are much easier on the installer's hands and arms. Also, wiring from the top of the terminal blocks allow installers to accurately and reliably see the wire fully inserted into the spring clamp.
- Safety: Never have a problem with faulty connections from loose screws again! Meets the same UL, and IEC standards as screw-type terminal blocks.
- Maintenance-free: The screwless spring clamp conforms to the wire with constant tension, making it maintenance-free.

Are there any trade-offs of going screwless versus screw-type?

Unless you need to clamp multiple wires to the same connection point, the answer is no. If you do, then there may be a slight trade-off in requiring more panel space than with screw terminal blocks. Unlike screw terminal blocks, screwless terminal block spring-clamps are designed to clamp a single wire, only. This is why multiple versions exist like the "one-to-two" or "two-to-two." These versions allow multiple wires to be connected together via multiple spring clamps.

How does it work?

Well, it's pretty simple: Push, Insert, Release. Just push your screwdriver into the spring clamp (a rectangular shaped hole) to open the spring clamp; insert the stripped wire into the clamp a circular shaped hole), and pull out your screwdriver to release the clamp against the wire. That's it. The connection is made.



How do the jumpers work?





Yes = Good, acceptable jumper
No = Bad, damaged jumper

DINnectors®

Screwless Double-Level Terminal Blocks

DN-QD12-A ***DN-QD12X-A***

Double-level terminal blocks offer twice the wiring density of feed-through blocks. The DN-QD12X-A version is supplied with an internal jumper to common all four of its connection points.

LED version

This style is available with LED indicator installed. The LED illuminates when voltage is present. The DN-QD12L2-A version is for 12 - 24 VAC/DC circuits, and includes current limiting elements.

Diode version

Typically, an inductive load produces a spike when it is turned off. These terminal blocks with built-in diode help protect your PLC's output circuits. (Please see application note AN-MISC-032 at http://support.automationdirect.com/docs/an-misc-032.pdf



DN-QD12X-A
(Euro QD2.5/35)





DN-QD12L2-A
(Euro QD2.5/35)





DN-QD12DR-A
(Euro QD2.5/35)



Ordering Information

	Part Number	Qty	Price	Part Number	Qty	Price	Part Number	Qty	Price	Part Number	Qty	Price
Gray Terminal Blk	***DN-QD12-A***	25	$67.00	***DN-QD12X-A***	10	$45.00	***DN-QD12L2-A***	10	$46.00	***DN-QD12DR-A***	10	$45.00
Blue Terminal Blk	***DN-QD12B-A***	25	$70.00	***DN-QD12XB-A***	10	$47.00	–			–		
Description	Double-level screwless terminal blocks			Double-level screwless cross-connected terminal blocks			Double-level screwless terminal blocks w/ LED installed for visual circuit indication			Double-level screwless terminal blocks w/diode installed for circuit protection		

Technical Specifications

Stripping Length	12mm [0.47 in]			12mm [0.47 in]			12mm [0.47 in]			12mm [0.47 in]		
Density	200/m [60 pcs/ft]			200/m [60 pcs/ft]			200/m [60 pcs/ft]			200/m [60 pcs/ft]		
UL Approval*	600V	20A	24-12 AWG	600V	20A	24-12AWG	600V	20A	24-12 AWG	600V	1A diode	24-12 AWG
VDE Approval	500V	24A	2.5 mm²	500V	24A	2.5 mm²	500V	24A	2.5 mm²	500V	1A diode	2.5 mm²
LED Voltage	–			–			12 -24 VAC/DC. 3.4 kΩ			–		
Operating Temp	Ambient air temperature: -20 to 105°C [-4 to 221°F] / Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F]											
SCCR Rating	10kA per Table SB4.1, 2009, UL 508A, Maximum short circuit current rating for unmarked components											
CE Conformity	CE (EN 60947-1 / EN 60947-7-1)											
Agency File #	UL E179129											

Accessories

End Covers		***DN-QDEC12***	25	$18.00	***DN-QDEC12***	25	$18.00	***DN-QDEC12***	25	$18.00	***DN-QDEC12***	25	$18.00
Jumpers	***2-pole***	***DN-2J2Y***	100	$47.50	***DN-2J2Y***	100	$47.50	***DN-2J2Y***	100	$47.50	***DN-2J2Y***	100	$47.50
		DN-2J2YMN	25	$14.50	***DN-2J2YMN***	25	$14.50	***DN-2J2YMN***	25	$14.50	***DN-2J2YMN***	25	$14.50
	3-pole	***DN-3J2Y***	100	$68.00	***DN-3J2Y***	100	$68.00	***DN-3J2Y***	100	$68.00	***DN-3J2Y***	100	$68.00
		DN-3J2YMN	25	$20.00	***DN-3J2YMN***	25	$20.00	***DN-3J2YMN***	25	$20.00	***DN-3J2YMN***	25	$20.00
	24-pole	***DN-24J2Y***	5	$31.00	***DN-24J2Y***	5	$31.00	***DN-24J2Y***	5	$31.00	***DN-24J2Y***	5	$31.00
Cutting Tool		***DN-J2CUT***	1	$87.00	***DN-J2CUT***	1	$87.00	***DN-J2CUT***	1	$87.00	***DN-J2CUT***	1	$87.00
35mm DIN Rail	***7.5 mm high***	***DN-R35S1***	10	$39.00	***DN-R35S1***	10	$39.00	***DN-R35S1***	10	$39.00	***DN-R35S1***	10	$39.00
		DN-R35S1-2	2	$11.00	***DN-R35S1-2***	2	$11.00	***DN-R35S1-2***	2	$11.00	***DN-R35S1-2***	2	$11.00
End Brackets		***DN-EB35***	50	$74.00	***DN-EB35***	50	$74.00	***DN-EB35***	50	$74.00	***DN-EB35***	50	$74.00
		DN-EB35MN	20	$34.50	***DN-EB35MN***	20	$34.50	***DN-EB35MN***	20	$34.50	***DN-EB35MN***	20	$34.50
		DN-EB35-A	50	$52.50	***DN-EB35-A***	50	$52.50	***DN-EB35-A***	50	$52.50	***DN-EB35-A***	50	$52.50
		DN-EB35-A-10	10	$13.00	***DN-EB35-A-10***	10	$13.00	***DN-EB35-A-10***	10	$13.00	***DN-EB35-A-10***	10	$13.00
		DN-QEB35	50	$47.00	***DN-QEB35***	50	$47.00	***DN-QEB35***	50	$47.00	***DN-QEB35***	50	$47.00
		DN-QEB35-10	10	$12.50	***DN-QEB35-10***	10	$12.50	***DN-QEB35-10***	10	$12.50	***DN-QEB35-10***	10	$12.50
Angled Support Bracket		***DN-ASB1***	50	$107.00	***DN-ASB1***	50	$107.00	***DN-ASB1***	50	$107.00	***DN-ASB1***	50	$107.00
Marking Tags		DN-QL Series	500	various	DN-QL Series	500	various	DN-QL Series	500	various	DN-QL Series	500	various

***Copper wire only**

For more information on accessories, see the DIN*nector*s Accessories section of this chapter.

Dimensions

DN-QD12-A Series



Note: Jumpering and testing capability on bottom level only, for DN-QD12X, DN-QD12L2 and DN-QD12DR.

DINnectors Accessories

Jumpers

Multi-pole jumper bars for DIN*nector* terminal blocks

DN-12JL14B-A

Multi-pole Jumper Bars								
Part Number	Qty	Price	Number of Poles	Rating (V)	Rating (A)	Tightening Torque	Insulation Color	For Use With Terminal Block Series
Screw-down Connection								
DN-2J6	100	$84.00	2	600	65	0.5 Nm [4.4 Lb-In]	–	DN-T6
DN-3J6	100	$145.00	3	600	65		–	
DN-4J6	100	$186.00	4	600	65		–	
DN-55J6	1	$29.00	55	600	65		–	
DN-24J8	5	$45.00	24	600	50	0.6 Nm [5.3 lb-in]	Green	DN-T8
Push-in Connection								
DN-2J2Y	100	$47.50	2	600	25	–	Orange	DN-T12-A, DN-EMX, DN-Q12-A, DN-QD12-A, DN-QEMX, DN-QKBD12-A
DN-2J2YMN	25	$14.50	2	600	25		Orange	
DN-3J2Y	100	$68.00	3	600	25		Orange	
DN-3J2YMN	25	$20.00	3	600	25		Orange	
DN-24J2Y	5	$31.00	24	600	25		Orange	
DN-2J4Y	100	$50.50	2	600	25		Yellow	DN-T10-A, DN-D10-A, DN-M10-A, DN-Q10-A
DN-2J4YMN	25	$16.00	2	600	25		Yellow	
DN-3J4Y	100	$81.00	3	600	25		Yellow	
DN-3J4YMN	25	$24.00	3	600	25		Yellow	
DN-24J4Y	5	$32.50	24	600	25		Yellow	
DN-2JL14-A	100	$74.00	2	300	20		Red	DN-TL-A
DN-2JL14-AMN	25	$16.50	2	300	20		Red	
DN-2JL14B-A	100	$74.00	2	300	20		Blue	
DN-2JL14B-AMN	25	$16.50	2	300	20		Blue	
DN-3JL14-A	100	$109.00	3	300	20		Red	
DN-3JL14-AMN	25	$25.50	3	300	20		Red	
DN-3JL14B-A	100	$109.00	3	300	20		Blue	
DN-3JL14B-AMN	25	$25.50	3	300	20		Blue	
DN-12JL14-A	10	$29.00	12	300	20		Red	
DN-12JL14B-A	10	$29.00	12	300	20		Blue	
DN-12JFE	10	$66.00	12	300	25		Blue	DN-FE4
DN-2J6Y	100	$66.00	2	600	30		Green	DN-Q8-A
DN-2J6YMN	25	$16.50	2	600	30		Green	
DN-3J6Y	100	$92.00	3	600	30		Green	DN-Q8-A
DN-3J6YMN	25	$26.00	3	600	30		Green	
DN-12J6Y	10	$39.00	12	600	30		Green	DN-Q8-A

Dimensions

mm [inches]

DN-24J8



DN-xJ2Y / DN-xJ2YMN



DN-xJ4Y / DN-xJ4YMN



DN-xJL14 / DN-xJL14x-AMN, DN-xJ14x-A



DN-12JFE



DN-xJ6Y / DN-xJ6YMN



DINnectors Accessories

Modifying a DN-24J8 jumper bar to the required number of poles

1) Place the insulating part into the jumper bar and insert screws, based on number of poles required. (For instance, in the following example, 5 poles are required). Click into place.

2) Using a cutting tool, cut the insulating part at the edge of the jumper bar (see below).



3) Hold the metal jumper bar and insulating jumper with two hands, placing fingers to the left and right of the pole you wish to cut, repeatedly flexing up and down (1 or 2 times should be sufficient) until the jumper bar and insulating jumper break in two.



4) Remove the small remaining piece of jumper (see below). This is important to ensure appropriate insulation distance in the case of contiguously applied jumpers in sequence. This step also facilitates the placement of a separator terminal if the bridge is positioned as the last terminal of a group.

5) The jumpers now are ready to be screwed onto DN-T8 series terminal blocks.

Jumper Cutting Tools

Jumper cutting tools maintain protective covering.

Jumper Cutting Tools			
Part Number	*Description*	*Qty*	*Price*
DN-J2CUT	DIN*nector* jumper cutting tool, for use with DN-2J2Y, DN-3J2Y and DN-24J2Y jumpers.	1	$87.00
DN-J4CUT	DIN*nector* jumper cutting tool, for use with DN-2J4Y, DN-3J4Y and DN-24J4Y jumpers.	1	$87.00
DN-J6CUT	DIN*nector* jumper cutting tool, for use with DN-12J6Y jumpers.	1	$130.00
DN-JL14CUT	DIN*nector* jumper cutting tool, for use with DN-12JL14-A and DN-12JL14B-A jumpers.	1	$123.00
DN-JXCUT	DIN*nector* jumper cutting tool, for use with DN-J2DIE, DN-J4DIE, DN-J6DIE, DN-JL14DIE and DN-JFEDIE dies.	1	$84.00
DN-JFECUT	DIN*nector* jumper cutting tool, for use with DN-12JFE jumpers.	1	$101.00
DN-JKIT	DIN*nector* cutting tool kit for DN series jumpers. Includes (1) DN-JXCUT cutting tool, (5) dies (DN-J2DIE, DN-J4DIE, DN-J6DIE, DN-JL14DIE, and DN-JFEDIE).	1	$344.00
DN-TOOL2	DIN*nector* tool kit, for use with DN series terminal blocks, includes (1) spring opening tool for DN-Q series screwless terminal blocks and (1) jumper removal tool for J2, J4, J6, and JL14 jumpers.	1	$12.50

Replacement Dies		
Part Number	*Description*	*Price*
DN-J2DIE	DIN*nector* die set, replacement. Package of 2. For use with jumper cutting tools DN-J2CUT or DN-JXCUT.	$130.00
DN-J4DIE	DIN*nector* die set, replacement. Package of 2. For use with jumper cutting tools DN-J4CUT or DN-JXCUT.	$130.00
DN-JFEDIE	DIN*nector* die set, replacement. Package of 2. For use with jumper cutting tools DN-JFECUT or DN-JXCUT.	$101.00
DN-J6DIE	DIN*nector* die set, replacement. Package of 2. For use with jumper cutting tools DN-J6CUT or DN-JXCUT.	$130.00
DN-JL14DIE	DIN*nector* die set, replacement. Package of 2. For use with jumper cutting tools DN-JL14CUT or DN-JXCUT.	$130.00

DN-J2CUT

DN-J4CUT

DN-JKIT

DN-TOOL2

DINnectors Accessories

Terminal Plugs

DN-xxPLUG / DN-xxPLUGMN



Accessories – Terminal Plugs							
Plugs* Part Number	Qty	Price	Plugs* Part Number	Qty	Price	Number of Poles	Length mm [in]
DN-2PLUG	200	$127.00	DN-2PLUGMN	10	$8.00	2	10.2 [0.40]
DN-3PLUG	200	$195.00	DN-3PLUGMN	10	$12.50	3	15.2 [0.60]
DN-4PLUG	100	$130.00	DN-4PLUGMN	10	$16.00	4	20.3 [0.80]
DN-5PLUG	100	$150.00	DN-5PLUGMN	10	$20.00	5	25.4 [1.00]
DN-6PLUG	100	$194.00	DN-6PLUGMN	10	$20.00	6	30.5 [1.20]
DN-7PLUG	50	$101.00	DN-7PLUGMN	5	$16.00	7	35.6 [1.40]
DN-8PLUG	50	$129.00	DN-8PLUGMN	5	$16.00	8	40.6 [1.60]
DN-9PLUG	50	$141.00	DN-9PLUGMN	5	$16.50	9	45.7 [1.80]
DN-10PLUG	50	$150.00	DN-10PLUGMN	5	$18.50	10	50.8 [2.00]
DN-11PLUG	50	$177.00	DN-11PLUGMN	5	$21.50	11	55.9 [2.20]
DN-12PLUG	50	$194.00	DN-12PLUGMN	5	$22.00	12	61.0 [2.40]

Terminal Plugs Ratings	
Voltage/Current	300V, 12A
Wire Gauge	14–22 AWG, CU only
Torque	Tightening Torque: 0.51 N·m [4.5 lb·in]
Usage Temperature	Ambient air temperature: -20 to 105°C [-4 to 221°F] Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F]
Agency Approvals	UL file #: E179129

Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

*** DN-xxPLUGs fit all DN-EMXxx & DN-QEMXxx plug-in terminal blocks**

Disconnect Blade

DN-DIS-BLADE
DN-DIS-BMN



Disconnect Blade			
Part Number	Description	Qty	Price
DN-DIS-BLADE	Terminal block disconnect blade for DN-FE2, DN-FE4, DN-DIS2 and DN-DIS4	50	$39.50
DN-DIS-BMN		10	$10.50

End Brackets



End Brackets		
Part Number	Description	Price
DN-EB15	DINnector snap-on end bracket, 7mm wide. Package of 100. For use with 15mm DIN rail.	$119.00
DN-EB15MN	DINnector snap-on end bracket, 7mm wide. Package of 20. For use with 15mm DIN rail.	$28.00
DN-EB35	DINnector screw-down end bracket, 9mm wide. Package of 50. For use with 35mm DIN rail.	$74.00
DN-EB35MN	DINnector screw-down end bracket, 9mm wide. Package of 20. For use with 35mm DIN rail.	$34.50
DN-EB35-A	DINnector screw-down end bracket, 6mm wide. Package of 50. For use with 35mm DIN rail.	$52.50
DN-EB35-A-10	DINnector screw-down end bracket, 6mm wide. Package of 10. For use with 35mm DIN rail.	$13.00
DN-QEB35	DINnector snap-on end bracket, 6mm wide. Package of 50. For use with 35mm DIN rail.	$47.00
DN-QEB35-10	DINnector snap-on end bracket, 6mm wide. Package of 10. For use with 35mm DIN rail.	$12.50

DN-EB15



DN-EB35-A



DN-EB35



DN-QEB35



For more information on accessories, see the "DINnectors Accessories" section of this section.

DINnectors Accessories

End Covers

Certain end covers can be used with multiple terminal block parts to cover and insulate the open side, or to put more space between adjacent blocks.

DINnectors End Covers

Part Number	Description	Price
DN-EC1210	DINnector terminal block end cover, gray. Package of 100. For use with DN-T12 or DN-T10 series terminal blocks.	$47.50
DN-EC1210MN	DINnector terminal block end cover, gray. Package of 25. For use with DN-T12 or DN-T10 series terminal blocks.	$16.00
DN-EC86	DINnector terminal block end cover, gray. Package of 100. For use with DN-T8 or DN-T6 series terminal blocks.	$51.50
DN-EC86MN	DINnector terminal block end cover, gray. Package of 25. For use with DN-T8 or DN-T6 series terminal blocks.	$16.00
DN-EC4	DINnector terminal block end cover, gray. Package of 50. For use with DN-T4 series terminal blocks.	$32.50
DN-EC4MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-T4 series terminal blocks.	$6.50
DN-EC1/0	DINnector terminal block end cover, gray. Package of 50. For use with DN-T1/0 series terminal blocks.	$37.00
DN-EC1/0MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-T1/0 series terminal blocks.	$9.00
DN-DEC10	DINnector terminal block end cover, gray. Package of 50. For use with DN-D10-A series terminal blocks.	$34.50
DN-DEC10MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-D10-A series terminal blocks.	$6.50
DN-EC14	DINnector terminal block end cover, gray. Package of 25. For use with DN-TL14 series terminal blocks.	$20.00
DN-EC14S	DINnector terminal block end cover, gray. Package of 25. For use with DN-TL14S series terminal blocks.	$16.50
DN-ECM10	DINnector terminal block end cover, gray. Package of 100. For use with DN-M10-A series terminal blocks.	$47.50
DN-ECM10MN	DINnector terminal block end cover, gray. Package of 25. For use with DN-M10-A series terminal blocks.	$16.00
DN-ECKBD	DINnector terminal block end cover, gray. Package of 100. For use with DN-KBD12 series terminal blocks.	$47.50
DN-ECKBDMN	DINnector terminal block end cover, gray. Package of 10. For use with DN-KBD12 series terminal blocks.	$6.50
DN-EMXM1EC1	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXM1 series terminal block leftside.	$16.50
DN-EMXM1EC2	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXM1 series terminal block rightside.	$16.50
DN-EMXDVEC1	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXDV series terminal block leftside.	$16.50
DN-EMXDVEC2	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXDV series terminal block rightside.	$16.50
DN-FESEP	DINnector terminal block end cover, gray. Package of 50. For use with DN-FE and DN-DIS series terminal blocks.	$29.00
DN-FESEP-10	DINnector terminal block end cover, gray. Package of 10. For use with DN-FE and DN-DIS series terminal blocks.	$6.00
DN-QEC12	DINnector terminal block end cover, gray. Package of 50. For use with DN-Q12-A or DN-QG12 series terminal blocks.	$23.50
DN-QEC12MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-Q12-A or DN-QG12 series terminal blocks.	$6.00
DN-QEC10	DINnector terminal block end cover, gray. Package of 50. For use with DN-Q10-A or DN-QG10 series terminal blocks.	$23.50
DN-QEC10MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-Q10-A or DN-QG10 series terminal blocks.	$6.00
DN-QEC8	DINnector terminal block end cover, gray. Package of 50. For use with DN-Q8-A or DN-QG8 series terminal blocks.	$28.00
DN-QEC8MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-Q8-A or DN-QG8 series terminal blocks.	$6.50
DN-QEC12-1-2	DINnector terminal block end cover, gray. Package of 25. For use with DN-Q12-1-2-A series terminal blocks.	$16.50
DN-QEC12-2-2	DINnector terminal block end cover, gray. Package of 25. For use with DN-Q12-2-2-A series terminal blocks.	$18.00
DN-QDEC12	DINnector terminal block end cover, gray. Package of 25. For use with DN-QD12 series terminal blocks.	$18.00

Spacers

Spacers are used to put more space between adjacent blocks.

DINnectors Spacers

Part Number	Description	Qty	Price
DN-S1210	Spacer for DN-T12-A and DN-T10-A series terminal blocks	100	$56.00
DN-S1210MN		25	$17.50
DN-S86	Spacer for DN-T8 and DN-T6 series terminal blocks	100	$67.00
DN-S86MN		25	$15.50
DN-EMXM1SPA1	Spacer for DN-EMXM1 and DN-QEMXM1 single-level plug-in terminal blocks	25	$14.50
DN-EMXDVSPA1	Spacer for DN-EMXDV and DN-QEMXDV double-level plug-in terminal blocks	25	$16.00
DN-FESPA	Spacer for DN-FE sockets and DN-DIS disconnects	50	$29.00
DN-FESPA-10		10	$6.00

Top Covers

DINnectors Top Covers

Part Number	Description	For Use With	Qty	Price
DN-C12	Top cover, clear, printed electrical symbol.	DN-T12-A	100	$68.00
DN-C12MN			25	$15.50
DN-C10	Top cover, clear, printed electrical symbol.	DN-T10-A	100	$68.00
DN-C10MN			25	$15.50
DN-C86	Top cover, clear, printed electrical symbol.	DN-T8 DN-T6	100	$68.00
DN-C86MN			25	$15.50
DN-DC10	Top cover, clear, printed electrical symbol.	DN-D10	100	$66.00
DN-DC10MN			25	$15.50
DN-MC10	Top cover, clear, printed electrical symbol.	DN-M10	100	$70.00
DN-MC10MN			25	$15.50

DINnectors® Accessories

DIN*nector* End Covers and Spacers Dimensions				
Part Number		*Length mm[in]*	*Height mm [in]*	*Thickness mm [in]*
DN-EC1210	DN-EC1210MN	44 [1.73]	35 [1.38]	1.5 [0.06]
DN-S1210	DN-S1210MN	55 [2.17]	44 [1.73]	
DN-EC86	DN-EC86MN	50 [1.97]	43 [1.69]	
DN-S86	DN-S86MN	55 [2.17]	49 [1.93]	
DN-EC4	DN-EC4MN	56 [2.21]	48 [1.89]	
DN-EC1/0	DN-EC1/0MN	62 [2.44]	60 [2.36]	
DN-DEC10	DN-DEC10MN	72 [2.80]	49 [1.93]	
DN-EC14	–	78 [3.08]	55 [2.17]	
DN-EC14S	–	55 [2.17]	50 [1.97]	
DN-ECM10	DN-ECM10MN	32 [1.26]	27 [1.06]	
DN-ECKBD	DN-ECKBDMN	52 [2.05]	34.5 [1.36]	
DN-EMXM1EC1	DN-EMXM1EC2	as shown on next page		
DN-EMXDVEC1	DN-EMXDVEC2			
DN-EMXDVSPA1	DN-EMXM1SPA1			
DN-FESPA	DN-FESPA-10			
DN-FESEP	DN-FESEP-10			
DN-QEC12	DN-QEC12MN	50 [1.97]	23 [0.9]	1.5 [0.06]
DN-QEC10	DN-QEC10MN	57.4 [2.26]	33.6 [1.32]	
DN-QEC8	DN-QEC8MN	63 [2.48]	38.5 [1.52]	
DN-QEC12-1-2	–	68.5 [2.70]	28.5 [1.12]	
DN-QEC12-2-2	–	87.5 [3.44]	28.5 [1.12]	
DN-QDEC12	–	98 [3.86]	37 [1.46]	

DN-EC1210 (MN) DN-EC86 (MN), DN-EC4 (MN), DN-EC1/0 (MN), DN-ECKBD (MN), DN-S1210 (MN), DN-S86 (MN)



DN-EC14



DN-EC14S



DN-DEC10 / DN-DEC10MN



DN-ECM10
DN-ECM10MN



DN-QEC12 (MN), DN-QEC10 (MN)
DN-QEC8 (MN),
DN-QEC12-1-2, DN-QEC12-2-2



DN-QDEC12



Dimensional Drawings

DN-EMXM1EC1



DN-EMXM1EC2



DN-EMXDVSPA1



DN-EMXM1SPA1



DN-EMXDVEC1



DN-EMXDVEC2



DN-FESEP, DN-FESEP-10



DN-FESPA, DN-FESPA-10



Marking Tags Cross Reference Charts - Screwless

DIN*nector* Marking Tags Cross Reference - Screwless				
Block Type	***DN-QL***	***DN-LA***	***DN-LT***	***DN-EMLBL***
DN-Q12	X	–	–	–
DN-Q10	X	–	–	–
DN-Q8	X	–	–	–
DN-QD12	X	–	–	–
DN-Q12-1-2	X	–	–	–
DN-Q12-1-2L	X	–	–	–
DN-Q12-1-2D	X	–	–	–
DN-QKBD	X	–	–	–
DN-Q12-2-2	X	–	–	–
DN-Q12-2-2L	X	–	–	–
DN-Q12-2-2D	X	–	–	–
DN-QEMXM1	–	X	X	X
DN-QEMXDV	–	X	X	X
DN-QG12	X	–	–	–
DN-QG10	X	–	–	–
DN-QG8	X	–	–	–
DN-QG12-1-2	X	–	–	–
DN-QG12-2-2	X	–	–	–

Marking Tags

Marking Tags DN-L Series			
Part Number	**Marking Sequence**	**Qty**	**Price**
DN-L50	1-50	500	$61.50
DN-L100	51-100	500	$61.50
DN-L150	101-150	500	$61.50
DN-L200	151-200	500	$61.50
DN-L250	201-250	500	$61.50
DN-L300	251-300	500	$61.50
DN-L350	301-350	500	$61.50
DN-L400	351-400	500	$61.50
DN-L450	401-450	500	$61.50
DN-LB	Blank	500	$42.00
DN-LS	L1, L2, L3, L, N, GND, +, -, COM,COM*	500	$61.50

Dimensions



- The marking sequence of 50 tags (i.e. 101-150) is printed 10 times in each package of 500.
- The DN-L tags fit all DIN*nectors* 6mm wide and wider.
- There will be a gap between tags on blocks wider than 6mm.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-LA Series			
Part Number	**Marking Sequence**	**Qty**	**Price**
DN-LA100	1-100	500	$61.50
DN-LA200	101-200	500	$61.50
DN-LA300	201-300	500	$61.50
DN-LA400	301-400	500	$61.50
DN-LAB	Blank Tags	500	$61.50
DN-LAS	L1, L2, L3, L, N, GND, +, -, COM,COM*	500	$61.50

Dimensions



- The marking sequence of 100 tags (i.e. 1-100) is printed five times in each package of 500.
- The DN-LA tags fit all DIN*nectors* 5mm wide and wider. There will be a gap between tags on blocks wider than 5mm.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-LAT Series			
Part Number	**Marking Sequence**	**Qty**	**Price**
DN-LAT100-A	1-100	500	$54.00
DN-LAT200-A	101-200	500	$54.00
DN-LAT300-A	201-300	500	$54.00
DN-LAT400-A	301-400	500	$54.00
DN-LAT500-A	401-500	500	$54.00
DN-LAT600-A	501-600	500	$54.00
DN-LATB-A	Blank Tags	500	$39.00
DN-LATS-A	L1, L2, L3, L, N, +,-, COM,COM*	500	$54.00

Dimensions



- The marking sequence of 500 tags (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

Marking Tags DN-QL Series			
Part Number	**Marking Sequence**	**Qty**	**Price**
DN-QL100	1-100	500	$47.00
DN-QL200	101-200	500	$47.00
DN-QL300	201-300	500	$47.00
DN-QL400	301.400	500	$47.00
DN-QL500	401-500	500	$47.00
DN-QLB	Blank Tags	500	$39.50
DN-QLS	L1, L2, L3, L, N, +,-, COM,COM*	500	$54.00

Dimensions



- The marking sequence of 500 (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

DINnectors Accessories

Marking Tags continued

Marking Tags DN-LT Series			
Part Number	Marking Sequence	Qty	Price
DN-LT15	1-5	100	$11.00
DN-LT60	6-0	100	$11.00
DN-LT1	1	100	$11.00
DN-LT2	2	100	$11.00
DN-LT3	3	100	$11.00
DN-LT4	4	100	$11.00
DN-LT5	5	100	$11.00
DN-LT6	6	100	$11.00
DN-LT7	7	100	$11.00
DN-LT8	8	100	$11.00
DN-LT9	9	100	$11.00
DN-LT0	0	100	$11.00
DN-LTBLNK	Unprinted	100	$11.00
DN-LTA	A	100	$11.00
DN-LTB	B	100	$11.00
DN-LTC	C	100	$11.00
DN-LTD	D	100	$11.00
DN-LTE	E	100	$11.00
DN-LTF	F	100	$11.00
DN-LTG	G	100	$11.00
DN-LTH	H	100	$11.00
DN-LTI	I	100	$11.00
DN-LTJ	J	100	$11.00
DN-LTK	K	100	$11.00
DN-LTL	L	100	$11.00
DN-LTM	M	100	$11.00
DN-LTN	N	100	$11.00
–	–	–	–
DN-LTP	P	100	$11.00
DN-LTQ	Q	100	$11.00
DN-LTR	R	100	$11.00
DN-LTS	S	100	$11.00
DN-LTT	T	100	$11.00
DN-LTU	U	100	$11.00
DN-LTV	V	100	$11.00
DN-LTW	W	100	$11.00
DN-LTX	X	100	$11.00
DN-LTY	Y	100	$11.00
DN-LTZ	Z	100	$11.00
DN-LTGND	⏚	100	$11.00
DN-LTPOS	+	100	$11.00
DN-LTNEG	-	100	$11.00
DN-LTAC	~	100	$11.00
DN-LTDC	=	100	$11.00



- These marking tags allow the flexibility of creating custom marking sequences on site.
- The DN-M series supports a maximum of three digits (tags), while other DIN*nectors* support up to four digits (tags).
- Material: Thermoplastic with heat embossed black print.

DN-MTA marking tag adapter



DN-MTA dimensions



Part Number	Description	Qty	Price
DN-MTA	Marking tag adapter holds up to six DN-LT tags	50	$16.00

Note: DN-MTA adapter does not fit DN-T12-A terminal blocks.

DINnectors® Accessories

Terminal Marking Accessories

DN-EMLBL1

DN-EMLBL2

DN-EMLBL3

Part Number	Description	For Use With	Qty	Price
DN-EMLBL1	Blank labels	DN-EMPEG1 pin protectors for DN-xEMXxx plug-in terminal blocks	100	$10.00
DN-EMLBL2	Labels printed 1 – 12		100	$14.50
DN-EMLBL3	Labels printed 13 – 24		100	$14.50

Marking Pen – for terminal and wire marking tags

- Permanent
- Smudge-proof
- Waterproof
- Weatherproof
- Lightfast (won't fade)
- Dries in seconds (excellent for left-handed users)
- Dry-safe (pen can be left uncapped for days without drying out)
- Low odor ink

Part Number	Description	Qty	Price
DN-MP	Staedtler-Mars marking pen, for use with blank marking tags. Permanent Ink, fine tip.	1	$4.50

Marking pen

Wire Marking Accessories

DN-WMTAG1 wire tags & DN-WM-x wire tag holders

Part Number	Description	For Use With	Qty	Price
DN-WMTAG1	Wire tag – blank	all DN-WM-x wire tag holders	525	$66.00
DN-WM-1	Wire tag holder, clear, 12mm length, 0.051–0.118 in diameter; for 22–16 AWG wire	DN-WMTAG1	200	$14.00
DN-WM-2	Wire tag holder, clear, 12mm length, 0.098–0.196 in diameter; for 16-11 AWG wire		200	$14.00
DN-WM-3	Wire tag holder, clear, 12mm length, 0.157–0.393 in diameter; for 13–5 AWG wire		100	$9.00
DN-WM-4	Wire tag holder, clear, 12mm length, 0.314–0.629 in diameter; for 5AWG wire		100	$8.50