SCHMERSAL 22mm IP69K Indicator Lights

NMLBL

NMLGB

NMLGN

NMLRT

NMLWS

22mm IP69K Indicator Lights*					
Part Number	***NMLBL***	***NMLGB***	***NMLGN***	***NMLRT***	***NMLWS***
Dome color	Blue	Yellow	Green	Red	White
Price	$16.00	$16.00	$16.00	$16.00	$16.00
Drawing Link	PDF	PDF	PDF	PDF	PDF
Description	Indicator light (purchase light block and LED or bulb separately)				
Mounting diameter	22.3 mm [0.88 in]				
Dome material	Polyamide-12				
Front ring material	ABS, chromium-plated				
Front panel thickness	1.5 to 6 mm				
Weight	30g [1.06 oz]				
Mounting screws tightening torque	0.6 N·m [0.44 lb·ft]				
Ambient temperature	-25 to +80°C [-13 to +176°F]				
Shock resistance	< 50g				
Vibration resistance	5g				
Ingress protection rating	IP67 and IP69K				
Standards	IEC 60947-5-1; IEC 60947-1; UL File E57648, CE				

***Operator only. Purchase contact and light blocks separately.**

SCHMERSAL Light Terminal Blocks

ELDE.Nxx230

ELDE.Nxx24

ELE

ELE230

Light Terminal Blocks

Part Number	Color	Price	Drawing Link	Voltage	Wattage	Diagram	Function
ELDE.NBL230	Blue	$45.50	PDF	115-230 VAC	4	X1 X2	Integrated LED
ELDE.NBL24		$24.50	PDF	24 VAC/VDC	0.4		
ELDE.NGB230	Yellow	$45.50	PDF	115-230 VAC	4		
ELDE.NGB24		$24.50	PDF	24 VAC/VDC	0.4		
ELDE.NGN230	Green	$45.50	PDF	115-230 VAC	4		
ELDE.NGN24		$24.50	PDF	24 VAC/VDC	0.4		
ELDE.NRT230	Red	$45.50	PDF	115-230 VAC	4		
ELDE.NRT24		$24.50	PDF	24 VAC/VDC	0.4		
ELDE.NWS230	White	$45.50	PDF	115-230 VAC	4		
ELDE.NWS24		$24.50	PDF	24 VAC/VDC	0.4		
ELE	–	$10.50	PDF	24 VAC/VDC	1	X1 X2	Ba9S Lamp holder
ELE230	–	$28.00	PDF	115-230 VAC	1	X1 X2	

Ba9S Bulbs for ELE and ELE230 Light Terminal Blocks

Part Number	Color	Price	Qty	Lamp Voltage	Current Consumption	Power Consumption	Lamp Durability
APX510-24R	Red	$17.00	2	24V AC/DC	12mA AC 11mA DC	0.8 W	30,000h
APX510-24G	Green	$17.00					
APX510-24Y	Yellow	$17.00					
APX510-24S	Blue	$63.00					
APX510-24O	Orange	$17.00					

APX510-24R

Replacement LED Lamps for ELE and ELE230 Light Terminal Blocks

Part Number	Color	Price	Qty	Lamp Voltage	Current Consumption	Power Consumption	Lamp Durability
ECX1911-2	Red	$17.50	2	24V AC/DC	14mA	0.6 W	100,000h
ECX1912-2	Green	$22.00			13mA		
ECX1913-2	Yellow	$17.50			13.3 mA		
ECX1914-2	Blue	$23.50			13mA		
ECX1915-2	White	$28.00			19mA		

ECX1915-2

NOTE: ELE230 has transformer to step down to 24V

Mounting Flange

Part Number	Price	Description	Drawing Link
ELM	$5.00	Schmersal mounting flange, replacement. For use with E and N series illuminated pushbuttons.	PDF

ELM

SCHMERSAL Contact Blocks

EF03.2

EF10.1

EF103.2

EF220.2

EF303.2

Contact Blocks

Part Number	Price	Qty.	Drawing Link	Contacts	Mounting Position	Travel Diagram (mm)	Wiring Diagram	Application
EF10.1*	$9.25	1	PDF	1 N.C.	1			Standard
EF10.2*	$9.25	1	PDF		2			
EF10.3*	$9.25	1	PDF		3			
EF03.1	$9.25	1	PDF	1 N.O.	1			
EF03.2	$9.25	1	PDF		2			
EF03.3	$9.25	1	PDF		3			
EF110.1*	$14.00	1	PDF	2 N.C.	1			
EF110.2*	$14.50	1	PDF		2			
EF110.3*	$14.50	1	PDF		3			
EF033.1	$14.50	1	PDF	2 N.O.	1			
EF033.2	$14.50	1	PDF		2			
EF033.3	$14.50	1	PDF		3			
EF103.1*	$11.50	1	PDF	1 N.C. / 1 N.O.	1			
EF103.2*	$11.50	1	PDF		2			
EF103.3*	$11.50	1	PDF		3			
EF220.1**	$14.50	1	PDF	2 N.C.	1			Emergency Stop
EF220.2**	$14.50	1	PDF		2			
EF220.3**	$14.50	1	PDF		3			
EF303.1**	$11.50	1	PDF	1 N.C. / 1 N.O.	1			
EF303.2**	$11.50	1	PDF		2			
EF303.3**	$11.50	1	PDF		3			

*Not suitable for Emergency Stop devices
**Not suitable for maintained selector switches NWS/NWT

Travel Diagram Legend
= contact closed
= contact open
Numbers indicate distance in mm

EFM

Mounting Flange

Part Number	Price	Description	Drawing Link
EFM	$5.00	Schmersal mounting flange, replacement. For use with E and N series pushbuttons.	PDF

SCHMERSAL

Contact Blocks and Light Terminal Blocks Overview

Features

- A self-cleaning contact bridge system, known as Elan four-way system, which is particularly suitable for low voltage applications and has a lower switching capacity of 5VDC/3.2 mA (max. 400VAC/8A). It is designed in the form of a bent twin contact bridge, with parallel and also diagonal operation.
- Block mounting via snap-on stainless steel springs.
- Complete terminal designations visible at a glance in compliance with IEC 60 947-1 (VDE 0660, Part 100) with a complete function and sequence number (refer also to product ranges). The function number identifies the N.C. and N.O. contact. The sequence number specifies the number and the order of the contacts on the complete switching device.
- N.C. contacts with positive opening in compliance with IEC 60 947-5-1 (VDE 0660 Part 200).
- Galvanically isolated contact circuits in 2-pole blocks.
- High resistance to shock and vibrations.





Technical Specifications

	Contact Blocks	Light Blocks (ELE)	Light Blocks (ELDE)
General description	Contact element	Light terminal block w/Ba9S base	Light terminal block w/LED
Enclosure material	Plastic, glass fiber reinforced	Plastic, glass fiber reinforced	Plastic, glass fiber reinforced
Contact material	Fine-silver, phosphor bronze or brass carrier	–	–
Utilization category	AC-15: 250 V / 8 A DC-13: 24 V / 5 A	–	–
Suitability for low voltages	≥ 5VDC / 3.2 mA	–	–
Rated insulation voltage Ui	400V	440V	440V
Rated impulse withstand voltage U_{imp}	4kV	–	–
Thermal test current Ithe	10A	–	–
Max. fuse rating	10A gG D-fuse slow blow	10A gG T-slow blow	10A gG T-slow blow
Wire size	0.5 mm² to 2.5 mm² (20 - 14 AWG)		
Tightening torque wire connection	Maximum 1 N·m (0.74 lb·ft)		
NEMA contact rating	A300 / P300	–	–
Switching frequency	1200 s/h	–	–
Switching capacity	5VDC / 3.2 mA (max 400VAC / 8A)	–	–
Mechanical life	10,000,000 operation	–	–
Resistance to shock	110 g/4ms to 30 g/18ms no bouncing	–	–
Resistance to vibration	> 20 g/10ms to 200Hz	–	–
Ambient temperature	-25 to +80°C [-13 to +176°F]		
Ingress protection rating	IP20 terminals / IP40 switching compartment	IP20 terminals	IP20 terminals
Standards	IEC 60947-5-1; IEC 60947-1; UL File E57648		

NEMA Contact Rating Designation

	Thermal Current	Voltage	Volt amperes
A300	10	300 AC	N/A
P300	5	300 DC	138

SCHMERSAL Accessories

NB

NDP-70-ES

EDT-25-5ST

NZSO-V4A

IP69K Accessories

Part Number	Price	Drawing Link	Description
NB	$11.50	PDF	Schmersal pilot device hole seal, 22mm, silver.
NDP-70-ES	$9.25	N/A	Schmersal legend plate, metal, round, yellow field, yellow background, black engraved text, legend plate marking "Emergency Stop". For use with 22mm pilot devices.
NUE	$6.50	N/A	Schmersal pilot device hole adapter, reduces from 30.5 mm to 22.3 mm. Adapter ring, seal and washer included.
EDT-25-5ST	$6.75	N/A	Schmersal pilot device seal, replacement. Package of 5.
NZSO-V4A	$3.75	N/A	Schmersal legend plate, metal, rectangular, gray field, gray background, legend plate marking "blank". For use with 22mm pilot devices.

NUE



*Included in NUE kit.

SCHMERSAL Control and Signaling Devices 22mm IP69K

Schmersal control and signaling devices have a number of special design features that make the devices suitable for food processing, pharmaceutical, and medical applications. When utilized in food processing machines, these devices comply with the special cleaning requirements of the industry to prevent cross-contamination, particularly when used in machines that process raw goods. With an ingress protection rating of IP69K, Schmersal control and signaling devices are also suitable for marine applications, traffic systems, commercial vehicles, and in dusty and dirty environments.

Features

- Special seals prevent product residue from penetrating in the gaps between the fixed and moving device parts, thus preventing the collection of dirt and bacteria in places that are not easily accessible for cleaning.
- Smooth designs make the devices easy to clean.
- Modular contact and light terminal blocks make the devices easy to install.



IP69K Ingress Protection Rating Overview

IP69K high-pressure cleaning test
This rating applies to devices tested in accordance with DIN 40050-9. The goal of this test is to duplicate pressure cleaning conditions on a plant floor. In the test fixture, the devices are exposed to a 1450psi spray of water at a temperature of 175˚F. The duration of each cleaning cycle is 30 seconds. The test is performed at specified angles using a spray nozzle located at a distance of 4" from the devices. Devices with this rating must withstand test conditions and still be operable. This rating ensures water proofing protection that exceeds NEMA 4X rating.

Thermal endurance
In pressure environments, controls and signaling devices can be exposed to extreme temperature conditions. To meet the criteria for IP69K rating, devices must undergo a thermal shock test by cycling the environmental temperature to ensure consistent high reliability.



SCHMERSAL Modular Design Flexibility

Non-Illuminated Devices

NDT Series
Non-illuminated pushbuttons

NDP Series
Mushroom pushbuttons

NW Series
Selector Switches

NDRZ Series
Emergency Stop Pushbuttons

Accessories
(Purchase Separately)

Accessory
(Purchase Separately)

Mounting Flange
(Included)

Mounting Flange
(Included)

Contact Blocks
(Purchase Separately)

Contact Blocks
(Purchase Separately)

Illuminated Devices

NDL Series
Illuminated Pushbuttons

NML Series
Indicator Lights

Accessories
(Purchase Separately)

Mounting Flange
(Included)

Contacts and Light Terminal Blocks
(Purchase Separately)